

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912048

Luminaire Tested: DFN2DIP-SQ3F0-110D040US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912048
REPORT IS A COMBINATION OF REPORTS P899875 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D040US850-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16002.8 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 142.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912048

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912048

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US850-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	80	80	80
1	104	99	95	91	98	94	91	88	86	83	80	78	76	74	70	69	67
2	94	87	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42
5	73	60	52	46	69	58	50	44	53	46	42	48	43	39	44	40	36
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	36	32
7	62	49	41	35	59	47	40	34	44	37	32	40	34	30	37	32	29
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5439	5439	5439
5°	5444	5359	5397
10°	5396	5284	5322
15°	5314	5193	5207
20°	5203	5069	5088
25°	5093	4921	4951
30°	4955	4782	4777
35°	4825	4620	4594
40°	4665	4456	4419
45°	4506	4291	4240
50°	4331	4118	4033
55°	4147	3918	3842
60°	3940	3681	3624
65°	3713	3435	3366
70°	3424	3134	3088
75°	3025	2774	2828
80°	2543	2315	2338
85°	1791	1534	1530

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4506 cd/sqm

TEST NUMBER: P912048

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.8	2.8
10°-20°	1257.0	7.9
20°-30°	1847.3	11.5
30°-40°	2145.5	13.4
40°-50°	2142.9	13.4
50°-60°	1868.5	11.7
60°-70°	1381.3	8.6
70°-80°	781.5	4.9
80°-90°	210.2	1.3
90°-100°	86.8	0.5
100°-110°	275.8	1.7
110°-120°	472.0	2.9
120°-130°	620.8	3.9
130°-140°	696.8	4.4
140°-150°	683.3	4.3
150°-160°	573.2	3.6
160°-170°	380.1	2.4
170°-180°	132.9	0.8
0°-30°	3551.1	22.2
0°-40°	5696.6	35.6
0°-60°	9708.0	60.7
0°-90°	12081.0	75.5
90°-120°	834.7	5.2
90°-150°	2835.6	17.7
90°-180°	3922.0	24.5
0°-180°	16002.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4747	4747	4747	4747	4747	
5°	4747	4729	4678	4715	4706	451
15°	4519	4491	4432	4450	4428	1273
25°	4090	4053	3976	3984	3976	1882
35°	3528	3483	3410	3382	3359	2203
45°	2871	2839	2770	2721	2702	2216
55°	2173	2145	2091	2036	2013	1943
65°	1465	1438	1392	1351	1328	1449
75°	766	758	735	708	717	818
85°	187	182	178	164	160	209
90°	1	15	42	39	40	15
95°	62	74	76	76	74	69
105°	255	258	260	263	263	269
115°	474	480	478	477	474	469
125°	689	700	696	692	691	616
135°	891	904	907	906	902	689
145°	1082	1090	1097	1098	1094	676
155°	1237	1240	1244	1250	1246	569
165°	1346	1345	1345	1353	1347	380
175°	1400	1397	1394	1403	1396	133
180°	1403	1403	1403	1403	1403	

TEST NUMBER: P912048

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4746.7	4746.7	4746.7	4746.7	4746.7
2.5°	4774.2	4751.5	4701.2	4746.7	4738.0
5°	4746.7	4728.8	4678.4	4714.7	4706.0
7.5°	4714.7	4687.6	4637.3	4674.1	4664.9
10°	4664.9	4632.8	4578.2	4614.4	4600.9
12.5°	4596.1	4569.0	4514.3	4537.0	4527.8
15°	4518.6	4491.4	4431.9	4450.3	4427.6
17.5°	4422.7	4395.6	4336.1	4358.8	4336.1
20°	4317.7	4290.5	4226.6	4240.2	4222.3
22.5°	4213.1	4171.8	4112.3	4112.3	4103.1
25°	4089.5	4053.3	3975.8	3984.5	3975.8
27.5°	3952.5	3920.5	3861.4	3847.9	3825.2
30°	3816.0	3779.1	3710.8	3697.3	3678.9
32.5°	3669.7	3642.6	3569.4	3541.8	3523.4
35°	3528.3	3482.8	3409.6	3382.0	3359.3
37.5°	3368.5	3327.3	3254.2	3222.2	3199.5
40°	3204.3	3167.5	3094.4	3053.7	3035.3
42.5°	3044.5	3007.7	2935.1	2889.1	2862.0
45°	2871.2	2839.2	2770.4	2720.6	2702.2
47.5°	2702.2	2670.3	2597.1	2546.7	2519.5
50°	2524.0	2501.2	2437.2	2373.4	2350.6
52.5°	2350.6	2318.6	2259.6	2209.1	2177.2
55°	2172.9	2145.2	2090.6	2035.8	2013.1
57.5°	1994.6	1971.9	1912.4	1857.6	1839.2
60°	1816.4	1798.6	1734.6	1684.2	1670.7
62.5°	1643.1	1611.2	1565.6	1520.1	1501.7
65°	1465.3	1437.7	1392.2	1351.1	1328.4
67.5°	1282.8	1259.6	1218.9	1187.0	1168.6
70°	1113.8	1095.4	1054.2	1022.3	1004.3
72.5°	940.4	922.0	899.3	867.3	853.7
75°	766.5	757.9	734.6	707.5	716.7
77.5°	611.6	593.2	584.0	570.5	556.9
80°	456.7	451.8	442.6	429.1	419.9
82.5°	310.4	310.4	306.1	287.7	287.7
85°	187.0	182.5	178.2	164.1	159.8
87.5°	82.3	73.1	63.9	50.3	45.5
90°	1.2	15.2	41.5	38.9	40.1
92.5°	26.2	35.5	36.8	38.0	38.0
95°	61.8	73.6	75.7	75.7	73.6
97.5°	102.8	113.8	118.4	118.4	118.4
100°	150.2	159.9	163.2	163.2	162.0
102.5°	200.1	207.3	211.9	213.1	211.9
105°	254.6	258.0	260.5	262.6	262.6
107.5°	308.7	313.8	313.8	314.6	308.7
110°	361.2	368.0	368.0	368.0	364.6

TEST NUMBER: P912048

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	417.9	425.1	423.7	420.4	417.9
115°	473.7	480.5	478.3	477.1	473.7
117.5°	529.1	538.4	532.5	529.1	525.8
120°	585.0	594.2	585.0	585.0	581.1
122.5°	635.7	647.5	641.7	638.2	635.7
125°	689.0	699.6	696.2	692.3	691.1
127.5°	741.0	754.1	749.5	744.4	741.0
130°	789.6	804.9	802.8	800.3	795.6
132.5°	844.2	856.0	856.9	850.9	847.6
135°	891.2	904.3	906.8	905.5	902.2
137.5°	943.6	954.2	956.3	955.4	950.4
140°	989.7	1000.3	1006.2	1006.2	1001.5
142.5°	1037.1	1047.7	1051.0	1052.3	1047.7
145°	1081.9	1090.4	1097.1	1098.5	1093.8
147.5°	1122.1	1132.6	1137.7	1139.8	1135.2
150°	1163.6	1170.8	1175.4	1179.2	1175.4
152.5°	1200.4	1207.5	1213.5	1218.1	1213.5
155°	1237.1	1240.5	1244.3	1250.3	1246.4
157.5°	1268.9	1271.4	1273.5	1282.0	1276.0
160°	1297.2	1299.7	1301.0	1308.2	1303.1
162.5°	1323.4	1323.4	1324.7	1332.7	1326.8
165°	1345.9	1344.6	1344.6	1353.0	1347.1
167.5°	1366.2	1362.3	1362.3	1370.8	1364.8
170°	1381.4	1377.9	1376.7	1385.1	1377.9
172.5°	1391.9	1388.6	1387.2	1395.8	1388.6
175°	1400.4	1397.0	1394.5	1402.9	1395.8
177.5°	1405.1	1401.7	1399.1	1406.3	1399.1
180°	1402.9	1402.9	1402.9	1402.9	1402.9

TEST NUMBER: P912048

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.20	16.35	15.91	17.07	17.93	14.76	15.91	15.46	16.63	17.48
	3H	16.88	17.91	17.60	18.65	19.53	16.39	17.42	17.11	18.16	19.04
	4H	17.48	18.45	18.21	19.19	20.09	16.98	17.96	17.72	18.70	19.60
	6H	17.89	18.79	18.64	19.54	20.45	17.39	18.29	18.14	19.04	19.95
	8H	18.00	18.86	18.76	19.63	20.54	17.50	18.36	18.26	19.13	20.04
	12H	18.06	18.87	18.82	19.64	20.58	17.55	18.37	18.31	19.13	20.07
4H	2H	15.69	16.67	16.43	17.41	18.31	15.34	16.31	16.08	17.06	17.96
	3H	17.58	18.40	18.33	19.17	20.09	17.17	17.99	17.92	18.77	19.68
	4H	18.30	19.04	19.07	19.82	20.77	17.88	18.62	18.65	19.40	20.34
	6H	18.83	19.47	19.61	20.28	21.23	18.40	19.04	19.18	19.84	20.79
	8H	18.98	19.58	19.77	20.38	21.35	18.55	19.15	19.33	19.95	20.91
	12H	19.07	19.61	19.88	20.43	21.40	18.62	19.16	19.43	19.98	20.95
8H	4H	18.52	19.12	19.31	19.92	20.88	18.14	18.74	18.93	19.54	20.50
	6H	19.16	19.65	19.97	20.49	21.46	18.77	19.27	19.59	20.11	21.08
	8H	19.38	19.82	20.20	20.66	21.64	18.98	19.43	19.81	20.26	21.25
	12H	19.52	19.91	20.35	20.74	21.78	19.11	19.50	19.94	20.33	21.37
12H	4H	18.52	19.06	19.33	19.88	20.85	18.15	18.69	18.96	19.51	20.48
	6H	19.19	19.63	20.01	20.47	21.45	18.81	19.26	19.64	20.10	21.08
	8H	19.44	19.83	20.27	20.66	21.70	19.06	19.45	19.89	20.28	21.32

END OF REPORT