

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906647

Luminaire Tested: DFN2DIP-SQ3F0-120D080US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906647
REPORT IS A COMBINATION OF REPORTS P901470 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-120D080US835-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18120.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 186.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906647
CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US835-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P906647

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56		56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53	49		49
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46	42		42
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36		36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31		31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31	27		27
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27	24		24
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22		22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20		20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18		18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16		16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5683	5683	5683
5°	5688	5589	5626
10°	5628	5475	5442
15°	5547	5291	5157
20°	5441	5038	4808
25°	5332	4755	4471
30°	5188	4465	4045
35°	5046	4154	3670
40°	4901	3833	3241
45°	4733	3476	2852
50°	4559	3117	2473
55°	4377	2734	2108
60°	4167	2333	1733
65°	3924	1927	1558
70°	3629	1548	1407
75°	3259	1356	1276
80°	2723	1125	1100
85°	1847	733	816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4733 cd/sqm



TEST NUMBER: P906647

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.8	2.6
10°-20°	1276.0	7.0
20°-30°	1791.5	9.9
30°-40°	1952.8	10.8
40°-50°	1794.9	9.9
50°-60°	1409.6	7.8
60°-70°	917.5	5.1
70°-80°	472.3	2.6
80°-90°	125.3	0.7
90°-100°	89.0	0.5
100°-110°	331.9	1.8
110°-120°	880.2	4.9
120°-130°	1459.9	8.1
130°-140°	1550.7	8.6
140°-150°	1441.2	8.0
150°-160°	1158.7	6.4
160°-170°	746.6	4.1
170°-180°	257.0	1.4
0°-30°	3532.3	19.5
0°-40°	5485.2	30.3
0°-60°	8689.6	48.0
0°-90°	10204.7	56.3
90°-120°	1301.1	7.2
90°-150°	5752.9	31.7
90°-180°	7915.0	43.7
0°-180°	18120.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4960	4960	4960	4960	4960	
5°	4960	4937	4879	4919	4906	470
15°	4717	4668	4515	4430	4385	1329
25°	4282	4138	3842	3658	3590	1969
35°	3690	3460	3066	2783	2684	2309
45°	3016	2715	2244	1925	1818	2329
55°	2293	1943	1459	1190	1104	2049
65°	1549	1185	781	629	615	1535
75°	826	511	359	328	323	873
85°	193	99	85	85	85	221
90°	2	23	39	49	53	17
95°	127	62	76	86	84	150
105°	594	653	119	141	148	635
115°	1123	1156	1205	301	160	1106
125°	1588	1614	1651	1664	1670	1416
135°	1965	1997	2014	2034	2030	1518
145°	2280	2278	2311	2325	2315	1426
155°	2510	2493	2516	2528	2512	1157
165°	2645	2634	2639	2653	2639	747
175°	2706	2692	2696	2710	2690	258
180°	2700	2700	2700	2700	2700	



TEST NUMBER: P906647

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4959.6	4959.6	4959.6	4959.6	4959.6
2.5°	4982.0	4959.6	4910.1	4955.3	4946.2
5°	4959.6	4937.2	4878.6	4919.1	4905.8
7.5°	4919.1	4892.4	4829.6	4847.2	4824.8
10°	4865.3	4833.9	4744.3	4730.5	4703.9
12.5°	4798.1	4757.7	4636.2	4609.6	4560.1
15°	4717.2	4667.7	4515.3	4430.0	4385.3
17.5°	4622.9	4551.0	4362.4	4263.9	4192.0
20°	4515.3	4425.3	4201.0	4089.1	3990.0
22.5°	4398.6	4295.3	4034.8	3882.4	3815.3
25°	4282.0	4138.1	3841.9	3658.1	3590.5
27.5°	4142.9	3990.0	3662.4	3451.5	3348.1
30°	3994.8	3823.9	3464.8	3236.2	3114.8
32.5°	3851.0	3644.3	3276.7	3007.2	2894.8
35°	3689.6	3460.5	3065.7	2782.9	2683.8
37.5°	3532.4	3285.3	2868.1	2558.1	2446.2
40°	3366.2	3097.2	2661.5	2342.9	2226.2
42.5°	3195.7	2908.6	2455.3	2122.9	2011.0
45°	3016.2	2715.3	2244.3	1925.3	1817.6
47.5°	2845.7	2527.2	2042.4	1723.4	1624.8
50°	2657.2	2338.6	1844.8	1534.8	1441.0
52.5°	2472.9	2136.2	1656.2	1360.0	1274.8
55°	2293.4	1943.4	1458.6	1189.5	1104.3
57.5°	2109.5	1750.5	1283.8	1032.4	960.5
60°	1921.0	1561.9	1099.5	871.0	799.1
62.5°	1737.2	1378.1	942.4	727.2	691.4
65°	1548.6	1184.8	781.0	628.6	614.8
67.5°	1369.1	1005.2	628.6	551.9	538.6
70°	1180.5	830.5	520.5	475.7	457.6
72.5°	1001.0	668.6	435.2	399.5	390.5
75°	825.7	511.4	359.1	327.6	323.3
77.5°	651.0	363.3	282.9	264.8	255.7
80°	489.1	260.5	215.2	197.6	197.6
82.5°	341.0	175.2	148.1	139.0	139.0
85°	192.9	98.6	85.2	85.2	85.2
87.5°	71.9	35.7	35.7	31.4	31.4
90°	1.9	23.4	39.0	48.9	52.7
92.5°	48.9	41.1	46.9	50.8	52.7
95°	126.9	62.4	76.1	86.1	84.0
97.5°	228.5	68.4	99.5	105.6	107.4
100°	345.9	78.2	111.4	126.9	130.8
102.5°	474.7	470.9	115.3	136.6	142.7
105°	593.9	652.6	119.2	140.6	148.5
107.5°	732.6	781.3	123.2	144.5	152.4
110°	865.6	906.4	342.0	146.6	154.3



TEST NUMBER: P906647

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US835-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	990.6	1025.6	992.5	150.3	156.4
115°	1123.3	1156.5	1205.4	300.9	160.3
117.5°	1238.6	1277.6	1311.0	1031.4	519.7
120°	1367.6	1396.8	1432.1	1455.5	1191.7
122.5°	1476.8	1508.2	1547.4	1559.0	1561.1
125°	1588.2	1613.7	1650.8	1664.5	1670.3
127.5°	1689.8	1717.2	1746.7	1766.1	1768.0
130°	1785.6	1816.9	1838.3	1859.9	1858.0
132.5°	1883.3	1908.8	1930.2	1947.8	1945.9
135°	1965.4	1996.7	2014.1	2033.9	2029.9
137.5°	2051.3	2074.7	2094.4	2113.9	2108.1
140°	2135.2	2151.0	2172.4	2190.0	2180.2
142.5°	2205.8	2219.4	2244.7	2260.3	2250.5
145°	2280.0	2277.9	2311.1	2324.8	2315.0
147.5°	2344.3	2338.5	2371.6	2381.4	2373.7
150°	2406.9	2393.2	2424.5	2436.1	2426.4
152.5°	2459.6	2444.0	2473.2	2485.1	2471.4
155°	2510.4	2493.0	2516.4	2528.0	2512.5
157.5°	2551.4	2535.9	2553.5	2567.2	2551.4
160°	2586.7	2574.9	2586.7	2598.3	2584.6
162.5°	2617.8	2606.2	2615.9	2629.6	2612.0
165°	2645.2	2633.6	2639.4	2653.0	2639.4
167.5°	2666.7	2654.9	2660.9	2674.6	2657.0
170°	2684.4	2672.5	2676.5	2690.2	2672.5
172.5°	2696.0	2684.4	2688.3	2702.0	2684.4
175°	2705.7	2692.0	2696.0	2709.6	2690.2
177.5°	2709.6	2696.0	2698.0	2711.7	2694.1
180°	2699.9	2699.9	2699.9	2699.9	2699.9



TEST NUMBER: P906647
 CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.72	14.60	14.63	15.53	16.71	9.68	10.57	10.59	11.49	12.67
	3H	15.40	16.19	16.32	17.12	18.33	10.87	11.66	11.79	12.59	13.80
	4H	16.01	16.75	16.94	17.69	18.90	11.32	12.06	12.25	13.00	14.21
	6H	16.43	17.11	17.37	18.06	19.28	11.63	12.32	12.58	13.26	14.49
	8H	16.55	17.21	17.51	18.17	19.39	11.72	12.38	12.68	13.34	14.56
	12H	16.61	17.24	17.57	18.19	19.44	11.76	12.39	12.72	13.34	14.59
4H	2H	13.74	14.49	14.68	15.43	16.64	10.28	11.03	11.22	11.96	13.18
	3H	15.57	16.19	16.52	17.16	18.39	11.63	12.25	12.58	13.22	14.45
	4H	16.26	16.83	17.22	17.79	19.04	12.17	12.74	13.13	13.70	14.95
	6H	16.78	17.26	17.75	18.25	19.50	12.59	13.07	13.56	14.06	15.31
	8H	16.95	17.40	17.92	18.38	19.65	12.71	13.17	13.69	14.15	15.41
	12H	17.04	17.45	18.04	18.45	19.72	12.78	13.19	13.77	14.18	15.46
8H	4H	16.23	16.69	17.21	17.67	18.93	12.45	12.91	13.43	13.89	15.15
	6H	16.80	17.17	17.80	18.19	19.46	12.97	13.34	13.97	14.36	15.63
	8H	17.01	17.34	18.02	18.35	19.63	13.15	13.48	14.16	14.49	15.78
	12H	17.15	17.44	18.16	18.44	19.77	13.27	13.56	14.28	14.56	15.89
12H	4H	16.19	16.60	17.18	17.59	18.86	12.46	12.87	13.45	13.87	15.14
	6H	16.77	17.10	17.78	18.11	19.39	13.01	13.35	14.02	14.35	15.64
	8H	16.99	17.28	18.00	18.28	19.61	13.22	13.51	14.23	14.51	15.85