

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912064

Luminaire Tested: DFN2DIP-SQ3F0-110D080US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912064
REPORT IS A COMBINATION OF REPORTS P899947 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D080US850-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19928.7 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 172.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912064

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912064

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	110	110	110	110		103	103	103	103		89	89	89		77	77	77		66	66	66
1	100	96	92	88		94	90	86	83		78	76	73		68	66	64		58	57	56
2	91	84	77	72		85	78	73	68		69	64	61		60	56	54		51	49	47
3	83	74	66	60		78	69	62	57		61	55	51		53	49	45		45	42	40
4	76	65	57	51		71	61	54	48		54	48	44		47	43	39		41	37	34
5	70	58	50	44		65	55	47	42		48	42	38		42	38	34		37	33	30
6	65	52	44	38		60	49	42	36		44	38	33		38	33	30		33	29	26
7	60	47	39	33		56	45	37	32		40	34	29		35	30	26		30	27	24
8	55	43	35	30		52	41	33	28		36	30	26		32	27	24		28	24	21
9	52	39	32	26		48	37	30	25		33	27	23		29	25	21		26	22	19
10	48	36	29	24		45	34	27	23		31	25	21		27	23	19		24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5439	5439	5439
5°	5444	5359	5397
10°	5396	5284	5322
15°	5314	5193	5207
20°	5203	5069	5088
25°	5093	4921	4951
30°	4955	4782	4777
35°	4825	4620	4594
40°	4665	4456	4419
45°	4506	4291	4240
50°	4331	4118	4033
55°	4147	3918	3842
60°	3940	3681	3624
65°	3713	3435	3366
70°	3424	3134	3088
75°	3025	2774	2828
80°	2543	2315	2338
85°	1791	1534	1530

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4506 cd/sqm

TEST NUMBER: P912064

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.8	2.2
10°-20°	1257.0	6.3
20°-30°	1847.3	9.3
30°-40°	2145.5	10.8
40°-50°	2142.9	10.8
50°-60°	1868.5	9.4
60°-70°	1381.3	6.9
70°-80°	781.5	3.9
80°-90°	214.2	1.1
90°-100°	173.6	0.9
100°-110°	551.7	2.8
110°-120°	944.1	4.7
120°-130°	1241.6	6.2
130°-140°	1393.7	7.0
140°-150°	1366.6	6.9
150°-160°	1146.4	5.8
160°-170°	760.3	3.8
170°-180°	265.7	1.3
0°-30°	3551.1	17.8
0°-40°	5696.6	28.6
0°-60°	9708.0	48.7
0°-90°	12085.0	60.6
90°-120°	1669.4	8.4
90°-150°	5671.3	28.5
90°-180°	7844.0	39.4
0°-180°	19928.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4747	4747	4747	4747	4747	
5°	4747	4729	4678	4715	4706	451
15°	4519	4491	4432	4450	4428	1273
25°	4090	4053	3976	3984	3976	1882
35°	3528	3483	3410	3382	3359	2203
45°	2871	2839	2770	2721	2702	2216
55°	2173	2145	2091	2036	2013	1943
65°	1465	1438	1392	1351	1328	1449
75°	766	758	735	708	717	818
85°	187	182	178	164	160	209
90°	3	30	83	78	80	19
95°	124	147	151	151	147	137
105°	509	516	521	525	525	537
115°	947	961	957	954	947	937
125°	1378	1399	1392	1385	1382	1231
135°	1782	1809	1814	1811	1804	1378
145°	2164	2181	2194	2197	2188	1352
155°	2474	2481	2489	2500	2493	1139
165°	2692	2689	2689	2706	2694	759
175°	2801	2794	2789	2806	2792	266
180°	2806	2806	2806	2806	2806	

TEST NUMBER: P912064

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4746.7	4746.7	4746.7	4746.7	4746.7
2.5°	4774.2	4751.5	4701.2	4746.7	4738.0
5°	4746.7	4728.8	4678.4	4714.7	4706.0
7.5°	4714.7	4687.6	4637.3	4674.1	4664.9
10°	4664.9	4632.8	4578.2	4614.4	4600.9
12.5°	4596.1	4569.0	4514.3	4537.0	4527.8
15°	4518.6	4491.4	4431.9	4450.3	4427.6
17.5°	4422.7	4395.6	4336.1	4358.8	4336.1
20°	4317.7	4290.5	4226.6	4240.2	4222.3
22.5°	4213.1	4171.8	4112.3	4112.3	4103.1
25°	4089.5	4053.3	3975.8	3984.5	3975.8
27.5°	3952.5	3920.5	3861.4	3847.9	3825.2
30°	3816.0	3779.1	3710.8	3697.3	3678.9
32.5°	3669.7	3642.6	3569.4	3541.8	3523.4
35°	3528.3	3482.8	3409.6	3382.0	3359.3
37.5°	3368.5	3327.3	3254.2	3222.2	3199.5
40°	3204.3	3167.5	3094.4	3053.7	3035.3
42.5°	3044.5	3007.7	2935.1	2889.1	2862.0
45°	2871.2	2839.2	2770.4	2720.6	2702.2
47.5°	2702.2	2670.3	2597.1	2546.7	2519.5
50°	2524.0	2501.2	2437.2	2373.4	2350.6
52.5°	2350.6	2318.6	2259.6	2209.1	2177.2
55°	2172.9	2145.2	2090.6	2035.8	2013.1
57.5°	1994.6	1971.9	1912.4	1857.6	1839.2
60°	1816.4	1798.6	1734.6	1684.2	1670.7
62.5°	1643.1	1611.2	1565.6	1520.1	1501.7
65°	1465.3	1437.7	1392.2	1351.1	1328.4
67.5°	1282.8	1259.6	1218.9	1187.0	1168.6
70°	1113.8	1095.4	1054.2	1022.3	1004.3
72.5°	940.4	922.0	899.3	867.3	853.7
75°	766.5	757.9	734.6	707.5	716.7
77.5°	611.6	593.2	584.0	570.5	556.9
80°	456.7	451.8	442.6	429.1	419.9
82.5°	310.4	310.4	306.1	287.7	287.7
85°	187.0	182.5	178.2	164.1	159.8
87.5°	82.3	73.1	63.9	50.3	45.5
90°	2.6	30.5	83.0	77.9	80.4
92.5°	52.5	71.1	73.6	76.1	76.1
95°	123.5	147.2	151.4	151.4	147.2
97.5°	205.6	227.6	236.9	236.9	236.9
100°	300.3	319.7	326.5	326.5	323.9
102.5°	400.1	414.5	423.7	426.3	423.7
105°	509.3	516.0	521.1	525.3	525.3
107.5°	617.5	627.7	627.7	629.4	617.5
110°	722.4	735.9	735.9	735.9	729.2

TEST NUMBER: P912064

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	835.7	850.2	847.6	840.8	835.7
115°	947.4	960.9	956.7	954.2	947.4
117.5°	1058.2	1076.8	1065.0	1058.2	1051.4
120°	1169.9	1188.5	1169.9	1169.9	1162.2
122.5°	1271.4	1295.1	1283.2	1276.5	1271.4
125°	1377.9	1399.1	1392.3	1384.7	1382.3
127.5°	1482.1	1508.2	1498.9	1488.8	1482.1
130°	1579.3	1609.7	1605.5	1600.5	1591.2
132.5°	1688.5	1712.1	1713.8	1702.0	1695.2
135°	1782.3	1808.6	1813.7	1811.1	1804.3
137.5°	1887.2	1908.4	1912.6	1910.9	1900.7
140°	1979.5	2000.5	2012.4	2012.4	2003.1
142.5°	2074.2	2095.3	2102.1	2104.7	2095.3
145°	2163.9	2180.7	2194.3	2196.8	2187.5
147.5°	2244.2	2265.4	2275.4	2279.8	2270.5
150°	2327.1	2341.4	2350.7	2358.4	2350.7
152.5°	2400.7	2415.1	2426.9	2436.3	2426.9
155°	2474.3	2481.1	2488.7	2500.5	2492.9
157.5°	2537.7	2542.8	2547.0	2563.9	2552.1
160°	2594.4	2599.5	2602.0	2616.4	2606.3
162.5°	2646.9	2646.9	2649.4	2665.5	2653.6
165°	2691.7	2689.1	2689.1	2706.1	2694.2
167.5°	2732.2	2724.7	2724.7	2741.6	2729.7
170°	2762.7	2756.0	2753.4	2770.4	2756.0
172.5°	2783.9	2777.2	2774.6	2791.5	2777.2
175°	2800.8	2794.0	2788.9	2805.9	2791.5
177.5°	2810.1	2803.3	2798.2	2812.6	2798.2
180°	2805.9	2805.9	2805.9	2805.9	2805.9

TEST NUMBER: P912064

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.05	15.01	14.91	15.90	17.01	13.60	14.57	14.46	15.45	16.56
	3H	15.71	16.58	16.58	17.47	18.61	15.22	16.09	16.09	16.98	18.12
	4H	16.30	17.12	17.19	18.02	19.17	15.81	16.63	16.70	17.52	18.67
	6H	16.70	17.46	17.60	18.36	19.52	16.20	16.96	17.10	17.86	19.02
	8H	16.81	17.53	17.72	18.45	19.61	16.31	17.03	17.22	17.95	19.11
	12H	16.86	17.55	17.77	18.46	19.65	16.35	17.04	17.26	17.95	19.14
4H	2H	14.52	15.34	15.41	16.24	17.38	14.16	14.98	15.06	15.88	17.03
	3H	16.39	17.07	17.29	18.00	19.16	15.98	16.66	16.88	17.59	18.76
	4H	17.10	17.73	18.02	18.65	19.84	16.68	17.30	17.59	18.23	19.42
	6H	17.62	18.16	18.55	19.11	20.30	17.19	17.73	18.12	18.67	19.86
	8H	17.77	18.27	18.70	19.22	20.42	17.33	17.84	18.26	18.78	19.98
	12H	17.85	18.30	18.80	19.26	20.47	17.40	17.85	18.35	18.81	20.02
8H	4H	17.30	17.81	18.24	18.75	19.95	16.93	17.43	17.86	18.37	19.58
	6H	17.93	18.35	18.89	19.33	20.54	17.55	17.97	18.51	18.95	20.15
	8H	18.15	18.52	19.12	19.49	20.71	17.76	18.13	18.73	19.10	20.32
	12H	18.28	18.61	19.26	19.58	20.84	17.87	18.20	18.85	19.17	20.43
12H	4H	17.29	17.75	18.25	18.71	19.92	16.93	17.38	17.88	18.34	19.55
	6H	17.96	18.33	18.93	19.31	20.52	17.59	17.96	18.56	18.93	20.15
	8H	18.21	18.53	19.18	19.50	20.76	17.82	18.15	18.80	19.12	20.38