

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906657

Luminaire Tested: DFN2DIP-SQ3F0-120D110US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906657
REPORT IS A COMBINATION OF REPORTS P901523 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-120D110US835-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22770.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 211.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906657

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906657

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	87	91	87	84	81	74	72	69	62	61	59	51	50	49
2	89	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41
3	82	72	65	59	75	67	61	55	57	52	48	48	45	42	40	37	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5350	5350	5350
5°	5355	5272	5309
10°	5308	5197	5236
15°	5227	5108	5122
20°	5118	4986	5005
25°	5010	4840	4870
30°	4875	4704	4699
35°	4746	4545	4519
40°	4589	4383	4347
45°	4432	4221	4171
50°	4260	4051	3967
55°	4080	3854	3780
60°	3876	3621	3565
65°	3653	3379	3311
70°	3368	3083	3038
75°	2976	2729	2782
80°	2501	2277	2300
85°	1761	1509	1505

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4432 cd/sqm

TEST NUMBER: P906657

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.5	1.9
10°-20°	1236.5	5.4
20°-30°	1817.2	8.0
30°-40°	2110.5	9.3
40°-50°	2107.9	9.3
50°-60°	1838.0	8.1
60°-70°	1358.7	6.0
70°-80°	768.7	3.4
80°-90°	209.4	0.9
90°-100°	122.4	0.5
100°-110°	456.3	2.0
110°-120°	1210.3	5.3
120°-130°	2007.3	8.8
130°-140°	2132.2	9.4
140°-150°	1981.7	8.7
150°-160°	1593.2	7.0
160°-170°	1026.6	4.5
170°-180°	353.3	1.6
0°-30°	3493.1	15.3
0°-40°	5603.7	24.6
0°-60°	9549.6	41.9
0°-90°	11886.5	52.2
90°-120°	1789.0	7.9
90°-150°	7910.3	34.7
90°-180°	10883.0	47.8
0°-180°	22770.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4669	4669	4669	4669	4669	
5°	4669	4652	4602	4638	4629	443
15°	4445	4418	4360	4378	4355	1252
25°	4023	3987	3911	3920	3911	1851
35°	3471	3426	3354	3327	3304	2167
45°	2824	2793	2725	2676	2658	2180
55°	2137	2110	2056	2003	1980	1911
65°	1442	1414	1370	1329	1307	1425
75°	754	746	723	696	705	805
85°	184	180	175	162	157	205
90°	3	32	54	67	72	21
95°	174	86	105	118	116	207
105°	817	897	164	193	204	873
115°	1544	1590	1658	414	220	1521
125°	2184	2219	2270	2289	2297	1948
135°	2702	2746	2769	2797	2791	2088
145°	3135	3132	3178	3197	3183	1961
155°	3452	3428	3460	3476	3455	1591
165°	3637	3621	3629	3648	3629	1028
175°	3720	3702	3707	3726	3699	354
180°	3712	3712	3712	3712	3712	

TEST NUMBER: P906657

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4669.3	4669.3	4669.3	4669.3	4669.3
2.5°	4696.4	4674.0	4624.5	4669.3	4660.7
5°	4669.3	4651.6	4602.1	4637.8	4629.2
7.5°	4637.8	4611.1	4561.6	4597.8	4588.8
10°	4588.8	4557.3	4503.5	4539.2	4525.9
12.5°	4521.1	4494.4	4440.6	4463.0	4453.9
15°	4444.9	4418.2	4359.6	4377.7	4355.3
17.5°	4350.6	4323.9	4265.3	4287.7	4265.3
20°	4247.2	4220.5	4157.7	4171.0	4153.4
22.5°	4144.3	4103.8	4045.2	4045.2	4036.2
25°	4022.8	3987.1	3910.9	3919.5	3910.9
27.5°	3888.0	3856.6	3798.5	3785.1	3762.8
30°	3753.7	3717.5	3650.3	3637.0	3618.9
32.5°	3609.8	3583.2	3511.2	3484.1	3466.0
35°	3470.7	3426.0	3354.0	3326.9	3304.5
37.5°	3313.5	3273.1	3201.1	3169.7	3147.3
40°	3152.1	3115.9	3043.9	3003.9	2985.8
42.5°	2994.9	2958.7	2887.2	2842.0	2815.3
45°	2824.3	2792.9	2725.2	2676.2	2658.1
47.5°	2658.1	2626.6	2554.7	2505.2	2478.5
50°	2482.8	2460.4	2397.5	2334.6	2312.2
52.5°	2312.2	2280.8	2222.7	2173.1	2141.7
55°	2137.4	2110.3	2056.4	2002.6	1980.2
57.5°	1962.1	1939.7	1881.1	1827.3	1809.2
60°	1786.8	1769.2	1706.3	1656.8	1643.4
62.5°	1616.3	1584.8	1540.1	1495.3	1477.2
65°	1441.5	1414.3	1369.5	1329.0	1306.7
67.5°	1261.9	1239.0	1199.0	1167.6	1149.5
70°	1095.6	1077.5	1037.0	1005.6	988.0
72.5°	925.1	907.0	884.6	853.2	839.8
75°	754.1	745.5	722.6	696.0	705.0
77.5°	601.6	583.5	574.5	561.1	547.8
80°	449.2	444.4	435.4	422.1	413.0
82.5°	305.3	305.3	301.1	283.0	283.0
85°	183.9	179.6	175.3	161.5	157.2
87.5°	81.0	71.9	62.9	49.5	44.8
90°	2.6	32.2	53.6	67.3	72.4
92.5°	67.3	56.5	64.4	69.9	72.4
95°	174.5	85.8	104.6	118.3	115.5
97.5°	314.2	94.1	136.8	145.1	147.7
100°	475.6	107.5	153.1	174.5	179.9
102.5°	652.6	647.5	158.5	187.9	196.2
105°	816.6	897.3	164.0	193.3	204.2
107.5°	1007.4	1074.3	169.4	198.7	209.6
110°	1190.1	1246.3	470.2	201.6	212.1

TEST NUMBER: P906657

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1362.1	1410.2	1364.6	206.7	215.0
115°	1544.5	1590.1	1657.5	413.7	220.4
117.5°	1703.1	1756.7	1802.6	1418.2	714.5
120°	1880.4	1920.6	1969.1	2001.3	1638.6
122.5°	2030.7	2073.7	2127.6	2143.6	2146.5
125°	2183.8	2218.9	2269.9	2288.7	2296.7
127.5°	2323.5	2361.1	2401.6	2428.4	2431.0
130°	2455.2	2498.3	2527.6	2557.3	2554.8
132.5°	2589.5	2624.6	2654.0	2678.2	2675.7
135°	2702.5	2745.5	2769.4	2796.6	2791.1
137.5°	2820.5	2852.7	2879.8	2906.6	2898.6
140°	2936.0	2957.6	2987.0	3011.2	2997.8
142.5°	3032.9	3051.7	3086.5	3107.9	3094.5
145°	3135.0	3132.1	3177.7	3196.6	3183.2
147.5°	3223.4	3215.4	3261.0	3274.4	3263.9
150°	3309.5	3290.7	3333.7	3349.7	3336.3
152.5°	3381.9	3360.5	3400.7	3417.0	3398.2
155°	3451.8	3427.8	3460.0	3476.0	3454.6
157.5°	3508.2	3486.8	3511.1	3529.9	3508.2
160°	3556.7	3540.4	3556.7	3572.6	3553.8
162.5°	3599.4	3583.5	3596.9	3615.7	3591.5
165°	3637.1	3621.1	3629.1	3647.9	3629.1
167.5°	3666.7	3650.5	3658.8	3677.6	3653.4
170°	3691.0	3674.7	3680.1	3699.0	3674.7
172.5°	3706.9	3691.0	3696.4	3715.2	3691.0
175°	3720.3	3701.5	3706.9	3725.8	3699.0
177.5°	3725.8	3706.9	3709.8	3728.6	3704.4
180°	3712.4	3712.4	3712.4	3712.4	3712.4

TEST NUMBER: P906657

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.27	14.15	14.20	15.10	16.34	12.82	13.70	13.76	14.66	15.90
	3H	14.92	15.71	15.87	16.68	17.94	14.43	15.22	15.38	16.19	17.45
	4H	15.51	16.26	16.47	17.23	18.50	15.02	15.76	15.98	16.73	18.00
	6H	15.91	16.60	16.88	17.57	18.85	15.41	16.10	16.38	17.07	18.35
	8H	16.01	16.67	16.99	17.66	18.94	15.51	16.17	16.49	17.16	18.44
	12H	16.06	16.68	17.04	17.67	18.97	15.55	16.17	16.54	17.16	18.46
4H	2H	13.73	14.47	14.70	15.44	16.71	13.37	14.12	14.34	15.09	16.36
	3H	15.59	16.21	16.57	17.21	18.50	15.18	15.81	16.16	16.80	18.09
	4H	16.30	16.87	17.29	17.86	19.17	15.88	16.45	16.86	17.44	18.75
	6H	16.81	17.30	17.81	18.32	19.63	16.38	16.87	17.38	17.89	19.19
	8H	16.96	17.42	17.96	18.43	19.75	16.52	16.98	17.52	17.99	19.31
	12H	17.03	17.45	18.05	18.47	19.80	16.58	17.00	17.60	18.02	19.35
8H	4H	16.49	16.95	17.50	17.96	19.28	16.12	16.58	17.12	17.58	18.91
	6H	17.12	17.50	18.15	18.55	19.87	16.74	17.12	17.76	18.17	19.49
	8H	17.34	17.67	18.37	18.71	20.05	16.94	17.28	17.98	18.32	19.65
	12H	17.47	17.76	18.50	18.79	20.17	17.06	17.35	18.09	18.38	19.76
12H	4H	16.48	16.89	17.50	17.92	19.25	16.11	16.53	17.13	17.55	18.88
	6H	17.15	17.48	18.18	18.52	19.86	16.78	17.11	17.81	18.15	19.49
	8H	17.39	17.68	18.42	18.71	20.09	17.01	17.30	18.04	18.33	19.71