

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912066

Luminaire Tested: DFN2DIP-SQ3F0-110D080US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912066
REPORT IS A COMBINATION OF REPORTS P899948 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D080US850-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18220.9 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 172.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912066

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912066

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		63	63	63
1	100	96	92	89		93	89	86	83		77	75	73		66	65	63		56	55	54
2	91	84	78	73		85	79	74	69		68	65	61		59	56	54		50	48	46
3	84	75	67	62		78	70	64	58		61	56	52		53	49	46		45	42	40
4	77	66	59	53		71	62	55	50		54	49	45		47	43	40		40	37	35
5	71	59	52	46		66	56	49	43		49	43	39		43	38	35		37	33	31
6	65	54	46	40		61	50	43	38		44	39	34		39	34	31		34	30	27
7	61	49	41	35		57	46	39	34		40	35	31		35	31	28		31	27	25
8	56	44	37	31		53	42	35	30		37	31	27		33	28	25		28	25	22
9	53	41	33	28		49	38	32	27		34	29	25		30	26	22		26	23	20
10	49	37	30	26		46	35	29	24		32	26	22		28	24	20		24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5777	5777	5777
5°	5782	5681	5720
10°	5722	5566	5532
15°	5639	5378	5242
20°	5531	5121	4888
25°	5421	4834	4545
30°	5274	4539	4112
35°	5129	4223	3731
40°	4982	3896	3295
45°	4812	3534	2900
50°	4635	3169	2514
55°	4450	2779	2143
60°	4236	2372	1762
65°	3989	1959	1583
70°	3689	1573	1430
75°	3313	1378	1297
80°	2768	1144	1119
85°	1878	745	829

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4812 cd/sqm

TEST NUMBER: P912066

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.5	2.6
10°-20°	1297.2	7.1
20°-30°	1821.2	10.0
30°-40°	1985.2	10.9
40°-50°	1824.6	10.0
50°-60°	1433.0	7.9
60°-70°	932.7	5.1
70°-80°	480.1	2.6
80°-90°	130.6	0.7
90°-100°	173.6	1.0
100°-110°	551.7	3.0
110°-120°	944.1	5.2
120°-130°	1241.6	6.8
130°-140°	1393.7	7.6
140°-150°	1366.6	7.5
150°-160°	1146.4	6.3
160°-170°	760.3	4.2
170°-180°	265.7	1.5
0°-30°	3590.9	19.7
0°-40°	5576.1	30.6
0°-60°	8833.7	48.5
0°-90°	10377.1	57.0
90°-120°	1669.4	9.2
90°-150°	5671.3	31.1
90°-180°	7844.0	43.0
0°-180°	18220.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5042	5042	5042	5042	5042	
5°	5042	5019	4960	5001	4987	478
15°	4795	4745	4590	4504	4458	1351
25°	4353	4207	3906	3719	3650	2002
35°	3751	3518	3117	2829	2728	2348
45°	3066	2760	2282	1957	1848	2368
55°	2331	1976	1483	1209	1123	2083
65°	1574	1204	794	639	625	1561
75°	839	520	365	333	329	888
85°	196	100	87	87	87	225
90°	3	30	83	78	80	18
95°	124	147	151	151	147	137
105°	509	516	521	525	525	537
115°	947	961	957	954	947	937
125°	1378	1399	1392	1385	1382	1231
135°	1782	1809	1814	1811	1804	1378
145°	2164	2181	2194	2197	2188	1352
155°	2474	2481	2489	2500	2493	1139
165°	2692	2689	2689	2706	2694	759
175°	2801	2794	2789	2806	2792	266
180°	2806	2806	2806	2806	2806	



TEST NUMBER: P912066

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5041.8	5041.8	5041.8	5041.8	5041.8
2.5°	5064.6	5041.8	4991.5	5037.5	5028.3
5°	5041.8	5019.1	4959.6	5000.7	4987.2
7.5°	5000.7	4973.5	4909.7	4927.6	4904.8
10°	4946.0	4914.0	4823.0	4809.0	4781.9
12.5°	4877.7	4836.6	4713.1	4686.0	4635.6
15°	4795.4	4745.1	4590.2	4503.5	4458.0
17.5°	4699.6	4626.5	4434.8	4334.5	4261.4
20°	4590.2	4498.7	4270.6	4156.9	4056.2
22.5°	4471.6	4366.5	4101.7	3946.8	3878.5
25°	4352.9	4206.8	3905.7	3718.8	3650.1
27.5°	4211.6	4056.2	3723.1	3508.7	3403.6
30°	4061.0	3887.3	3522.3	3289.8	3166.4
32.5°	3914.9	3704.7	3331.0	3057.1	2942.8
35°	3750.7	3517.9	3116.6	2829.1	2728.4
37.5°	3591.1	3339.8	2915.7	2600.5	2486.8
40°	3422.0	3148.6	2705.6	2381.7	2263.1
42.5°	3248.7	2956.8	2496.0	2158.1	2044.3
45°	3066.3	2760.3	2281.5	1957.2	1847.8
47.5°	2892.9	2569.1	2076.3	1751.9	1651.7
50°	2701.2	2377.4	1875.4	1560.3	1464.9
52.5°	2513.9	2171.6	1683.7	1382.6	1295.9
55°	2331.3	1975.6	1482.7	1209.3	1122.6
57.5°	2144.6	1779.5	1305.1	1049.6	976.4
60°	1952.8	1587.9	1117.8	885.4	812.3
62.5°	1766.0	1401.0	958.1	739.3	702.9
65°	1574.2	1204.4	793.9	639.0	624.9
67.5°	1391.8	1021.9	639.0	561.0	547.5
70°	1200.0	844.3	529.1	483.6	465.2
72.5°	1017.5	679.7	442.5	406.1	396.9
75°	839.4	519.9	365.0	333.0	328.7
77.5°	661.7	369.4	287.6	269.2	259.9
80°	497.2	264.8	218.8	201.0	201.0
82.5°	346.6	178.1	150.6	141.4	141.4
85°	196.1	100.3	86.6	86.6	86.6
87.5°	73.1	36.3	36.3	31.9	31.9
90°	2.6	30.5	83.0	77.9	80.4
92.5°	52.5	71.1	73.6	76.1	76.1
95°	123.5	147.2	151.4	151.4	147.2
97.5°	205.6	227.6	236.9	236.9	236.9
100°	300.3	319.7	326.5	326.5	323.9
102.5°	400.1	414.5	423.7	426.3	423.7
105°	509.3	516.0	521.1	525.3	525.3
107.5°	617.5	627.7	627.7	629.4	617.5
110°	722.4	735.9	735.9	735.9	729.2

TEST NUMBER: P912066

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	835.7	850.2	847.6	840.8	835.7
115°	947.4	960.9	956.7	954.2	947.4
117.5°	1058.2	1076.8	1065.0	1058.2	1051.4
120°	1169.9	1188.5	1169.9	1169.9	1162.2
122.5°	1271.4	1295.1	1283.2	1276.5	1271.4
125°	1377.9	1399.1	1392.3	1384.7	1382.3
127.5°	1482.1	1508.2	1498.9	1488.8	1482.1
130°	1579.3	1609.7	1605.5	1600.5	1591.2
132.5°	1688.5	1712.1	1713.8	1702.0	1695.2
135°	1782.3	1808.6	1813.7	1811.1	1804.3
137.5°	1887.2	1908.4	1912.6	1910.9	1900.7
140°	1979.5	2000.5	2012.4	2012.4	2003.1
142.5°	2074.2	2095.3	2102.1	2104.7	2095.3
145°	2163.9	2180.7	2194.3	2196.8	2187.5
147.5°	2244.2	2265.4	2275.4	2279.8	2270.5
150°	2327.1	2341.4	2350.7	2358.4	2350.7
152.5°	2400.7	2415.1	2426.9	2436.3	2426.9
155°	2474.3	2481.1	2488.7	2500.5	2492.9
157.5°	2537.7	2542.8	2547.0	2563.9	2552.1
160°	2594.4	2599.5	2602.0	2616.4	2606.3
162.5°	2646.9	2646.9	2649.4	2665.5	2653.6
165°	2691.7	2689.1	2689.1	2706.1	2694.2
167.5°	2732.2	2724.7	2724.7	2741.6	2729.7
170°	2762.7	2756.0	2753.4	2770.4	2756.0
172.5°	2783.9	2777.2	2774.6	2791.5	2777.2
175°	2800.8	2794.0	2788.9	2805.9	2791.5
177.5°	2810.1	2803.3	2798.2	2812.6	2798.2
180°	2805.9	2805.9	2805.9	2805.9	2805.9

TEST NUMBER: P912066

CATALOG NUMBER: DFN2DIP-SQ3F0-110D080US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.83	14.72	14.73	15.64	16.81	9.79	10.68	10.69	11.60	12.77
	3H	15.51	16.31	16.42	17.23	18.43	10.98	11.78	11.89	12.70	13.90
	4H	16.12	16.87	17.05	17.80	19.01	11.43	12.18	12.36	13.11	14.32
	6H	16.54	17.23	17.48	18.17	19.39	11.75	12.44	12.69	13.38	14.59
	8H	16.66	17.32	17.61	18.28	19.49	11.83	12.49	12.78	13.45	14.66
	12H	16.73	17.35	17.68	18.30	19.54	11.88	12.50	12.83	13.45	14.69
4H	2H	13.85	14.61	14.79	15.54	16.74	10.39	11.14	11.33	12.08	13.28
	3H	15.68	16.31	16.63	17.27	18.49	11.74	12.37	12.69	13.33	14.55
	4H	16.38	16.94	17.33	17.90	19.15	12.29	12.85	13.24	13.81	15.06
	6H	16.89	17.38	17.86	18.36	19.60	12.70	13.19	13.67	14.17	15.42
	8H	17.06	17.52	18.03	18.49	19.75	12.83	13.29	13.80	14.26	15.52
	12H	17.16	17.57	18.15	18.56	19.82	12.89	13.30	13.88	14.29	15.56
8H	4H	16.35	16.80	17.31	17.78	19.04	12.57	13.02	13.54	14.00	15.26
	6H	16.91	17.29	17.90	18.30	19.56	13.08	13.46	14.07	14.47	15.73
	8H	17.12	17.46	18.13	18.46	19.73	13.27	13.60	14.27	14.60	15.88
	12H	17.26	17.55	18.27	18.55	19.87	13.38	13.68	14.39	14.67	15.99
12H	4H	16.30	16.71	17.29	17.70	18.97	12.57	12.99	13.56	13.98	15.24
	6H	16.88	17.22	17.89	18.22	19.50	13.13	13.46	14.13	14.47	15.74
	8H	17.10	17.40	18.11	18.39	19.72	13.34	13.63	14.34	14.63	15.95

END OF REPORT