

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912114

Luminaire Tested: DFN2DIP-SQ3F0-120D110US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912114
REPORT IS A COMBINATION OF REPORTS P900004 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-120D110US850-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22107.9 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 211.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912114

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912114

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32
5	70	58	51	45	64	54	47	42	47	42	37	40	36	33	34	31	28
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6302	6302	6302
5°	6308	6198	6240
10°	6242	6072	6035
15°	6152	5867	5719
20°	6034	5587	5332
25°	5914	5273	4959
30°	5753	4952	4486
35°	5596	4607	4070
40°	5435	4250	3594
45°	5249	3855	3163
50°	5056	3457	2742
55°	4855	3032	2338
60°	4621	2587	1922
65°	4352	2137	1728
70°	4025	1716	1560
75°	3614	1504	1415
80°	3020	1248	1220
85°	2048	813	905

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5249 cd/sqm

TEST NUMBER: P912114

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.5	2.3
10°-20°	1415.1	6.4
20°-30°	1986.8	9.0
30°-40°	2165.7	9.8
40°-50°	1990.5	9.0
50°-60°	1563.2	7.1
60°-70°	1017.5	4.6
70°-80°	523.8	2.4
80°-90°	144.7	0.7
90°-100°	238.7	1.1
100°-110°	758.6	3.4
110°-120°	1298.1	5.9
120°-130°	1707.2	7.7
130°-140°	1916.3	8.7
140°-150°	1879.1	8.5
150°-160°	1576.3	7.1
160°-170°	1045.4	4.7
170°-180°	365.4	1.7
0°-30°	3917.3	17.7
0°-40°	6083.0	27.5
0°-60°	9636.8	43.6
0°-90°	11322.7	51.2
90°-120°	2295.4	10.4
90°-150°	7798.0	35.3
90°-180°	10785.0	48.8
0°-180°	22107.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5500	5500	5500	5500	5500	
5°	5500	5475	5410	5455	5440	522
15°	5231	5176	5008	4913	4863	1474
25°	4749	4589	4261	4057	3982	2184
35°	4092	3838	3400	3086	2976	2561
45°	3345	3011	2489	2135	2016	2583
55°	2543	2155	1618	1319	1225	2273
65°	1717	1314	866	697	682	1703
75°	916	567	398	363	358	969
85°	214	109	94	94	94	246
90°	3	42	114	107	110	22
95°	170	202	208	208	202	189
105°	700	710	716	722	722	739
115°	1303	1321	1316	1312	1303	1288
125°	1895	1924	1914	1904	1900	1693
135°	2451	2487	2494	2490	2481	1894
145°	2975	2998	3017	3021	3008	1859
155°	3402	3411	3422	3438	3428	1566
165°	3701	3698	3698	3721	3704	1044
175°	3851	3842	3835	3858	3838	366
180°	3858	3858	3858	3858	3858	

TEST NUMBER: P912114

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5500.2	5500.2	5500.2	5500.2	5500.2
2.5°	5525.0	5500.2	5445.3	5495.4	5485.3
5°	5500.2	5475.4	5410.4	5455.3	5440.5
7.5°	5455.3	5425.7	5356.0	5375.5	5350.7
10°	5395.6	5360.8	5261.4	5246.1	5216.6
12.5°	5321.1	5276.3	5141.5	5112.0	5057.2
15°	5231.4	5176.5	5007.5	4912.9	4863.3
17.5°	5126.8	5047.1	4837.9	4728.7	4648.9
20°	5007.5	4907.7	4658.9	4534.8	4424.9
22.5°	4878.0	4763.5	4474.6	4305.6	4231.2
25°	4748.7	4589.2	4260.7	4056.8	3981.9
27.5°	4594.5	4424.9	4061.6	3827.7	3713.0
30°	4430.2	4240.7	3842.5	3588.9	3454.3
32.5°	4270.8	4041.5	3633.9	3335.0	3210.3
35°	4091.8	3837.7	3399.9	3086.2	2976.3
37.5°	3917.4	3643.4	3180.7	2836.9	2712.8
40°	3733.1	3434.8	2951.6	2598.3	2468.9
42.5°	3544.0	3225.6	2722.9	2354.3	2230.2
45°	3345.0	3011.3	2488.9	2135.2	2015.7
47.5°	3155.9	2802.7	2265.0	1911.3	1801.9
50°	2946.8	2593.5	2045.9	1702.1	1598.1
52.5°	2742.4	2369.0	1836.7	1508.2	1413.8
55°	2543.4	2155.2	1617.6	1319.2	1224.7
57.5°	2339.4	1941.3	1423.7	1144.9	1065.2
60°	2130.4	1732.1	1219.3	965.9	886.2
62.5°	1926.6	1528.3	1045.1	806.5	766.8
65°	1717.4	1313.9	866.1	697.1	681.8
67.5°	1518.3	1114.8	697.1	612.1	597.3
70°	1309.2	921.0	577.2	527.6	507.5
72.5°	1110.1	741.5	482.6	443.0	433.1
75°	915.7	567.1	398.2	363.3	358.5
77.5°	722.0	402.9	313.7	293.7	283.6
80°	542.4	288.9	238.7	219.1	219.1
82.5°	378.2	194.3	164.2	154.2	154.2
85°	213.9	109.3	94.5	94.5	94.5
87.5°	79.7	39.6	39.6	34.8	34.8
90°	3.4	41.9	114.0	107.0	110.5
92.5°	72.1	97.7	101.1	104.7	104.7
95°	169.8	202.4	208.2	208.2	202.4
97.5°	282.7	312.8	325.7	325.7	325.7
100°	412.9	439.6	448.9	448.9	445.5
102.5°	550.2	569.9	582.8	586.2	582.8
105°	700.2	709.5	716.5	722.3	722.3
107.5°	849.1	863.0	863.0	865.4	849.1
110°	993.3	1012.0	1012.0	1012.0	1002.6

TEST NUMBER: P912114

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1149.1	1168.9	1165.4	1156.1	1149.1
115°	1302.7	1321.3	1315.5	1312.1	1302.7
117.5°	1455.1	1480.6	1464.3	1455.1	1445.8
120°	1608.6	1634.2	1608.6	1608.6	1598.2
122.5°	1748.2	1780.7	1764.4	1755.1	1748.2
125°	1894.7	1923.8	1914.5	1904.0	1900.5
127.5°	2037.8	2073.8	2061.1	2047.1	2037.8
130°	2171.5	2213.5	2207.6	2200.6	2187.8
132.5°	2321.6	2354.2	2356.5	2340.2	2330.9
135°	2450.7	2486.7	2493.7	2490.3	2480.9
137.5°	2594.9	2624.0	2629.8	2627.4	2613.6
140°	2721.7	2750.8	2767.1	2767.1	2754.3
142.5°	2852.0	2881.1	2890.4	2893.8	2881.1
145°	2975.2	2998.5	3017.1	3020.6	3007.8
147.5°	3085.8	3114.8	3128.8	3134.6	3121.8
150°	3199.8	3219.5	3232.3	3242.8	3232.3
152.5°	3300.9	3320.7	3337.0	3349.8	3337.0
155°	3402.2	3411.4	3421.9	3438.2	3427.7
157.5°	3489.4	3496.3	3502.1	3525.4	3509.1
160°	3567.3	3574.3	3577.7	3597.6	3583.6
162.5°	3639.4	3639.4	3643.0	3665.0	3648.7
165°	3701.1	3697.5	3697.5	3720.8	3704.5
167.5°	3756.8	3746.4	3746.4	3769.7	3753.4
170°	3798.8	3789.5	3786.0	3809.2	3789.5
172.5°	3827.8	3818.5	3815.1	3838.4	3818.5
175°	3851.1	3841.8	3834.8	3858.1	3838.4
177.5°	3863.9	3854.6	3847.6	3867.4	3847.6
180°	3858.1	3858.1	3858.1	3858.1	3858.1

TEST NUMBER: P912114

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.62	14.46	14.57	15.43	16.68	9.58	10.42	10.53	11.39	12.64
	3H	15.29	16.05	16.26	17.02	18.30	10.76	11.52	11.73	12.49	13.77
	4H	15.90	16.61	16.88	17.59	18.88	11.21	11.92	12.19	12.90	14.19
	6H	16.32	16.97	17.31	17.96	19.26	11.53	12.18	12.52	13.16	14.46
	8H	16.44	17.07	17.44	18.06	19.36	11.61	12.24	12.61	13.24	14.53
	12H	16.50	17.09	17.50	18.09	19.41	11.65	12.25	12.66	13.24	14.56
4H	2H	13.64	14.35	14.62	15.33	16.61	10.18	10.89	11.16	11.86	13.15
	3H	15.46	16.05	16.46	17.06	18.36	11.52	12.11	12.51	13.12	14.42
	4H	16.15	16.69	17.15	17.69	19.02	12.06	12.60	13.06	13.60	14.93
	6H	16.66	17.13	17.68	18.15	19.47	12.48	12.94	13.49	13.96	15.29
	8H	16.84	17.27	17.85	18.28	19.62	12.60	13.03	13.61	14.05	15.39
	12H	16.93	17.32	17.96	18.35	19.69	12.66	13.05	13.69	14.08	15.43
8H	4H	16.12	16.55	17.13	17.57	18.91	12.34	12.77	13.35	13.79	15.13
	6H	16.68	17.04	17.72	18.10	19.43	12.85	13.21	13.89	14.27	15.60
	8H	16.89	17.21	17.94	18.25	19.61	13.04	13.35	14.08	14.40	15.75
	12H	17.03	17.31	18.08	18.34	19.74	13.15	13.43	14.20	14.47	15.86
12H	4H	16.07	16.46	17.10	17.49	18.84	12.34	12.73	13.38	13.77	15.11
	6H	16.65	16.97	17.70	18.01	19.37	12.90	13.21	13.94	14.26	15.61
	8H	16.87	17.15	17.92	18.19	19.59	13.10	13.38	14.15	14.42	15.82