

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909125

Luminaire Tested: DFN2DIP-SQ3F0-050D090US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909125
REPORT IS A COMBINATION OF REPORTS P901473 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D090US840-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13996.7 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 110.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909125

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909125

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	33	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	26	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	21	19
6	61	49	41	35	55	44	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2251	2251	2251
5°	2253	2218	2234
10°	2234	2187	2203
15°	2199	2149	2155
20°	2154	2098	2106
25°	2108	2037	2049
30°	2051	1979	1978
35°	1997	1912	1902
40°	1931	1844	1829
45°	1865	1776	1755
50°	1793	1705	1669
55°	1717	1622	1590
60°	1631	1524	1500
65°	1537	1422	1393
70°	1417	1297	1278
75°	1252	1148	1171
80°	1052	958	968
85°	741	634	633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2100 cd/sqm

TEST NUMBER: P909125

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	1.3
10°-20°	520.3	3.7
20°-30°	764.6	5.5
30°-40°	888.1	6.3
40°-50°	887.0	6.3
50°-60°	773.4	5.5
60°-70°	571.7	4.1
70°-80°	323.5	2.3
80°-90°	90.8	0.6
90°-100°	101.2	0.7
100°-110°	377.0	2.7
110°-120°	1000.0	7.1
120°-130°	1658.6	11.8
130°-140°	1761.8	12.6
140°-150°	1637.4	11.7
150°-160°	1316.4	9.4
160°-170°	848.2	6.1
170°-180°	292.0	2.1
0°-30°	1469.8	10.5
0°-40°	2357.9	16.8
0°-60°	4018.3	28.7
0°-90°	5004.2	35.8
90°-120°	1478.2	10.6
90°-150°	6535.9	46.7
90°-180°	8992.0	64.2
0°-180°	13996.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1965	1965	1965	1965	1965	
5°	1965	1957	1936	1952	1948	187
15°	1870	1859	1834	1842	1833	527
25°	1693	1678	1646	1649	1646	779
35°	1460	1442	1411	1400	1390	912
45°	1188	1175	1147	1126	1118	917
55°	899	888	865	843	833	804
65°	606	595	576	559	550	600
75°	317	314	304	293	297	339
85°	77	76	74	68	66	86
90°	2	27	44	56	60	13
95°	144	71	86	98	95	171
105°	675	741	135	160	169	721
115°	1276	1314	1370	342	182	1256
125°	1804	1833	1876	1891	1898	1609
135°	2233	2268	2288	2311	2306	1725
145°	2590	2588	2626	2641	2630	1620
155°	2852	2832	2859	2872	2854	1314
165°	3005	2992	2999	3014	2999	849
175°	3074	3058	3063	3078	3056	293
180°	3067	3067	3067	3067	3067	

TEST NUMBER: P909125

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US840-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.7	1964.7	1964.7	1964.7	1964.7
2.5°	1976.1	1966.7	1945.9	1964.7	1961.2
5°	1964.7	1957.3	1936.4	1951.5	1947.9
7.5°	1951.5	1940.3	1919.5	1934.7	1930.9
10°	1930.9	1917.6	1895.0	1910.0	1904.4
12.5°	1902.4	1891.2	1868.6	1877.9	1874.1
15°	1870.3	1859.1	1834.4	1842.1	1832.6
17.5°	1830.6	1819.4	1794.7	1804.1	1794.7
20°	1787.2	1775.9	1749.5	1755.0	1747.7
22.5°	1743.8	1726.8	1702.1	1702.1	1698.3
25°	1692.7	1677.7	1645.6	1649.2	1645.6
27.5°	1636.0	1622.8	1598.3	1592.7	1583.3
30°	1579.4	1564.3	1536.0	1530.4	1522.8
32.5°	1518.9	1507.7	1477.4	1466.0	1458.4
35°	1460.4	1441.6	1411.3	1399.9	1390.5
37.5°	1394.2	1377.3	1347.0	1333.7	1324.3
40°	1326.4	1311.1	1280.8	1263.9	1256.4
42.5°	1260.2	1245.0	1214.9	1195.8	1184.6
45°	1188.4	1175.2	1146.7	1126.1	1118.4
47.5°	1118.4	1105.2	1075.0	1054.1	1042.9
50°	1044.7	1035.3	1008.9	982.4	972.9
52.5°	972.9	959.7	935.2	914.4	901.2
55°	899.4	888.0	865.3	842.6	833.2
57.5°	825.6	816.2	791.5	768.9	761.2
60°	751.8	744.5	718.0	697.1	691.6
62.5°	680.1	666.9	648.0	629.1	621.6
65°	606.5	595.1	576.2	559.3	549.8
67.5°	531.0	521.4	504.5	491.3	483.6
70°	461.0	453.4	436.4	423.1	415.8
72.5°	389.3	381.6	372.2	359.0	353.4
75°	317.3	313.7	304.1	292.9	296.7
77.5°	253.2	245.5	241.8	236.1	230.6
80°	189.0	187.0	183.2	177.6	173.8
82.5°	128.5	128.5	126.6	119.1	119.1
85°	77.4	75.5	73.7	68.0	66.1
87.5°	34.0	30.3	26.5	20.8	18.9
90°	2.1	26.7	44.2	55.6	59.8
92.5°	55.6	46.7	53.2	57.8	59.8
95°	144.2	70.9	86.4	97.8	95.4
97.5°	259.6	77.8	113.1	119.9	122.0
100°	392.9	88.9	126.5	144.2	148.7
102.5°	539.3	535.0	131.0	155.2	162.1
105°	674.7	741.4	135.4	159.8	168.6
107.5°	832.3	887.7	140.0	164.2	173.2
110°	983.3	1029.8	388.5	166.5	175.3

TEST NUMBER: P909125

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1125.4	1165.2	1127.5	170.8	177.6
115°	1276.2	1313.8	1369.5	341.8	182.1
117.5°	1407.1	1451.5	1489.3	1171.8	590.4
120°	1553.7	1586.9	1627.0	1653.6	1353.9
122.5°	1677.9	1713.4	1758.0	1771.1	1773.5
125°	1804.3	1833.3	1875.5	1891.1	1897.6
127.5°	1919.8	1950.9	1984.4	2006.5	2008.6
130°	2028.6	2064.3	2088.5	2112.9	2110.9
132.5°	2139.6	2168.6	2192.8	2212.9	2210.8
135°	2232.9	2268.5	2288.3	2310.7	2306.2
137.5°	2330.5	2357.0	2379.4	2401.6	2395.0
140°	2425.8	2443.8	2468.0	2488.0	2477.0
142.5°	2506.0	2521.5	2550.2	2567.9	2556.9
145°	2590.3	2587.9	2625.7	2641.2	2630.1
147.5°	2663.3	2656.8	2694.4	2705.5	2696.7
150°	2734.5	2719.0	2754.5	2767.6	2756.6
152.5°	2794.3	2776.6	2809.8	2823.3	2807.7
155°	2852.1	2832.3	2858.8	2872.1	2854.4
157.5°	2898.7	2881.0	2901.0	2916.6	2898.7
160°	2938.7	2925.3	2938.7	2951.9	2936.4
162.5°	2974.1	2960.8	2971.9	2987.5	2967.5
165°	3005.2	2991.9	2998.6	3014.1	2998.6
167.5°	3029.7	3016.3	3023.0	3038.6	3018.6
170°	3049.7	3036.3	3040.7	3056.3	3036.3
172.5°	3062.9	3049.7	3054.1	3069.7	3049.7
175°	3073.9	3058.4	3062.9	3078.4	3056.3
177.5°	3078.4	3062.9	3065.2	3080.8	3060.8
180°	3067.4	3067.4	3067.4	3067.4	3067.4

TEST NUMBER: P909125

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.57	9.32	9.64	10.39	11.85	8.13	8.88	9.20	9.95	11.41
	3H	10.22	10.89	11.30	11.97	13.45	9.73	10.40	10.81	11.48	12.96
	4H	10.80	11.44	11.89	12.52	14.00	10.31	10.94	11.40	12.02	13.51
	6H	11.19	11.78	12.29	12.86	14.36	10.69	11.27	11.79	12.36	13.86
	8H	11.29	11.85	12.39	12.95	14.44	10.79	11.34	11.89	12.45	13.94
	12H	11.33	11.86	12.44	12.96	14.47	10.82	11.35	11.93	12.45	13.96
4H	2H	9.02	9.65	10.12	10.73	12.22	8.66	9.30	9.76	10.38	11.86
	3H	10.87	11.40	11.97	12.51	14.00	10.46	10.99	11.56	12.10	13.60
	4H	11.57	12.06	12.68	13.16	14.68	11.15	11.64	12.26	12.73	14.25
	6H	12.08	12.49	13.19	13.62	15.13	11.64	12.06	12.76	13.18	14.70
	8H	12.22	12.61	13.34	13.73	15.25	11.78	12.17	12.90	13.29	14.82
	12H	12.29	12.64	13.42	13.77	15.30	11.84	12.19	12.97	13.32	14.85
8H	4H	11.76	12.15	12.87	13.26	14.79	11.38	11.77	12.50	12.88	14.41
	6H	12.38	12.70	13.51	13.85	15.38	11.99	12.31	13.13	13.47	14.99
	8H	12.59	12.87	13.74	14.01	15.55	12.20	12.48	13.34	13.62	15.16
	12H	12.72	12.96	13.86	14.10	15.68	12.30	12.55	13.45	13.69	15.27
12H	4H	11.74	12.09	12.87	13.21	14.75	11.37	11.72	12.50	12.85	14.38
	6H	12.40	12.69	13.55	13.82	15.37	12.03	12.31	13.18	13.45	14.99
	8H	12.64	12.88	13.78	14.02	15.60	12.26	12.50	13.40	13.64	15.22

END OF REPORT