

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909133

Luminaire Tested: DFN2DIP-SQ3F0-050D110US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909133
REPORT IS A COMBINATION OF REPORTS P901509 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D110US840-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15996.2 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 128.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909133

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909133

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	80	77	74	64	62	60	48	47	46	34	34	33
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28
3	78	69	61	56	70	62	56	51	49	45	41	38	35	32	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	33	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	15
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	15	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2251	2251	2251
5°	2253	2218	2234
10°	2234	2187	2203
15°	2199	2149	2155
20°	2154	2098	2106
25°	2108	2037	2049
30°	2051	1979	1978
35°	1997	1912	1902
40°	1931	1844	1829
45°	1865	1776	1755
50°	1793	1705	1669
55°	1717	1622	1590
60°	1631	1524	1500
65°	1537	1422	1393
70°	1417	1297	1278
75°	1252	1148	1171
80°	1052	958	968
85°	741	634	633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2567 cd/sqm

TEST NUMBER: P909133

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	1.2
10°-20°	520.3	3.3
20°-30°	764.6	4.8
30°-40°	888.1	5.6
40°-50°	887.0	5.5
50°-60°	773.4	4.8
60°-70°	571.7	3.6
70°-80°	323.5	2.0
80°-90°	92.0	0.6
90°-100°	123.6	0.8
100°-110°	460.8	2.9
110°-120°	1222.2	7.6
120°-130°	2027.1	12.7
130°-140°	2153.3	13.5
140°-150°	2001.2	12.5
150°-160°	1608.9	10.1
160°-170°	1036.7	6.5
170°-180°	356.8	2.2
0°-30°	1469.8	9.2
0°-40°	2357.9	14.7
0°-60°	4018.3	25.1
0°-90°	5005.4	31.3
90°-120°	1806.7	11.3
90°-150°	7988.3	49.9
90°-180°	10991.0	68.7
0°-180°	15996.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1965	1965	1965	1965	1965	
5°	1965	1957	1936	1952	1948	187
15°	1870	1859	1834	1842	1833	527
25°	1693	1678	1646	1649	1646	779
35°	1460	1442	1411	1400	1390	912
45°	1188	1175	1147	1126	1118	917
55°	899	888	865	843	833	804
65°	606	595	576	559	550	600
75°	317	314	304	293	297	339
85°	77	76	74	68	66	86
90°	3	32	54	68	73	15
95°	176	87	106	120	117	209
105°	825	906	166	195	206	881
115°	1560	1606	1674	418	223	1536
125°	2205	2241	2292	2311	2319	1967
135°	2729	2773	2797	2824	2819	2108
145°	3166	3163	3209	3228	3215	1980
155°	3486	3462	3494	3510	3489	1606
165°	3673	3657	3665	3684	3665	1038
175°	3757	3738	3744	3763	3736	358
180°	3749	3749	3749	3749	3749	

TEST NUMBER: P909133

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US840-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.7	1964.7	1964.7	1964.7	1964.7
2.5°	1976.1	1966.7	1945.9	1964.7	1961.2
5°	1964.7	1957.3	1936.4	1951.5	1947.9
7.5°	1951.5	1940.3	1919.5	1934.7	1930.9
10°	1930.9	1917.6	1895.0	1910.0	1904.4
12.5°	1902.4	1891.2	1868.6	1877.9	1874.1
15°	1870.3	1859.1	1834.4	1842.1	1832.6
17.5°	1830.6	1819.4	1794.7	1804.1	1794.7
20°	1787.2	1775.9	1749.5	1755.0	1747.7
22.5°	1743.8	1726.8	1702.1	1702.1	1698.3
25°	1692.7	1677.7	1645.6	1649.2	1645.6
27.5°	1636.0	1622.8	1598.3	1592.7	1583.3
30°	1579.4	1564.3	1536.0	1530.4	1522.8
32.5°	1518.9	1507.7	1477.4	1466.0	1458.4
35°	1460.4	1441.6	1411.3	1399.9	1390.5
37.5°	1394.2	1377.3	1347.0	1333.7	1324.3
40°	1326.4	1311.1	1280.8	1263.9	1256.4
42.5°	1260.2	1245.0	1214.9	1195.8	1184.6
45°	1188.4	1175.2	1146.7	1126.1	1118.4
47.5°	1118.4	1105.2	1075.0	1054.1	1042.9
50°	1044.7	1035.3	1008.9	982.4	972.9
52.5°	972.9	959.7	935.2	914.4	901.2
55°	899.4	888.0	865.3	842.6	833.2
57.5°	825.6	816.2	791.5	768.9	761.2
60°	751.8	744.5	718.0	697.1	691.6
62.5°	680.1	666.9	648.0	629.1	621.6
65°	606.5	595.1	576.2	559.3	549.8
67.5°	531.0	521.4	504.5	491.3	483.6
70°	461.0	453.4	436.4	423.1	415.8
72.5°	389.3	381.6	372.2	359.0	353.4
75°	317.3	313.7	304.1	292.9	296.7
77.5°	253.2	245.5	241.8	236.1	230.6
80°	189.0	187.0	183.2	177.6	173.8
82.5°	128.5	128.5	126.6	119.1	119.1
85°	77.4	75.5	73.7	68.0	66.1
87.5°	34.0	30.3	26.5	20.8	18.9
90°	2.6	32.5	54.1	68.0	73.1
92.5°	68.0	57.1	65.0	70.6	73.1
95°	176.2	86.6	105.6	119.5	116.6
97.5°	317.3	95.0	138.1	146.5	149.2
100°	480.3	108.6	154.6	176.2	181.7
102.5°	659.0	653.9	160.1	189.8	198.1
105°	824.7	906.2	165.6	195.2	206.2
107.5°	1017.3	1084.9	171.1	200.7	211.7
110°	1201.8	1258.6	474.8	203.6	214.2

TEST NUMBER: P909133

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1375.5	1424.1	1378.1	208.7	217.1
115°	1559.7	1605.8	1673.9	417.8	222.6
117.5°	1719.9	1774.0	1820.4	1432.2	721.5
120°	1899.0	1939.5	1988.5	2021.0	1654.8
122.5°	2050.7	2094.2	2148.6	2164.7	2167.7
125°	2205.3	2240.8	2292.3	2311.3	2319.4
127.5°	2346.4	2384.4	2425.3	2452.4	2455.0
130°	2479.4	2522.9	2552.5	2582.5	2580.0
132.5°	2615.0	2650.5	2680.2	2704.6	2702.1
135°	2729.2	2772.6	2796.7	2824.2	2818.6
137.5°	2848.3	2880.8	2908.2	2935.3	2927.2
140°	2965.0	2986.8	3016.5	3040.9	3027.4
142.5°	3062.8	3081.8	3116.9	3138.6	3125.0
145°	3165.9	3163.0	3209.0	3228.1	3214.6
147.5°	3255.2	3247.1	3293.2	3306.7	3296.1
150°	3342.2	3323.2	3366.6	3382.7	3369.2
152.5°	3415.3	3393.7	3434.2	3450.7	3431.7
155°	3485.9	3461.6	3494.1	3510.3	3488.7
157.5°	3542.8	3521.2	3545.7	3564.7	3542.8
160°	3591.8	3575.3	3591.8	3607.8	3588.9
162.5°	3634.9	3618.9	3632.4	3651.4	3626.9
165°	3673.0	3656.8	3664.9	3683.9	3664.9
167.5°	3702.9	3686.5	3694.9	3713.9	3689.4
170°	3727.4	3711.0	3716.4	3735.5	3711.0
172.5°	3743.5	3727.4	3732.9	3751.9	3727.4
175°	3757.0	3738.0	3743.5	3762.6	3735.5
177.5°	3762.6	3743.5	3746.4	3765.4	3740.9
180°	3749.0	3749.0	3749.0	3749.0	3749.0

TEST NUMBER: P909133

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.02	8.73	9.12	9.83	11.35	7.57	8.29	8.68	9.39	10.90
	3H	9.66	10.30	10.77	11.41	12.94	9.17	9.81	10.28	10.92	12.45
	4H	10.24	10.85	11.36	11.96	13.49	9.75	10.35	10.87	11.46	13.00
	6H	10.63	11.19	11.76	12.30	13.85	10.13	10.69	11.26	11.80	13.35
	8H	10.73	11.26	11.86	12.39	13.93	10.23	10.76	11.36	11.88	13.43
	12H	10.77	11.27	11.91	12.39	13.96	10.26	10.76	11.40	11.89	13.45
4H	2H	8.46	9.06	9.58	10.17	11.71	8.10	8.71	9.23	9.82	11.36
	3H	10.30	10.81	11.44	11.95	13.50	9.90	10.40	11.03	11.54	13.09
	4H	11.01	11.47	12.15	12.60	14.17	10.58	11.05	11.72	12.17	13.74
	6H	11.51	11.91	12.65	13.06	14.62	11.08	11.48	12.22	12.62	14.19
	8H	11.65	12.03	12.80	13.17	14.74	11.22	11.59	12.36	12.73	14.31
	12H	11.72	12.06	12.88	13.21	14.79	11.27	11.61	12.43	12.76	14.34
8H	4H	11.19	11.56	12.33	12.70	14.28	10.81	11.18	11.95	12.32	13.90
	6H	11.81	12.12	12.97	13.30	14.87	11.42	11.73	12.59	12.91	14.49
	8H	12.02	12.29	13.19	13.45	15.05	11.63	11.90	12.80	13.06	14.65
	12H	12.14	12.38	13.32	13.54	15.17	11.73	11.97	12.91	13.13	14.76
12H	4H	11.17	11.50	12.33	12.65	14.24	10.80	11.14	11.96	12.29	13.87
	6H	11.83	12.10	13.00	13.26	14.86	11.46	11.73	12.63	12.89	14.49
	8H	12.06	12.30	13.24	13.46	15.09	11.68	11.92	12.86	13.08	14.71

END OF REPORT