

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914558

Luminaire Tested: DFN2DIP-SQ3F0-040D120US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914558
REPORT IS A COMBINATION OF REPORTS P900006 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-040D120US927-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11106.3 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 126.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914558

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P914558

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US927-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18
5	64	54	46	40	57	48	42	37	38	33	29	28	25	22	19	17	16
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	14	12	11
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1501	1501	1501
5°	1502	1476	1486
10°	1486	1446	1437
15°	1465	1397	1362
20°	1437	1330	1270
25°	1408	1256	1181
30°	1370	1179	1068
35°	1332	1097	969
40°	1294	1012	856
45°	1250	918	753
50°	1204	823	653
55°	1156	722	557
60°	1100	616	458
65°	1036	509	411
70°	958	409	371
75°	860	358	337
80°	719	297	291
85°	487	194	215

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3024 cd/sqm

TEST NUMBER: P914558

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	1.1
10°-20°	336.9	3.0
20°-30°	473.1	4.3
30°-40°	515.7	4.6
40°-50°	473.9	4.3
50°-60°	372.2	3.4
60°-70°	242.3	2.2
70°-80°	124.7	1.1
80°-90°	40.4	0.4
90°-100°	186.0	1.7
100°-110°	591.1	5.3
110°-120°	1011.6	9.1
120°-130°	1330.4	12.0
130°-140°	1493.3	13.4
140°-150°	1464.3	13.2
150°-160°	1228.4	11.1
160°-170°	814.6	7.3
170°-180°	284.7	2.6
0°-30°	932.7	8.4
0°-40°	1448.4	13.0
0°-60°	2294.6	20.7
0°-90°	2701.9	24.3
90°-120°	1788.7	16.1
90°-150°	6076.6	54.7
90°-180°	8404.0	75.7
0°-180°	11106.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1310	1310	1310	1310	1310	
5°	1310	1304	1288	1299	1296	124
15°	1246	1233	1192	1170	1158	351
25°	1131	1093	1014	966	948	520
35°	974	914	810	735	709	610
45°	796	717	593	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	3	33	89	83	86	11
95°	132	158	162	162	158	147
105°	546	553	558	563	563	576
115°	1015	1030	1025	1022	1015	1004
125°	1476	1499	1492	1484	1481	1319
135°	1910	1938	1943	1940	1933	1476
145°	2318	2337	2351	2354	2344	1449
155°	2651	2658	2667	2679	2671	1220
165°	2884	2881	2881	2900	2887	814
175°	3001	2994	2988	3006	2991	285
180°	3006	3006	3006	3006	3006	

TEST NUMBER: P914558

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.6	1309.6	1309.6	1309.6	1309.6
2.5°	1315.6	1309.6	1296.6	1308.5	1306.1
5°	1309.6	1303.7	1288.2	1298.9	1295.5
7.5°	1298.9	1291.9	1275.3	1279.9	1274.1
10°	1284.8	1276.4	1252.8	1249.1	1242.1
12.5°	1267.0	1256.3	1224.2	1217.2	1204.1
15°	1245.6	1232.6	1192.3	1169.8	1158.0
17.5°	1220.8	1201.7	1151.9	1125.9	1106.9
20°	1192.3	1168.5	1109.3	1079.7	1053.6
22.5°	1161.5	1134.2	1065.4	1025.2	1007.5
25°	1130.7	1092.7	1014.5	966.0	948.1
27.5°	1094.0	1053.6	967.1	911.4	884.1
30°	1054.9	1009.7	914.9	854.5	822.5
32.5°	1016.9	962.3	865.2	794.1	764.4
35°	974.3	913.8	809.5	734.8	708.7
37.5°	932.8	867.5	757.3	675.5	645.9
40°	888.9	817.8	702.8	618.7	587.9
42.5°	843.8	768.0	648.3	560.5	531.0
45°	796.5	717.0	592.6	508.4	480.0
47.5°	751.5	667.3	539.3	455.1	429.0
50°	701.6	617.5	487.1	405.3	380.5
52.5°	653.0	564.1	437.4	359.1	336.6
55°	605.6	513.2	385.2	314.1	291.6
57.5°	557.1	462.2	339.0	272.6	253.7
60°	507.2	412.4	290.3	230.0	211.0
62.5°	458.8	363.9	248.8	192.0	182.6
65°	408.9	312.8	206.2	166.0	162.3
67.5°	361.6	265.5	166.0	145.8	142.2
70°	311.7	219.3	137.4	125.6	120.8
72.5°	264.4	176.6	114.9	105.5	103.1
75°	218.0	135.1	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.8	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	2.7	32.6	88.8	83.4	86.1
92.5°	56.2	76.1	78.8	81.6	81.6
95°	132.3	157.7	162.2	162.2	157.7
97.5°	220.2	243.8	253.8	253.8	253.8
100°	321.8	342.6	349.8	349.8	347.1
102.5°	428.7	444.1	454.1	456.9	454.1
105°	545.7	552.9	558.3	562.8	562.8
107.5°	661.6	672.6	672.6	674.3	661.6
110°	774.0	788.5	788.5	788.5	781.3



TEST NUMBER: P914558

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	895.5	910.9	908.2	900.9	895.5
115°	1015.1	1029.7	1025.1	1022.4	1015.1
117.5°	1133.8	1153.8	1141.1	1133.8	1126.6
120°	1253.5	1273.4	1253.5	1253.5	1245.4
122.5°	1362.3	1387.7	1375.0	1367.7	1362.3
125°	1476.5	1499.1	1491.9	1483.8	1481.0
127.5°	1588.0	1616.0	1606.1	1595.2	1588.0
130°	1692.2	1724.8	1720.3	1714.8	1704.9
132.5°	1809.1	1834.5	1836.3	1823.6	1816.4
135°	1909.7	1937.8	1943.3	1940.5	1933.3
137.5°	2022.1	2044.8	2049.3	2047.5	2036.6
140°	2120.9	2143.6	2156.2	2156.2	2146.3
142.5°	2222.5	2245.1	2252.3	2255.0	2245.1
145°	2318.5	2336.6	2351.1	2353.9	2343.9
147.5°	2404.6	2427.2	2438.2	2442.7	2432.7
150°	2493.5	2508.8	2518.8	2527.0	2518.8
152.5°	2572.3	2587.7	2600.4	2610.4	2600.4
155°	2651.1	2658.4	2666.6	2679.2	2671.1
157.5°	2719.2	2724.5	2729.1	2747.2	2734.5
160°	2779.8	2785.3	2788.0	2803.4	2792.5
162.5°	2836.0	2836.0	2838.8	2856.0	2843.3
165°	2884.1	2881.4	2881.4	2899.5	2886.8
167.5°	2927.6	2919.4	2919.4	2937.6	2924.9
170°	2960.2	2952.9	2950.2	2968.4	2952.9
172.5°	2982.9	2975.6	2972.9	2991.0	2975.6
175°	3001.0	2993.7	2988.3	3006.4	2991.0
177.5°	3011.0	3003.7	2998.2	3013.7	2998.2
180°	3006.4	3006.4	3006.4	3006.4	3006.4

TEST NUMBER: P914558

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US927-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.44	6.10	6.59	7.23	8.83	1.40	2.06	2.55	3.19	4.79
	3H	7.10	7.69	8.26	8.83	10.45	2.57	3.15	3.73	4.30	5.91
	4H	7.70	8.25	8.87	9.40	11.02	3.01	3.56	4.18	4.71	6.33
	6H	8.10	8.62	9.28	9.77	11.39	3.31	3.82	4.49	4.97	6.60
	8H	8.22	8.71	9.40	9.88	11.50	3.39	3.88	4.57	5.05	6.67
	12H	8.28	8.74	9.46	9.90	11.54	3.43	3.89	4.61	5.05	6.69
4H	2H	5.43	5.99	6.61	7.14	8.76	1.97	2.53	3.15	3.68	5.29
	3H	7.24	7.71	8.42	8.88	10.51	3.30	3.76	4.48	4.93	6.56
	4H	7.92	8.35	9.11	9.51	11.16	3.83	4.26	5.02	5.42	7.07
	6H	8.42	8.79	9.61	9.97	11.61	4.24	4.60	5.42	5.78	7.42
	8H	8.59	8.93	9.78	10.11	11.76	4.36	4.70	5.54	5.87	7.53
	12H	8.68	8.99	9.88	10.17	11.83	4.41	4.72	5.61	5.91	7.56
8H	4H	7.88	8.22	9.06	9.39	11.05	4.10	4.44	5.28	5.61	7.27
	6H	8.43	8.71	9.64	9.93	11.58	4.60	4.88	5.81	6.10	7.75
	8H	8.64	8.89	9.85	10.08	11.75	4.79	5.03	6.00	6.22	7.90
	12H	8.77	8.99	9.98	10.18	11.88	4.89	5.11	6.11	6.30	8.00
12H	4H	7.82	8.13	9.02	9.31	10.97	4.09	4.40	5.30	5.59	7.25
	6H	8.40	8.65	9.61	9.84	11.51	4.65	4.89	5.86	6.09	7.76
	8H	8.61	8.83	9.83	10.02	11.72	4.84	5.06	6.06	6.25	7.95

END OF REPORT