

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914565

Luminaire Tested: DFN2DIP-SQ3F0-050D050US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914565
REPORT IS A COMBINATION OF REPORTS P901401 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D050US927-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7842.6 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 79.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914565

CATALOG NUMBER: DFN2DIP-SQ3F0-050D050US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P914565

CATALOG NUMBER: DFN2DIP-SQ3F0-050D050US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1766	1766	1766
5°	1768	1740	1752
10°	1752	1716	1728
15°	1725	1686	1691
20°	1689	1646	1652
25°	1654	1598	1608
30°	1609	1553	1551
35°	1567	1500	1492
40°	1515	1447	1435
45°	1463	1393	1377
50°	1406	1337	1310
55°	1347	1272	1248
60°	1279	1195	1177
65°	1206	1115	1093
70°	1112	1018	1003
75°	982	901	918
80°	826	752	759
85°	581	497	497

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1463 cd/sqm

TEST NUMBER: P914565

CATALOG NUMBER: DFN2DIP-SQ3F0-050D050US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.1	1.8
10°-20°	408.1	5.2
20°-30°	599.8	7.6
30°-40°	696.6	8.9
40°-50°	695.8	8.9
50°-60°	606.7	7.7
60°-70°	448.5	5.7
70°-80°	253.7	3.2
80°-90°	69.3	0.9
90°-100°	44.1	0.6
100°-110°	164.3	2.1
110°-120°	435.8	5.6
120°-130°	722.8	9.2
130°-140°	767.8	9.8
140°-150°	713.6	9.1
150°-160°	573.7	7.3
160°-170°	369.7	4.7
170°-180°	127.2	1.6
0°-30°	1153.0	14.7
0°-40°	1849.6	23.6
0°-60°	3152.1	40.2
0°-90°	3923.6	50.0
90°-120°	644.2	8.2
90°-150°	2848.4	36.3
90°-180°	3919.0	50.0
0°-180°	7842.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1541	1541	1541	1541	1541	
5°	1541	1535	1519	1531	1528	146
15°	1467	1458	1439	1445	1438	413
25°	1328	1316	1291	1294	1291	611
35°	1146	1131	1107	1098	1091	715
45°	932	922	900	883	877	719
55°	706	697	679	661	654	631
65°	476	467	452	439	431	470
75°	249	246	238	230	233	266
85°	61	59	58	53	52	68
90°	1	12	19	24	26	7
95°	63	31	38	43	42	74
105°	294	323	59	70	74	314
115°	556	573	597	149	79	548
125°	786	799	817	824	827	701
135°	973	989	997	1007	1005	752
145°	1129	1128	1144	1151	1146	706
155°	1243	1234	1246	1252	1244	573
165°	1310	1304	1307	1314	1307	370
175°	1340	1333	1335	1342	1332	127
180°	1337	1337	1337	1337	1337	

TEST NUMBER: P914565

CATALOG NUMBER: DFN2DIP-SQ3F0-050D050US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1541.2	1541.2	1541.2	1541.2	1541.2
2.5°	1550.1	1542.8	1526.5	1541.2	1538.4
5°	1541.2	1535.4	1519.0	1530.8	1528.0
7.5°	1530.8	1522.0	1505.7	1517.7	1514.7
10°	1514.7	1504.3	1486.5	1498.3	1493.9
12.5°	1492.3	1483.5	1465.8	1473.1	1470.1
15°	1467.1	1458.3	1439.0	1445.0	1437.6
17.5°	1436.0	1427.2	1407.9	1415.2	1407.9
20°	1401.9	1393.1	1372.4	1376.7	1370.9
22.5°	1367.9	1354.6	1335.2	1335.2	1332.2
25°	1327.9	1316.1	1290.9	1293.7	1290.9
27.5°	1283.3	1273.0	1253.8	1249.3	1242.0
30°	1239.0	1227.1	1204.9	1200.5	1194.5
32.5°	1191.5	1182.7	1159.0	1150.0	1144.1
35°	1145.6	1130.8	1107.1	1098.1	1090.8
37.5°	1093.7	1080.4	1056.6	1046.2	1038.9
40°	1040.5	1028.5	1004.7	991.5	985.6
42.5°	988.6	976.6	953.0	938.0	929.2
45°	932.2	921.9	899.5	883.4	877.3
47.5°	877.3	867.0	843.3	826.9	818.1
50°	819.5	812.1	791.4	770.6	763.2
52.5°	763.2	752.8	733.6	717.3	706.9
55°	705.5	696.6	678.7	661.0	653.6
57.5°	647.6	640.2	620.9	603.2	597.1
60°	589.8	584.0	563.2	546.8	542.5
62.5°	533.5	523.2	508.3	493.5	487.6
65°	475.8	466.8	452.0	438.7	431.3
67.5°	416.5	409.0	395.8	385.4	379.4
70°	361.6	355.7	342.3	331.9	326.1
72.5°	305.4	299.4	292.0	281.6	277.2
75°	248.9	246.1	238.5	229.7	232.7
77.5°	198.6	192.6	189.6	185.2	180.9
80°	148.3	146.7	143.7	139.3	136.3
82.5°	100.8	100.8	99.3	93.4	93.4
85°	60.7	59.3	57.8	53.3	51.9
87.5°	26.7	23.8	20.8	16.3	14.8
90°	1.0	11.6	19.3	24.2	26.1
92.5°	24.2	20.4	23.2	25.2	26.1
95°	62.8	30.9	37.7	42.6	41.6
97.5°	113.1	33.9	49.3	52.3	53.2
100°	171.3	38.7	55.1	62.8	64.8
102.5°	235.0	233.1	57.1	67.7	70.7
105°	294.1	323.1	59.0	69.6	73.5
107.5°	362.7	386.8	61.0	71.5	75.5
110°	428.6	448.8	169.3	72.6	76.4

TEST NUMBER: P914565

CATALOG NUMBER: DFN2DIP-SQ3F0-050D050US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.4	507.8	491.4	74.5	77.4
115°	556.2	572.6	596.8	149.0	79.4
117.5°	613.2	632.6	649.1	510.6	257.3
120°	677.1	691.6	709.0	720.6	590.0
122.5°	731.2	746.7	766.1	771.9	772.9
125°	786.3	799.0	817.4	824.1	827.0
127.5°	836.6	850.2	864.8	874.4	875.4
130°	884.1	899.6	910.1	920.8	920.0
132.5°	932.5	945.1	955.6	964.4	963.5
135°	973.1	988.6	997.2	1007.0	1005.0
137.5°	1015.6	1027.2	1037.0	1046.6	1043.8
140°	1057.2	1065.0	1075.5	1084.3	1079.5
142.5°	1092.1	1098.9	1111.4	1119.1	1114.3
145°	1128.9	1127.8	1144.2	1151.0	1146.2
147.5°	1160.7	1157.8	1174.3	1179.1	1175.3
150°	1191.7	1184.9	1200.4	1206.2	1201.3
152.5°	1217.7	1210.1	1224.6	1230.4	1223.6
155°	1242.9	1234.3	1245.9	1251.6	1244.0
157.5°	1263.2	1255.5	1264.2	1271.1	1263.2
160°	1280.7	1274.9	1280.7	1286.4	1279.7
162.5°	1296.1	1290.4	1295.1	1301.9	1293.2
165°	1309.6	1303.9	1306.8	1313.5	1306.8
167.5°	1320.3	1314.5	1317.5	1324.2	1315.5
170°	1329.0	1323.2	1325.2	1331.9	1323.2
172.5°	1334.8	1329.0	1331.0	1337.8	1329.0
175°	1339.7	1332.8	1334.8	1341.6	1331.9
177.5°	1341.6	1334.8	1335.9	1342.6	1333.9
180°	1336.7	1336.7	1336.7	1336.7	1336.7

TEST NUMBER: P914565

CATALOG NUMBER: DFN2DIP-SQ3F0-050D050US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.22	10.08	10.17	11.05	12.32	8.77	9.63	9.73	10.61	11.88
	3H	10.87	11.64	11.84	12.63	13.92	10.38	11.16	11.35	12.14	13.43
	4H	11.46	12.19	12.44	13.17	14.48	10.96	11.69	11.94	12.68	13.98
	6H	11.85	12.53	12.85	13.52	14.83	11.35	12.03	12.35	13.02	14.33
	8H	11.96	12.60	12.96	13.61	14.92	11.45	12.10	12.45	13.10	14.41
	12H	12.00	12.61	13.01	13.61	14.95	11.49	12.10	12.50	13.11	14.44
4H	2H	9.67	10.40	10.66	11.39	12.69	9.32	10.05	10.31	11.04	12.34
	3H	11.53	12.14	12.53	13.16	14.47	11.13	11.74	12.12	12.75	14.07
	4H	12.24	12.80	13.25	13.81	15.15	11.82	12.38	12.83	13.39	14.73
	6H	12.76	13.24	13.77	14.27	15.60	12.32	12.80	13.34	13.84	15.17
	8H	12.90	13.35	13.92	14.38	15.73	12.47	12.91	13.48	13.94	15.29
	12H	12.97	13.38	14.01	14.42	15.78	12.52	12.93	13.56	13.97	15.33
8H	4H	12.44	12.89	13.46	13.91	15.26	12.06	12.51	13.08	13.53	14.88
	6H	13.06	13.43	14.10	14.50	15.85	12.68	13.05	13.72	14.12	15.46
	8H	13.28	13.61	14.33	14.66	16.03	12.89	13.21	13.94	14.27	15.63
	12H	13.41	13.70	14.46	14.74	16.15	13.00	13.29	14.05	14.33	15.74
12H	4H	12.42	12.83	13.46	13.87	15.22	12.05	12.46	13.09	13.50	14.85
	6H	13.09	13.42	14.14	14.47	15.84	12.72	13.05	13.77	14.10	15.46
	8H	13.33	13.62	14.38	14.66	16.07	12.95	13.24	14.00	14.28	15.69