

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914594

Luminaire Tested: DFN2DIP-SQ3F0-050D120US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914594
REPORT IS A COMBINATION OF REPORTS P900008 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D120US927-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11779.7 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 136.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914594

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLFL

Luminous Intensity Polar Plot



TEST NUMBER: P914594

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37			29
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31			25
2	85	78	72	68	76	70	65	61	55	52	49	42	40	38	29	28	27			21
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23			18
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	22	20			16
5	65	54	47	41	58	49	42	38	39	34	31	30	27	24	21	19	18			14
6	60	49	41	36	54	44	37	33	35	30	27	27	24	21	19	17	16			12
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14			11
8	52	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	13			10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11			9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10			8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1876	1876	1876
5°	1877	1845	1857
10°	1858	1807	1796
15°	1831	1746	1702
20°	1796	1663	1587
25°	1760	1569	1476
30°	1712	1474	1335
35°	1665	1371	1211
40°	1618	1265	1070
45°	1562	1147	941
50°	1505	1029	816
55°	1445	902	696
60°	1375	770	572
65°	1295	636	514
70°	1198	511	465
75°	1076	448	421
80°	899	372	363
85°	610	242	269

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3024 cd/sqm

TEST NUMBER: P914594

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	1.3
10°-20°	421.2	3.6
20°-30°	591.3	5.0
30°-40°	644.6	5.5
40°-50°	592.4	5.0
50°-60°	465.3	3.9
60°-70°	302.9	2.6
70°-80°	155.9	1.3
80°-90°	48.3	0.4
90°-100°	186.0	1.6
100°-110°	591.1	5.0
110°-120°	1011.6	8.6
120°-130°	1330.4	11.3
130°-140°	1493.3	12.7
140°-150°	1464.3	12.4
150°-160°	1228.4	10.4
160°-170°	814.6	6.9
170°-180°	284.7	2.4
0°-30°	1165.9	9.9
0°-40°	1810.5	15.4
0°-60°	2868.2	24.3
0°-90°	3375.3	28.7
90°-120°	1788.7	15.2
90°-150°	6076.6	51.6
90°-180°	8404.0	71.3
0°-180°	11779.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1637	1630	1610	1624	1619	155
15°	1557	1541	1490	1462	1448	439
25°	1413	1366	1268	1207	1185	650
35°	1218	1142	1012	918	886	762
45°	996	896	741	636	600	769
55°	757	641	481	393	364	676
65°	511	391	258	208	203	507
75°	273	169	118	108	107	288
85°	64	33	28	28	28	73
90°	3	33	89	83	86	12
95°	132	158	162	162	158	147
105°	546	553	558	563	563	576
115°	1015	1030	1025	1022	1015	1004
125°	1476	1499	1492	1484	1481	1319
135°	1910	1938	1943	1940	1933	1476
145°	2318	2337	2351	2354	2344	1449
155°	2651	2658	2667	2679	2671	1220
165°	2884	2881	2881	2900	2887	814
175°	3001	2994	2988	3006	2991	285
180°	3006	3006	3006	3006	3006	

TEST NUMBER: P914594

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1637.0	1637.0	1637.0	1637.0	1637.0
2.5°	1644.4	1637.0	1620.7	1635.6	1632.6
5°	1637.0	1629.7	1610.3	1623.7	1619.3
7.5°	1623.7	1614.9	1594.1	1600.0	1592.5
10°	1605.9	1595.5	1566.0	1561.5	1552.6
12.5°	1583.7	1570.4	1530.3	1521.5	1505.1
15°	1557.0	1540.7	1490.4	1462.3	1447.5
17.5°	1525.9	1502.2	1439.9	1407.4	1383.6
20°	1490.4	1460.7	1386.6	1349.7	1317.0
22.5°	1451.9	1417.8	1331.8	1281.5	1259.3
25°	1413.3	1365.9	1268.1	1207.4	1185.1
27.5°	1367.5	1317.0	1208.9	1139.2	1105.2
30°	1318.6	1262.2	1143.7	1068.2	1028.1
32.5°	1271.1	1202.9	1081.6	992.6	955.5
35°	1217.8	1142.2	1011.9	918.5	885.9
37.5°	1165.9	1084.4	946.7	844.4	807.5
40°	1111.1	1022.3	878.4	773.3	734.8
42.5°	1054.9	960.0	810.4	700.7	663.8
45°	995.6	896.3	740.8	635.5	599.9
47.5°	939.3	834.2	674.1	568.9	536.3
50°	877.1	771.9	608.9	506.6	475.6
52.5°	816.3	705.1	546.7	448.9	420.8
55°	757.0	641.4	481.4	392.6	364.5
57.5°	696.3	577.8	423.7	340.8	317.0
60°	634.1	515.6	362.9	287.5	263.7
62.5°	573.4	454.9	311.1	240.0	228.2
65°	511.1	391.1	257.8	207.5	203.0
67.5°	451.9	331.8	207.5	182.2	177.8
70°	389.7	274.1	171.8	157.0	151.1
72.5°	330.4	220.7	143.7	131.9	128.9
75°	272.6	168.8	118.5	108.1	106.7
77.5°	214.8	119.9	93.4	87.4	84.4
80°	161.4	86.0	71.1	65.2	65.2
82.5°	112.6	57.8	48.9	45.9	45.9
85°	63.7	32.6	28.1	28.1	28.1
87.5°	23.8	11.8	11.8	10.4	10.4
90°	2.7	32.6	88.8	83.4	86.1
92.5°	56.2	76.1	78.8	81.6	81.6
95°	132.3	157.7	162.2	162.2	157.7
97.5°	220.2	243.8	253.8	253.8	253.8
100°	321.8	342.6	349.8	349.8	347.1
102.5°	428.7	444.1	454.1	456.9	454.1
105°	545.7	552.9	558.3	562.8	562.8
107.5°	661.6	672.6	672.6	674.3	661.6
110°	774.0	788.5	788.5	788.5	781.3

TEST NUMBER: P914594

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	895.5	910.9	908.2	900.9	895.5
115°	1015.1	1029.7	1025.1	1022.4	1015.1
117.5°	1133.8	1153.8	1141.1	1133.8	1126.6
120°	1253.5	1273.4	1253.5	1253.5	1245.4
122.5°	1362.3	1387.7	1375.0	1367.7	1362.3
125°	1476.5	1499.1	1491.9	1483.8	1481.0
127.5°	1588.0	1616.0	1606.1	1595.2	1588.0
130°	1692.2	1724.8	1720.3	1714.8	1704.9
132.5°	1809.1	1834.5	1836.3	1823.6	1816.4
135°	1909.7	1937.8	1943.3	1940.5	1933.3
137.5°	2022.1	2044.8	2049.3	2047.5	2036.6
140°	2120.9	2143.6	2156.2	2156.2	2146.3
142.5°	2222.5	2245.1	2252.3	2255.0	2245.1
145°	2318.5	2336.6	2351.1	2353.9	2343.9
147.5°	2404.6	2427.2	2438.2	2442.7	2432.7
150°	2493.5	2508.8	2518.8	2527.0	2518.8
152.5°	2572.3	2587.7	2600.4	2610.4	2600.4
155°	2651.1	2658.4	2666.6	2679.2	2671.1
157.5°	2719.2	2724.5	2729.1	2747.2	2734.5
160°	2779.8	2785.3	2788.0	2803.4	2792.5
162.5°	2836.0	2836.0	2838.8	2856.0	2843.3
165°	2884.1	2881.4	2881.4	2899.5	2886.8
167.5°	2927.6	2919.4	2919.4	2937.6	2924.9
170°	2960.2	2952.9	2950.2	2968.4	2952.9
172.5°	2982.9	2975.6	2972.9	2991.0	2975.6
175°	3001.0	2993.7	2988.3	3006.4	2991.0
177.5°	3011.0	3003.7	2998.2	3013.7	2998.2
180°	3006.4	3006.4	3006.4	3006.4	3006.4

TEST NUMBER: P914594

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.87	7.56	8.00	8.67	10.22	2.84	3.52	3.96	4.63	6.18
	3H	8.54	9.15	9.67	10.27	11.83	4.01	4.62	5.14	5.74	7.30
	4H	9.13	9.71	10.28	10.84	12.41	4.44	5.02	5.59	6.15	7.72
	6H	9.54	10.08	10.70	11.20	12.78	4.75	5.28	5.90	6.41	7.99
	8H	9.66	10.17	10.82	11.31	12.89	4.84	5.34	5.99	6.48	8.06
	12H	9.72	10.20	10.88	11.34	12.93	4.87	5.35	6.03	6.49	8.08
4H	2H	6.87	7.45	8.02	8.58	10.15	3.41	3.99	4.56	5.11	6.68
	3H	8.68	9.16	9.84	10.31	11.90	4.74	5.22	5.89	6.37	7.95
	4H	9.37	9.81	10.52	10.95	12.55	5.28	5.72	6.43	6.86	8.46
	6H	9.87	10.25	11.03	11.41	13.00	5.68	6.06	6.84	7.22	8.81
	8H	10.04	10.39	11.20	11.54	13.15	5.80	6.16	6.96	7.31	8.92
	12H	10.12	10.44	11.30	11.61	13.22	5.86	6.18	7.03	7.34	8.95
8H	4H	9.32	9.67	10.48	10.83	12.44	5.54	5.90	6.70	7.05	8.66
	6H	9.88	10.17	11.06	11.36	12.97	6.05	6.34	7.23	7.53	9.14
	8H	10.09	10.34	11.28	11.52	13.14	6.23	6.49	7.42	7.66	9.28
	12H	10.22	10.44	11.41	11.61	13.27	6.34	6.56	7.53	7.73	9.39
12H	4H	9.27	9.59	10.44	10.75	12.36	5.54	5.86	6.72	7.02	8.64
	6H	9.85	10.10	11.04	11.28	12.90	6.09	6.35	7.28	7.52	9.15
	8H	10.06	10.28	11.25	11.45	13.11	6.29	6.52	7.48	7.69	9.34