

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914595

Luminaire Tested: DFN2DIP-SQ3F0-050D120US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914595
REPORT IS A COMBINATION OF REPORTS P901528 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D120US927-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12777.9 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 136.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914595

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P914595

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34	26		
1	93	89	85	82	83	79	76	74	62	60	58	46	44	43	31	30	29	23		
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19		
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	24	23	22	17		
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15		
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13		
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15	11		
7	55	44	36	31	49	39	33	28	31	27	23	24	20	18	17	15	13	10		
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12	9		
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11	8		
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1876	1876	1876
5°	1877	1845	1857
10°	1858	1807	1796
15°	1831	1746	1702
20°	1796	1663	1587
25°	1760	1569	1476
30°	1712	1474	1335
35°	1665	1371	1211
40°	1618	1265	1070
45°	1562	1147	941
50°	1505	1029	816
55°	1445	902	696
60°	1375	770	572
65°	1295	636	514
70°	1198	511	465
75°	1076	448	421
80°	899	372	363
85°	610	242	269

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2198 cd/sqm

TEST NUMBER: P914595

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	1.2
10°-20°	421.2	3.3
20°-30°	591.3	4.6
30°-40°	644.6	5.0
40°-50°	592.4	4.6
50°-60°	465.3	3.6
60°-70°	302.9	2.4
70°-80°	155.9	1.2
80°-90°	45.4	0.4
90°-100°	105.8	0.8
100°-110°	394.4	3.1
110°-120°	1045.9	8.2
120°-130°	1734.7	13.6
130°-140°	1842.7	14.4
140°-150°	1712.6	13.4
150°-160°	1376.9	10.8
160°-170°	887.2	6.9
170°-180°	305.4	2.4
0°-30°	1165.9	9.1
0°-40°	1810.5	14.2
0°-60°	2868.2	22.4
0°-90°	3372.4	26.4
90°-120°	1546.1	12.1
90°-150°	6836.0	53.5
90°-180°	9405.0	73.6
0°-180°	12777.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1637	1630	1610	1624	1619	155
15°	1557	1541	1490	1462	1448	439
25°	1413	1366	1268	1207	1185	650
35°	1218	1142	1012	918	886	762
45°	996	896	741	636	600	769
55°	757	641	481	393	364	676
65°	511	391	258	208	203	507
75°	273	169	118	108	107	288
85°	64	33	28	28	28	73
90°	2	28	46	58	63	12
95°	151	74	90	102	100	179
105°	706	776	142	167	176	754
115°	1335	1374	1432	358	190	1314
125°	1887	1918	1962	1978	1985	1683
135°	2335	2373	2393	2417	2412	1804
145°	2709	2707	2746	2762	2751	1694
155°	2983	2962	2990	3004	2986	1375
165°	3143	3129	3136	3153	3136	888
175°	3215	3199	3204	3220	3197	306
180°	3208	3208	3208	3208	3208	

TEST NUMBER: P914595

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1637.0	1637.0	1637.0	1637.0	1637.0
2.5°	1644.4	1637.0	1620.7	1635.6	1632.6
5°	1637.0	1629.7	1610.3	1623.7	1619.3
7.5°	1623.7	1614.9	1594.1	1600.0	1592.5
10°	1605.9	1595.5	1566.0	1561.5	1552.6
12.5°	1583.7	1570.4	1530.3	1521.5	1505.1
15°	1557.0	1540.7	1490.4	1462.3	1447.5
17.5°	1525.9	1502.2	1439.9	1407.4	1383.6
20°	1490.4	1460.7	1386.6	1349.7	1317.0
22.5°	1451.9	1417.8	1331.8	1281.5	1259.3
25°	1413.3	1365.9	1268.1	1207.4	1185.1
27.5°	1367.5	1317.0	1208.9	1139.2	1105.2
30°	1318.6	1262.2	1143.7	1068.2	1028.1
32.5°	1271.1	1202.9	1081.6	992.6	955.5
35°	1217.8	1142.2	1011.9	918.5	885.9
37.5°	1165.9	1084.4	946.7	844.4	807.5
40°	1111.1	1022.3	878.4	773.3	734.8
42.5°	1054.9	960.0	810.4	700.7	663.8
45°	995.6	896.3	740.8	635.5	599.9
47.5°	939.3	834.2	674.1	568.9	536.3
50°	877.1	771.9	608.9	506.6	475.6
52.5°	816.3	705.1	546.7	448.9	420.8
55°	757.0	641.4	481.4	392.6	364.5
57.5°	696.3	577.8	423.7	340.8	317.0
60°	634.1	515.6	362.9	287.5	263.7
62.5°	573.4	454.9	311.1	240.0	228.2
65°	511.1	391.1	257.8	207.5	203.0
67.5°	451.9	331.8	207.5	182.2	177.8
70°	389.7	274.1	171.8	157.0	151.1
72.5°	330.4	220.7	143.7	131.9	128.9
75°	272.6	168.8	118.5	108.1	106.7
77.5°	214.8	119.9	93.4	87.4	84.4
80°	161.4	86.0	71.1	65.2	65.2
82.5°	112.6	57.8	48.9	45.9	45.9
85°	63.7	32.6	28.1	28.1	28.1
87.5°	23.8	11.8	11.8	10.4	10.4
90°	2.2	27.8	46.3	58.1	62.6
92.5°	58.1	48.8	55.7	60.4	62.6
95°	150.8	74.1	90.4	102.3	99.8
97.5°	271.6	81.4	118.3	125.4	127.6
100°	411.0	92.9	132.3	150.8	155.5
102.5°	564.0	559.6	137.0	162.4	169.5
105°	705.7	775.5	141.7	167.1	176.4
107.5°	870.5	928.4	146.4	171.7	181.1
110°	1028.5	1077.0	406.3	174.2	183.3

TEST NUMBER: P914595

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1177.1	1218.7	1179.3	178.6	185.8
115°	1334.7	1374.2	1432.3	357.5	190.5
117.5°	1471.8	1518.1	1557.8	1225.6	617.5
120°	1625.1	1659.8	1701.7	1729.6	1416.1
122.5°	1754.9	1792.2	1838.7	1852.5	1855.0
125°	1887.2	1917.6	1961.7	1977.9	1984.8
127.5°	2007.9	2040.5	2075.5	2098.6	2100.9
130°	2121.8	2159.0	2184.4	2210.0	2207.8
132.5°	2237.8	2268.2	2293.5	2314.5	2312.3
135°	2335.4	2372.7	2393.3	2416.8	2412.1
137.5°	2437.5	2465.3	2488.7	2511.8	2505.0
140°	2537.3	2556.0	2581.3	2602.3	2590.7
142.5°	2621.0	2637.3	2667.4	2685.8	2674.2
145°	2709.3	2706.8	2746.2	2762.5	2750.8
147.5°	2785.6	2778.7	2818.2	2829.8	2820.6
150°	2860.0	2843.8	2881.0	2894.8	2883.2
152.5°	2922.6	2904.1	2938.9	2952.9	2936.7
155°	2983.0	2962.3	2990.2	3004.0	2985.5
157.5°	3031.8	3013.3	3034.3	3050.5	3031.8
160°	3073.7	3059.6	3073.7	3087.4	3071.2
162.5°	3110.7	3096.9	3108.4	3124.7	3103.8
165°	3143.1	3129.4	3136.2	3152.6	3136.2
167.5°	3168.8	3154.7	3161.9	3178.2	3157.2
170°	3189.7	3175.7	3180.4	3196.6	3175.7
172.5°	3203.5	3189.7	3194.5	3210.7	3189.7
175°	3215.1	3198.8	3203.5	3219.8	3196.6
177.5°	3219.8	3203.5	3206.0	3222.3	3201.4
180°	3208.3	3208.3	3208.3	3208.3	3208.3

TEST NUMBER: P914595

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.54	7.21	7.69	8.34	9.92	2.51	3.17	3.65	4.30	5.88
	3H	8.21	8.80	9.35	9.94	11.53	3.68	4.27	4.82	5.41	7.00
	4H	8.80	9.37	9.96	10.51	12.10	4.11	4.68	5.27	5.82	7.41
	6H	9.21	9.73	10.38	10.87	12.48	4.42	4.94	5.59	6.08	7.69
	8H	9.33	9.83	10.50	10.98	12.58	4.50	5.00	5.67	6.15	7.75
	12H	9.39	9.86	10.56	11.00	12.63	4.54	5.01	5.71	6.16	7.78
4H	2H	6.54	7.11	7.71	8.24	9.84	3.08	3.65	4.24	4.78	6.38
	3H	8.35	8.82	9.52	9.98	11.59	4.41	4.88	5.58	6.04	7.65
	4H	9.03	9.47	10.20	10.62	12.24	4.94	5.38	6.11	6.53	8.15
	6H	9.53	9.91	10.71	11.08	12.69	5.35	5.72	6.52	6.89	8.51
	8H	9.70	10.05	10.88	11.21	12.85	5.47	5.81	6.64	6.98	8.61
	12H	9.79	10.10	10.98	11.28	12.92	5.52	5.84	6.71	7.01	8.65
8H	4H	8.99	9.33	10.16	10.50	12.13	5.21	5.55	6.38	6.72	8.35
	6H	9.54	9.83	10.74	11.03	12.66	5.71	6.00	6.91	7.20	8.83
	8H	9.75	10.00	10.95	11.19	12.84	5.90	6.15	7.10	7.33	8.98
	12H	9.88	10.10	11.09	11.28	12.96	6.00	6.22	7.21	7.40	9.09
12H	4H	8.93	9.24	10.12	10.42	12.06	5.20	5.52	6.40	6.69	8.33
	6H	9.52	9.76	10.72	10.95	12.60	5.76	6.01	6.96	7.19	8.84
	8H	9.72	9.94	10.93	11.13	12.81	5.96	6.18	7.16	7.36	9.04

END OF REPORT