

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914630

Luminaire Tested: DFN2DIP-SQ3F0-060D120US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914630
REPORT IS A COMBINATION OF REPORTS P900010 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-060D120US927-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12453.0 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 147.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914630

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P914630

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2251	2251	2251
5°	2253	2214	2229
10°	2229	2169	2155
15°	2197	2096	2042
20°	2155	1995	1904
25°	2112	1883	1771
30°	2055	1769	1602
35°	1998	1645	1454
40°	1941	1518	1284
45°	1875	1377	1130
50°	1806	1235	979
55°	1734	1083	835
60°	1650	924	686
65°	1554	763	617
70°	1437	613	557
75°	1291	537	506
80°	1079	446	436
85°	732	290	323

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3024 cd/sqm

TEST NUMBER: P914630

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	1.5
10°-20°	505.4	4.1
20°-30°	709.6	5.7
30°-40°	773.5	6.2
40°-50°	710.9	5.7
50°-60°	558.3	4.5
60°-70°	363.4	2.9
70°-80°	187.1	1.5
80°-90°	56.3	0.5
90°-100°	186.0	1.5
100°-110°	591.1	4.7
110°-120°	1011.6	8.1
120°-130°	1330.4	10.7
130°-140°	1493.3	12.0
140°-150°	1464.3	11.8
150°-160°	1228.4	9.9
160°-170°	814.6	6.5
170°-180°	284.7	2.3
0°-30°	1399.1	11.2
0°-40°	2172.6	17.4
0°-60°	3441.9	27.6
0°-90°	4048.7	32.5
90°-120°	1788.7	14.4
90°-150°	6076.6	48.8
90°-180°	8404.0	67.5
0°-180°	12453.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1964	1956	1932	1948	1943	186
15°	1868	1849	1788	1755	1737	527
25°	1696	1639	1522	1449	1422	780
35°	1461	1371	1214	1102	1063	915
45°	1195	1076	889	763	720	923
55°	908	770	578	471	437	812
65°	613	469	309	249	244	608
75°	327	203	142	130	128	346
85°	76	39	34	34	34	88
90°	3	33	89	83	86	12
95°	132	158	162	162	158	147
105°	546	553	558	563	563	576
115°	1015	1030	1025	1022	1015	1004
125°	1476	1499	1492	1484	1481	1319
135°	1910	1938	1943	1940	1933	1476
145°	2318	2337	2351	2354	2344	1449
155°	2651	2658	2667	2679	2671	1220
165°	2884	2881	2881	2900	2887	814
175°	3001	2994	2988	3006	2991	285
180°	3006	3006	3006	3006	3006	

TEST NUMBER: P914630

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.5	1964.5	1964.5	1964.5	1964.5
2.5°	1973.3	1964.5	1944.8	1962.7	1959.1
5°	1964.5	1955.6	1932.4	1948.4	1943.1
7.5°	1948.4	1937.8	1913.0	1919.9	1911.1
10°	1927.1	1914.6	1879.2	1873.7	1863.1
12.5°	1900.5	1884.4	1836.4	1825.8	1806.2
15°	1868.4	1848.8	1788.4	1754.7	1736.9
17.5°	1831.1	1802.6	1727.9	1688.9	1660.4
20°	1788.4	1752.8	1664.0	1619.6	1580.4
22.5°	1742.2	1701.3	1598.1	1537.8	1511.2
25°	1696.1	1639.1	1521.8	1449.0	1422.2
27.5°	1641.0	1580.4	1450.6	1367.1	1326.2
30°	1582.3	1514.6	1372.4	1281.8	1233.7
32.5°	1525.3	1443.5	1297.9	1191.1	1146.6
35°	1461.4	1370.7	1214.3	1102.2	1063.0
37.5°	1399.2	1301.2	1136.1	1013.3	968.9
40°	1333.3	1226.8	1054.2	928.0	881.8
42.5°	1265.8	1152.1	972.5	840.8	796.5
45°	1194.7	1075.5	889.0	762.6	719.9
47.5°	1127.2	1001.0	809.0	682.6	643.6
50°	1052.5	926.3	730.7	607.9	570.8
52.5°	979.5	846.1	656.0	538.7	504.9
55°	908.4	769.8	577.7	471.2	437.4
57.5°	835.6	693.3	508.5	408.9	380.4
60°	760.9	618.7	435.5	345.0	316.5
62.5°	688.1	545.9	373.3	288.0	273.9
65°	613.4	469.3	309.3	249.0	243.5
67.5°	542.2	398.2	249.0	218.6	213.3
70°	467.5	328.9	206.1	188.5	181.3
72.5°	396.5	264.8	172.4	158.3	154.6
75°	327.1	202.6	142.2	129.8	128.1
77.5°	257.9	143.9	112.0	104.9	101.3
80°	193.7	103.1	85.2	78.3	78.3
82.5°	135.1	69.4	58.6	55.1	55.1
85°	76.4	39.1	33.7	33.7	33.7
87.5°	28.5	14.2	14.2	12.4	12.4
90°	2.7	32.6	88.8	83.4	86.1
92.5°	56.2	76.1	78.8	81.6	81.6
95°	132.3	157.7	162.2	162.2	157.7
97.5°	220.2	243.8	253.8	253.8	253.8
100°	321.8	342.6	349.8	349.8	347.1
102.5°	428.7	444.1	454.1	456.9	454.1
105°	545.7	552.9	558.3	562.8	562.8
107.5°	661.6	672.6	672.6	674.3	661.6
110°	774.0	788.5	788.5	788.5	781.3

TEST NUMBER: P914630

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	895.5	910.9	908.2	900.9	895.5
115°	1015.1	1029.7	1025.1	1022.4	1015.1
117.5°	1133.8	1153.8	1141.1	1133.8	1126.6
120°	1253.5	1273.4	1253.5	1253.5	1245.4
122.5°	1362.3	1387.7	1375.0	1367.7	1362.3
125°	1476.5	1499.1	1491.9	1483.8	1481.0
127.5°	1588.0	1616.0	1606.1	1595.2	1588.0
130°	1692.2	1724.8	1720.3	1714.8	1704.9
132.5°	1809.1	1834.5	1836.3	1823.6	1816.4
135°	1909.7	1937.8	1943.3	1940.5	1933.3
137.5°	2022.1	2044.8	2049.3	2047.5	2036.6
140°	2120.9	2143.6	2156.2	2156.2	2146.3
142.5°	2222.5	2245.1	2252.3	2255.0	2245.1
145°	2318.5	2336.6	2351.1	2353.9	2343.9
147.5°	2404.6	2427.2	2438.2	2442.7	2432.7
150°	2493.5	2508.8	2518.8	2527.0	2518.8
152.5°	2572.3	2587.7	2600.4	2610.4	2600.4
155°	2651.1	2658.4	2666.6	2679.2	2671.1
157.5°	2719.2	2724.5	2729.1	2747.2	2734.5
160°	2779.8	2785.3	2788.0	2803.4	2792.5
162.5°	2836.0	2836.0	2838.8	2856.0	2843.3
165°	2884.1	2881.4	2881.4	2899.5	2886.8
167.5°	2927.6	2919.4	2919.4	2937.6	2924.9
170°	2960.2	2952.9	2950.2	2968.4	2952.9
172.5°	2982.9	2975.6	2972.9	2991.0	2975.6
175°	3001.0	2993.7	2988.3	3006.4	2991.0
177.5°	3011.0	3003.7	2998.2	3013.7	2998.2
180°	3006.4	3006.4	3006.4	3006.4	3006.4

TEST NUMBER: P914630

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.03	8.74	9.13	9.83	11.33	3.99	4.70	5.09	5.79	7.29
	3H	9.69	10.32	10.80	11.43	12.95	5.16	5.79	6.27	6.90	8.42
	4H	10.29	10.89	11.41	11.99	13.52	5.60	6.20	6.72	7.30	8.83
	6H	10.70	11.26	11.83	12.36	13.90	5.91	6.46	7.04	7.57	9.11
	8H	10.83	11.35	11.96	12.47	14.00	6.00	6.52	7.13	7.64	9.17
	12H	10.88	11.38	12.02	12.49	14.05	6.03	6.53	7.17	7.64	9.20
4H	2H	8.03	8.63	9.16	9.73	11.26	4.57	5.17	5.69	6.27	7.79
	3H	9.84	10.34	10.97	11.47	13.01	5.90	6.40	7.03	7.53	9.06
	4H	10.53	10.98	11.66	12.10	13.66	6.44	6.90	7.57	8.01	9.57
	6H	11.03	11.42	12.17	12.56	14.11	6.84	7.23	7.98	8.38	9.93
	8H	11.20	11.57	12.34	12.70	14.26	6.97	7.33	8.11	8.46	10.03
	12H	11.29	11.62	12.44	12.76	14.33	7.02	7.35	8.18	8.50	10.07
8H	4H	10.48	10.85	11.62	11.98	13.55	6.71	7.07	7.85	8.20	9.77
	6H	11.04	11.34	12.20	12.52	14.08	7.21	7.51	8.37	8.69	10.25
	8H	11.25	11.52	12.42	12.67	14.25	7.40	7.66	8.56	8.81	10.40
	12H	11.38	11.61	12.55	12.77	14.38	7.50	7.74	8.67	8.89	10.50
12H	4H	10.43	10.76	11.59	11.91	13.48	6.70	7.03	7.86	8.18	9.75
	6H	11.01	11.28	12.18	12.43	14.01	7.26	7.52	8.42	8.68	10.26
	8H	11.23	11.46	12.40	12.61	14.23	7.46	7.69	8.63	8.84	10.46

END OF REPORT