

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909246

Luminaire Tested: DFN2DIP-SQ3F0-080D120US840-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P909246  
REPORT IS A COMBINATION OF REPORTS P900014 AND P896733  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-080D120US840-RLLFLL  
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 17591.9 lumens  
Efficiency: N/A  
Efficacy: 103.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 170.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9952  
Total Harmonic Distortion (THDi): 0.069  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P909246  
CATALOG NUMBER: DFN2DIP-SQ3F0-080D120US840-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P909246

CATALOG NUMBER: DFN2DIP-SQ3F0-080D120US840-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19			
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15			
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3826	3826	3826
5°	3830	3763	3788
10°	3789	3686	3663
15°	3735	3562	3472
20°	3663	3392	3237
25°	3590	3201	3010
30°	3493	3006	2723
35°	3397	2797	2471
40°	3299	2580	2182
45°	3186	2340	1920
50°	3069	2099	1665
55°	2947	1840	1419
60°	2805	1571	1167
65°	2642	1297	1049
70°	2444	1042	947
75°	2194	913	859
80°	1833	758	741
85°	1244	494	550

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 3856 cd/sqm



TEST NUMBER: P909246

CATALOG NUMBER: DFN2DIP-SQ3F0-080D120US840-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	312.9	1.8
10°-20°	859.1	4.9
20°-30°	1206.1	6.9
30°-40°	1314.7	7.5
40°-50°	1208.4	6.9
50°-60°	949.0	5.4
60°-70°	617.7	3.5
70°-80°	318.0	1.8
80°-90°	92.1	0.5
90°-100°	237.2	1.3
100°-110°	753.5	4.3
110°-120°	1289.5	7.3
120°-130°	1696.0	9.6
130°-140°	1903.6	10.8
140°-150°	1866.7	10.6
150°-160°	1565.9	8.9
160°-170°	1038.5	5.9
170°-180°	363.0	2.1
0°-30°	2378.1	13.5
0°-40°	3692.9	21.0
0°-60°	5850.2	33.3
0°-90°	6878.0	39.1
90°-120°	2280.2	13.0
90°-150°	7746.5	44.0
90°-180°	10714.0	60.9
0°-180°	17591.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3339	3339	3339	3339	3339	
5°	3339	3324	3284	3312	3303	317
15°	3176	3142	3040	2982	2952	895
25°	2883	2786	2587	2463	2417	1326
35°	2484	2330	2064	1874	1807	1555
45°	2031	1828	1511	1296	1224	1568
55°	1544	1308	982	801	744	1380
65°	1043	798	526	423	414	1034
75°	556	344	242	221	218	588
85°	130	66	57	57	57	149
90°	3	42	113	106	110	17
95°	169	201	207	207	201	188
105°	696	705	712	718	718	734
115°	1294	1313	1307	1303	1294	1280
125°	1882	1911	1902	1892	1888	1682
135°	2434	2470	2477	2474	2465	1882
145°	2956	2979	2997	3001	2988	1847
155°	3380	3389	3399	3416	3405	1556
165°	3677	3673	3673	3696	3680	1037
175°	3826	3816	3810	3832	3813	363
180°	3832	3832	3832	3832	3832	



TEST NUMBER: P909246

CATALOG NUMBER: DFN2DIP-SQ3F0-080D120US840-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3339.0	3339.0	3339.0	3339.0	3339.0
2.5°	3354.1	3339.0	3305.7	3336.1	3330.0
5°	3339.0	3324.0	3284.5	3311.8	3302.8
7.5°	3311.8	3293.8	3251.5	3263.4	3248.2
10°	3275.5	3254.4	3194.1	3184.8	3166.8
12.5°	3230.4	3203.1	3121.3	3103.3	3070.0
15°	3175.8	3142.5	3039.9	2982.5	2952.3
17.5°	3112.3	3063.9	2937.0	2870.6	2822.2
20°	3039.9	2979.3	2828.3	2753.0	2686.2
22.5°	2961.3	2891.7	2716.4	2613.8	2568.6
25°	2882.8	2786.0	2586.6	2462.9	2417.3
27.5°	2789.1	2686.2	2465.7	2323.7	2254.1
30°	2689.5	2574.3	2332.7	2178.8	2097.0
32.5°	2592.6	2453.6	2206.1	2024.6	1948.9
35°	2484.0	2329.8	2064.0	1873.6	1806.9
37.5°	2378.1	2211.8	1931.0	1722.2	1646.9
40°	2266.3	2085.2	1791.8	1577.3	1498.7
42.5°	2151.5	1958.2	1652.9	1429.3	1353.8
45°	2030.6	1828.1	1511.0	1296.2	1223.8
47.5°	1915.9	1701.4	1375.0	1160.2	1093.9
50°	1788.9	1574.5	1242.0	1033.3	970.1
52.5°	1664.9	1438.1	1115.0	915.6	858.3
55°	1544.0	1308.4	982.0	800.8	743.5
57.5°	1420.3	1178.5	864.3	695.1	646.6
60°	1293.2	1051.6	740.2	586.3	538.0
62.5°	1169.5	927.8	634.5	489.6	465.5
65°	1042.6	797.6	525.7	423.2	413.8
67.5°	921.7	676.8	423.2	371.5	362.6
70°	794.8	559.2	350.4	320.2	308.1
72.5°	673.9	450.1	293.1	269.0	262.9
75°	555.9	344.4	241.8	220.6	217.7
77.5°	438.3	244.6	190.5	178.2	172.2
80°	329.2	175.4	144.9	133.0	133.0
82.5°	229.5	118.0	99.7	93.6	93.6
85°	129.9	66.3	57.4	57.4	57.4
87.5°	48.4	24.0	24.0	21.2	21.2
90°	3.4	41.6	113.2	106.3	109.8
92.5°	71.6	97.0	100.5	104.0	104.0
95°	168.6	201.1	206.8	206.8	201.1
97.5°	280.7	310.8	323.6	323.6	323.6
100°	410.2	436.8	446.0	446.0	442.5
102.5°	546.5	566.1	578.9	582.4	578.9
105°	695.6	704.8	711.8	717.5	717.5
107.5°	843.4	857.4	857.4	859.6	843.4
110°	986.7	1005.2	1005.2	1005.2	996.0



TEST NUMBER: P909246

CATALOG NUMBER: DFN2DIP-SQ3F0-080D120US840-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1141.6	1161.2	1157.7	1148.5	1141.6
115°	1294.0	1312.6	1306.8	1303.3	1294.0
117.5°	1445.4	1470.9	1454.7	1445.4	1436.2
120°	1598.0	1623.4	1598.0	1598.0	1587.6
122.5°	1736.7	1769.0	1752.8	1743.5	1736.7
125°	1882.2	1911.1	1901.9	1891.5	1887.9
127.5°	2024.4	2060.1	2047.4	2033.6	2024.4
130°	2157.2	2198.8	2193.0	2186.1	2173.3
132.5°	2306.2	2338.6	2340.9	2324.7	2315.5
135°	2434.5	2470.3	2477.3	2473.8	2464.6
137.5°	2577.8	2606.7	2612.4	2610.1	2596.3
140°	2703.7	2732.6	2748.8	2748.8	2736.0
142.5°	2833.2	2862.1	2871.2	2874.7	2862.1
145°	2955.6	2978.7	2997.2	3000.7	2988.0
147.5°	3065.3	3094.2	3108.2	3113.9	3101.2
150°	3178.7	3198.2	3211.0	3221.4	3211.0
152.5°	3279.1	3298.7	3315.0	3327.7	3315.0
155°	3379.6	3388.9	3399.3	3415.5	3405.1
157.5°	3466.4	3473.2	3479.0	3502.1	3486.0
160°	3543.7	3550.7	3554.1	3573.8	3559.9
162.5°	3615.3	3615.3	3618.9	3640.8	3624.6
165°	3676.6	3673.2	3673.2	3696.2	3680.1
167.5°	3732.1	3721.7	3721.7	3744.8	3728.6
170°	3773.7	3764.4	3760.9	3784.1	3764.4
172.5°	3802.5	3793.3	3789.8	3812.9	3793.3
175°	3825.7	3816.4	3809.5	3832.5	3812.9
177.5°	3838.4	3829.1	3822.1	3841.8	3822.1
180°	3832.5	3832.5	3832.5	3832.5	3832.5



TEST NUMBER: P909246  
 CATALOG NUMBER: DFN2DIP-SQ3F0-080D120US840-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.66	11.41	11.71	12.46	13.88	6.62	7.37	7.67	8.42	9.84
	3H	12.33	13.00	13.39	14.06	15.50	7.80	8.47	8.86	9.53	10.97
	4H	12.93	13.56	14.00	14.63	16.07	8.24	8.87	9.31	9.94	11.38
	6H	13.34	13.93	14.43	14.99	16.45	8.55	9.13	9.63	10.20	11.66
	8H	13.47	14.02	14.55	15.10	16.56	8.64	9.19	9.72	10.27	11.73
	12H	13.52	14.05	14.61	15.13	16.60	8.67	9.20	9.76	10.28	11.75
4H	2H	10.67	11.30	11.75	12.36	13.81	7.21	7.84	8.28	8.90	10.35
	3H	12.48	13.01	13.57	14.10	15.56	8.54	9.07	9.63	10.16	11.62
	4H	13.17	13.65	14.26	14.73	16.21	9.08	9.56	10.17	10.64	12.12
	6H	13.68	14.09	14.78	15.19	16.67	9.49	9.90	10.59	11.01	12.48
	8H	13.85	14.23	14.95	15.33	16.82	9.61	10.00	10.71	11.09	12.58
	12H	13.94	14.29	15.05	15.39	16.89	9.67	10.02	10.78	11.13	12.62
8H	4H	13.13	13.52	14.23	14.61	16.10	9.35	9.74	10.45	10.83	12.32
	6H	13.69	14.01	14.81	15.14	16.63	9.86	10.18	10.98	11.31	12.80
	8H	13.90	14.18	15.03	15.30	16.81	10.04	10.32	11.17	11.44	12.95
	12H	14.03	14.28	15.16	15.39	16.94	10.15	10.40	11.28	11.51	13.06
12H	4H	13.08	13.43	14.19	14.54	16.03	9.35	9.70	10.47	10.81	12.30
	6H	13.66	13.94	14.79	15.06	16.57	9.91	10.19	11.03	11.30	12.81
	8H	13.88	14.12	15.01	15.24	16.78	10.11	10.35	11.24	11.47	13.01