

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914680

Luminaire Tested: DFN2DIP-SQ3F0-080D070US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914680
REPORT IS A COMBINATION OF REPORTS P899923 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-080D070US927-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11181.7 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 128.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914680
CATALOG NUMBER: DFN2DIP-SQ3F0-080D070US927-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P914680
 CATALOG NUMBER: DFN2DIP-SQ3F0-080D070US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52	47
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44	40
3	82	73	65	59	76	68	61	56	59	54	50	50	47	43	43	40	37	34
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28	25
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22
7	59	47	39	33	55	44	37	31	38	32	28	33	29	25	28	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	23	20	17
9	51	39	31	26	47	36	30	25	32	26	23	28	23	20	24	21	18	16
10	48	36	28	23	44	34	27	22	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2825	2825	2825
5°	2828	2784	2804
10°	2803	2745	2765
15°	2761	2698	2705
20°	2703	2633	2643
25°	2646	2556	2572
30°	2574	2485	2482
35°	2507	2400	2387
40°	2424	2315	2296
45°	2341	2229	2203
50°	2250	2139	2095
55°	2155	2036	1996
60°	2047	1912	1883
65°	1929	1784	1749
70°	1779	1628	1604
75°	1571	1442	1469
80°	1321	1203	1214
85°	930	797	795

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2341 cd/sqm



TEST NUMBER: P914680

CATALOG NUMBER: DFN2DIP-SQ3F0-080D070US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.1	2.1
10°-20°	653.0	5.8
20°-30°	959.7	8.6
30°-40°	1114.6	10.0
40°-50°	1113.2	10.0
50°-60°	970.7	8.7
60°-70°	717.6	6.4
70°-80°	406.0	3.6
80°-90°	112.1	1.0
90°-100°	108.5	1.0
100°-110°	344.8	3.1
110°-120°	590.1	5.3
120°-130°	776.1	6.9
130°-140°	871.1	7.8
140°-150°	854.2	7.6
150°-160°	716.6	6.4
160°-170°	475.2	4.2
170°-180°	166.1	1.5
0°-30°	1844.8	16.5
0°-40°	2959.4	26.5
0°-60°	5043.4	45.1
0°-90°	6279.0	56.2
90°-120°	1043.4	9.3
90°-150°	3544.8	31.7
90°-180°	4903.0	43.8
0°-180°	11181.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2466	2466	2466	2466	2466	
5°	2466	2457	2430	2449	2445	234
15°	2348	2333	2302	2312	2300	661
25°	2125	2106	2066	2070	2066	978
35°	1833	1809	1771	1757	1745	1145
45°	1492	1475	1439	1413	1404	1151
55°	1129	1114	1086	1058	1046	1009
65°	761	747	723	702	690	753
75°	398	394	382	368	372	425
85°	97	95	93	85	83	108
90°	2	19	52	49	50	11
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1372	1373	1367	845
155°	1546	1551	1556	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P914680

CATALOG NUMBER: DFN2DIP-SQ3F0-080D070US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2465.9	2465.9	2465.9	2465.9	2465.9
2.5°	2480.2	2468.4	2442.3	2465.9	2461.4
5°	2465.9	2456.6	2430.5	2449.3	2444.8
7.5°	2449.3	2435.2	2409.1	2428.2	2423.4
10°	2423.4	2406.8	2378.4	2397.2	2390.2
12.5°	2387.7	2373.6	2345.2	2357.0	2352.2
15°	2347.5	2333.4	2302.4	2312.0	2300.2
17.5°	2297.6	2283.5	2252.6	2264.4	2252.6
20°	2243.1	2229.0	2195.8	2202.8	2193.5
22.5°	2188.7	2167.3	2136.4	2136.4	2131.6
25°	2124.6	2105.7	2065.5	2070.0	2065.5
27.5°	2053.3	2036.8	2006.0	1999.0	1987.2
30°	1982.4	1963.3	1927.9	1920.8	1911.2
32.5°	1906.5	1892.4	1854.3	1840.0	1830.5
35°	1832.9	1809.3	1771.3	1757.0	1745.2
37.5°	1749.9	1728.5	1690.6	1674.0	1662.2
40°	1664.7	1645.5	1607.6	1586.4	1576.8
42.5°	1581.7	1562.5	1524.8	1500.9	1486.8
45°	1491.6	1475.0	1439.2	1413.3	1403.8
47.5°	1403.8	1387.2	1349.2	1323.0	1308.9
50°	1311.2	1299.4	1266.1	1233.0	1221.1
52.5°	1221.1	1204.5	1173.9	1147.7	1131.1
55°	1128.8	1114.4	1086.1	1057.6	1045.8
57.5°	1036.3	1024.4	993.5	965.0	955.4
60°	943.6	934.4	901.1	875.0	867.9
62.5°	853.6	837.0	813.3	789.7	780.1
65°	761.3	746.9	723.3	701.9	690.1
67.5°	666.4	654.3	633.2	616.6	607.0
70°	578.6	569.0	547.7	531.1	521.7
72.5°	488.5	479.0	467.1	450.6	443.5
75°	398.2	393.7	381.7	367.6	372.3
77.5°	317.7	308.2	303.4	296.4	289.3
80°	237.3	234.7	230.0	222.9	218.1
82.5°	161.3	161.3	159.0	149.4	149.4
85°	97.1	94.8	92.6	85.3	83.0
87.5°	42.8	38.0	33.2	26.1	23.7
90°	1.6	19.0	51.8	48.6	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.7	94.7	92.0
97.5°	128.5	142.2	148.1	148.1	148.1
100°	187.7	199.9	204.1	204.1	202.5
102.5°	250.1	259.0	264.9	266.5	264.9
105°	318.3	322.5	325.7	328.4	328.4
107.5°	386.0	392.3	392.3	393.4	386.0
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P914680

CATALOG NUMBER: DFN2DIP-SQ3F0-080D070US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.4	531.4	529.8	525.5	522.4
115°	592.2	600.6	598.0	596.4	592.2
117.5°	661.4	673.0	665.7	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.1	797.8	794.6
125°	861.3	874.5	870.3	865.5	864.0
127.5°	926.3	942.7	936.9	930.6	926.3
130°	987.1	1006.1	1003.5	1000.4	994.5
132.5°	1055.3	1070.2	1071.2	1063.8	1059.5
135°	1114.0	1130.4	1133.6	1131.9	1127.7
137.5°	1179.6	1192.8	1195.4	1194.4	1188.0
140°	1237.2	1250.5	1257.8	1257.8	1252.0
142.5°	1296.4	1309.6	1313.8	1315.4	1309.6
145°	1352.5	1363.0	1371.5	1373.1	1367.3
147.5°	1402.7	1415.9	1422.3	1424.9	1419.1
150°	1454.5	1463.5	1469.3	1474.1	1469.3
152.5°	1500.5	1509.5	1516.9	1522.7	1516.9
155°	1546.5	1550.7	1555.5	1562.9	1558.1
157.5°	1586.2	1589.4	1592.0	1602.6	1595.1
160°	1621.6	1624.8	1626.3	1635.3	1629.0
162.5°	1654.4	1654.4	1656.0	1666.0	1658.6
165°	1682.4	1680.8	1680.8	1691.4	1683.9
167.5°	1707.8	1703.0	1703.0	1713.6	1706.2
170°	1726.8	1722.6	1721.0	1731.5	1722.6
172.5°	1740.0	1735.7	1734.2	1744.8	1735.7
175°	1750.6	1746.4	1743.2	1753.7	1744.8
177.5°	1756.4	1752.1	1749.0	1758.0	1749.0
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P914680
 CATALOG NUMBER: DFN2DIP-SQ3F0-080D070US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.40	12.31	12.30	13.24	14.42	10.95	11.87	11.85	12.79	13.97
	3H	13.06	13.88	13.97	14.81	16.02	12.57	13.39	13.48	14.32	15.53
	4H	13.64	14.42	14.57	15.36	16.57	13.15	13.93	14.08	14.87	16.08
	6H	14.04	14.76	14.98	15.70	16.93	13.54	14.26	14.48	15.20	16.43
	8H	14.15	14.83	15.09	15.79	17.02	13.64	14.33	14.59	15.29	16.52
	12H	14.20	14.85	15.15	15.80	17.05	13.69	14.34	14.64	15.29	16.54
4H	2H	11.86	12.64	12.79	13.58	14.79	11.50	12.28	12.44	13.22	14.44
	3H	13.73	14.38	14.67	15.34	16.57	13.32	13.97	14.26	14.94	16.16
	4H	14.44	15.03	15.39	15.99	17.25	14.01	14.61	14.97	15.57	16.82
	6H	14.95	15.47	15.92	16.45	17.70	14.52	15.03	15.49	16.02	17.27
	8H	15.10	15.58	16.07	16.56	17.83	14.66	15.14	15.63	16.12	17.39
	12H	15.17	15.61	16.16	16.60	17.88	14.73	15.16	15.71	16.15	17.43
8H	4H	14.64	15.11	15.61	16.09	17.36	14.26	14.74	15.23	15.72	16.98
	6H	15.26	15.66	16.26	16.68	17.95	14.88	15.28	15.87	16.30	17.56
	8H	15.48	15.83	16.48	16.84	18.12	15.09	15.44	16.09	16.45	17.73
	12H	15.61	15.92	16.62	16.92	18.25	15.20	15.51	16.21	16.51	17.84
12H	4H	14.62	15.06	15.61	16.05	17.32	14.25	14.69	15.24	15.68	16.95
	6H	15.29	15.64	16.30	16.65	17.93	14.92	15.27	15.92	16.28	17.56
	8H	15.53	15.84	16.54	16.84	18.17	15.15	15.46	16.16	16.46	17.79