

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909314

Luminaire Tested: DFN2DIP-SQ3F0-100D110US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909314
REPORT IS A COMBINATION OF REPORTS P900000 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D110US840-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18414.9 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 184.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909314

CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P909314

CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34
4	75	64	57	51	69	60	53	48	51	46	42	42	38	35	34	32	30
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4782	4782	4782
5°	4787	4703	4735
10°	4736	4608	4579
15°	4668	4452	4340
20°	4579	4240	4046
25°	4487	4001	3763
30°	4366	3758	3404
35°	4246	3496	3089
40°	4124	3225	2728
45°	3983	2926	2400
50°	3837	2623	2081
55°	3684	2301	1774
60°	3506	1964	1459
65°	3302	1621	1311
70°	3054	1302	1184
75°	2742	1141	1074
80°	2291	948	926
85°	1554	617	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3983 cd/sqm

TEST NUMBER: P909314

CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.2	2.1
10°-20°	1073.8	5.8
20°-30°	1507.6	8.2
30°-40°	1643.4	8.9
40°-50°	1510.5	8.2
50°-60°	1186.3	6.4
60°-70°	772.1	4.2
70°-80°	397.5	2.2
80°-90°	111.4	0.6
90°-100°	217.4	1.2
100°-110°	690.8	3.8
110°-120°	1182.1	6.4
120°-130°	1554.6	8.4
130°-140°	1745.0	9.5
140°-150°	1711.2	9.3
150°-160°	1435.4	7.8
160°-170°	951.9	5.2
170°-180°	332.7	1.8
0°-30°	2972.6	16.1
0°-40°	4616.1	25.1
0°-60°	7312.8	39.7
0°-90°	8593.8	46.7
90°-120°	2090.2	11.4
90°-150°	7101.0	38.6
90°-180°	9821.0	53.3
0°-180°	18414.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4174	4174	4174	4174	4174	
5°	4174	4155	4106	4140	4128	396
15°	3970	3928	3800	3728	3690	1119
25°	3604	3482	3233	3078	3022	1657
35°	3105	2912	2580	2342	2259	1943
45°	2538	2285	1889	1620	1530	1960
55°	1930	1636	1228	1001	929	1725
65°	1303	997	657	529	517	1292
75°	695	430	302	276	272	735
85°	162	83	72	72	72	186
90°	3	38	104	98	101	18
95°	155	184	190	190	184	172
105°	638	646	652	658	658	673
115°	1186	1203	1198	1195	1186	1173
125°	1725	1752	1743	1734	1731	1542
135°	2232	2264	2271	2268	2259	1725
145°	2709	2730	2747	2751	2739	1693
155°	3098	3106	3116	3131	3121	1426
165°	3370	3367	3367	3388	3373	951
175°	3507	3498	3492	3513	3495	333
180°	3513	3513	3513	3513	3513	

TEST NUMBER: P909314

CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4173.8	4173.8	4173.8	4173.8	4173.8
2.5°	4192.6	4173.8	4132.1	4170.1	4162.6
5°	4173.8	4154.9	4105.6	4139.7	4128.4
7.5°	4139.7	4117.2	4064.3	4079.1	4060.4
10°	4094.4	4067.9	3992.6	3981.0	3958.6
12.5°	4037.9	4003.8	3901.6	3879.2	3837.5
15°	3969.8	3928.1	3799.8	3728.1	3690.5
17.5°	3890.4	3829.9	3671.3	3588.3	3527.8
20°	3799.8	3724.1	3535.3	3441.2	3357.8
22.5°	3701.7	3614.7	3395.5	3267.3	3210.8
25°	3603.5	3482.5	3233.2	3078.5	3021.6
27.5°	3486.5	3357.8	3082.1	2904.6	2817.6
30°	3361.8	3217.9	2915.8	2723.5	2621.3
32.5°	3240.9	3066.9	2757.5	2530.7	2436.1
35°	3104.9	2912.3	2580.0	2342.0	2258.6
37.5°	2972.7	2764.7	2413.7	2152.8	2058.6
40°	2832.9	2606.5	2239.8	1971.7	1873.5
42.5°	2689.4	2447.7	2066.3	1786.6	1692.3
45°	2538.3	2285.0	1888.8	1620.2	1529.6
47.5°	2394.9	2126.8	1718.8	1450.3	1367.4
50°	2236.1	1968.0	1552.5	1291.6	1212.6
52.5°	2081.0	1797.8	1393.8	1144.5	1072.8
55°	1930.0	1635.5	1227.5	1001.1	929.3
57.5°	1775.3	1473.1	1080.5	868.8	808.3
60°	1616.6	1314.4	925.3	733.0	672.5
62.5°	1461.9	1159.7	793.0	612.0	581.9
65°	1303.2	997.0	657.2	529.0	517.4
67.5°	1152.2	846.0	529.0	464.4	453.2
70°	993.4	698.9	438.0	400.3	385.2
72.5°	842.3	562.6	366.3	336.2	328.6
75°	694.9	430.4	302.2	275.7	272.1
77.5°	547.9	305.8	238.0	222.8	215.2
80°	411.5	219.2	181.2	166.3	166.3
82.5°	286.9	147.4	124.6	117.0	117.0
85°	162.3	82.9	71.7	71.7	71.7
87.5°	60.5	30.1	30.1	26.5	26.5
90°	3.1	38.2	103.8	97.5	100.6
92.5°	65.6	89.0	92.1	95.3	95.3
95°	154.6	184.3	189.6	189.6	184.3
97.5°	257.4	284.9	296.6	296.6	296.6
100°	376.0	400.3	408.8	408.8	405.7
102.5°	501.0	519.0	530.7	533.8	530.7
105°	637.6	646.1	652.5	657.7	657.7
107.5°	773.2	785.9	785.9	788.0	773.2
110°	904.5	921.5	921.5	921.5	913.0

TEST NUMBER: P909314

CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1046.4	1064.4	1061.3	1052.8	1046.4
115°	1186.3	1203.2	1197.9	1194.8	1186.3
117.5°	1325.0	1348.3	1333.4	1325.0	1316.6
120°	1464.8	1488.1	1464.8	1464.8	1455.3
122.5°	1592.0	1621.5	1606.7	1598.2	1592.0
125°	1725.4	1751.8	1743.3	1733.8	1730.6
127.5°	1855.6	1888.4	1876.8	1864.1	1855.6
130°	1977.4	2015.6	2010.2	2003.9	1992.3
132.5°	2114.1	2143.7	2145.9	2131.0	2122.5
135°	2231.6	2264.4	2270.8	2267.7	2259.2
137.5°	2363.0	2389.4	2394.7	2392.6	2380.0
140°	2478.4	2504.9	2519.7	2519.7	2508.1
142.5°	2597.1	2623.5	2632.0	2635.1	2623.5
145°	2709.3	2730.5	2747.4	2750.6	2739.0
147.5°	2810.0	2836.4	2849.1	2854.4	2842.8
150°	2913.8	2931.7	2943.4	2952.9	2943.4
152.5°	3005.9	3023.8	3038.7	3050.4	3038.7
155°	3098.1	3106.4	3116.0	3130.9	3121.3
157.5°	3177.4	3183.8	3189.1	3210.3	3195.4
160°	3248.4	3254.8	3257.9	3276.0	3263.3
162.5°	3314.1	3314.1	3317.3	3337.4	3322.6
165°	3370.2	3367.0	3367.0	3388.2	3373.4
167.5°	3421.0	3411.5	3411.5	3432.7	3417.9
170°	3459.2	3450.7	3447.6	3468.7	3450.7
172.5°	3485.7	3477.2	3474.0	3495.2	3477.2
175°	3506.9	3498.4	3492.0	3513.2	3495.2
177.5°	3518.5	3510.0	3503.6	3521.7	3503.6
180°	3513.2	3513.2	3513.2	3513.2	3513.2

TEST NUMBER: P909314

CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.23	13.03	13.22	14.03	15.35	8.19	8.99	9.18	9.99	11.31
	3H	13.90	14.62	14.90	15.63	16.97	9.37	10.09	10.37	11.10	12.44
	4H	14.50	15.18	15.52	16.20	17.55	9.81	10.49	10.83	11.51	12.86
	6H	14.92	15.55	15.95	16.56	17.92	10.13	10.75	11.15	11.77	13.13
	8H	15.04	15.64	16.08	16.67	18.03	10.21	10.81	11.25	11.84	13.20
	12H	15.10	15.67	16.14	16.69	18.08	10.25	10.82	11.29	11.85	13.23
4H	2H	12.24	12.92	13.26	13.93	15.28	8.78	9.46	9.80	10.47	11.82
	3H	14.06	14.63	15.09	15.67	17.03	10.12	10.68	11.15	11.72	13.09
	4H	14.75	15.27	15.79	16.30	17.69	10.66	11.18	11.70	12.21	13.60
	6H	15.26	15.70	16.31	16.76	18.14	11.07	11.52	12.12	12.57	13.95
	8H	15.43	15.85	16.48	16.89	18.29	11.20	11.61	12.24	12.66	14.06
	12H	15.52	15.90	16.59	16.96	18.36	11.26	11.63	12.32	12.69	14.09
8H	4H	14.71	15.13	15.76	16.18	17.57	10.94	11.35	11.98	12.40	13.79
	6H	15.27	15.62	16.35	16.71	18.10	11.44	11.79	12.52	12.88	14.27
	8H	15.49	15.79	16.57	16.86	18.28	11.63	11.93	12.71	13.01	14.42
	12H	15.62	15.89	16.70	16.95	18.41	11.74	12.01	12.82	13.08	14.53
12H	4H	14.67	15.04	15.73	16.10	17.50	10.94	11.31	12.00	12.38	13.78
	6H	15.25	15.55	16.33	16.62	18.04	11.49	11.79	12.57	12.87	14.28
	8H	15.46	15.73	16.55	16.80	18.25	11.70	11.96	12.78	13.03	14.48