

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914824

Luminaire Tested: DFN2DIP-SQ3F0-120D070US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914824
REPORT IS A COMBINATION OF REPORTS P899931 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-120D070US927-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14318.7 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 178.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914824
CATALOG NUMBER: DFN2DIP-SQ3F0-120D070US927-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P914824
 CATALOG NUMBER: DFN2DIP-SQ3F0-120D070US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66			
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	62	61	60	55			
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46			
3	84	74	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39			
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37	34			
5	71	59	51	44	66	56	48	43	50	44	39	44	39	36	39	35	32	29			
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	28	26			
7	61	48	40	34	57	45	38	33	41	35	30	37	32	28	33	28	25	23			
8	56	44	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20			
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	18			
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4238	4238	4238
5°	4242	4176	4206
10°	4205	4117	4148
15°	4141	4047	4057
20°	4054	3950	3965
25°	3969	3834	3858
30°	3862	3727	3723
35°	3760	3600	3580
40°	3635	3472	3444
45°	3511	3344	3304
50°	3375	3209	3143
55°	3232	3053	2994
60°	3070	2868	2824
65°	2893	2677	2623
70°	2668	2442	2406
75°	2358	2162	2204
80°	1981	1804	1822
85°	1395	1196	1192

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3511 cd/sqm



TEST NUMBER: P914824

CATALOG NUMBER: DFN2DIP-SQ3F0-120D070US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.1	2.4
10°-20°	979.5	6.8
20°-30°	1439.5	10.1
30°-40°	1671.9	11.7
40°-50°	1669.9	11.7
50°-60°	1456.0	10.2
60°-70°	1076.3	7.5
70°-80°	609.0	4.3
80°-90°	165.7	1.2
90°-100°	108.5	0.8
100°-110°	344.8	2.4
110°-120°	590.1	4.1
120°-130°	776.1	5.4
130°-140°	871.1	6.1
140°-150°	854.2	6.0
150°-160°	716.6	5.0
160°-170°	475.2	3.3
170°-180°	166.1	1.2
0°-30°	2767.2	19.3
0°-40°	4439.1	31.0
0°-60°	7565.0	52.8
0°-90°	9416.1	65.8
90°-120°	1043.4	7.3
90°-150°	3544.8	24.8
90°-180°	4903.0	34.2
0°-180°	14318.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3699	3699	3699	3699	3699	
5°	3699	3685	3646	3674	3667	351
15°	3521	3500	3454	3468	3450	992
25°	3187	3158	3098	3105	3098	1466
35°	2749	2714	2657	2636	2618	1717
45°	2237	2212	2159	2120	2106	1727
55°	1693	1672	1629	1586	1569	1514
65°	1142	1120	1085	1053	1035	1129
75°	597	591	572	551	558	638
85°	146	142	139	128	124	162
90°	2	19	52	49	50	14
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1372	1373	1367	845
155°	1546	1551	1556	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P914824

CATALOG NUMBER: DFN2DIP-SQ3F0-120D070US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3698.9	3698.9	3698.9	3698.9	3698.9
2.5°	3720.4	3702.7	3663.4	3698.9	3692.1
5°	3698.9	3684.9	3645.7	3674.0	3667.2
7.5°	3674.0	3652.8	3613.6	3642.3	3635.2
10°	3635.2	3610.2	3567.6	3595.9	3585.3
12.5°	3581.5	3560.4	3517.8	3535.5	3528.3
15°	3521.2	3500.0	3453.6	3467.9	3450.2
17.5°	3446.5	3425.3	3378.9	3396.6	3378.9
20°	3364.6	3343.4	3293.7	3304.2	3290.2
22.5°	3283.0	3251.0	3204.5	3204.5	3197.4
25°	3186.8	3158.5	3098.1	3105.0	3098.1
27.5°	3080.0	3055.1	3009.1	2998.5	2980.8
30°	2973.6	2944.9	2891.7	2881.2	2866.8
32.5°	2859.6	2838.5	2781.5	2760.0	2745.7
35°	2749.4	2714.0	2657.0	2635.5	2617.8
37.5°	2624.9	2592.9	2535.9	2511.0	2493.2
40°	2497.0	2468.4	2411.3	2379.6	2365.3
42.5°	2372.5	2343.8	2287.2	2251.4	2230.2
45°	2237.4	2212.5	2158.9	2120.0	2105.7
47.5°	2105.7	2080.7	2023.8	1984.6	1963.4
50°	1966.8	1949.1	1899.3	1849.4	1831.7
52.5°	1831.7	1806.8	1760.8	1721.5	1696.6
55°	1693.2	1671.7	1629.0	1586.4	1568.7
57.5°	1554.3	1536.6	1490.2	1447.6	1433.2
60°	1415.5	1401.5	1351.7	1312.5	1301.9
62.5°	1280.4	1255.4	1220.0	1184.5	1170.2
65°	1141.9	1120.4	1084.9	1052.8	1035.1
67.5°	999.7	981.5	949.8	925.0	910.6
70°	867.9	853.6	821.5	796.6	782.7
72.5°	732.8	718.5	700.8	675.9	665.3
75°	597.4	590.6	572.4	551.4	558.5
77.5°	476.6	462.2	455.1	444.5	434.0
80°	355.8	352.0	344.9	334.4	327.2
82.5°	241.9	241.9	238.5	224.2	224.2
85°	145.7	142.3	138.9	127.9	124.5
87.5°	64.2	57.0	49.8	39.2	35.5
90°	1.6	19.0	51.8	48.6	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.7	94.7	92.0
97.5°	128.5	142.2	148.1	148.1	148.1
100°	187.7	199.9	204.1	204.1	202.5
102.5°	250.1	259.0	264.9	266.5	264.9
105°	318.3	322.5	325.7	328.4	328.4
107.5°	386.0	392.3	392.3	393.4	386.0
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P914824

CATALOG NUMBER: DFN2DIP-SQ3F0-120D070US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.4	531.4	529.8	525.5	522.4
115°	592.2	600.6	598.0	596.4	592.2
117.5°	661.4	673.0	665.7	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.1	797.8	794.6
125°	861.3	874.5	870.3	865.5	864.0
127.5°	926.3	942.7	936.9	930.6	926.3
130°	987.1	1006.1	1003.5	1000.4	994.5
132.5°	1055.3	1070.2	1071.2	1063.8	1059.5
135°	1114.0	1130.4	1133.6	1131.9	1127.7
137.5°	1179.6	1192.8	1195.4	1194.4	1188.0
140°	1237.2	1250.5	1257.8	1257.8	1252.0
142.5°	1296.4	1309.6	1313.8	1315.4	1309.6
145°	1352.5	1363.0	1371.5	1373.1	1367.3
147.5°	1402.7	1415.9	1422.3	1424.9	1419.1
150°	1454.5	1463.5	1469.3	1474.1	1469.3
152.5°	1500.5	1509.5	1516.9	1522.7	1516.9
155°	1546.5	1550.7	1555.5	1562.9	1558.1
157.5°	1586.2	1589.4	1592.0	1602.6	1595.1
160°	1621.6	1624.8	1626.3	1635.3	1629.0
162.5°	1654.4	1654.4	1656.0	1666.0	1658.6
165°	1682.4	1680.8	1680.8	1691.4	1683.9
167.5°	1707.8	1703.0	1703.0	1713.6	1706.2
170°	1726.8	1722.6	1721.0	1731.5	1722.6
172.5°	1740.0	1735.7	1734.2	1744.8	1735.7
175°	1750.6	1746.4	1743.2	1753.7	1744.8
177.5°	1756.4	1752.1	1749.0	1758.0	1749.0
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P914824
 CATALOG NUMBER: DFN2DIP-SQ3F0-120D070US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.59	14.62	14.40	15.45	16.48	13.15	14.17	13.96	15.01	16.03
	3H	15.26	16.18	16.08	17.02	18.08	14.77	15.69	15.59	16.53	17.59
	4H	15.85	16.72	16.69	17.57	18.64	15.36	16.23	16.20	17.08	18.14
	6H	16.26	17.06	17.11	17.92	19.00	15.76	16.56	16.61	17.42	18.50
	8H	16.37	17.13	17.23	18.00	19.08	15.87	16.63	16.73	17.50	18.58
	12H	16.42	17.15	17.28	18.01	19.12	15.91	16.64	16.78	17.51	18.61
4H	2H	14.07	14.94	14.91	15.79	16.85	13.72	14.58	14.56	15.43	16.50
	3H	15.95	16.67	16.80	17.55	18.63	15.54	16.26	16.39	17.14	18.23
	4H	16.66	17.32	17.53	18.20	19.31	16.24	16.90	17.11	17.78	18.89
	6H	17.18	17.75	18.07	18.66	19.77	16.75	17.32	17.63	18.23	19.34
	8H	17.33	17.87	18.22	18.77	19.89	16.90	17.43	17.78	18.33	19.45
	12H	17.41	17.89	18.32	18.81	19.94	16.96	17.45	17.87	18.36	19.49
8H	4H	16.87	17.40	17.75	18.30	19.42	16.49	17.03	17.38	17.92	19.05
	6H	17.50	17.94	18.41	18.88	20.01	17.12	17.56	18.03	18.50	19.62
	8H	17.72	18.11	18.64	19.04	20.18	17.33	17.72	18.25	18.65	19.79
	12H	17.86	18.20	18.78	19.12	20.32	17.44	17.79	18.37	18.71	19.91
12H	4H	16.86	17.34	17.77	18.26	19.39	16.49	16.97	17.40	17.89	19.02
	6H	17.53	17.92	18.45	18.85	20.00	17.16	17.55	18.08	18.48	19.62
	8H	17.78	18.12	18.70	19.04	20.24	17.40	17.74	18.32	18.66	19.86