

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914831

Luminaire Tested: DFN2DIP-SQ3F0-120D080US927-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P914831  
REPORT IS A COMBINATION OF REPORTS P901470 AND P898289  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-120D080US927-RLLONL  
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 14354.3 lumens  
Efficiency: N/A  
Efficacy: 77.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 186.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9957  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P914831  
CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US927-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P914831

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US927-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56	56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53	49	49	49	49
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46	42	42	42	42
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31	31	31	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31	27	27	27	27
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27	24	24	24	24
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22	22	22	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18	18	18	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16	16	16	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4502	4502	4502
5°	4506	4427	4457
10°	4459	4337	4311
15°	4394	4191	4085
20°	4310	3991	3809
25°	4224	3767	3542
30°	4110	3537	3204
35°	3997	3291	2907
40°	3882	3036	2568
45°	3749	2754	2260
50°	3612	2469	1959
55°	3468	2166	1670
60°	3301	1848	1373
65°	3109	1526	1234
70°	2875	1226	1115
75°	2581	1074	1011
80°	2158	892	871
85°	1463	581	646

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3749 cd/sqm



TEST NUMBER: P914831

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US927-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	368.2	2.6
10°-20°	1010.8	7.0
20°-30°	1419.2	9.9
30°-40°	1547.0	10.8
40°-50°	1421.9	9.9
50°-60°	1116.7	7.8
60°-70°	726.9	5.1
70°-80°	374.2	2.6
80°-90°	99.3	0.7
90°-100°	70.5	0.5
100°-110°	262.9	1.8
110°-120°	697.3	4.9
120°-130°	1156.5	8.1
130°-140°	1228.4	8.6
140°-150°	1141.7	8.0
150°-160°	917.9	6.4
160°-170°	591.5	4.1
170°-180°	203.6	1.4
0°-30°	2798.2	19.5
0°-40°	4345.2	30.3
0°-60°	6883.7	48.0
0°-90°	8084.0	56.3
90°-120°	1030.7	7.2
90°-150°	4557.3	31.7
90°-180°	6270.0	43.7
0°-180°	14354.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3929	3929	3929	3929	3929	
5°	3929	3911	3865	3897	3886	373
15°	3737	3698	3577	3509	3474	1053
25°	3392	3278	3044	2898	2844	1560
35°	2923	2741	2429	2205	2126	1829
45°	2389	2151	1778	1525	1440	1845
55°	1817	1540	1156	942	875	1623
65°	1227	939	619	498	487	1216
75°	654	405	284	260	256	692
85°	153	78	68	68	68	175
90°	2	18	31	39	42	14
95°	100	49	60	68	66	119
105°	470	517	94	111	118	503
115°	890	916	955	238	127	876
125°	1258	1278	1308	1319	1323	1122
135°	1557	1582	1596	1611	1608	1203
145°	1806	1804	1831	1842	1834	1130
155°	1989	1975	1993	2003	1990	916
165°	2096	2086	2091	2102	2091	592
175°	2143	2133	2136	2146	2131	204
180°	2139	2139	2139	2139	2139	



TEST NUMBER: P914831

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US927-RLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3928.9	3928.9	3928.9	3928.9	3928.9
2.5°	3946.6	3928.9	3889.7	3925.5	3918.3
5°	3928.9	3911.2	3864.7	3896.8	3886.3
7.5°	3896.8	3875.7	3825.9	3839.9	3822.1
10°	3854.2	3829.3	3758.3	3747.4	3726.3
12.5°	3801.0	3769.0	3672.7	3651.6	3612.4
15°	3736.9	3697.7	3576.9	3509.4	3474.0
17.5°	3662.2	3605.2	3455.8	3377.8	3320.8
20°	3576.9	3505.6	3328.0	3239.3	3160.8
22.5°	3484.5	3402.7	3196.3	3075.6	3022.4
25°	3392.1	3278.1	3043.5	2897.9	2844.3
27.5°	3281.9	3160.8	2901.3	2734.2	2652.3
30°	3164.6	3029.2	2744.7	2563.7	2467.5
32.5°	3050.7	2886.9	2595.7	2382.2	2293.2
35°	2922.8	2741.3	2428.6	2204.6	2126.1
37.5°	2798.3	2602.6	2272.1	2026.5	1937.8
40°	2666.6	2453.5	2108.4	1856.0	1763.6
42.5°	2531.6	2304.1	1945.0	1681.7	1593.1
45°	2389.4	2151.0	1777.9	1525.2	1439.9
47.5°	2254.3	2002.0	1618.0	1365.2	1287.1
50°	2105.0	1852.6	1461.4	1215.8	1141.5
52.5°	1959.0	1692.3	1312.0	1077.4	1009.9
55°	1816.8	1539.5	1155.5	942.3	874.8
57.5°	1671.1	1386.7	1017.0	817.8	760.9
60°	1521.8	1237.3	871.0	690.0	633.0
62.5°	1376.2	1091.7	746.6	576.1	547.7
65°	1226.8	938.6	618.7	498.0	487.0
67.5°	1084.6	796.3	498.0	437.2	426.7
70°	935.2	657.9	412.3	376.8	362.5
72.5°	793.0	529.7	344.8	316.5	309.3
75°	654.1	405.1	284.5	259.5	256.1
77.5°	515.7	287.8	224.1	209.8	202.6
80°	387.5	206.4	170.5	156.5	156.5
82.5°	270.1	138.8	117.3	110.1	110.1
85°	152.8	78.1	67.5	67.5	67.5
87.5°	57.0	28.3	28.3	24.9	24.9
90°	1.5	18.5	30.9	38.7	41.7
92.5°	38.7	32.6	37.2	40.2	41.7
95°	100.5	49.4	60.3	68.2	66.5
97.5°	181.0	54.2	78.8	83.7	85.1
100°	274.0	61.9	88.2	100.5	103.6
102.5°	376.0	373.0	91.3	108.2	113.0
105°	470.5	517.0	94.4	111.4	117.6
107.5°	580.4	618.9	97.6	114.5	120.7
110°	685.7	718.0	270.9	116.1	122.2



TEST NUMBER: P914831

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US927-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	784.7	812.5	786.2	119.1	123.9
115°	889.9	916.2	954.9	238.4	127.0
117.5°	981.2	1012.1	1038.5	817.1	411.7
120°	1083.4	1106.5	1134.5	1153.0	944.0
122.5°	1169.9	1194.8	1225.8	1235.0	1236.7
125°	1258.1	1278.3	1307.7	1318.6	1323.2
127.5°	1338.6	1360.3	1383.7	1399.1	1400.6
130°	1414.5	1439.3	1456.3	1473.4	1471.9
132.5°	1491.9	1512.1	1529.1	1543.0	1541.5
135°	1557.0	1581.7	1595.5	1611.2	1608.0
137.5°	1625.0	1643.5	1659.1	1674.6	1670.0
140°	1691.5	1704.0	1720.9	1734.9	1727.1
142.5°	1747.4	1758.2	1778.2	1790.6	1782.8
145°	1806.2	1804.5	1830.8	1841.7	1833.9
147.5°	1857.1	1852.5	1878.7	1886.5	1880.4
150°	1906.7	1895.8	1920.6	1929.8	1922.1
152.5°	1948.4	1936.1	1959.2	1968.6	1957.8
155°	1988.7	1974.9	1993.4	2002.6	1990.4
157.5°	2021.2	2008.9	2022.8	2033.7	2021.2
160°	2049.1	2039.8	2049.1	2058.3	2047.5
162.5°	2073.8	2064.6	2072.3	2083.1	2069.2
165°	2095.5	2086.3	2090.9	2101.7	2090.9
167.5°	2112.5	2103.2	2107.9	2118.8	2104.8
170°	2126.5	2117.1	2120.3	2131.1	2117.1
172.5°	2135.7	2126.5	2129.6	2140.5	2126.5
175°	2143.4	2132.6	2135.7	2146.5	2131.1
177.5°	2146.5	2135.7	2137.3	2148.2	2134.2
180°	2138.8	2138.8	2138.8	2138.8	2138.8



TEST NUMBER: P914831  
 CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US927-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.91	13.80	13.82	14.72	15.90	8.87	9.76	9.78	10.68	11.86
	3H	14.59	15.38	15.51	16.31	17.52	10.06	10.85	10.98	11.78	12.99
	4H	15.20	15.94	16.13	16.88	18.09	10.51	11.25	11.44	12.19	13.40
	6H	15.62	16.30	16.56	17.25	18.47	10.82	11.51	11.77	12.45	13.68
	8H	15.74	16.40	16.70	17.36	18.58	10.91	11.57	11.87	12.53	13.75
	12H	15.80	16.43	16.76	17.38	18.63	10.95	11.58	11.91	12.53	13.78
4H	2H	12.93	13.68	13.87	14.62	15.83	9.47	10.22	10.41	11.15	12.37
	3H	14.76	15.38	15.71	16.35	17.58	10.82	11.44	11.77	12.41	13.64
	4H	15.45	16.02	16.41	16.98	18.23	11.36	11.93	12.32	12.89	14.14
	6H	15.97	16.45	16.94	17.44	18.69	11.78	12.27	12.75	13.25	14.50
	8H	16.14	16.60	17.11	17.57	18.84	11.90	12.36	12.88	13.34	14.61
	12H	16.24	16.64	17.23	17.64	18.91	11.97	12.38	12.96	13.37	14.65
8H	4H	15.42	15.88	16.40	16.86	18.12	11.64	12.10	12.62	13.08	14.35
	6H	15.99	16.36	16.99	17.38	18.65	12.16	12.53	13.16	13.55	14.82
	8H	16.20	16.53	17.21	17.54	18.82	12.34	12.67	13.35	13.68	14.97
	12H	16.34	16.63	17.35	17.63	18.96	12.46	12.75	13.47	13.75	15.08
12H	4H	15.38	15.79	16.37	16.78	18.05	11.65	12.06	12.64	13.06	14.33
	6H	15.96	16.29	16.97	17.30	18.59	12.20	12.54	13.21	13.54	14.83
	8H	16.18	16.47	17.19	17.47	18.80	12.41	12.70	13.42	13.71	15.04