

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917274

Luminaire Tested: DFN2DIP-SQ3F0-040D090US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917274
REPORT IS A COMBINATION OF REPORTS P899952 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-040D090US930-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9265.8 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 100.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917274

CATALOG NUMBER: DFN2DIP-SQ3F0-040D090US930-RLFL

Luminous Intensity Polar Plot



TEST NUMBER: P917274

CATALOG NUMBER: DFN2DIP-SQ3F0-040D090US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	89	86	83	84	80	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	38	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	33	29	32	27	24	25	22	19	18	16	14
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	36	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1544	1544	1544
5°	1546	1519	1529
10°	1530	1488	1479
15°	1508	1438	1401
20°	1479	1369	1307
25°	1449	1292	1215
30°	1410	1213	1099
35°	1371	1129	997
40°	1332	1042	881
45°	1286	945	775
50°	1239	847	672
55°	1190	743	573
60°	1132	634	471
65°	1067	524	423
70°	986	421	382
75°	886	369	347
80°	740	306	299
85°	502	200	222

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2332 cd/sqm

TEST NUMBER: P917274

CATALOG NUMBER: DFN2DIP-SQ3F0-040D090US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.4
10°-20°	346.8	3.7
20°-30°	486.9	5.3
30°-40°	530.7	5.7
40°-50°	487.8	5.3
50°-60°	383.1	4.1
60°-70°	249.3	2.7
70°-80°	128.4	1.4
80°-90°	39.4	0.4
90°-100°	143.6	1.5
100°-110°	456.3	4.9
110°-120°	780.8	8.4
120°-130°	1026.9	11.1
130°-140°	1152.6	12.4
140°-150°	1130.3	12.2
150°-160°	948.2	10.2
160°-170°	628.8	6.8
170°-180°	219.8	2.4
0°-30°	960.0	10.4
0°-40°	1490.7	16.1
0°-60°	2361.5	25.5
0°-90°	2778.6	30.0
90°-120°	1380.7	14.9
90°-150°	4690.5	50.6
90°-180°	6487.0	70.0
0°-180°	9265.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1348	1348	1348	1348	1348	
5°	1348	1342	1326	1337	1333	128
15°	1282	1268	1227	1204	1192	361
25°	1164	1125	1044	994	976	535
35°	1003	940	833	756	729	628
45°	820	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	60
90°	2	25	69	64	66	9
95°	102	122	125	125	122	114
105°	421	427	431	434	434	444
115°	784	795	791	789	784	775
125°	1140	1157	1152	1145	1143	1018
135°	1474	1496	1500	1498	1492	1139
145°	1790	1804	1815	1817	1809	1118
155°	2046	2052	2058	2068	2062	942
165°	2226	2224	2224	2238	2228	628
175°	2316	2311	2307	2321	2309	220
180°	2321	2321	2321	2321	2321	

TEST NUMBER: P917274

CATALOG NUMBER: DFN2DIP-SQ3F0-040D090US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.9	1347.9	1347.9	1347.9	1347.9
2.5°	1354.0	1347.9	1334.4	1346.7	1344.2
5°	1347.9	1341.7	1325.8	1336.8	1333.3
7.5°	1336.8	1329.6	1312.5	1317.3	1311.2
10°	1322.3	1313.7	1289.3	1285.6	1278.4
12.5°	1304.0	1293.0	1260.0	1252.7	1239.3
15°	1282.0	1268.5	1227.1	1204.0	1191.8
17.5°	1256.4	1236.8	1185.5	1158.8	1139.2
20°	1227.1	1202.6	1141.7	1111.3	1084.3
22.5°	1195.4	1167.3	1096.5	1055.1	1036.9
25°	1163.7	1124.6	1044.1	994.2	975.7
27.5°	1125.9	1084.3	995.3	938.0	909.9
30°	1085.7	1039.2	941.6	879.5	846.5
32.5°	1046.6	990.4	890.5	817.3	786.7
35°	1002.7	940.4	833.2	756.3	729.4
37.5°	960.0	892.8	779.4	695.2	664.8
40°	914.8	841.7	723.3	636.7	605.0
42.5°	868.5	790.4	667.2	576.9	546.5
45°	819.7	737.9	609.9	523.3	494.0
47.5°	773.4	686.8	555.1	468.4	441.6
50°	722.1	635.5	501.3	417.1	391.6
52.5°	672.1	580.6	450.1	369.6	346.4
55°	623.3	528.2	396.4	323.3	300.1
57.5°	573.3	475.7	348.9	280.5	261.1
60°	522.0	424.4	298.8	236.7	217.2
62.5°	472.1	374.5	256.1	197.6	187.9
65°	420.9	322.0	212.2	170.8	167.1
67.5°	372.1	273.2	170.8	150.0	146.3
70°	320.8	225.7	141.5	129.3	124.3
72.5°	272.1	181.7	118.3	108.6	106.2
75°	224.4	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.5
80°	132.9	70.8	58.5	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.2	23.2	23.2
87.5°	19.6	9.7	9.7	8.6	8.6
90°	2.1	25.2	68.6	64.3	66.4
92.5°	43.4	58.8	60.9	62.9	62.9
95°	102.2	121.7	125.2	125.2	121.7
97.5°	170.0	188.2	195.9	195.9	195.9
100°	248.3	264.5	270.0	270.0	268.0
102.5°	330.9	342.8	350.5	352.6	350.5
105°	421.2	426.7	431.0	434.5	434.5
107.5°	510.7	519.1	519.1	520.5	510.7
110°	597.5	608.7	608.7	608.7	603.1

TEST NUMBER: P917274

CATALOG NUMBER: DFN2DIP-SQ3F0-040D090US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	691.2	703.1	701.0	695.4	691.2
115°	783.6	794.8	791.2	789.2	783.6
117.5°	875.2	890.6	880.8	875.2	869.6
120°	967.6	982.9	967.6	967.6	961.2
122.5°	1051.5	1071.1	1061.4	1055.7	1051.5
125°	1139.7	1157.2	1151.6	1145.2	1143.2
127.5°	1225.7	1247.4	1239.7	1231.3	1225.7
130°	1306.2	1331.4	1327.9	1323.6	1316.0
132.5°	1396.4	1416.0	1417.4	1407.6	1402.1
135°	1474.1	1495.7	1500.0	1497.9	1492.3
137.5°	1560.8	1578.3	1581.8	1580.5	1572.1
140°	1637.1	1654.6	1664.3	1664.3	1656.7
142.5°	1715.5	1732.9	1738.5	1740.7	1732.9
145°	1789.7	1803.6	1814.8	1816.9	1809.2
147.5°	1856.1	1873.6	1882.0	1885.5	1877.8
150°	1924.7	1936.6	1944.2	1950.5	1944.2
152.5°	1985.5	1997.4	2007.2	2014.9	2007.2
155°	2046.4	2051.9	2058.3	2068.1	2061.8
157.5°	2098.8	2103.1	2106.6	2120.5	2110.7
160°	2145.7	2149.9	2152.1	2163.9	2155.5
162.5°	2189.1	2189.1	2191.2	2204.5	2194.7
165°	2226.2	2224.1	2224.1	2238.1	2228.3
167.5°	2259.8	2253.5	2253.5	2267.4	2257.6
170°	2285.0	2279.3	2277.3	2291.2	2279.3
172.5°	2302.4	2296.9	2294.7	2308.8	2296.9
175°	2316.4	2310.8	2306.6	2320.7	2308.8
177.5°	2324.1	2318.5	2314.3	2326.2	2314.3
180°	2320.7	2320.7	2320.7	2320.7	2320.7

TEST NUMBER: P917274

CATALOG NUMBER: DFN2DIP-SQ3F0-040D090US930-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.39	7.08	7.50	8.18	9.72	2.35	3.04	3.46	4.14	5.68
	3H	8.05	8.66	9.17	9.78	11.33	3.52	4.13	4.64	5.25	6.80
	4H	8.65	9.23	9.78	10.35	11.90	3.96	4.54	5.09	5.66	7.21
	6H	9.06	9.60	10.20	10.72	12.28	4.26	4.80	5.41	5.92	7.49
	8H	9.18	9.69	10.32	10.82	12.38	4.35	4.86	5.49	5.99	7.55
	12H	9.23	9.72	10.38	10.85	12.43	4.38	4.87	5.53	6.00	7.58
4H	2H	6.38	6.97	7.53	8.09	9.64	2.92	3.51	4.06	4.62	6.18
	3H	8.20	8.68	9.34	9.83	11.39	4.25	4.74	5.40	5.88	7.45
	4H	8.88	9.33	10.03	10.46	12.04	4.79	5.24	5.94	6.37	7.95
	6H	9.38	9.76	10.54	10.92	12.50	5.19	5.58	6.35	6.73	8.31
	8H	9.55	9.91	10.71	11.06	12.65	5.32	5.67	6.47	6.82	8.41
	12H	9.64	9.96	10.81	11.12	12.72	5.37	5.69	6.54	6.85	8.45
8H	4H	8.83	9.19	9.99	10.34	11.93	5.06	5.41	6.21	6.56	8.15
	6H	9.39	9.68	10.57	10.87	12.46	5.56	5.86	6.74	7.04	8.63
	8H	9.60	9.86	10.78	11.03	12.64	5.75	6.00	6.93	7.17	8.78
	12H	9.73	9.96	10.92	11.12	12.77	5.85	6.08	7.04	7.24	8.89
12H	4H	8.78	9.10	9.95	10.26	11.86	5.05	5.38	6.22	6.53	8.13
	6H	9.36	9.62	10.54	10.79	12.40	5.61	5.86	6.79	7.03	8.64
	8H	9.58	9.80	10.76	10.97	12.61	5.81	6.03	6.99	7.20	8.84

END OF REPORT