

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917311

Luminaire Tested: DFN2DIP-SQ3F0-050D090US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917311
REPORT IS A COMBINATION OF REPORTS P901474 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D090US930-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10729.3 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 110.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917311

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917311

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	28	27	25
4	72	62	54	49	65	56	50	45	45	40	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	22	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	18	16	16	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1930	1930	1930
5°	1932	1899	1911
10°	1912	1860	1848
15°	1884	1797	1752
20°	1848	1711	1633
25°	1811	1615	1519
30°	1762	1517	1374
35°	1714	1411	1247
40°	1665	1302	1101
45°	1608	1181	969
50°	1549	1059	840
55°	1487	929	716
60°	1416	793	589
65°	1333	655	529
70°	1233	526	478
75°	1107	461	433
80°	925	382	374
85°	627	249	277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1696 cd/sqm

TEST NUMBER: P917311

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	1.5
10°-20°	433.5	4.0
20°-30°	608.6	5.7
30°-40°	663.4	6.2
40°-50°	609.7	5.7
50°-60°	478.8	4.5
60°-70°	311.7	2.9
70°-80°	160.4	1.5
80°-90°	45.3	0.4
90°-100°	81.7	0.8
100°-110°	304.4	2.8
110°-120°	807.3	7.5
120°-130°	1339.0	12.5
130°-140°	1422.3	13.3
140°-150°	1321.9	12.3
150°-160°	1062.8	9.9
160°-170°	684.8	6.4
170°-180°	235.7	2.2
0°-30°	1200.0	11.2
0°-40°	1863.4	17.4
0°-60°	2951.9	27.5
0°-90°	3469.3	32.3
90°-120°	1193.4	11.1
90°-150°	5276.6	49.2
90°-180°	7260.0	67.7
0°-180°	10729.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1685	1677	1657	1671	1667	160
15°	1602	1586	1534	1505	1490	452
25°	1455	1406	1305	1243	1220	669
35°	1253	1176	1042	945	912	784
45°	1025	922	762	654	617	791
55°	779	660	496	404	375	696
65°	526	402	265	214	209	521
75°	280	174	122	111	110	297
85°	66	34	29	29	29	75
90°	2	22	36	45	48	10
95°	116	57	70	79	77	138
105°	545	599	109	129	136	582
115°	1030	1061	1106	276	147	1014
125°	1457	1480	1514	1527	1532	1299
135°	1803	1831	1847	1866	1862	1393
145°	2091	2089	2120	2132	2123	1308
155°	2303	2287	2308	2319	2304	1061
165°	2426	2416	2421	2433	2421	685
175°	2482	2469	2473	2485	2467	236
180°	2476	2476	2476	2476	2476	

TEST NUMBER: P917311

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.8	1684.8	1684.8	1684.8	1684.8
2.5°	1692.4	1684.8	1668.0	1683.3	1680.2
5°	1684.8	1677.2	1657.3	1671.0	1666.6
7.5°	1671.0	1662.0	1640.6	1646.7	1639.0
10°	1652.8	1642.1	1611.7	1607.0	1597.9
12.5°	1629.9	1616.2	1575.0	1565.9	1549.1
15°	1602.5	1585.7	1533.9	1505.0	1489.7
17.5°	1570.4	1546.1	1482.0	1448.5	1424.0
20°	1533.9	1503.3	1427.1	1389.1	1355.4
22.5°	1494.3	1459.1	1370.7	1318.9	1296.1
25°	1454.6	1405.7	1305.1	1242.7	1219.7
27.5°	1407.4	1355.4	1244.1	1172.5	1137.4
30°	1357.1	1299.0	1177.0	1099.3	1058.1
32.5°	1308.2	1238.0	1113.1	1021.6	983.4
35°	1253.4	1175.6	1041.5	945.3	911.7
37.5°	1200.0	1116.1	974.4	869.0	831.0
40°	1143.5	1052.1	904.1	795.9	756.3
42.5°	1085.7	988.1	834.1	721.1	683.1
45°	1024.7	922.4	762.4	654.0	617.4
47.5°	966.7	858.5	693.8	585.5	552.0
50°	902.7	794.4	626.7	521.4	489.5
52.5°	840.1	725.7	562.6	462.0	433.1
55°	779.1	660.1	495.5	404.1	375.1
57.5°	716.6	594.7	436.1	350.7	326.3
60°	652.6	530.6	373.5	295.9	271.4
62.5°	590.1	468.1	320.2	247.0	234.9
65°	526.0	402.5	265.3	213.5	208.9
67.5°	465.0	341.5	213.5	187.5	183.0
70°	401.0	282.1	176.8	161.6	155.5
72.5°	340.1	227.1	147.9	135.7	132.6
75°	280.5	173.7	122.0	111.3	109.8
77.5°	221.1	123.4	96.1	89.9	86.8
80°	166.2	88.5	73.1	67.1	67.1
82.5°	115.9	59.5	50.3	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.5	12.1	12.1	10.7	10.7
90°	1.7	21.5	35.7	44.9	48.3
92.5°	44.9	37.7	43.0	46.6	48.3
95°	116.4	57.2	69.8	78.9	77.0
97.5°	209.6	62.8	91.3	96.8	98.5
100°	317.2	71.7	102.2	116.4	120.0
102.5°	435.4	431.9	105.7	125.3	130.9
105°	544.7	598.6	109.3	129.0	136.2
107.5°	672.0	716.6	113.0	132.6	139.8
110°	793.9	831.4	313.6	134.4	141.5

TEST NUMBER: P917311

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	908.6	940.7	910.3	137.9	143.4
115°	1030.3	1060.7	1105.6	276.0	147.0
117.5°	1136.0	1171.8	1202.4	946.1	476.6
120°	1254.3	1281.2	1313.5	1335.0	1093.1
122.5°	1354.6	1383.3	1419.3	1429.9	1431.8
125°	1456.7	1480.1	1514.2	1526.7	1532.0
127.5°	1549.9	1575.0	1602.1	1619.9	1621.6
130°	1637.8	1666.6	1686.1	1705.8	1704.2
132.5°	1727.4	1750.8	1770.3	1786.6	1784.9
135°	1802.7	1831.4	1847.4	1865.5	1861.9
137.5°	1881.5	1902.9	1921.0	1938.9	1933.6
140°	1958.4	1972.9	1992.5	2008.7	1999.8
142.5°	2023.2	2035.7	2058.9	2073.1	2064.3
145°	2091.2	2089.3	2119.8	2132.3	2123.4
147.5°	2150.2	2144.9	2175.3	2184.3	2177.2
150°	2207.7	2195.1	2223.8	2234.4	2225.5
152.5°	2255.9	2241.7	2268.5	2279.3	2266.8
155°	2302.6	2286.6	2308.0	2318.7	2304.4
157.5°	2340.2	2326.0	2342.1	2354.7	2340.2
160°	2372.5	2361.7	2372.5	2383.2	2370.6
162.5°	2401.1	2390.4	2399.3	2411.9	2395.8
165°	2426.2	2415.5	2420.9	2433.4	2420.9
167.5°	2446.0	2435.1	2440.6	2453.2	2437.0
170°	2462.1	2451.3	2454.9	2467.4	2451.3
172.5°	2472.8	2462.1	2465.7	2478.3	2462.1
175°	2481.7	2469.1	2472.8	2485.3	2467.4
177.5°	2485.3	2472.8	2474.7	2487.2	2471.1
180°	2476.4	2476.4	2476.4	2476.4	2476.4

TEST NUMBER: P917311

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.48	8.18	8.58	9.28	10.78	3.44	4.14	4.54	5.24	6.74
	3H	9.14	9.77	10.25	10.87	12.39	4.61	5.24	5.72	6.34	7.86
	4H	9.74	10.34	10.86	11.44	12.97	5.05	5.65	6.17	6.75	8.28
	6H	10.15	10.70	11.28	11.81	13.35	5.36	5.91	6.49	7.01	8.55
	8H	10.27	10.79	11.40	11.92	13.45	5.44	5.96	6.57	7.09	8.62
	12H	10.33	10.82	11.46	11.94	13.49	5.48	5.97	6.61	7.09	8.64
4H	2H	7.48	8.08	8.61	9.18	10.71	4.02	4.61	5.14	5.72	7.24
	3H	9.29	9.79	10.42	10.92	12.46	5.35	5.84	6.48	6.97	8.51
	4H	9.97	10.43	11.11	11.55	13.11	5.88	6.34	7.02	7.46	9.02
	6H	10.48	10.87	11.62	12.01	13.56	6.29	6.68	7.43	7.82	9.37
	8H	10.65	11.01	11.79	12.15	13.71	6.41	6.78	7.55	7.91	9.48
	12H	10.73	11.06	11.89	12.21	13.78	6.47	6.80	7.62	7.94	9.52
8H	4H	9.93	10.30	11.07	11.43	13.00	6.15	6.52	7.29	7.65	9.22
	6H	10.49	10.79	11.65	11.96	13.53	6.66	6.96	7.82	8.13	9.70
	8H	10.70	10.96	11.87	12.12	13.70	6.84	7.10	8.01	8.26	9.84
	12H	10.83	11.06	12.00	12.21	13.83	6.95	7.18	8.12	8.33	9.95
12H	4H	9.88	10.21	11.03	11.35	12.93	6.15	6.48	7.31	7.63	9.20
	6H	10.46	10.72	11.63	11.88	13.46	6.70	6.97	7.87	8.12	9.71
	8H	10.67	10.90	11.84	12.06	13.67	6.90	7.13	8.07	8.29	9.91

END OF REPORT