

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917325

Luminaire Tested: DFN2DIP-SQ3F0-060D040US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917325
REPORT IS A COMBINATION OF REPORTS P901385 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-060D040US930-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8071.4 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 83.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917325

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917325

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2181	2181	2181
5°	2183	2149	2164
10°	2164	2119	2134
15°	2131	2082	2088
20°	2086	2032	2040
25°	2042	1973	1985
30°	1987	1918	1916
35°	1935	1853	1842
40°	1871	1787	1772
45°	1807	1721	1700
50°	1737	1651	1617
55°	1663	1571	1541
60°	1580	1476	1453
65°	1489	1377	1350
70°	1373	1257	1238
75°	1213	1113	1134
80°	1020	928	938
85°	717	615	614

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1807 cd/sqm

TEST NUMBER: P917325

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	2.2
10°-20°	504.1	6.2
20°-30°	740.8	9.2
30°-40°	860.4	10.7
40°-50°	859.3	10.6
50°-60°	749.3	9.3
60°-70°	553.9	6.9
70°-80°	313.4	3.9
80°-90°	84.6	1.0
90°-100°	36.3	0.4
100°-110°	135.3	1.7
110°-120°	358.8	4.4
120°-130°	595.1	7.4
130°-140°	632.1	7.8
140°-150°	587.5	7.3
150°-160°	472.3	5.9
160°-170°	304.4	3.8
170°-180°	104.8	1.3
0°-30°	1424.0	17.6
0°-40°	2284.3	28.3
0°-60°	3892.9	48.2
0°-90°	4844.8	60.0
90°-120°	530.4	6.6
90°-150°	2345.2	29.1
90°-180°	3227.0	40.0
0°-180°	8071.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1876	1891	1887	181
15°	1812	1801	1777	1785	1776	510
25°	1640	1625	1594	1598	1594	755
35°	1415	1397	1367	1356	1347	884
45°	1151	1138	1111	1091	1084	889
55°	871	860	838	816	807	779
65°	588	577	558	542	533	581
75°	307	304	295	284	287	328
85°	75	73	71	66	64	84
90°	1	10	16	20	21	7
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	679	681	577
135°	801	814	821	829	828	619
145°	929	929	942	948	944	581
155°	1023	1016	1026	1030	1024	472
165°	1078	1074	1076	1082	1076	305
175°	1103	1097	1099	1105	1097	105
180°	1101	1101	1101	1101	1101	

TEST NUMBER: P917325

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1903.4	1903.4	1903.4	1903.4	1903.4
2.5°	1914.5	1905.4	1885.1	1903.4	1899.9
5°	1903.4	1896.2	1876.0	1890.6	1887.1
7.5°	1890.6	1879.8	1859.5	1874.3	1870.6
10°	1870.6	1857.8	1835.8	1850.4	1844.9
12.5°	1843.1	1832.1	1810.2	1819.3	1815.7
15°	1811.9	1801.1	1777.2	1784.6	1775.5
17.5°	1773.5	1762.7	1738.8	1747.8	1738.8
20°	1731.4	1720.5	1694.8	1700.3	1693.1
22.5°	1689.5	1672.9	1649.0	1649.0	1645.4
25°	1639.9	1625.4	1594.2	1597.7	1594.2
27.5°	1584.9	1572.1	1548.4	1543.0	1533.9
30°	1530.2	1515.4	1488.1	1482.6	1475.2
32.5°	1471.5	1460.7	1431.3	1420.2	1412.9
35°	1414.9	1396.6	1367.3	1356.2	1347.0
37.5°	1350.8	1334.2	1305.0	1292.1	1283.0
40°	1284.9	1270.2	1240.9	1224.6	1217.2
42.5°	1220.8	1206.1	1177.0	1158.5	1147.6
45°	1151.4	1138.5	1110.9	1091.0	1083.5
47.5°	1083.5	1070.7	1041.5	1021.2	1010.3
50°	1012.1	1003.0	977.4	951.7	942.6
52.5°	942.6	929.8	906.0	885.9	873.1
55°	871.3	860.2	838.3	816.4	807.2
57.5°	799.9	790.8	766.9	744.9	737.5
60°	728.4	721.2	695.6	675.4	669.9
62.5°	658.8	646.0	627.8	609.5	602.2
65°	587.6	576.6	558.3	541.8	532.6
67.5°	514.4	505.1	488.8	476.0	468.6
70°	446.6	439.3	422.7	409.9	402.8
72.5°	377.1	369.7	360.6	347.8	342.3
75°	307.4	303.9	294.6	283.7	287.4
77.5°	245.2	237.9	234.2	228.8	223.3
80°	183.1	181.2	177.5	172.0	168.4
82.5°	124.5	124.5	122.7	115.4	115.4
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.4	25.6	20.2	18.3
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.1	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	141.0	31.9	45.4	51.7	53.3
102.5°	193.5	192.0	47.0	55.7	58.1
105°	242.1	266.0	48.6	57.3	60.5
107.5°	298.6	318.5	50.2	58.9	62.1
110°	352.9	369.5	139.4	59.8	62.9

TEST NUMBER: P917325

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US930-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.8	418.1	404.6	61.3	63.8
115°	457.9	471.4	491.4	122.6	65.4
117.5°	504.9	520.8	534.4	420.4	211.8
120°	557.5	569.4	583.8	593.4	485.8
122.5°	602.0	614.8	630.8	635.5	636.3
125°	647.4	657.9	672.9	678.6	680.9
127.5°	688.8	700.0	712.0	720.0	720.7
130°	727.9	740.7	749.3	758.1	757.4
132.5°	767.7	778.1	786.8	794.0	793.3
135°	801.2	814.0	821.1	829.1	827.5
137.5°	836.2	845.7	853.8	861.7	859.3
140°	870.4	876.9	885.6	892.8	888.8
142.5°	899.2	904.7	915.1	921.4	917.5
145°	929.4	928.6	942.1	947.7	943.7
147.5°	955.6	953.2	966.8	970.8	967.7
150°	981.1	975.6	988.4	993.1	989.1
152.5°	1002.7	996.3	1008.2	1013.0	1007.5
155°	1023.4	1016.3	1025.8	1030.5	1024.2
157.5°	1040.1	1033.7	1041.0	1046.5	1040.1
160°	1054.4	1049.6	1054.4	1059.2	1053.6
162.5°	1067.1	1062.4	1066.4	1072.0	1064.8
165°	1078.3	1073.6	1075.9	1081.5	1075.9
167.5°	1087.1	1082.2	1084.8	1090.3	1083.1
170°	1094.3	1089.5	1091.0	1096.7	1089.5
172.5°	1099.0	1094.3	1095.9	1101.5	1094.3
175°	1102.9	1097.4	1099.0	1104.6	1096.7
177.5°	1104.6	1099.0	1099.8	1105.5	1098.3
180°	1100.7	1100.7	1100.7	1100.7	1100.7

TEST NUMBER: P917325

CATALOG NUMBER: DFN2DIP-SQ3F0-060D040US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.82	11.78	11.69	12.67	13.79	10.38	11.34	11.25	12.23	13.35
	3H	12.49	13.35	13.37	14.25	15.39	12.00	12.86	12.88	13.75	14.90
	4H	13.08	13.89	13.97	14.79	15.95	12.58	13.40	13.48	14.30	15.46
	6H	13.48	14.23	14.38	15.14	16.31	12.98	13.73	13.88	14.64	15.81
	8H	13.58	14.30	14.50	15.23	16.39	13.08	13.80	14.00	14.72	15.89
	12H	13.63	14.31	14.55	15.24	16.43	13.12	13.80	14.04	14.73	15.92
4H	2H	11.29	12.11	12.19	13.01	14.17	10.94	11.75	11.84	12.65	13.81
	3H	13.16	13.84	14.07	14.78	15.95	12.75	13.43	13.66	14.37	15.54
	4H	13.88	14.50	14.80	15.43	16.62	13.45	14.07	14.37	15.00	16.20
	6H	14.39	14.93	15.33	15.88	17.08	13.96	14.50	14.90	15.45	16.65
	8H	14.54	15.04	15.48	15.99	17.20	14.11	14.61	15.04	15.55	16.76
	12H	14.62	15.07	15.58	16.03	17.25	14.17	14.62	15.13	15.59	16.80
8H	4H	14.08	14.58	15.01	15.52	16.74	13.70	14.20	14.64	15.15	16.36
	6H	14.71	15.12	15.67	16.11	17.32	14.32	14.74	15.29	15.73	16.94
	8H	14.92	15.29	15.90	16.27	17.50	14.53	14.90	15.50	15.88	17.11
	12H	15.06	15.38	16.03	16.35	17.63	14.65	14.97	15.62	15.94	17.22
12H	4H	14.07	14.52	15.02	15.48	16.70	13.70	14.15	14.65	15.11	16.33
	6H	14.74	15.10	15.71	16.08	17.31	14.36	14.73	15.34	15.71	16.94
	8H	14.98	15.30	15.95	16.27	17.55	14.60	14.92	15.57	15.89	17.17