

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917394

Luminaire Tested: DFN2DIP-SQ3F0-070D120US930-RLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P917394  
REPORT IS A COMBINATION OF REPORTS P900012 AND P896733  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-070D120US930-RLLFLL  
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13509.4 lumens  
Efficiency: N/A  
Efficacy: 84.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 159.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9963  
Total Harmonic Distortion (THDi): 0.065  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P917394

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US930-RLLFLL

### Luminous Intensity Polar Plot



TEST NUMBER: P917394

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US930-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80  |     |     |     | 70 |    |    |    | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 104 | 104 | 104 | 104 | 94 | 94 | 94 | 94 | 76 | 76 | 76 | 59 | 59 | 59 | 43 | 43 | 43 |
| 1   | 95  | 91  | 87  | 84  | 86 | 82 | 79 | 77 | 67 | 64 | 63 | 52 | 51 | 49 | 39 | 38 | 37 |
| 2   | 87  | 80  | 74  | 69  | 78 | 72 | 68 | 63 | 59 | 55 | 52 | 46 | 44 | 42 | 34 | 33 | 32 |
| 3   | 79  | 70  | 63  | 58  | 72 | 64 | 58 | 53 | 52 | 48 | 44 | 41 | 38 | 36 | 31 | 29 | 27 |
| 4   | 73  | 62  | 55  | 49  | 66 | 57 | 50 | 45 | 46 | 42 | 38 | 37 | 34 | 31 | 28 | 26 | 24 |
| 5   | 67  | 56  | 48  | 42  | 60 | 51 | 44 | 39 | 42 | 37 | 33 | 33 | 30 | 27 | 25 | 23 | 21 |
| 6   | 62  | 50  | 42  | 37  | 56 | 46 | 39 | 34 | 38 | 33 | 29 | 30 | 26 | 24 | 23 | 21 | 19 |
| 7   | 57  | 45  | 38  | 32  | 51 | 41 | 35 | 30 | 34 | 29 | 25 | 27 | 24 | 21 | 21 | 19 | 17 |
| 8   | 53  | 41  | 34  | 28  | 48 | 38 | 31 | 26 | 31 | 26 | 23 | 25 | 21 | 19 | 19 | 17 | 15 |
| 9   | 49  | 37  | 30  | 25  | 45 | 34 | 28 | 24 | 29 | 24 | 20 | 23 | 20 | 17 | 18 | 15 | 14 |
| 10  | 46  | 34  | 27  | 23  | 42 | 32 | 25 | 21 | 26 | 22 | 18 | 21 | 18 | 15 | 17 | 14 | 12 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2703 | 2703 | 2703 |
| 5°  | 2705 | 2658 | 2676 |
| 10° | 2677 | 2604 | 2588 |
| 15° | 2638 | 2516 | 2453 |
| 20° | 2588 | 2396 | 2287 |
| 25° | 2536 | 2261 | 2126 |
| 30° | 2467 | 2124 | 1924 |
| 35° | 2400 | 1976 | 1746 |
| 40° | 2331 | 1823 | 1541 |
| 45° | 2251 | 1653 | 1357 |
| 50° | 2168 | 1482 | 1176 |
| 55° | 2082 | 1300 | 1002 |
| 60° | 1982 | 1110 | 824  |
| 65° | 1866 | 916  | 741  |
| 70° | 1726 | 736  | 669  |
| 75° | 1550 | 645  | 607  |
| 80° | 1295 | 536  | 523  |
| 85° | 878  | 349  | 388  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3112 cd/sqm

TEST NUMBER: P917394

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US930-RLFL

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 221.1   | 1.6       |
| 10°-20°   | 606.9   | 4.5       |
| 20°-30°   | 852.0   | 6.3       |
| 30°-40°   | 928.8   | 6.9       |
| 40°-50°   | 853.6   | 6.3       |
| 50°-60°   | 670.4   | 5.0       |
| 60°-70°   | 436.4   | 3.2       |
| 70°-80°   | 224.6   | 1.7       |
| 80°-90°   | 66.1    | 0.5       |
| 90°-100°  | 191.5   | 1.4       |
| 100°-110° | 608.3   | 4.5       |
| 110°-120° | 1041.1  | 7.7       |
| 120°-130° | 1369.2  | 10.1      |
| 130°-140° | 1536.9  | 11.4      |
| 140°-150° | 1507.1  | 11.2      |
| 150°-160° | 1264.2  | 9.4       |
| 160°-170° | 838.4   | 6.2       |
| 170°-180° | 293.0   | 2.2       |
| 0°-30°    | 1679.9  | 12.4      |
| 0°-40°    | 2608.7  | 19.3      |
| 0°-60°    | 4132.7  | 30.6      |
| 0°-90°    | 4859.8  | 36.0      |
| 90°-120°  | 1840.9  | 13.6      |
| 90°-150°  | 6254.0  | 46.3      |
| 90°-180°  | 8650.0  | 64.0      |
| 0°-180°   | 13509.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|------|------|-------|------|-------|------|------|
| 0°   | 2359 | 2359  | 2359 | 2359  | 2359 |      |
| 5°   | 2359 | 2348  | 2320 | 2340  | 2333 | 224  |
| 15°  | 2244 | 2220  | 2147 | 2107  | 2086 | 632  |
| 25°  | 2036 | 1968  | 1827 | 1740  | 1708 | 937  |
| 35°  | 1755 | 1646  | 1458 | 1324  | 1276 | 1098 |
| 45°  | 1434 | 1291  | 1067 | 916   | 864  | 1108 |
| 55°  | 1091 | 924   | 694  | 566   | 525  | 975  |
| 65°  | 736  | 564   | 371  | 299   | 292  | 730  |
| 75°  | 393  | 243   | 171  | 156   | 154  | 415  |
| 85°  | 92   | 47    | 40   | 40    | 40   | 105  |
| 90°  | 3    | 34    | 91   | 86    | 89   | 13   |
| 95°  | 136  | 162   | 167  | 167   | 162  | 152  |
| 105° | 562  | 569   | 575  | 579   | 579  | 593  |
| 115° | 1045 | 1060  | 1055 | 1052  | 1045 | 1033 |
| 125° | 1520 | 1543  | 1536 | 1527  | 1524 | 1358 |
| 135° | 1965 | 1994  | 2000 | 1997  | 1990 | 1519 |
| 145° | 2386 | 2405  | 2420 | 2423  | 2412 | 1491 |
| 155° | 2728 | 2736  | 2744 | 2757  | 2749 | 1256 |
| 165° | 2968 | 2966  | 2966 | 2984  | 2971 | 837  |
| 175° | 3089 | 3081  | 3076 | 3094  | 3078 | 293  |
| 180° | 3094 | 3094  | 3094 | 3094  | 3094 |      |

TEST NUMBER: P917394

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US930-RLFL

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 0°     | 2358.7 | 2358.7 | 2358.7 | 2358.7 | 2358.7 |
| 2.5°   | 2369.3 | 2358.7 | 2335.2 | 2356.7 | 2352.4 |
| 5°     | 2358.7 | 2348.1 | 2320.3 | 2339.5 | 2333.1 |
| 7.5°   | 2339.5 | 2326.8 | 2296.9 | 2305.3 | 2294.7 |
| 10°    | 2313.9 | 2299.0 | 2256.3 | 2249.8 | 2237.1 |
| 12.5°  | 2281.9 | 2262.7 | 2205.0 | 2192.3 | 2168.7 |
| 15°    | 2243.5 | 2219.9 | 2147.4 | 2106.9 | 2085.6 |
| 17.5°  | 2198.6 | 2164.5 | 2074.8 | 2027.8 | 1993.6 |
| 20°    | 2147.4 | 2104.6 | 1998.0 | 1944.7 | 1897.6 |
| 22.5°  | 2092.0 | 2042.8 | 1918.9 | 1846.4 | 1814.5 |
| 25°    | 2036.5 | 1968.0 | 1827.2 | 1739.8 | 1707.6 |
| 27.5°  | 1970.3 | 1897.6 | 1741.8 | 1641.5 | 1592.4 |
| 30°    | 1899.9 | 1818.6 | 1647.8 | 1539.1 | 1481.4 |
| 32.5°  | 1831.5 | 1733.2 | 1558.4 | 1430.2 | 1376.7 |
| 35°    | 1754.7 | 1645.8 | 1458.1 | 1323.6 | 1276.4 |
| 37.5°  | 1680.0 | 1562.4 | 1364.1 | 1216.6 | 1163.4 |
| 40°    | 1600.9 | 1473.0 | 1265.8 | 1114.3 | 1058.7 |
| 42.5°  | 1519.9 | 1383.3 | 1167.7 | 1009.6 | 956.4  |
| 45°    | 1434.5 | 1291.4 | 1067.4 | 915.7  | 864.5  |
| 47.5°  | 1353.4 | 1201.9 | 971.3  | 819.6  | 772.7  |
| 50°    | 1263.7 | 1112.2 | 877.3  | 729.9  | 685.3  |
| 52.5°  | 1176.1 | 1015.9 | 787.7  | 646.8  | 606.3  |
| 55°    | 1090.7 | 924.2  | 693.7  | 565.7  | 525.2  |
| 57.5°  | 1003.3 | 832.5  | 610.6  | 491.0  | 456.8  |
| 60°    | 913.6  | 742.8  | 522.9  | 414.3  | 380.0  |
| 62.5°  | 826.1  | 655.4  | 448.2  | 345.8  | 328.8  |
| 65°    | 736.5  | 563.5  | 371.4  | 299.0  | 292.4  |
| 67.5°  | 651.1  | 478.1  | 299.0  | 262.4  | 256.2  |
| 70°    | 561.4  | 394.9  | 247.5  | 226.2  | 217.6  |
| 72.5°  | 476.1  | 318.0  | 207.0  | 190.0  | 185.7  |
| 75°    | 392.7  | 243.2  | 170.7  | 155.8  | 153.8  |
| 77.5°  | 309.6  | 172.8  | 134.5  | 125.9  | 121.6  |
| 80°    | 232.6  | 123.8  | 102.4  | 94.0   | 94.0   |
| 82.5°  | 162.2  | 83.3   | 70.4   | 66.1   | 66.1   |
| 85°    | 91.7   | 46.9   | 40.5   | 40.5   | 40.5   |
| 87.5°  | 34.2   | 17.0   | 17.0   | 14.9   | 14.9   |
| 90°    | 2.8    | 33.6   | 91.4   | 85.9   | 88.6   |
| 92.5°  | 57.8   | 78.4   | 81.1   | 84.0   | 84.0   |
| 95°    | 136.2  | 162.3  | 167.0  | 167.0  | 162.3  |
| 97.5°  | 226.7  | 250.9  | 261.2  | 261.2  | 261.2  |
| 100°   | 331.2  | 352.6  | 360.0  | 360.0  | 357.3  |
| 102.5° | 441.2  | 457.1  | 467.3  | 470.2  | 467.3  |
| 105°   | 561.6  | 569.0  | 574.6  | 579.3  | 579.3  |
| 107.5° | 680.9  | 692.2  | 692.2  | 694.0  | 680.9  |
| 110°   | 796.6  | 811.5  | 811.5  | 811.5  | 804.1  |

TEST NUMBER: P917394

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US930-RLFL

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 112.5° | 921.6  | 937.5  | 934.7  | 927.2  | 921.6  |
| 115°   | 1044.7 | 1059.7 | 1055.0 | 1052.2 | 1044.7 |
| 117.5° | 1166.9 | 1187.5 | 1174.4 | 1166.9 | 1159.5 |
| 120°   | 1290.1 | 1310.6 | 1290.1 | 1290.1 | 1281.7 |
| 122.5° | 1402.1 | 1428.2 | 1415.1 | 1407.6 | 1402.1 |
| 125°   | 1519.6 | 1542.9 | 1535.5 | 1527.1 | 1524.2 |
| 127.5° | 1634.3 | 1663.2 | 1652.9 | 1641.8 | 1634.3 |
| 130°   | 1741.6 | 1775.1 | 1770.5 | 1764.9 | 1754.6 |
| 132.5° | 1861.9 | 1888.1 | 1889.9 | 1876.8 | 1869.4 |
| 135°   | 1965.4 | 1994.4 | 2000.0 | 1997.2 | 1989.7 |
| 137.5° | 2081.1 | 2104.4 | 2109.1 | 2107.2 | 2096.1 |
| 140°   | 2182.8 | 2206.1 | 2219.2 | 2219.2 | 2208.9 |
| 142.5° | 2287.3 | 2310.6 | 2318.1 | 2320.8 | 2310.6 |
| 145°   | 2386.1 | 2404.8 | 2419.7 | 2422.6 | 2412.3 |
| 147.5° | 2474.8 | 2498.1 | 2509.3 | 2514.0 | 2503.7 |
| 150°   | 2566.2 | 2582.0 | 2592.3 | 2600.7 | 2592.3 |
| 152.5° | 2647.4 | 2663.2 | 2676.3 | 2686.6 | 2676.3 |
| 155°   | 2728.5 | 2736.0 | 2744.4 | 2757.4 | 2749.0 |
| 157.5° | 2798.5 | 2804.1 | 2808.7 | 2827.4 | 2814.3 |
| 160°   | 2861.0 | 2866.6 | 2869.4 | 2885.3 | 2874.0 |
| 162.5° | 2918.8 | 2918.8 | 2921.6 | 2939.3 | 2926.3 |
| 165°   | 2968.3 | 2965.5 | 2965.5 | 2984.1 | 2971.0 |
| 167.5° | 3013.0 | 3004.6 | 3004.6 | 3023.3 | 3010.2 |
| 170°   | 3046.6 | 3039.1 | 3036.3 | 3055.0 | 3039.1 |
| 172.5° | 3069.9 | 3062.4 | 3059.7 | 3078.3 | 3062.4 |
| 175°   | 3088.6 | 3081.1 | 3075.5 | 3094.1 | 3078.3 |
| 177.5° | 3098.9 | 3091.4 | 3085.7 | 3101.6 | 3085.7 |
| 180°   | 3094.1 | 3094.1 | 3094.1 | 3094.1 | 3094.1 |

TEST NUMBER: P917394

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US930-RLLFLL

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |      |      |      |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|------|------|------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7  | 0.5  | 0.5  | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3  | 0.5  | 0.3  | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2  | 0.2  | 0.2  | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |      |      |      |       |
| X=2H            | Y=2H | 9.09             | 9.82  | 10.17 | 10.89 | 12.35 | 5.06           | 5.78 | 6.13 | 6.85 | 8.32  |
|                 | 3H   | 10.76            | 11.41 | 11.84 | 12.49 | 13.97 | 6.23           | 6.88 | 7.31 | 7.96 | 9.44  |
|                 | 4H   | 11.36            | 11.98 | 12.45 | 13.06 | 14.54 | 6.67           | 7.29 | 7.76 | 8.37 | 9.85  |
|                 | 6H   | 11.77            | 12.34 | 12.88 | 13.43 | 14.92 | 6.98           | 7.55 | 8.08 | 8.63 | 10.13 |
|                 | 8H   | 11.89            | 12.43 | 13.00 | 13.53 | 15.02 | 7.06           | 7.60 | 8.17 | 8.70 | 10.20 |
|                 | 12H  | 11.95            | 12.46 | 13.06 | 13.56 | 15.07 | 7.10           | 7.61 | 8.21 | 8.71 | 10.22 |
| 4H              | 2H   | 9.10             | 9.71  | 10.20 | 10.80 | 12.28 | 5.64           | 6.25 | 6.74 | 7.33 | 8.82  |
|                 | 3H   | 10.91            | 11.43 | 12.02 | 12.53 | 14.03 | 6.97           | 7.48 | 8.08 | 8.59 | 10.09 |
|                 | 4H   | 11.60            | 12.07 | 12.71 | 13.17 | 14.68 | 7.51           | 7.98 | 8.62 | 9.08 | 10.59 |
|                 | 6H   | 12.10            | 12.50 | 13.22 | 13.63 | 15.14 | 7.91           | 8.32 | 9.03 | 9.44 | 10.95 |
|                 | 8H   | 12.27            | 12.65 | 13.39 | 13.76 | 15.29 | 8.04           | 8.41 | 9.16 | 9.53 | 11.05 |
|                 | 12H  | 12.36            | 12.70 | 13.50 | 13.83 | 15.36 | 8.09           | 8.43 | 9.23 | 9.56 | 11.09 |
| 8H              | 4H   | 11.56            | 11.93 | 12.67 | 13.05 | 14.57 | 7.78           | 8.15 | 8.90 | 9.27 | 10.79 |
|                 | 6H   | 12.11            | 12.42 | 13.25 | 13.58 | 15.10 | 8.28           | 8.59 | 9.42 | 9.75 | 11.27 |
|                 | 8H   | 12.33            | 12.60 | 13.47 | 13.73 | 15.28 | 8.47           | 8.74 | 9.61 | 9.88 | 11.42 |
|                 | 12H  | 12.46            | 12.69 | 13.61 | 13.83 | 15.41 | 8.58           | 8.82 | 9.73 | 9.95 | 11.53 |
| 12H             | 4H   | 11.50            | 11.84 | 12.64 | 12.97 | 14.50 | 7.78           | 8.12 | 8.91 | 9.24 | 10.77 |
|                 | 6H   | 12.09            | 12.36 | 13.23 | 13.49 | 15.04 | 8.33           | 8.60 | 9.48 | 9.74 | 11.28 |
|                 | 8H   | 12.30            | 12.54 | 13.45 | 13.67 | 15.25 | 8.53           | 8.77 | 9.68 | 9.90 | 11.48 |

END OF REPORT