

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917425

Luminaire Tested: DFN2DIP-SQ3F0-080D110US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917425
REPORT IS A COMBINATION OF REPORTS P901515 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-080D110US930-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15335.8 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 162.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917425
CATALOG NUMBER: DFN2DIP-SQ3F0-080D110US930-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P917425
 CATALOG NUMBER: DFN2DIP-SQ3F0-080D110US930-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	49	49	49	42
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41	41	41	41	35
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	35	35	35	30
3	80	70	63	57	72	65	58	53	53	49	45	43	40	37	34	31	30	30	30	30	25
4	73	62	54	49	66	57	50	45	47	42	38	38	35	32	30	28	25	25	25	25	22
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22	22	22	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	20	20	20	17
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17	17	17	17	15
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16	16	16	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	14	14	14	12
10	46	34	27	22	42	31	25	21	27	21	18	22	18	15	18	15	13	13	13	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2908	2908	2908
5°	2911	2865	2886
10°	2885	2825	2846
15°	2841	2777	2784
20°	2782	2710	2720
25°	2723	2631	2647
30°	2650	2557	2554
35°	2580	2470	2456
40°	2494	2382	2363
45°	2409	2294	2267
50°	2316	2202	2156
55°	2217	2095	2054
60°	2107	1968	1937
65°	1985	1836	1800
70°	1831	1676	1651
75°	1618	1483	1512
80°	1360	1238	1250
85°	958	820	818

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2409 cd/sqm



TEST NUMBER: P917425

CATALOG NUMBER: DFN2DIP-SQ3F0-080D110US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.9	1.6
10°-20°	672.1	4.4
20°-30°	987.7	6.4
30°-40°	1147.1	7.5
40°-50°	1145.7	7.5
50°-60°	999.0	6.5
60°-70°	738.5	4.8
70°-80°	417.8	2.7
80°-90°	115.6	0.8
90°-100°	99.8	0.7
100°-110°	372.1	2.4
110°-120°	986.7	6.4
120°-130°	1636.6	10.7
130°-140°	1738.4	11.3
140°-150°	1615.7	10.5
150°-160°	1298.9	8.5
160°-170°	837.0	5.5
170°-180°	288.1	1.9
0°-30°	1898.6	12.4
0°-40°	3045.8	19.9
0°-60°	5190.5	33.8
0°-90°	6462.5	42.1
90°-120°	1458.6	9.5
90°-150°	6449.2	42.1
90°-180°	8873.0	57.9
0°-180°	15335.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2538	2538	2538	2538	2538	
5°	2538	2528	2501	2521	2516	241
15°	2416	2402	2370	2379	2367	680
25°	2186	2167	2126	2130	2126	1006
35°	1886	1862	1823	1808	1796	1178
45°	1535	1518	1481	1455	1445	1185
55°	1162	1147	1118	1088	1076	1039
65°	784	769	744	722	710	775
75°	410	405	393	378	383	438
85°	100	98	95	88	85	112
90°	2	26	44	55	59	14
95°	142	70	85	96	94	169
105°	666	732	134	158	166	711
115°	1259	1296	1351	337	180	1240
125°	1780	1809	1851	1866	1872	1588
135°	2203	2238	2258	2280	2276	1702
145°	2556	2554	2591	2606	2595	1599
155°	2814	2795	2821	2834	2816	1297
165°	2965	2952	2959	2974	2959	838
175°	3033	3018	3022	3038	3016	289
180°	3027	3027	3027	3027	3027	



TEST NUMBER: P917425

CATALOG NUMBER: DFN2DIP-SQ3F0-080D110US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2537.9	2537.9	2537.9	2537.9	2537.9
2.5°	2552.6	2540.5	2513.6	2537.9	2533.2
5°	2537.9	2528.3	2501.4	2520.8	2516.2
7.5°	2520.8	2506.3	2479.4	2499.1	2494.2
10°	2494.2	2477.0	2447.8	2467.2	2460.0
12.5°	2457.4	2442.9	2413.6	2425.8	2420.9
15°	2416.0	2401.5	2369.6	2379.4	2367.3
17.5°	2364.7	2350.2	2318.3	2330.5	2318.3
20°	2308.5	2294.0	2259.8	2267.1	2257.5
22.5°	2252.6	2230.6	2198.7	2198.7	2193.8
25°	2186.5	2167.1	2125.7	2130.4	2125.7
27.5°	2113.3	2096.2	2064.6	2057.3	2045.2
30°	2040.3	2020.6	1984.1	1976.9	1967.0
32.5°	1962.1	1947.6	1908.5	1893.7	1883.9
35°	1886.4	1862.1	1823.0	1808.2	1796.1
37.5°	1801.0	1779.0	1739.9	1722.8	1710.7
40°	1713.3	1693.5	1654.5	1632.7	1622.9
42.5°	1627.8	1608.1	1569.3	1544.7	1530.2
45°	1535.1	1518.0	1481.2	1454.6	1444.8
47.5°	1444.8	1427.7	1388.5	1361.6	1347.1
50°	1349.5	1337.3	1303.1	1268.9	1256.8
52.5°	1256.8	1239.7	1208.1	1181.2	1164.1
55°	1161.7	1147.0	1117.8	1088.5	1076.3
57.5°	1066.5	1054.3	1022.5	993.2	983.3
60°	971.2	961.6	927.4	900.5	893.2
62.5°	878.5	861.4	837.1	812.8	802.9
65°	783.5	768.7	744.4	722.4	710.2
67.5°	685.8	673.4	651.7	634.6	624.8
70°	595.5	585.6	563.7	546.6	537.0
72.5°	502.8	493.0	480.8	463.7	456.5
75°	409.9	405.2	392.8	378.3	383.2
77.5°	327.0	317.2	312.3	305.0	297.7
80°	244.2	241.6	236.7	229.4	224.5
82.5°	166.0	166.0	163.6	153.8	153.8
85°	100.0	97.6	95.3	87.8	85.4
87.5°	44.0	39.1	34.2	26.9	24.4
90°	2.1	26.3	43.7	54.9	59.0
92.5°	54.9	46.1	52.5	57.0	59.0
95°	142.3	70.0	85.3	96.4	94.2
97.5°	256.2	76.7	111.5	118.3	120.4
100°	387.8	87.6	124.8	142.3	146.7
102.5°	532.1	527.9	129.2	153.2	160.0
105°	665.8	731.6	133.7	157.6	166.5
107.5°	821.3	875.9	138.1	162.0	170.9
110°	970.3	1016.1	383.4	164.4	172.9



TEST NUMBER: P917425

CATALOG NUMBER: DFN2DIP-SQ3F0-080D110US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1110.5	1149.7	1112.6	168.5	175.3
115°	1259.2	1296.4	1351.4	337.3	179.7
117.5°	1388.5	1432.2	1469.7	1156.3	582.5
120°	1533.1	1565.9	1605.4	1631.7	1335.9
122.5°	1655.6	1690.7	1734.6	1747.7	1750.0
125°	1780.4	1809.1	1850.6	1866.0	1872.5
127.5°	1894.3	1925.0	1958.0	1979.9	1982.0
130°	2001.7	2036.9	2060.7	2085.0	2082.9
132.5°	2111.2	2139.8	2163.8	2183.5	2181.5
135°	2203.3	2238.4	2257.9	2280.1	2275.6
137.5°	2299.5	2325.8	2347.9	2369.7	2363.2
140°	2393.7	2411.3	2435.3	2455.0	2444.1
142.5°	2472.7	2488.0	2516.4	2533.9	2522.9
145°	2556.0	2553.6	2590.8	2606.2	2595.3
147.5°	2628.0	2621.5	2658.7	2669.6	2661.1
150°	2698.2	2682.9	2718.0	2731.0	2720.1
152.5°	2757.3	2739.8	2772.6	2785.9	2770.5
155°	2814.2	2794.7	2820.9	2834.0	2816.5
157.5°	2860.2	2842.8	2862.6	2877.9	2860.2
160°	2899.8	2886.5	2899.8	2912.7	2897.4
162.5°	2934.6	2921.6	2932.5	2947.9	2928.1
165°	2965.3	2952.3	2958.8	2974.1	2958.8
167.5°	2989.5	2976.2	2983.0	2998.3	2978.6
170°	3009.3	2996.0	3000.4	3015.8	2996.0
172.5°	3022.2	3009.3	3013.7	3029.0	3009.3
175°	3033.2	3017.8	3022.2	3037.6	3015.8
177.5°	3037.6	3022.2	3024.6	3039.9	3020.2
180°	3026.7	3026.7	3026.7	3026.7	3026.7



TEST NUMBER: P917425
 CATALOG NUMBER: DFN2DIP-SQ3F0-080D110US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.17	10.97	11.20	12.00	13.38	9.73	10.52	10.75	11.55	12.93
	3H	11.82	12.54	12.86	13.58	14.97	11.33	12.05	12.37	13.09	14.48
	4H	12.41	13.08	13.45	14.12	15.53	11.91	12.59	12.96	13.63	15.04
	6H	12.80	13.42	13.85	14.47	15.88	12.30	12.92	13.35	13.97	15.38
	8H	12.90	13.49	13.96	14.55	15.97	12.40	12.99	13.46	14.05	15.47
	12H	12.94	13.51	14.01	14.56	16.00	12.44	13.00	13.50	14.05	15.49
4H	2H	10.62	11.30	11.67	12.34	13.75	10.27	10.94	11.32	11.98	13.39
	3H	12.48	13.04	13.54	14.11	15.53	12.07	12.63	13.13	13.70	15.12
	4H	13.18	13.70	14.25	14.76	16.20	12.76	13.28	13.83	14.34	15.78
	6H	13.69	14.14	14.77	15.22	16.66	13.26	13.70	14.33	14.79	16.22
	8H	13.84	14.25	14.91	15.33	16.78	13.40	13.81	14.48	14.89	16.34
	12H	13.91	14.28	15.00	15.37	16.83	13.46	13.83	14.55	14.92	16.38
8H	4H	13.37	13.79	14.45	14.86	16.31	13.00	13.41	14.07	14.49	15.94
	6H	13.99	14.34	15.09	15.46	16.90	13.61	13.95	14.71	15.07	16.52
	8H	14.21	14.51	15.32	15.61	17.08	13.82	14.12	14.92	15.22	16.69
	12H	14.34	14.60	15.44	15.70	17.20	13.93	14.19	15.03	15.29	16.79
12H	4H	13.35	13.73	14.45	14.82	16.27	12.99	13.36	14.08	14.45	15.91
	6H	14.02	14.32	15.13	15.42	16.89	13.65	13.95	14.75	15.05	16.52
	8H	14.26	14.52	15.36	15.62	17.12	13.88	14.14	14.98	15.24	16.74