

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911961

Luminaire Tested: DFN2DIP-SQ3F0-080D090US850-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P911961  
REPORT IS A COMBINATION OF REPORTS P901479 AND P898289  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-080D090US850-FLLONL  
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 18664.5 lumens  
Efficiency: N/A  
Efficacy: 129.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 144.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9952  
Total Harmonic Distortion (THDi): 0.069  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P911961  
CATALOG NUMBER: DFN2DIP-SQ3F0-080D090US850-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P911961  
 CATALOG NUMBER: DFN2DIP-SQ3F0-080D090US850-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47	47	47	47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40	40	40	40
2	88	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38	33	33	33	33
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32	28	28	28	28
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24	24
5	68	56	48	42	62	52	45	39	44	39	34	37	32	29	30	27	24	21	21	21	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21	18	18	18	18
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	21	19	16	16	16	16
8	53	41	34	28	49	38	31	27	33	27	23	28	23	20	23	19	17	15	15	15	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13	13
10	47	34	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14	12	12	12	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3955	3955	3955
5°	3959	3898	3925
10°	3925	3843	3871
15°	3864	3777	3787
20°	3784	3686	3700
25°	3704	3579	3601
30°	3604	3478	3475
35°	3509	3360	3341
40°	3393	3241	3214
45°	3277	3121	3084
50°	3150	2995	2933
55°	3016	2849	2794
60°	2865	2677	2635
65°	2700	2498	2448
70°	2490	2280	2246
75°	2200	2018	2057
80°	1849	1683	1700
85°	1302	1115	1113

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3277 cd/sqm



TEST NUMBER: P911961

CATALOG NUMBER: DFN2DIP-SQ3F0-080D090US850-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	324.9	1.7
10°-20°	914.2	4.9
20°-30°	1343.5	7.2
30°-40°	1560.4	8.4
40°-50°	1558.4	8.3
50°-60°	1358.9	7.3
60°-70°	1004.5	5.4
70°-80°	568.4	3.0
80°-90°	155.9	0.8
90°-100°	111.1	0.6
100°-110°	414.0	2.2
110°-120°	1098.2	5.9
120°-130°	1821.4	9.8
130°-140°	1934.7	10.4
140°-150°	1798.1	9.6
150°-160°	1445.6	7.7
160°-170°	931.5	5.0
170°-180°	320.6	1.7
0°-30°	2582.6	13.8
0°-40°	4143.0	22.2
0°-60°	7060.4	37.8
0°-90°	8789.2	47.1
90°-120°	1623.3	8.7
90°-150°	7177.5	38.5
90°-180°	9875.0	52.9
0°-180°	18664.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3452	3452	3452	3452	3452	
5°	3452	3439	3402	3429	3423	328
15°	3286	3267	3223	3237	3220	926
25°	2974	2948	2892	2898	2892	1369
35°	2566	2533	2480	2460	2443	1602
45°	2088	2065	2015	1979	1965	1612
55°	1580	1560	1520	1481	1464	1413
65°	1066	1046	1012	983	966	1054
75°	558	551	534	515	521	595
85°	136	133	130	119	116	152
90°	2	29	49	61	66	17
95°	158	78	95	107	105	188
105°	741	814	149	175	185	792
115°	1401	1443	1504	375	200	1380
125°	1982	2013	2060	2077	2084	1767
135°	2452	2491	2513	2538	2533	1894
145°	2845	2842	2883	2900	2888	1779
155°	3132	3110	3140	3154	3135	1443
165°	3300	3286	3293	3310	3293	932
175°	3376	3359	3364	3381	3356	321
180°	3368	3368	3368	3368	3368	



TEST NUMBER: P911961

CATALOG NUMBER: DFN2DIP-SQ3F0-080D090US850-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3452.1	3452.1	3452.1	3452.1	3452.1
2.5°	3472.2	3455.6	3419.0	3452.1	3445.8
5°	3452.1	3439.1	3402.5	3428.9	3422.6
7.5°	3428.9	3409.2	3372.6	3399.3	3392.7
10°	3392.7	3369.4	3329.6	3355.9	3346.2
12.5°	3342.6	3322.9	3283.1	3299.6	3293.0
15°	3286.3	3266.6	3223.2	3236.6	3220.1
17.5°	3216.5	3196.8	3153.4	3170.1	3153.4
20°	3140.1	3120.4	3073.9	3083.8	3070.7
22.5°	3064.1	3034.1	2990.8	2990.8	2984.1
25°	2974.2	2947.8	2891.5	2897.8	2891.5
27.5°	2874.5	2851.3	2808.3	2798.5	2781.9
30°	2775.3	2748.4	2698.9	2689.0	2675.6
32.5°	2668.9	2649.2	2595.9	2575.9	2562.6
35°	2566.0	2533.0	2479.7	2459.7	2443.1
37.5°	2449.8	2419.8	2366.7	2343.4	2326.9
40°	2330.5	2303.6	2250.5	2220.9	2207.5
42.5°	2214.2	2187.4	2134.6	2101.1	2081.5
45°	2088.1	2064.8	2014.8	1978.6	1965.3
47.5°	1965.3	1942.0	1888.7	1852.1	1832.4
50°	1835.6	1819.1	1772.5	1726.0	1709.5
52.5°	1709.5	1686.2	1643.3	1606.7	1583.4
55°	1580.2	1560.1	1520.4	1480.6	1464.0
57.5°	1450.7	1434.2	1390.8	1351.0	1337.6
60°	1321.0	1308.1	1261.5	1224.9	1215.0
62.5°	1194.9	1171.8	1138.6	1105.6	1092.1
65°	1065.7	1045.7	1012.5	982.6	966.0
67.5°	932.9	916.0	886.4	863.2	849.8
70°	810.0	796.6	766.8	743.5	730.4
72.5°	683.9	670.6	654.0	630.8	620.9
75°	557.5	551.2	534.3	514.6	521.2
77.5°	444.8	431.4	424.7	414.9	405.0
80°	332.1	328.6	321.9	312.1	305.3
82.5°	225.8	225.8	222.6	209.2	209.2
85°	136.0	132.7	129.6	119.4	116.2
87.5°	59.9	53.2	46.5	36.6	33.2
90°	2.3	29.3	48.6	61.1	65.7
92.5°	61.1	51.2	58.4	63.4	65.7
95°	158.4	77.9	94.9	107.4	104.8
97.5°	285.1	85.4	124.2	131.6	134.0
100°	431.5	97.6	139.0	158.4	163.2
102.5°	592.2	587.5	143.8	170.5	178.0
105°	740.9	814.2	148.7	175.4	185.2
107.5°	914.0	974.8	153.7	180.3	190.2
110°	1079.8	1130.8	426.6	182.9	192.5



TEST NUMBER: P911961

CATALOG NUMBER: DFN2DIP-SQ3F0-080D090US850-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1235.9	1279.6	1238.2	187.5	195.1
115°	1401.4	1442.8	1503.9	375.4	200.0
117.5°	1545.3	1594.0	1635.6	1286.9	648.3
120°	1706.2	1742.7	1786.7	1815.9	1486.8
122.5°	1842.6	1881.6	1930.5	1945.0	1947.6
125°	1981.5	2013.3	2059.6	2076.7	2083.9
127.5°	2108.2	2142.4	2179.2	2203.5	2205.8
130°	2227.8	2266.9	2293.5	2320.4	2318.1
132.5°	2349.6	2381.5	2408.1	2430.2	2427.8
135°	2452.1	2491.1	2512.9	2537.5	2532.6
137.5°	2559.2	2588.4	2613.0	2637.3	2630.1
140°	2663.9	2683.7	2710.3	2732.2	2720.2
142.5°	2752.0	2769.1	2800.6	2820.0	2807.9
145°	2844.6	2841.9	2883.4	2900.5	2888.3
147.5°	2924.8	2917.6	2958.9	2971.1	2961.5
150°	3003.0	2985.9	3024.9	3039.3	3027.2
152.5°	3068.6	3049.2	3085.7	3100.4	3083.4
155°	3132.0	3110.3	3139.5	3154.0	3134.6
157.5°	3183.3	3163.9	3185.8	3202.9	3183.3
160°	3227.2	3212.4	3227.2	3241.7	3224.6
162.5°	3266.0	3251.5	3263.7	3280.8	3258.8
165°	3300.2	3285.6	3293.0	3310.0	3293.0
167.5°	3327.1	3312.4	3319.8	3336.9	3314.9
170°	3349.1	3334.3	3339.2	3356.3	3334.3
172.5°	3363.6	3349.1	3353.9	3371.0	3349.1
175°	3375.7	3358.6	3363.6	3380.6	3356.3
177.5°	3380.6	3363.6	3366.1	3383.2	3361.3
180°	3368.5	3368.5	3368.5	3368.5	3368.5



TEST NUMBER: P911961  
 CATALOG NUMBER: DFN2DIP-SQ3F0-080D090US850-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.74	12.58	12.72	13.57	14.88	11.30	12.13	12.28	13.13	14.44
	3H	13.39	14.14	14.39	15.15	16.48	12.90	13.65	13.90	14.66	15.99
	4H	13.98	14.69	14.98	15.69	17.04	13.48	14.19	14.49	15.20	16.54
	6H	14.37	15.03	15.39	16.04	17.39	13.87	14.53	14.89	15.54	16.89
	8H	14.47	15.10	15.50	16.13	17.48	13.97	14.60	14.99	15.62	16.97
	12H	14.52	15.11	15.55	16.13	17.51	14.01	14.60	15.04	15.63	17.00
4H	2H	12.19	12.90	13.21	13.91	15.25	11.84	12.55	12.85	13.56	14.90
	3H	14.05	14.64	15.07	15.68	17.04	13.64	14.24	14.67	15.27	16.63
	4H	14.76	15.30	15.79	16.33	17.71	14.34	14.88	15.37	15.91	17.29
	6H	15.27	15.74	16.31	16.79	18.16	14.84	15.31	15.88	16.36	17.73
	8H	15.42	15.85	16.46	16.90	18.29	14.98	15.42	16.02	16.46	17.85
	12H	15.49	15.88	16.55	16.94	18.33	15.04	15.43	16.10	16.49	17.89
8H	4H	14.95	15.39	15.99	16.43	17.82	14.58	15.01	15.61	16.05	17.44
	6H	15.58	15.94	16.64	17.02	18.41	15.19	15.55	16.26	16.64	18.03
	8H	15.79	16.11	16.86	17.18	18.59	15.40	15.72	16.47	16.79	18.19
	12H	15.92	16.20	17.00	17.26	18.71	15.51	15.79	16.58	16.85	18.30
12H	4H	14.94	15.33	15.99	16.39	17.78	14.57	14.96	15.63	16.02	17.41
	6H	15.60	15.92	16.68	16.99	18.40	15.23	15.55	16.30	16.62	18.03
	8H	15.84	16.12	16.92	17.19	18.63	15.46	15.74	16.54	16.80	18.25