

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919981

Luminaire Tested: DFN2DIP-SQ3F0-040D040US935-FLLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P919981  
REPORT IS A COMBINATION OF REPORTS P901381 AND P898289  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-040D040US935-FLLONL  
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6819.0 lumens  
Efficiency: N/A  
Efficacy: 108.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 62.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P919981  
CATALOG NUMBER: DFN2DIP-SQ3F0-040D040US935-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P919981  
 CATALOG NUMBER: DFN2DIP-SQ3F0-040D040US935-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47	50	48	47	42
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40	44	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	39	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	31	28	26	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23	28	25	23	20
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20	26	23	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1535	1535	1535
5°	1537	1513	1524
10°	1524	1492	1503
15°	1500	1466	1470
20°	1469	1431	1437
25°	1438	1389	1398
30°	1399	1350	1349
35°	1362	1304	1297
40°	1317	1258	1248
45°	1272	1211	1197
50°	1223	1163	1139
55°	1171	1106	1085
60°	1112	1039	1023
65°	1048	970	950
70°	967	885	872
75°	854	783	798
80°	718	653	660
85°	506	433	432

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1272 cd/sqm



TEST NUMBER: P919981

CATALOG NUMBER: DFN2DIP-SQ3F0-040D040US935-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.1	1.8
10°-20°	354.9	5.2
20°-30°	521.5	7.6
30°-40°	605.7	8.9
40°-50°	605.0	8.9
50°-60°	527.5	7.7
60°-70°	389.9	5.7
70°-80°	220.6	3.2
80°-90°	60.3	0.9
90°-100°	38.3	0.6
100°-110°	142.9	2.1
110°-120°	378.9	5.6
120°-130°	628.5	9.2
130°-140°	667.6	9.8
140°-150°	620.4	9.1
150°-160°	498.8	7.3
160°-170°	321.4	4.7
170°-180°	110.6	1.6
0°-30°	1002.5	14.7
0°-40°	1608.3	23.6
0°-60°	2740.7	40.2
0°-90°	3411.6	50.0
90°-120°	560.1	8.2
90°-150°	2476.6	36.3
90°-180°	3407.0	50.0
0°-180°	6819.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1340	1335	1321	1331	1329	127
15°	1276	1268	1251	1256	1250	359
25°	1154	1144	1122	1125	1122	531
35°	996	983	963	955	948	622
45°	810	802	782	768	763	626
55°	614	606	590	575	568	548
65°	414	406	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	59
90°	1	10	17	21	23	6
95°	55	27	33	37	36	65
105°	256	281	51	60	64	273
115°	484	498	519	130	69	476
125°	684	695	711	717	719	610
135°	846	860	867	876	874	654
145°	982	981	995	1001	997	614
155°	1081	1073	1083	1088	1082	498
165°	1139	1134	1136	1142	1136	322
175°	1165	1159	1161	1166	1158	111
180°	1162	1162	1162	1162	1162	



TEST NUMBER: P919981

CATALOG NUMBER: DFN2DIP-SQ3F0-040D040US935-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1340.1	1340.1	1340.1	1340.1	1340.1
2.5°	1347.9	1341.4	1327.2	1340.1	1337.6
5°	1340.1	1335.0	1320.8	1331.0	1328.6
7.5°	1331.0	1323.4	1309.1	1319.6	1317.0
10°	1317.0	1307.9	1292.5	1302.8	1298.9
12.5°	1297.5	1289.9	1274.4	1280.9	1278.2
15°	1275.7	1268.0	1251.2	1256.4	1250.0
17.5°	1248.6	1241.0	1224.2	1230.5	1224.2
20°	1218.9	1211.3	1193.3	1197.0	1192.1
22.5°	1189.4	1177.8	1161.0	1161.0	1158.4
25°	1154.5	1144.3	1122.4	1124.9	1122.4
27.5°	1115.9	1106.8	1090.2	1086.3	1079.9
30°	1077.3	1066.9	1047.7	1043.8	1038.6
32.5°	1036.0	1028.4	1007.7	1000.0	994.7
35°	996.1	983.3	962.6	954.8	948.4
37.5°	951.0	939.3	918.7	909.7	903.3
40°	904.7	894.2	873.6	862.1	857.0
42.5°	859.5	849.1	828.6	815.6	808.0
45°	810.5	801.6	782.1	768.1	762.8
47.5°	762.8	753.8	733.2	719.0	711.4
50°	712.6	706.1	688.1	670.0	663.6
52.5°	663.6	654.6	637.9	623.7	614.7
55°	613.5	605.6	590.2	574.7	568.3
57.5°	563.1	556.7	539.8	524.4	519.3
60°	512.8	507.7	489.7	475.5	471.7
62.5°	463.9	454.9	442.0	429.1	424.0
65°	413.7	405.9	393.0	381.4	375.1
67.5°	362.1	355.6	344.1	335.1	329.9
70°	314.4	309.3	297.6	288.6	283.5
72.5°	265.5	260.3	253.9	244.9	241.0
75°	216.5	214.0	207.4	199.8	202.3
77.5°	172.6	167.5	164.9	161.0	157.2
80°	128.9	127.5	124.9	121.1	118.6
82.5°	87.6	87.6	86.4	81.2	81.2
85°	52.8	51.6	50.3	46.3	45.1
87.5°	23.2	20.7	18.1	14.2	12.8
90°	0.8	10.1	16.8	21.1	22.6
92.5°	21.1	17.7	20.1	21.9	22.6
95°	54.6	26.9	32.7	37.0	36.2
97.5°	98.4	29.4	42.9	45.5	46.2
100°	148.9	33.7	48.0	54.6	56.3
102.5°	204.3	202.8	49.6	58.8	61.4
105°	255.6	280.9	51.3	60.5	63.9
107.5°	315.4	336.4	53.0	62.3	65.6
110°	372.6	390.2	147.2	63.1	66.4



TEST NUMBER: P919981

CATALOG NUMBER: DFN2DIP-SQ3F0-040D040US935-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	426.5	441.5	427.2	64.7	67.3
115°	483.5	497.8	518.9	129.5	69.1
117.5°	533.2	550.0	564.4	444.0	223.7
120°	588.8	601.3	616.5	626.6	513.1
122.5°	635.8	649.3	666.2	671.1	672.0
125°	683.7	694.7	710.7	716.6	719.1
127.5°	727.5	739.3	751.9	760.3	761.1
130°	768.7	782.2	791.3	800.6	799.9
132.5°	810.7	821.7	830.9	838.5	837.8
135°	846.1	859.6	867.1	875.5	873.9
137.5°	883.0	893.1	901.6	910.0	907.5
140°	919.2	926.0	935.2	942.8	938.6
142.5°	949.6	955.4	966.4	973.0	968.9
145°	981.5	980.7	994.9	1000.8	996.6
147.5°	1009.2	1006.7	1021.0	1025.2	1021.9
150°	1036.1	1030.3	1043.8	1048.8	1044.6
152.5°	1058.9	1052.1	1064.7	1069.8	1063.9
155°	1080.7	1073.2	1083.3	1088.3	1081.6
157.5°	1098.4	1091.7	1099.3	1105.2	1098.4
160°	1113.5	1108.4	1113.5	1118.5	1112.7
162.5°	1127.0	1122.0	1126.2	1132.0	1124.5
165°	1138.8	1133.8	1136.3	1142.1	1136.3
167.5°	1148.1	1142.9	1145.6	1151.4	1143.8
170°	1155.6	1150.6	1152.2	1158.1	1150.6
172.5°	1160.6	1155.6	1157.4	1163.2	1155.6
175°	1164.8	1158.9	1160.6	1166.5	1158.1
177.5°	1166.5	1160.6	1161.5	1167.4	1159.9
180°	1162.3	1162.3	1162.3	1162.3	1162.3



TEST NUMBER: P919981  
 CATALOG NUMBER: DFN2DIP-SQ3F0-040D040US935-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.73	9.59	9.69	10.56	11.84	8.29	9.15	9.24	10.12	11.39
	3H	10.39	11.16	11.35	12.14	13.43	9.90	10.67	10.86	11.65	12.94
	4H	10.97	11.70	11.95	12.69	13.99	10.48	11.21	11.46	12.19	13.50
	6H	11.37	12.04	12.36	13.03	14.35	10.87	11.54	11.86	12.53	13.85
	8H	11.47	12.11	12.47	13.12	14.43	10.97	11.61	11.97	12.62	13.93
	12H	11.52	12.13	12.52	13.13	14.46	11.01	11.62	12.01	12.62	13.96
4H	2H	9.19	9.92	10.18	10.90	12.21	8.83	9.56	9.82	10.55	11.85
	3H	11.05	11.66	12.05	12.67	13.99	10.64	11.25	11.64	12.27	13.58
	4H	11.76	12.32	12.76	13.32	14.66	11.34	11.89	12.34	12.90	14.24
	6H	12.27	12.75	13.29	13.78	15.12	11.84	12.32	12.85	13.35	14.68
	8H	12.42	12.87	13.43	13.89	15.24	11.98	12.43	13.00	13.45	14.80
	12H	12.49	12.89	13.52	13.93	15.29	12.04	12.44	13.08	13.48	14.84
8H	4H	11.95	12.40	12.97	13.42	14.78	11.57	12.02	12.59	13.05	14.40
	6H	12.58	12.95	13.62	14.01	15.36	12.19	12.56	13.23	13.63	14.98
	8H	12.79	13.12	13.84	14.17	15.54	12.40	12.73	13.45	13.78	15.15
	12H	12.92	13.21	13.98	14.26	15.67	12.51	12.80	13.57	13.84	15.26
12H	4H	11.94	12.34	12.97	13.38	14.74	11.57	11.97	12.60	13.01	14.37
	6H	12.60	12.93	13.65	13.98	15.35	12.23	12.56	13.28	13.61	14.98
	8H	12.84	13.13	13.90	14.18	15.59	12.46	12.75	13.52	13.80	15.21