

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912086

Luminaire Tested: DFN2DIP-SQ3F0-120D040US850-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P912086  
REPORT IS A COMBINATION OF REPORTS P899878 AND P896733  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-120D040US850-RLLFLL  
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15237.6 lumens  
Efficiency: N/A  
Efficacy: 97.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 156.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9957  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P912086  
CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US850-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P912086

CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US850-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	78	78	78	74
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	70	69	68	68	68	68	64
2	95	88	82	77	90	84	79	74	76	72	68	69	66	63	63	60	58	58	58	58	55
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50	50	50	50	47
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44	44	44	44	41
5	74	63	54	48	70	60	53	47	55	49	44	51	45	42	46	42	39	39	39	39	36
6	69	57	48	43	65	54	47	41	50	44	39	46	41	37	42	38	35	35	35	35	32
7	64	51	43	38	61	49	42	37	46	39	35	42	37	33	39	34	31	31	31	31	29
8	59	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28	28	28	28	26
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26	26	26	26	24
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23	23	23	23	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6302	6302	6302
5°	6308	6198	6240
10°	6242	6072	6035
15°	6152	5867	5719
20°	6034	5587	5332
25°	5914	5273	4959
30°	5753	4952	4486
35°	5596	4607	4070
40°	5435	4250	3594
45°	5249	3855	3163
50°	5056	3457	2742
55°	4855	3032	2338
60°	4621	2587	1922
65°	4352	2137	1728
70°	4025	1716	1560
75°	3614	1504	1415
80°	3020	1248	1220
85°	2048	813	905

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5249 cd/sqm



TEST NUMBER: P912086

CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US850-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	515.5	3.4
10°-20°	1415.1	9.3
20°-30°	1986.8	13.0
30°-40°	2165.7	14.2
40°-50°	1990.5	13.1
50°-60°	1563.2	10.3
60°-70°	1017.5	6.7
70°-80°	523.8	3.4
80°-90°	137.7	0.9
90°-100°	86.8	0.6
100°-110°	275.8	1.8
110°-120°	472.0	3.1
120°-130°	620.8	4.1
130°-140°	696.8	4.6
140°-150°	683.3	4.5
150°-160°	573.2	3.8
160°-170°	380.1	2.5
170°-180°	132.9	0.9
0°-30°	3917.3	25.7
0°-40°	6083.0	39.9
0°-60°	9636.8	63.2
0°-90°	11315.8	74.3
90°-120°	834.7	5.5
90°-150°	2835.6	18.6
90°-180°	3922.0	25.7
0°-180°	15237.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	5500	5500	5500	5500	5500	
5°	5500	5475	5410	5455	5440	522
15°	5231	5176	5008	4913	4863	1474
25°	4749	4589	4261	4057	3982	2184
35°	4092	3838	3400	3086	2976	2561
45°	3345	3011	2489	2135	2016	2583
55°	2543	2155	1618	1319	1225	2273
65°	1717	1314	866	697	682	1703
75°	916	567	398	363	358	969
85°	214	109	94	94	94	246
90°	1	15	42	39	40	15
95°	62	74	76	76	74	69
105°	255	258	260	263	263	269
115°	474	480	478	477	474	469
125°	689	700	696	692	691	616
135°	891	904	907	906	902	689
145°	1082	1090	1097	1098	1094	676
155°	1237	1240	1244	1250	1246	569
165°	1346	1345	1345	1353	1347	380
175°	1400	1397	1394	1403	1396	133
180°	1403	1403	1403	1403	1403	



TEST NUMBER: P912086

CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US850-RLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	5500.2	5500.2	5500.2	5500.2	5500.2
2.5°	5525.0	5500.2	5445.3	5495.4	5485.3
5°	5500.2	5475.4	5410.4	5455.3	5440.5
7.5°	5455.3	5425.7	5356.0	5375.5	5350.7
10°	5395.6	5360.8	5261.4	5246.1	5216.6
12.5°	5321.1	5276.3	5141.5	5112.0	5057.2
15°	5231.4	5176.5	5007.5	4912.9	4863.3
17.5°	5126.8	5047.1	4837.9	4728.7	4648.9
20°	5007.5	4907.7	4658.9	4534.8	4424.9
22.5°	4878.0	4763.5	4474.6	4305.6	4231.2
25°	4748.7	4589.2	4260.7	4056.8	3981.9
27.5°	4594.5	4424.9	4061.6	3827.7	3713.0
30°	4430.2	4240.7	3842.5	3588.9	3454.3
32.5°	4270.8	4041.5	3633.9	3335.0	3210.3
35°	4091.8	3837.7	3399.9	3086.2	2976.3
37.5°	3917.4	3643.4	3180.7	2836.9	2712.8
40°	3733.1	3434.8	2951.6	2598.3	2468.9
42.5°	3544.0	3225.6	2722.9	2354.3	2230.2
45°	3345.0	3011.3	2488.9	2135.2	2015.7
47.5°	3155.9	2802.7	2265.0	1911.3	1801.9
50°	2946.8	2593.5	2045.9	1702.1	1598.1
52.5°	2742.4	2369.0	1836.7	1508.2	1413.8
55°	2543.4	2155.2	1617.6	1319.2	1224.7
57.5°	2339.4	1941.3	1423.7	1144.9	1065.2
60°	2130.4	1732.1	1219.3	965.9	886.2
62.5°	1926.6	1528.3	1045.1	806.5	766.8
65°	1717.4	1313.9	866.1	697.1	681.8
67.5°	1518.3	1114.8	697.1	612.1	597.3
70°	1309.2	921.0	577.2	527.6	507.5
72.5°	1110.1	741.5	482.6	443.0	433.1
75°	915.7	567.1	398.2	363.3	358.5
77.5°	722.0	402.9	313.7	293.7	283.6
80°	542.4	288.9	238.7	219.1	219.1
82.5°	378.2	194.3	164.2	154.2	154.2
85°	213.9	109.3	94.5	94.5	94.5
87.5°	79.7	39.6	39.6	34.8	34.8
90°	1.2	15.2	41.5	38.9	40.1
92.5°	26.2	35.5	36.8	38.0	38.0
95°	61.8	73.6	75.7	75.7	73.6
97.5°	102.8	113.8	118.4	118.4	118.4
100°	150.2	159.9	163.2	163.2	162.0
102.5°	200.1	207.3	211.9	213.1	211.9
105°	254.6	258.0	260.5	262.6	262.6
107.5°	308.7	313.8	313.8	314.6	308.7
110°	361.2	368.0	368.0	368.0	364.6



TEST NUMBER: P912086

CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US850-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	417.9	425.1	423.7	420.4	417.9
115°	473.7	480.5	478.3	477.1	473.7
117.5°	529.1	538.4	532.5	529.1	525.8
120°	585.0	594.2	585.0	585.0	581.1
122.5°	635.7	647.5	641.7	638.2	635.7
125°	689.0	699.6	696.2	692.3	691.1
127.5°	741.0	754.1	749.5	744.4	741.0
130°	789.6	804.9	802.8	800.3	795.6
132.5°	844.2	856.0	856.9	850.9	847.6
135°	891.2	904.3	906.8	905.5	902.2
137.5°	943.6	954.2	956.3	955.4	950.4
140°	989.7	1000.3	1006.2	1006.2	1001.5
142.5°	1037.1	1047.7	1051.0	1052.3	1047.7
145°	1081.9	1090.4	1097.1	1098.5	1093.8
147.5°	1122.1	1132.6	1137.7	1139.8	1135.2
150°	1163.6	1170.8	1175.4	1179.2	1175.4
152.5°	1200.4	1207.5	1213.5	1218.1	1213.5
155°	1237.1	1240.5	1244.3	1250.3	1246.4
157.5°	1268.9	1271.4	1273.5	1282.0	1276.0
160°	1297.2	1299.7	1301.0	1308.2	1303.1
162.5°	1323.4	1323.4	1324.7	1332.7	1326.8
165°	1345.9	1344.6	1344.6	1353.0	1347.1
167.5°	1366.2	1362.3	1362.3	1370.8	1364.8
170°	1381.4	1377.9	1376.7	1385.1	1377.9
172.5°	1391.9	1388.6	1387.2	1395.8	1388.6
175°	1400.4	1397.0	1394.5	1402.9	1395.8
177.5°	1405.1	1401.7	1399.1	1406.3	1399.1
180°	1402.9	1402.9	1402.9	1402.9	1402.9



TEST NUMBER: P912086  
 CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US850-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.53	16.61	16.25	17.34	18.22	11.49	12.57	12.21	13.31	14.18
	3H	17.22	18.18	17.96	18.93	19.85	12.69	13.65	13.43	14.40	15.32
	4H	17.84	18.74	18.59	19.50	20.43	13.15	14.06	13.90	14.81	15.74
	6H	18.27	19.10	19.04	19.87	20.81	13.47	14.31	14.24	15.08	16.02
	8H	18.40	19.19	19.18	19.98	20.92	13.57	14.36	14.35	15.15	16.09
	12H	18.47	19.23	19.25	20.01	20.97	13.62	14.38	14.40	15.16	16.12
4H	2H	15.58	16.48	16.33	17.24	18.17	12.11	13.02	12.87	13.78	14.70
	3H	17.42	18.17	18.19	18.97	19.91	13.48	14.23	14.25	15.03	15.97
	4H	18.12	18.80	18.91	19.60	20.57	14.03	14.71	14.82	15.51	16.48
	6H	18.64	19.23	19.45	20.05	21.03	14.45	15.04	15.26	15.86	16.84
	8H	18.82	19.37	19.63	20.19	21.17	14.58	15.14	15.39	15.95	16.94
	12H	18.92	19.42	19.75	20.26	21.25	14.66	15.15	15.48	15.99	16.98
8H	4H	18.10	18.65	18.91	19.47	20.46	14.32	14.88	15.13	15.69	16.68
	6H	18.67	19.13	19.51	19.99	20.97	14.84	15.30	15.68	16.16	17.15
	8H	18.89	19.29	19.73	20.15	21.15	15.03	15.43	15.88	16.29	17.30
	12H	19.03	19.39	19.88	20.23	21.30	15.15	15.51	16.00	16.36	17.42
12H	4H	18.07	18.56	18.89	19.40	20.39	14.34	14.83	15.17	15.67	16.66
	6H	18.65	19.05	19.50	19.91	20.91	14.89	15.30	15.74	16.15	17.16
	8H	18.88	19.23	19.73	20.08	21.14	15.11	15.46	15.96	16.31	17.37