

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914590

Luminaire Tested: DFN2DIP-SQ3F0-050D110US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914590
REPORT IS A COMBINATION OF REPORTS P899990 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D110US927-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11078.7 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 128.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914590

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P914590

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	26	24
4	72	61	54	48	64	55	49	44	44	40	36	34	31	29	24	23	21
5	66	55	47	41	59	50	43	38	40	35	31	31	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	47	36	30	26	30	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	16	16	14	12
10	45	33	27	22	40	31	24	20	25	20	17	20	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1876	1876	1876
5°	1877	1845	1857
10°	1858	1807	1796
15°	1831	1746	1702
20°	1796	1663	1587
25°	1760	1569	1476
30°	1712	1474	1335
35°	1665	1371	1211
40°	1618	1265	1070
45°	1562	1147	941
50°	1505	1029	816
55°	1445	902	696
60°	1375	770	572
65°	1295	636	514
70°	1198	511	465
75°	1076	448	421
80°	899	372	363
85°	610	242	269

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2771 cd/sqm

TEST NUMBER: P914590

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	1.4
10°-20°	421.2	3.8
20°-30°	591.3	5.3
30°-40°	644.6	5.8
40°-50°	592.4	5.3
50°-60°	465.3	4.2
60°-70°	302.9	2.7
70°-80°	155.9	1.4
80°-90°	47.6	0.4
90°-100°	170.5	1.5
100°-110°	541.8	4.9
110°-120°	927.3	8.4
120°-130°	1219.5	11.0
130°-140°	1368.8	12.4
140°-150°	1342.3	12.1
150°-160°	1126.0	10.2
160°-170°	746.7	6.7
170°-180°	261.0	2.4
0°-30°	1165.9	10.5
0°-40°	1810.5	16.3
0°-60°	2868.2	25.9
0°-90°	3374.6	30.5
90°-120°	1639.7	14.8
90°-150°	5570.3	50.3
90°-180°	7704.0	69.5
0°-180°	11078.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1637	1630	1610	1624	1619	155
15°	1557	1541	1490	1462	1448	439
25°	1413	1366	1268	1207	1185	650
35°	1218	1142	1012	918	886	762
45°	996	896	741	636	600	769
55°	757	641	481	393	364	676
65°	511	391	258	208	203	507
75°	273	169	118	108	107	288
85°	64	33	28	28	28	73
90°	2	30	81	76	79	11
95°	121	145	149	149	145	135
105°	500	507	512	516	516	528
115°	931	944	940	937	931	920
125°	1353	1374	1368	1360	1358	1209
135°	1751	1776	1781	1779	1772	1353
145°	2125	2142	2155	2158	2149	1328
155°	2430	2437	2444	2456	2448	1119
165°	2644	2641	2641	2658	2646	746
175°	2751	2744	2739	2756	2742	261
180°	2756	2756	2756	2756	2756	

TEST NUMBER: P914590

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1637.0	1637.0	1637.0	1637.0	1637.0
2.5°	1644.4	1637.0	1620.7	1635.6	1632.6
5°	1637.0	1629.7	1610.3	1623.7	1619.3
7.5°	1623.7	1614.9	1594.1	1600.0	1592.5
10°	1605.9	1595.5	1566.0	1561.5	1552.6
12.5°	1583.7	1570.4	1530.3	1521.5	1505.1
15°	1557.0	1540.7	1490.4	1462.3	1447.5
17.5°	1525.9	1502.2	1439.9	1407.4	1383.6
20°	1490.4	1460.7	1386.6	1349.7	1317.0
22.5°	1451.9	1417.8	1331.8	1281.5	1259.3
25°	1413.3	1365.9	1268.1	1207.4	1185.1
27.5°	1367.5	1317.0	1208.9	1139.2	1105.2
30°	1318.6	1262.2	1143.7	1068.2	1028.1
32.5°	1271.1	1202.9	1081.6	992.6	955.5
35°	1217.8	1142.2	1011.9	918.5	885.9
37.5°	1165.9	1084.4	946.7	844.4	807.5
40°	1111.1	1022.3	878.4	773.3	734.8
42.5°	1054.9	960.0	810.4	700.7	663.8
45°	995.6	896.3	740.8	635.5	599.9
47.5°	939.3	834.2	674.1	568.9	536.3
50°	877.1	771.9	608.9	506.6	475.6
52.5°	816.3	705.1	546.7	448.9	420.8
55°	757.0	641.4	481.4	392.6	364.5
57.5°	696.3	577.8	423.7	340.8	317.0
60°	634.1	515.6	362.9	287.5	263.7
62.5°	573.4	454.9	311.1	240.0	228.2
65°	511.1	391.1	257.8	207.5	203.0
67.5°	451.9	331.8	207.5	182.2	177.8
70°	389.7	274.1	171.8	157.0	151.1
72.5°	330.4	220.7	143.7	131.9	128.9
75°	272.6	168.8	118.5	108.1	106.7
77.5°	214.8	119.9	93.4	87.4	84.4
80°	161.4	86.0	71.1	65.2	65.2
82.5°	112.6	57.8	48.9	45.9	45.9
85°	63.7	32.6	28.1	28.1	28.1
87.5°	23.8	11.8	11.8	10.4	10.4
90°	2.5	29.9	81.4	76.4	78.9
92.5°	51.5	69.8	72.2	74.8	74.8
95°	121.3	144.6	148.7	148.7	144.6
97.5°	201.9	223.5	232.7	232.7	232.7
100°	294.9	314.0	320.7	320.7	318.2
102.5°	393.0	407.1	416.3	418.7	416.3
105°	500.2	506.8	511.8	515.9	515.9
107.5°	606.5	616.5	616.5	618.1	606.5
110°	709.6	722.9	722.9	722.9	716.2

TEST NUMBER: P914590

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US927-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	820.9	835.0	832.5	825.8	820.9
115°	930.6	943.8	939.7	937.2	930.6
117.5°	1039.4	1057.6	1046.0	1039.4	1032.8
120°	1149.1	1167.4	1149.1	1149.1	1141.6
122.5°	1248.8	1272.0	1260.4	1253.7	1248.8
125°	1353.4	1374.2	1367.5	1360.1	1357.6
127.5°	1455.6	1481.4	1472.3	1462.3	1455.6
130°	1551.2	1581.1	1576.9	1571.9	1562.8
132.5°	1658.4	1681.6	1683.3	1671.7	1665.0
135°	1750.6	1776.3	1781.3	1778.8	1772.2
137.5°	1853.6	1874.4	1878.5	1876.8	1866.9
140°	1944.2	1964.9	1976.6	1976.6	1967.5
142.5°	2037.3	2058.0	2064.7	2067.1	2058.0
145°	2125.3	2141.9	2155.2	2157.7	2148.6
147.5°	2204.2	2225.0	2235.0	2239.1	2230.0
150°	2285.7	2299.8	2308.9	2316.4	2308.9
152.5°	2357.9	2372.0	2383.7	2392.9	2383.7
155°	2430.3	2436.8	2444.4	2456.0	2448.5
157.5°	2492.5	2497.5	2501.6	2518.3	2506.6
160°	2548.2	2553.2	2555.7	2569.8	2559.9
162.5°	2599.7	2599.7	2602.2	2618.0	2606.4
165°	2643.7	2641.2	2641.2	2657.8	2646.2
167.5°	2683.6	2676.1	2676.1	2692.8	2681.1
170°	2713.5	2706.9	2704.4	2721.0	2706.9
172.5°	2734.3	2727.6	2725.2	2741.8	2727.6
175°	2750.9	2744.3	2739.3	2755.9	2741.8
177.5°	2760.0	2753.4	2748.4	2762.6	2748.4
180°	2755.9	2755.9	2755.9	2755.9	2755.9

TEST NUMBER: P914590

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.13	7.82	8.24	8.92	10.45	3.09	3.78	4.20	4.88	6.41
	3H	8.79	9.41	9.91	10.52	12.06	4.26	4.88	5.38	5.99	7.54
	4H	9.39	9.98	10.52	11.09	12.64	4.70	5.29	5.83	6.40	7.95
	6H	9.80	10.34	10.94	11.46	13.02	5.01	5.55	6.15	6.66	8.22
	8H	9.92	10.43	11.06	11.56	13.12	5.09	5.60	6.23	6.74	8.29
	12H	9.97	10.46	11.12	11.59	13.16	5.13	5.61	6.27	6.74	8.31
4H	2H	7.13	7.71	8.26	8.83	10.38	3.66	4.25	4.80	5.36	6.91
	3H	8.94	9.43	10.08	10.57	12.13	4.99	5.48	6.14	6.62	8.18
	4H	9.62	10.07	10.77	11.20	12.78	5.53	5.98	6.68	7.11	8.69
	6H	10.12	10.51	11.28	11.66	13.23	5.93	6.32	7.09	7.47	9.04
	8H	10.29	10.65	11.44	11.80	13.38	6.06	6.42	7.21	7.56	9.15
	12H	10.38	10.70	11.55	11.86	13.45	6.11	6.44	7.28	7.59	9.19
8H	4H	9.58	9.93	10.73	11.08	12.67	5.80	6.16	6.95	7.30	8.89
	6H	10.13	10.43	11.30	11.61	13.20	6.30	6.60	7.47	7.78	9.37
	8H	10.34	10.60	11.52	11.77	13.37	6.49	6.75	7.67	7.91	9.52
	12H	10.47	10.70	11.65	11.86	13.50	6.59	6.82	7.78	7.98	9.62
12H	4H	9.52	9.85	10.69	11.00	12.59	5.79	6.12	6.96	7.28	8.87
	6H	10.11	10.36	11.28	11.53	13.13	6.35	6.61	7.53	7.77	9.38
	8H	10.32	10.54	11.50	11.70	13.34	6.55	6.77	7.73	7.94	9.58

END OF REPORT