

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920094

Luminaire Tested: DFN2DIP-SQ3F0-070D050US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920094
REPORT IS A COMBINATION OF REPORTS P899886 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-070D050US935-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8932.8 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 102.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920094

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P920094

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		75	75	75		63	63	63
1	100	96	92	89		93	89	86	83		78	75	73		67	65	63		56	55	54
2	92	84	78	73		85	79	74	69		69	65	61		59	56	54		50	48	47
3	84	75	68	62		78	70	64	59		61	56	52		53	49	46		45	42	40
4	77	66	59	53		72	62	56	50		55	49	45		47	43	40		41	38	35
5	71	60	52	46		66	56	49	44		49	44	39		43	39	35		37	34	31
6	66	54	46	40		61	51	43	38		45	39	35		39	34	31		34	30	28
7	61	49	41	35		57	46	39	34		41	35	31		36	31	28		31	27	25
8	57	44	37	32		53	42	35	30		37	32	28		33	28	25		29	25	22
9	53	41	33	28		49	38	32	27		34	29	25		30	26	23		26	23	20
10	49	37	30	26		46	35	29	25		32	26	23		28	24	21		25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2854	2854	2854
5°	2857	2807	2826
10°	2827	2750	2733
15°	2786	2657	2590
20°	2733	2530	2415
25°	2678	2388	2246
30°	2606	2243	2032
35°	2534	2086	1843
40°	2461	1925	1628
45°	2377	1746	1433
50°	2290	1565	1242
55°	2198	1373	1059
60°	2093	1172	870
65°	1971	968	782
70°	1823	777	707
75°	1637	681	641
80°	1368	565	553
85°	928	368	410

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2377 cd/sqm

TEST NUMBER: P920094

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.5	2.6
10°-20°	640.9	7.2
20°-30°	899.8	10.1
30°-40°	980.8	11.0
40°-50°	901.5	10.1
50°-60°	708.0	7.9
60°-70°	460.8	5.2
70°-80°	237.2	2.7
80°-90°	64.4	0.7
90°-100°	84.2	0.9
100°-110°	267.7	3.0
110°-120°	458.1	5.1
120°-130°	602.5	6.7
130°-140°	676.3	7.6
140°-150°	663.1	7.4
150°-160°	556.3	6.2
160°-170°	368.9	4.1
170°-180°	128.9	1.4
0°-30°	1774.1	19.9
0°-40°	2754.9	30.8
0°-60°	4364.3	48.9
0°-90°	5126.8	57.4
90°-120°	810.0	9.1
90°-150°	2751.9	30.8
90°-180°	3806.0	42.6
0°-180°	8932.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2491	2491	2491	2491	2491	
5°	2491	2480	2450	2471	2464	236
15°	2369	2344	2268	2225	2202	668
25°	2151	2078	1930	1837	1803	989
35°	1853	1738	1540	1398	1348	1160
45°	1515	1364	1127	967	913	1170
55°	1152	976	732	597	555	1029
65°	778	595	392	316	309	771
75°	415	257	180	164	162	439
85°	97	50	43	43	43	111
90°	1	15	40	38	39	9
95°	60	72	73	73	72	67
105°	247	250	253	255	255	261
115°	460	466	464	463	460	455
125°	669	679	676	672	671	598
135°	865	878	880	879	876	669
145°	1050	1058	1065	1066	1061	656
155°	1201	1204	1208	1213	1210	553
165°	1306	1305	1305	1313	1307	368
175°	1359	1356	1353	1362	1354	129
180°	1362	1362	1362	1362	1362	

TEST NUMBER: P920094

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2491.0	2491.0	2491.0	2491.0	2491.0
2.5°	2502.1	2491.0	2466.1	2488.8	2484.2
5°	2491.0	2479.7	2450.3	2470.6	2463.9
7.5°	2470.6	2457.2	2425.7	2434.5	2423.3
10°	2443.6	2427.8	2382.8	2375.9	2362.5
12.5°	2409.8	2389.5	2328.6	2315.1	2290.3
15°	2369.2	2344.3	2267.8	2225.0	2202.5
17.5°	2321.9	2285.8	2191.1	2141.5	2105.4
20°	2267.8	2222.6	2110.0	2053.7	2004.0
22.5°	2209.2	2157.3	2026.4	1949.9	1916.2
25°	2150.6	2078.4	1929.6	1837.3	1803.4
27.5°	2080.8	2004.0	1839.4	1733.5	1681.6
30°	2006.4	1920.5	1740.2	1625.4	1564.4
32.5°	1934.1	1830.4	1645.7	1510.4	1453.9
35°	1853.0	1738.0	1539.8	1397.7	1348.0
37.5°	1774.2	1650.0	1440.5	1284.8	1228.6
40°	1690.7	1555.6	1336.7	1176.7	1118.1
42.5°	1605.1	1460.9	1233.1	1066.2	1010.0
45°	1514.9	1363.7	1127.2	967.0	912.9
47.5°	1429.3	1269.3	1025.8	865.6	816.1
50°	1334.5	1174.6	926.5	770.9	723.8
52.5°	1242.0	1072.9	831.8	683.0	640.2
55°	1151.8	976.0	732.5	597.4	554.7
57.5°	1059.5	879.2	644.8	518.5	482.4
60°	964.8	784.5	552.2	437.5	401.3
62.5°	872.4	692.2	473.3	365.2	347.2
65°	777.7	595.0	392.3	315.7	308.8
67.5°	687.6	504.9	315.7	277.2	270.5
70°	592.9	417.1	261.4	238.9	229.8
72.5°	502.7	335.8	218.6	200.7	196.1
75°	414.7	256.8	180.3	164.5	162.4
77.5°	326.9	182.4	142.1	132.9	128.5
80°	245.6	130.8	108.1	99.3	99.3
82.5°	171.3	88.0	74.4	69.8	69.8
85°	96.9	49.5	42.8	42.8	42.8
87.5°	36.1	17.9	17.9	15.8	15.8
90°	1.2	14.8	40.2	37.8	39.0
92.5°	25.5	34.4	35.7	36.9	36.9
95°	59.9	71.5	73.4	73.4	71.5
97.5°	99.7	110.4	114.9	114.9	114.9
100°	145.7	155.2	158.4	158.4	157.2
102.5°	194.2	201.1	205.6	206.9	205.6
105°	247.1	250.4	252.9	254.9	254.9
107.5°	299.6	304.5	304.5	305.4	299.6
110°	350.5	357.1	357.1	357.1	353.8

TEST NUMBER: P920094

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	405.5	412.5	411.3	408.0	405.5
115°	459.7	466.3	464.3	463.0	459.7
117.5°	513.5	522.5	516.8	513.5	510.2
120°	567.7	576.7	567.7	567.7	564.0
122.5°	616.9	628.4	622.7	619.4	616.9
125°	668.7	678.9	675.6	671.9	670.7
127.5°	719.1	731.8	727.4	722.4	719.1
130°	766.4	781.1	779.0	776.6	772.1
132.5°	819.3	830.8	831.6	825.9	822.6
135°	864.9	877.5	880.0	878.8	875.5
137.5°	915.8	926.0	928.1	927.2	922.3
140°	960.4	970.8	976.5	976.5	972.0
142.5°	1006.4	1016.8	1020.0	1021.2	1016.8
145°	1050.0	1058.2	1064.7	1066.0	1061.4
147.5°	1089.0	1099.2	1104.1	1106.2	1101.6
150°	1129.2	1136.2	1140.6	1144.4	1140.6
152.5°	1164.9	1171.9	1177.6	1182.2	1177.6
155°	1200.6	1203.8	1207.5	1213.3	1209.6
157.5°	1231.4	1233.8	1235.9	1244.1	1238.4
160°	1258.9	1261.4	1262.6	1269.5	1264.6
162.5°	1284.4	1284.4	1285.6	1293.4	1287.6
165°	1306.1	1304.8	1304.8	1313.1	1307.3
167.5°	1325.8	1322.1	1322.1	1330.3	1324.6
170°	1340.6	1337.3	1336.1	1344.3	1337.3
172.5°	1350.8	1347.5	1346.3	1354.5	1347.5
175°	1359.1	1355.7	1353.3	1361.5	1354.5
177.5°	1363.6	1360.3	1357.8	1364.8	1357.8
180°	1361.5	1361.5	1361.5	1361.5	1361.5

TEST NUMBER: P920094

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.42	12.31	12.32	13.23	14.39	7.38	8.27	8.28	9.19	10.35
	3H	13.10	13.90	14.01	14.82	16.01	8.57	9.37	9.48	10.29	11.48
	4H	13.71	14.46	14.63	15.39	16.59	9.02	9.77	9.94	10.70	11.90
	6H	14.13	14.82	15.06	15.76	16.97	9.33	10.03	10.27	10.96	12.18
	8H	14.25	14.91	15.20	15.87	17.08	9.42	10.09	10.37	11.04	12.25
	12H	14.32	14.94	15.26	15.89	17.12	9.47	10.10	10.42	11.04	12.27
4H	2H	11.44	12.20	12.37	13.13	14.33	7.98	8.74	8.91	9.66	10.86
	3H	13.27	13.90	14.21	14.86	16.07	9.33	9.96	10.27	10.92	12.13
	4H	13.96	14.54	14.91	15.49	16.73	9.87	10.45	10.83	11.40	12.64
	6H	14.48	14.97	15.44	15.95	17.19	10.29	10.78	11.25	11.76	13.00
	8H	14.65	15.11	15.62	16.08	17.33	10.42	10.88	11.38	11.85	13.10
	12H	14.75	15.16	15.73	16.15	17.41	10.48	10.89	11.46	11.88	13.14
8H	4H	13.94	14.39	14.90	15.37	16.62	10.16	10.62	11.12	11.59	12.84
	6H	14.50	14.88	15.49	15.89	17.14	10.67	11.05	11.66	12.06	13.31
	8H	14.71	15.05	15.71	16.05	17.32	10.86	11.19	11.85	12.19	13.46
	12H	14.85	15.14	15.85	16.14	17.45	10.97	11.27	11.97	12.26	13.58
12H	4H	13.89	14.30	14.87	15.29	16.55	10.16	10.58	11.15	11.56	12.82
	6H	14.47	14.81	15.47	15.81	17.08	10.72	11.05	11.72	12.05	13.32
	8H	14.69	14.99	15.70	15.98	17.30	10.92	11.22	11.93	12.21	13.53

END OF REPORT