

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920111

Luminaire Tested: DFN2DIP-SQ3F0-070D090US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920111
REPORT IS A COMBINATION OF REPORTS P901478 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-070D090US935-RLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12794.4 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 134.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920111

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920111

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	105	105	105	105		95	95	95	95		78	78	78		62	62	62		47	47	47
1	96	92	88	85		87	84	81	78		69	67	65		55	53	52		42	41	40
2	88	81	75	70		80	74	69	64		61	57	54		49	46	44		38	36	35
3	80	71	64	59		73	65	59	54		54	49	46		43	40	38		34	32	30
4	74	63	56	50		67	58	51	46		48	43	39		39	35	33		30	28	26
5	68	56	49	43		61	52	45	40		43	38	34		35	31	28		27	25	23
6	62	51	43	37		57	47	40	35		39	34	30		32	28	25		25	22	20
7	58	46	38	33		52	42	35	31		35	30	26		29	25	22		23	20	18
8	54	42	34	29		49	38	32	27		32	27	24		27	23	20		21	18	16
9	50	38	31	26		45	35	29	24		30	25	21		24	21	18		20	17	15
10	47	35	28	23		43	32	26	22		27	22	19		23	19	16		18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2854	2854	2854
5°	2857	2807	2826
10°	2827	2750	2733
15°	2786	2657	2590
20°	2733	2530	2415
25°	2678	2388	2246
30°	2606	2243	2032
35°	2534	2086	1843
40°	2461	1925	1628
45°	2377	1746	1433
50°	2290	1565	1242
55°	2198	1373	1059
60°	2093	1172	870
65°	1971	968	782
70°	1823	777	707
75°	1637	681	641
80°	1368	565	553
85°	928	368	410

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2377 cd/sqm

TEST NUMBER: P920111

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.5	1.8
10°-20°	640.9	5.0
20°-30°	899.8	7.0
30°-40°	980.8	7.7
40°-50°	901.5	7.0
50°-60°	708.0	5.5
60°-70°	460.8	3.6
70°-80°	237.2	1.9
80°-90°	65.2	0.5
90°-100°	86.2	0.7
100°-110°	321.5	2.5
110°-120°	852.6	6.7
120°-130°	1414.1	11.1
130°-140°	1502.1	11.7
140°-150°	1396.0	10.9
150°-160°	1122.4	8.8
160°-170°	723.2	5.7
170°-180°	248.9	1.9
0°-30°	1774.1	13.9
0°-40°	2754.9	21.5
0°-60°	4364.3	34.1
0°-90°	5127.5	40.1
90°-120°	1260.3	9.9
90°-150°	5572.4	43.6
90°-180°	7667.0	59.9
0°-180°	12794.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2491	2491	2491	2491	2491	
5°	2491	2480	2450	2471	2464	236
15°	2369	2344	2268	2225	2202	668
25°	2151	2078	1930	1837	1803	989
35°	1853	1738	1540	1398	1348	1160
45°	1515	1364	1127	967	913	1170
55°	1152	976	732	597	555	1029
65°	778	595	392	316	309	771
75°	415	257	180	164	162	439
85°	97	50	43	43	43	111
90°	2	23	38	47	51	12
95°	123	60	74	83	81	146
105°	575	632	116	136	144	615
115°	1088	1120	1168	291	155	1071
125°	1538	1563	1599	1612	1618	1372
135°	1904	1934	1951	1970	1966	1471
145°	2208	2206	2239	2252	2242	1381
155°	2432	2415	2437	2449	2434	1121
165°	2562	2551	2557	2570	2557	724
175°	2621	2608	2611	2625	2606	249
180°	2615	2615	2615	2615	2615	

TEST NUMBER: P920111

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2491.0	2491.0	2491.0	2491.0	2491.0
2.5°	2502.1	2491.0	2466.1	2488.8	2484.2
5°	2491.0	2479.7	2450.3	2470.6	2463.9
7.5°	2470.6	2457.2	2425.7	2434.5	2423.3
10°	2443.6	2427.8	2382.8	2375.9	2362.5
12.5°	2409.8	2389.5	2328.6	2315.1	2290.3
15°	2369.2	2344.3	2267.8	2225.0	2202.5
17.5°	2321.9	2285.8	2191.1	2141.5	2105.4
20°	2267.8	2222.6	2110.0	2053.7	2004.0
22.5°	2209.2	2157.3	2026.4	1949.9	1916.2
25°	2150.6	2078.4	1929.6	1837.3	1803.4
27.5°	2080.8	2004.0	1839.4	1733.5	1681.6
30°	2006.4	1920.5	1740.2	1625.4	1564.4
32.5°	1934.1	1830.4	1645.7	1510.4	1453.9
35°	1853.0	1738.0	1539.8	1397.7	1348.0
37.5°	1774.2	1650.0	1440.5	1284.8	1228.6
40°	1690.7	1555.6	1336.7	1176.7	1118.1
42.5°	1605.1	1460.9	1233.1	1066.2	1010.0
45°	1514.9	1363.7	1127.2	967.0	912.9
47.5°	1429.3	1269.3	1025.8	865.6	816.1
50°	1334.5	1174.6	926.5	770.9	723.8
52.5°	1242.0	1072.9	831.8	683.0	640.2
55°	1151.8	976.0	732.5	597.4	554.7
57.5°	1059.5	879.2	644.8	518.5	482.4
60°	964.8	784.5	552.2	437.5	401.3
62.5°	872.4	692.2	473.3	365.2	347.2
65°	777.7	595.0	392.3	315.7	308.8
67.5°	687.6	504.9	315.7	277.2	270.5
70°	592.9	417.1	261.4	238.9	229.8
72.5°	502.7	335.8	218.6	200.7	196.1
75°	414.7	256.8	180.3	164.5	162.4
77.5°	326.9	182.4	142.1	132.9	128.5
80°	245.6	130.8	108.1	99.3	99.3
82.5°	171.3	88.0	74.4	69.8	69.8
85°	96.9	49.5	42.8	42.8	42.8
87.5°	36.1	17.9	17.9	15.8	15.8
90°	1.8	22.7	37.7	47.4	51.0
92.5°	47.4	39.8	45.4	49.2	51.0
95°	123.0	60.4	73.7	83.3	81.4
97.5°	221.4	66.3	96.4	102.2	104.0
100°	335.0	75.8	107.9	123.0	126.7
102.5°	459.8	456.2	111.7	132.3	138.2
105°	575.2	632.1	115.5	136.2	143.8
107.5°	709.6	756.8	119.3	140.0	147.7
110°	838.4	878.0	331.2	142.0	149.5

TEST NUMBER: P920111

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	959.5	993.4	961.3	145.6	151.4
115°	1088.0	1120.2	1167.6	291.4	155.2
117.5°	1199.7	1237.5	1269.8	999.1	503.3
120°	1324.6	1353.0	1387.2	1409.8	1154.3
122.5°	1430.5	1460.9	1498.8	1510.0	1512.1
125°	1538.3	1563.1	1599.0	1612.3	1617.9
127.5°	1636.8	1663.3	1691.9	1710.7	1712.5
130°	1729.6	1760.0	1780.6	1801.5	1799.7
132.5°	1824.2	1848.9	1869.6	1886.7	1884.9
135°	1903.8	1934.1	1950.9	1970.0	1966.3
137.5°	1986.9	2009.6	2028.7	2047.5	2041.9
140°	2068.2	2083.5	2104.2	2121.2	2111.9
142.5°	2136.6	2149.8	2174.3	2189.3	2180.0
145°	2208.5	2206.4	2238.6	2251.9	2242.4
147.5°	2270.7	2265.1	2297.2	2306.7	2299.2
150°	2331.4	2318.2	2348.5	2359.7	2350.3
152.5°	2382.4	2367.3	2395.6	2407.1	2393.8
155°	2431.6	2414.8	2437.4	2448.7	2433.6
157.5°	2471.4	2456.3	2473.4	2486.6	2471.4
160°	2505.5	2494.1	2505.5	2516.8	2503.5
162.5°	2535.6	2524.4	2533.8	2547.1	2530.0
165°	2562.2	2550.9	2556.6	2569.8	2556.6
167.5°	2583.1	2571.6	2577.4	2590.7	2573.6
170°	2600.1	2588.7	2592.5	2605.7	2588.7
172.5°	2611.4	2600.1	2603.9	2617.2	2600.1
175°	2620.8	2607.5	2611.4	2624.6	2605.7
177.5°	2624.6	2611.4	2613.4	2626.6	2609.6
180°	2615.2	2615.2	2615.2	2615.2	2615.2

TEST NUMBER: P920111

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.75	10.51	10.80	11.55	12.96	5.71	6.47	6.76	7.52	8.92
	3H	11.42	12.10	12.48	13.15	14.58	6.89	7.57	7.94	8.62	10.05
	4H	12.02	12.66	13.09	13.72	15.15	7.33	7.97	8.40	9.03	10.46
	6H	12.44	13.03	13.51	14.09	15.53	7.65	8.23	8.72	9.29	10.74
	8H	12.56	13.12	13.64	14.20	15.64	7.73	8.29	8.81	9.37	10.81
	12H	12.62	13.15	13.70	14.22	15.68	7.77	8.30	8.85	9.37	10.83
4H	2H	9.76	10.40	10.83	11.46	12.89	6.30	6.94	7.37	7.99	9.43
	3H	11.58	12.11	12.66	13.19	14.64	7.63	8.17	8.71	9.25	10.70
	4H	12.26	12.75	13.35	13.83	15.29	8.17	8.66	9.26	9.74	11.21
	6H	12.77	13.19	13.86	14.29	15.75	8.58	9.00	9.68	10.10	11.56
	8H	12.94	13.33	14.03	14.42	15.90	8.71	9.10	9.80	10.19	11.66
	12H	13.03	13.38	14.14	14.49	15.97	8.76	9.12	9.87	10.22	11.70
8H	4H	12.22	12.61	13.32	13.70	15.18	8.45	8.84	9.54	9.93	11.40
	6H	12.78	13.10	13.90	14.24	15.71	8.95	9.27	10.07	10.41	11.88
	8H	13.00	13.28	14.12	14.39	15.89	9.14	9.42	10.26	10.53	12.03
	12H	13.13	13.38	14.25	14.48	16.02	9.25	9.50	10.37	10.61	12.14
12H	4H	12.17	12.53	13.28	13.63	15.11	8.45	8.80	9.56	9.90	11.39
	6H	12.76	13.04	13.88	14.15	15.65	9.00	9.28	10.12	10.40	11.89
	8H	12.97	13.22	14.10	14.33	15.86	9.20	9.45	10.33	10.56	12.09