

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914741

Luminaire Tested: DFN2DIP-SQ3F0-100D040US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914741
REPORT IS A COMBINATION OF REPORTS P901393 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D040US927-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10979.6 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 128.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914741
CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US927-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P914741

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	76	71
1	103	98	94	90	97	93	90	86	84	81	78	75	73	71	67	66	64	64	64	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	54	54	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	46	46	46	43
4	78	67	59	52	74	64	56	50	58	52	47	52	47	43	47	43	40	40	40	40	37
5	72	60	51	45	68	57	49	44	52	45	40	47	42	38	42	38	35	35	35	35	32
6	66	54	45	39	63	51	44	38	47	40	35	42	37	33	38	34	31	31	31	31	28
7	61	49	40	35	58	47	39	34	42	36	31	39	33	29	35	31	27	27	27	27	25
8	57	44	36	31	54	42	35	30	39	33	28	35	30	26	32	28	24	24	24	24	22
9	53	41	33	28	50	39	32	27	36	30	25	33	27	24	30	25	22	22	22	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3532	3532	3532
5°	3535	3480	3505
10°	3504	3431	3456
15°	3451	3372	3381
20°	3379	3291	3304
25°	3307	3195	3215
30°	3218	3105	3102
35°	3133	3000	2983
40°	3029	2894	2870
45°	2926	2787	2754
50°	2812	2674	2619
55°	2693	2544	2495
60°	2559	2390	2353
65°	2411	2230	2186
70°	2224	2035	2005
75°	1965	1802	1837
80°	1651	1503	1518
85°	1162	996	994

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2926 cd/sqm



TEST NUMBER: P914741

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.1	2.6
10°-20°	816.3	7.4
20°-30°	1199.6	10.9
30°-40°	1393.3	12.7
40°-50°	1391.5	12.7
50°-60°	1213.4	11.1
60°-70°	897.0	8.2
70°-80°	507.5	4.6
80°-90°	135.8	1.2
90°-100°	35.2	0.3
100°-110°	131.5	1.2
110°-120°	348.6	3.2
120°-130°	578.2	5.3
130°-140°	614.2	5.6
140°-150°	570.9	5.2
150°-160°	458.9	4.2
160°-170°	295.7	2.7
170°-180°	101.8	0.9
0°-30°	2306.0	21.0
0°-40°	3699.3	33.7
0°-60°	6304.2	57.4
0°-90°	7844.5	71.4
90°-120°	515.3	4.7
90°-150°	2278.7	20.8
90°-180°	3135.0	28.6
0°-180°	10979.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3082	3082	3082	3082	3082	
5°	3082	3071	3038	3062	3056	293
15°	2934	2917	2878	2890	2875	826
25°	2656	2632	2582	2587	2582	1222
35°	2291	2262	2214	2196	2181	1431
45°	1864	1844	1799	1767	1755	1439
55°	1411	1393	1358	1322	1307	1262
65°	952	934	904	877	863	941
75°	498	492	477	460	465	531
85°	121	119	116	107	104	135
90°	1	9	15	19	21	10
95°	50	25	30	34	33	60
105°	235	258	47	56	59	251
115°	445	458	477	119	64	438
125°	629	639	654	659	662	561
135°	778	791	798	806	804	601
145°	903	902	915	921	917	565
155°	994	988	997	1001	995	458
165°	1048	1043	1045	1051	1045	296
175°	1072	1066	1068	1073	1066	102
180°	1069	1069	1069	1069	1069	



TEST NUMBER: P914741

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3082.5	3082.5	3082.5	3082.5	3082.5
2.5°	3100.4	3085.5	3052.8	3082.5	3076.8
5°	3082.5	3070.8	3038.1	3061.7	3056.0
7.5°	3061.7	3044.0	3011.3	3035.2	3029.3
10°	3029.3	3008.5	2973.0	2996.6	2987.8
12.5°	2984.6	2967.0	2931.5	2946.3	2940.3
15°	2934.3	2916.7	2878.0	2890.0	2875.2
17.5°	2872.1	2854.5	2815.7	2830.5	2815.7
20°	2803.8	2786.2	2744.7	2753.5	2741.8
22.5°	2735.9	2709.2	2670.4	2670.4	2664.5
25°	2655.7	2632.1	2581.8	2587.4	2581.8
27.5°	2566.7	2545.9	2507.6	2498.8	2484.0
30°	2478.0	2454.1	2409.7	2400.9	2389.0
32.5°	2383.0	2365.5	2317.9	2300.0	2288.1
35°	2291.2	2261.7	2214.1	2196.2	2181.4
37.5°	2187.4	2160.7	2113.2	2092.5	2077.7
40°	2080.8	2056.9	2009.4	1983.1	1971.1
42.5°	1977.0	1953.1	1906.0	1876.1	1858.5
45°	1864.5	1843.7	1799.0	1766.6	1754.8
47.5°	1754.8	1734.0	1686.5	1653.8	1636.2
50°	1639.0	1624.2	1582.7	1541.2	1526.5
52.5°	1526.5	1505.7	1467.3	1434.6	1413.9
55°	1411.0	1393.1	1357.6	1322.0	1307.3
57.5°	1295.3	1280.5	1241.8	1206.3	1194.4
60°	1179.6	1167.9	1126.4	1093.7	1084.9
62.5°	1067.0	1046.2	1016.7	987.1	975.2
65°	951.6	933.7	904.1	877.3	862.6
67.5°	833.1	817.9	791.5	770.8	758.8
70°	723.3	711.3	684.6	663.8	652.2
72.5°	610.7	598.7	584.0	563.2	554.4
75°	497.8	492.2	477.1	459.5	465.4
77.5°	397.2	385.2	379.2	370.4	361.6
80°	296.5	293.4	287.4	278.6	272.7
82.5°	201.6	201.6	198.8	186.8	186.8
85°	121.4	118.6	115.7	106.6	103.8
87.5°	53.5	47.5	41.5	32.7	29.5
90°	0.7	9.3	15.4	19.4	20.8
92.5°	19.4	16.2	18.5	20.1	20.8
95°	50.2	24.7	30.1	34.1	33.3
97.5°	90.5	27.1	39.5	41.8	42.5
100°	137.0	31.0	44.1	50.2	51.8
102.5°	188.0	186.6	45.6	54.1	56.5
105°	235.2	258.5	47.2	55.7	58.8
107.5°	290.2	309.5	48.8	57.3	60.4
110°	342.9	359.0	135.5	58.1	61.1



TEST NUMBER: P914741

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	392.4	406.2	393.1	59.6	61.9
115°	444.9	458.0	477.4	119.1	63.5
117.5°	490.6	506.0	519.3	408.5	205.8
120°	541.7	553.3	567.2	576.5	472.1
122.5°	584.9	597.4	612.9	617.5	618.3
125°	629.1	639.2	653.9	659.3	661.6
127.5°	669.3	680.2	691.8	699.6	700.3
130°	707.3	719.7	728.1	736.6	735.9
132.5°	745.9	756.1	764.5	771.5	770.8
135°	778.5	790.9	797.8	805.6	804.1
137.5°	812.5	821.7	829.6	837.3	835.0
140°	845.7	852.0	860.5	867.4	863.6
142.5°	873.7	879.1	889.1	895.2	891.4
145°	903.1	902.3	915.4	920.8	916.9
147.5°	928.5	926.2	939.4	943.3	940.2
150°	953.3	947.9	960.4	965.0	961.1
152.5°	974.2	968.0	979.6	984.3	978.9
155°	994.3	987.5	996.7	1001.3	995.1
157.5°	1010.6	1004.4	1011.5	1016.8	1010.6
160°	1024.5	1019.9	1024.5	1029.1	1023.7
162.5°	1036.9	1032.3	1036.2	1041.6	1034.6
165°	1047.7	1043.1	1045.4	1050.8	1045.4
167.5°	1056.3	1051.5	1054.0	1059.4	1052.4
170°	1063.3	1058.6	1060.1	1065.6	1058.6
172.5°	1067.9	1063.3	1064.8	1070.2	1063.3
175°	1071.7	1066.3	1067.9	1073.2	1065.6
177.5°	1073.2	1067.9	1068.7	1074.1	1067.1
180°	1069.4	1069.4	1069.4	1069.4	1069.4



TEST NUMBER: P914741
 CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.40	14.49	14.15	15.27	16.19	12.96	14.05	13.71	14.82	15.75
	3H	15.07	16.06	15.84	16.84	17.80	14.58	15.57	15.35	16.35	17.31
	4H	15.67	16.60	16.45	17.39	18.36	15.18	16.10	15.95	16.89	17.86
	6H	16.08	16.93	16.87	17.73	18.72	15.58	16.43	16.37	17.23	18.22
	8H	16.19	17.00	16.99	17.82	18.81	15.69	16.50	16.49	17.32	18.30
	12H	16.24	17.02	17.05	17.83	18.84	15.73	16.51	16.54	17.32	18.33
4H	2H	13.89	14.81	14.67	15.60	16.57	13.53	14.46	14.31	15.25	16.22
	3H	15.77	16.54	16.56	17.37	18.35	15.36	16.13	16.16	16.96	17.94
	4H	16.49	17.19	17.30	18.02	19.03	16.06	16.77	16.87	17.59	18.61
	6H	17.01	17.62	17.84	18.47	19.49	16.58	17.19	17.41	18.04	19.06
	8H	17.16	17.73	17.99	18.58	19.61	16.73	17.30	17.56	18.14	19.17
	12H	17.25	17.76	18.10	18.62	19.66	16.80	17.31	17.65	18.17	19.21
8H	4H	16.70	17.27	17.53	18.11	19.14	16.32	16.89	17.15	17.73	18.77
	6H	17.33	17.81	18.19	18.69	19.72	16.95	17.42	17.81	18.31	19.34
	8H	17.55	17.97	18.42	18.85	19.90	17.16	17.58	18.03	18.46	19.51
	12H	17.69	18.06	18.56	18.93	20.04	17.28	17.65	18.15	18.52	19.63
12H	4H	16.69	17.21	17.54	18.07	19.11	16.33	16.84	17.18	17.70	18.74
	6H	17.36	17.78	18.23	18.66	19.71	16.99	17.41	17.86	18.29	19.34
	8H	17.61	17.98	18.48	18.85	19.96	17.23	17.60	18.10	18.47	19.58