

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914759

Luminaire Tested: DFN2DIP-SQ3F0-100D080US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914759
REPORT IS A COMBINATION OF REPORTS P901466 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D080US927-RLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13007.6 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 158.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914759
CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US927-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P914759

CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	99	95	91	87	91	88	84	82	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38
3	83	74	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	33
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	35	32	29
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19	16
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3751	3751	3751
5°	3755	3689	3714
10°	3715	3615	3592
15°	3662	3493	3404
20°	3592	3326	3174
25°	3520	3139	2952
30°	3425	2948	2670
35°	3331	2742	2423
40°	3235	2530	2140
45°	3124	2295	1883
50°	3010	2058	1632
55°	2890	1805	1391
60°	2751	1540	1144
65°	2590	1272	1028
70°	2396	1022	929
75°	2151	895	842
80°	1797	743	727
85°	1219	484	538

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3124 cd/sqm



TEST NUMBER: P914759

CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.9	2.4
10°-20°	842.4	6.5
20°-30°	1182.6	9.1
30°-40°	1289.2	9.9
40°-50°	1184.9	9.1
50°-60°	930.5	7.2
60°-70°	605.7	4.7
70°-80°	311.8	2.4
80°-90°	83.4	0.6
90°-100°	70.5	0.5
100°-110°	262.9	2.0
110°-120°	697.3	5.4
120°-130°	1156.5	8.9
130°-140°	1228.4	9.4
140°-150°	1141.7	8.8
150°-160°	917.9	7.1
160°-170°	591.5	4.5
170°-180°	203.6	1.6
0°-30°	2331.9	17.9
0°-40°	3621.0	27.8
0°-60°	5736.5	44.1
0°-90°	6737.3	51.8
90°-120°	1030.7	7.9
90°-150°	4557.3	35.0
90°-180°	6270.0	48.2
0°-180°	13007.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3274	3274	3274	3274	3274	
5°	3274	3259	3221	3247	3238	310
15°	3114	3081	2981	2924	2895	878
25°	2827	2732	2536	2415	2370	1300
35°	2436	2284	2024	1837	1772	1524
45°	1991	1792	1482	1271	1200	1538
55°	1514	1283	963	785	729	1353
65°	1022	782	516	415	406	1014
75°	545	338	237	216	213	577
85°	127	65	56	56	56	146
90°	2	18	31	39	42	12
95°	100	49	60	68	66	119
105°	470	517	94	111	118	503
115°	890	916	955	238	127	876
125°	1258	1278	1308	1319	1323	1122
135°	1557	1582	1596	1611	1608	1203
145°	1806	1804	1831	1842	1834	1130
155°	1989	1975	1993	2003	1990	916
165°	2096	2086	2091	2102	2091	592
175°	2143	2133	2136	2146	2131	204
180°	2139	2139	2139	2139	2139	



TEST NUMBER: P914759

CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3274.1	3274.1	3274.1	3274.1	3274.1
2.5°	3288.8	3274.1	3241.4	3271.2	3265.3
5°	3274.1	3259.3	3220.6	3247.4	3238.5
7.5°	3247.4	3229.7	3188.2	3199.9	3185.1
10°	3211.8	3191.1	3132.0	3122.9	3105.3
12.5°	3167.5	3140.8	3060.6	3043.0	3010.3
15°	3114.1	3081.3	2980.7	2924.5	2894.9
17.5°	3051.8	3004.3	2879.9	2814.8	2767.3
20°	2980.7	2921.3	2773.3	2699.4	2634.0
22.5°	2903.7	2835.5	2663.6	2563.0	2518.7
25°	2826.7	2731.8	2536.2	2414.9	2370.3
27.5°	2734.9	2634.0	2417.7	2278.5	2210.3
30°	2637.2	2524.3	2287.3	2136.4	2056.3
32.5°	2542.3	2405.8	2163.1	1985.2	1911.0
35°	2435.6	2284.5	2023.9	1837.1	1771.7
37.5°	2331.9	2168.8	1893.4	1688.8	1614.9
40°	2222.2	2044.6	1757.0	1546.7	1469.7
42.5°	2109.7	1920.1	1620.9	1401.4	1327.5
45°	1991.1	1792.5	1481.6	1271.0	1199.9
47.5°	1878.7	1668.3	1348.3	1137.7	1072.6
50°	1754.1	1543.8	1217.8	1013.2	951.3
52.5°	1632.4	1410.2	1093.4	897.8	841.5
55°	1513.9	1282.9	962.9	785.3	729.0
57.5°	1392.7	1155.6	847.6	681.5	634.1
60°	1268.1	1031.1	725.9	575.0	527.5
62.5°	1146.8	909.7	622.1	480.1	456.5
65°	1022.3	782.1	515.6	414.9	405.8
67.5°	903.8	663.6	414.9	364.3	355.5
70°	779.3	548.3	343.6	314.0	302.1
72.5°	660.8	441.3	287.3	263.7	257.8
75°	545.1	337.6	237.0	216.3	213.4
77.5°	429.8	239.9	186.7	174.8	168.8
80°	322.8	172.0	142.1	130.5	130.5
82.5°	225.1	115.7	97.8	91.8	91.8
85°	127.3	65.0	56.2	56.2	56.2
87.5°	47.5	23.6	23.6	20.8	20.8
90°	1.5	18.5	30.9	38.7	41.7
92.5°	38.7	32.6	37.2	40.2	41.7
95°	100.5	49.4	60.3	68.2	66.5
97.5°	181.0	54.2	78.8	83.7	85.1
100°	274.0	61.9	88.2	100.5	103.6
102.5°	376.0	373.0	91.3	108.2	113.0
105°	470.5	517.0	94.4	111.4	117.6
107.5°	580.4	618.9	97.6	114.5	120.7
110°	685.7	718.0	270.9	116.1	122.2



TEST NUMBER: P914759

CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	784.7	812.5	786.2	119.1	123.9
115°	889.9	916.2	954.9	238.4	127.0
117.5°	981.2	1012.1	1038.5	817.1	411.7
120°	1083.4	1106.5	1134.5	1153.0	944.0
122.5°	1169.9	1194.8	1225.8	1235.0	1236.7
125°	1258.1	1278.3	1307.7	1318.6	1323.2
127.5°	1338.6	1360.3	1383.7	1399.1	1400.6
130°	1414.5	1439.3	1456.3	1473.4	1471.9
132.5°	1491.9	1512.1	1529.1	1543.0	1541.5
135°	1557.0	1581.7	1595.5	1611.2	1608.0
137.5°	1625.0	1643.5	1659.1	1674.6	1670.0
140°	1691.5	1704.0	1720.9	1734.9	1727.1
142.5°	1747.4	1758.2	1778.2	1790.6	1782.8
145°	1806.2	1804.5	1830.8	1841.7	1833.9
147.5°	1857.1	1852.5	1878.7	1886.5	1880.4
150°	1906.7	1895.8	1920.6	1929.8	1922.1
152.5°	1948.4	1936.1	1959.2	1968.6	1957.8
155°	1988.7	1974.9	1993.4	2002.6	1990.4
157.5°	2021.2	2008.9	2022.8	2033.7	2021.2
160°	2049.1	2039.8	2049.1	2058.3	2047.5
162.5°	2073.8	2064.6	2072.3	2083.1	2069.2
165°	2095.5	2086.3	2090.9	2101.7	2090.9
167.5°	2112.5	2103.2	2107.9	2118.8	2104.8
170°	2126.5	2117.1	2120.3	2131.1	2117.1
172.5°	2135.7	2126.5	2129.6	2140.5	2126.5
175°	2143.4	2132.6	2135.7	2146.5	2131.1
177.5°	2146.5	2135.7	2137.3	2148.2	2134.2
180°	2138.8	2138.8	2138.8	2138.8	2138.8



TEST NUMBER: P914759
 CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.87	12.72	12.82	13.68	14.93	7.83	8.68	8.78	9.64	10.89
	3H	13.55	14.30	14.51	15.27	16.54	9.02	9.77	9.98	10.74	12.01
	4H	14.15	14.87	15.13	15.84	17.12	9.46	10.18	10.44	11.15	12.43
	6H	14.57	15.23	15.56	16.21	17.50	9.78	10.44	10.76	11.42	12.71
	8H	14.70	15.32	15.69	16.32	17.61	9.87	10.49	10.86	11.49	12.78
	12H	14.76	15.35	15.75	16.34	17.65	9.91	10.50	10.90	11.49	12.80
4H	2H	11.89	12.61	12.87	13.58	14.86	8.43	9.14	9.41	10.12	11.40
	3H	13.72	14.31	14.71	15.31	16.61	9.77	10.37	10.76	11.37	12.66
	4H	14.41	14.95	15.40	15.94	17.26	10.32	10.86	11.31	11.85	13.17
	6H	14.92	15.38	15.93	16.40	17.72	10.73	11.19	11.74	12.21	13.53
	8H	15.09	15.52	16.10	16.54	17.87	10.85	11.29	11.86	12.30	13.63
	12H	15.18	15.58	16.21	16.60	17.94	10.92	11.31	11.94	12.34	13.67
8H	4H	14.37	14.81	15.38	15.82	17.15	10.59	11.03	11.60	12.04	13.37
	6H	14.93	15.29	15.97	16.35	17.68	11.10	11.46	12.14	12.52	13.85
	8H	15.15	15.46	16.19	16.50	17.85	11.29	11.61	12.33	12.65	13.99
	12H	15.28	15.56	16.33	16.60	17.99	11.41	11.68	12.45	12.72	14.11
12H	4H	14.33	14.72	15.35	15.75	17.08	10.60	10.99	11.63	12.02	13.35
	6H	14.91	15.23	15.95	16.27	17.61	11.15	11.47	12.19	12.51	13.86
	8H	15.13	15.41	16.17	16.44	17.83	11.36	11.64	12.40	12.67	14.06