

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922738

Luminaire Tested: DFN2DIP-SQ3F0-040D110US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922738
REPORT IS A COMBINATION OF REPORTS P899988 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-040D110US940-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11712.6 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 118.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922738

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922738

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	93	89	85	82	82	79	76	73	62	60	58	45	44	43	30	30	29
2	85	78	72	67	75	69	65	61	54	51	48	40	38	36	27	26	25
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	21
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	48	42	37	38	34	30	29	26	23	20	18	16
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	15
7	55	43	36	31	49	39	33	28	31	26	23	24	20	18	16	14	13
8	51	39	32	27	46	36	29	25	28	24	20	21	18	16	15	13	12
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1689	1689	1689
5°	1691	1661	1672
10°	1673	1627	1617
15°	1649	1573	1533
20°	1617	1497	1429
25°	1585	1413	1329
30°	1542	1327	1202
35°	1500	1235	1091
40°	1457	1139	963
45°	1407	1033	848
50°	1355	926	735
55°	1301	812	626
60°	1239	693	515
65°	1166	573	463
70°	1079	460	418
75°	968	403	379
80°	809	334	327
85°	549	218	242

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3119 cd/sqm

TEST NUMBER: P922738

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	1.2
10°-20°	379.3	3.2
20°-30°	532.5	4.5
30°-40°	580.5	5.0
40°-50°	533.5	4.6
50°-60°	419.0	3.6
60°-70°	272.7	2.3
70°-80°	140.4	1.2
80°-90°	44.7	0.4
90°-100°	192.0	1.6
100°-110°	609.9	5.2
110°-120°	1043.8	8.9
120°-130°	1372.7	11.7
130°-140°	1540.8	13.2
140°-150°	1511.0	12.9
150°-160°	1267.5	10.8
160°-170°	840.6	7.2
170°-180°	293.8	2.5
0°-30°	1049.9	9.0
0°-40°	1630.4	13.9
0°-60°	2582.9	22.1
0°-90°	3040.6	26.0
90°-120°	1845.7	15.8
90°-150°	6270.1	53.5
90°-180°	8672.0	74.0
0°-180°	11712.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	3	34	92	86	89	12
95°	136	163	167	167	163	152
105°	563	570	576	581	581	594
115°	1048	1062	1058	1055	1048	1036
125°	1524	1547	1539	1531	1528	1361
135°	1970	2000	2005	2002	1995	1523
145°	2392	2411	2426	2429	2418	1495
155°	2736	2743	2752	2765	2756	1259
165°	2976	2973	2973	2992	2979	840
175°	3097	3089	3083	3102	3086	294
180°	3102	3102	3102	3102	3102	

TEST NUMBER: P922738

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	2.8	33.7	91.7	86.1	88.8
92.5°	58.0	78.6	81.3	84.2	84.2
95°	136.5	162.7	167.4	167.4	162.7
97.5°	227.3	251.6	261.9	261.9	261.9
100°	332.0	353.5	361.0	361.0	358.2
102.5°	442.4	458.2	468.6	471.4	468.6
105°	563.0	570.5	576.1	580.8	580.8
107.5°	682.7	693.9	693.9	695.8	682.7
110°	798.7	813.7	813.7	813.7	806.2

TEST NUMBER: P922738

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	924.0	939.9	937.1	929.6	924.0
115°	1047.5	1062.4	1057.7	1055.0	1047.5
117.5°	1170.0	1190.5	1177.4	1170.0	1162.5
120°	1293.4	1314.0	1293.4	1293.4	1285.0
122.5°	1405.7	1431.8	1418.7	1411.2	1405.7
125°	1523.5	1546.8	1539.4	1531.0	1528.1
127.5°	1638.5	1667.5	1657.2	1646.0	1638.5
130°	1746.1	1779.8	1775.0	1769.4	1759.2
132.5°	1866.7	1892.9	1894.8	1881.7	1874.2
135°	1970.5	1999.5	2005.1	2002.3	1994.8
137.5°	2086.5	2109.9	2114.5	2112.6	2101.5
140°	2188.4	2211.8	2224.9	2224.9	2214.7
142.5°	2293.2	2316.6	2324.1	2326.8	2316.6
145°	2392.3	2411.0	2426.0	2428.8	2418.5
147.5°	2481.2	2504.5	2515.8	2520.4	2510.2
150°	2572.9	2588.7	2599.0	2607.5	2599.0
152.5°	2654.2	2670.0	2683.2	2693.5	2683.2
155°	2735.6	2743.0	2751.5	2764.6	2756.1
157.5°	2805.7	2811.3	2815.9	2834.7	2821.5
160°	2868.4	2874.0	2876.7	2892.7	2881.5
162.5°	2926.3	2926.3	2929.2	2946.9	2933.8
165°	2975.9	2973.1	2973.1	2991.8	2978.7
167.5°	3020.8	3012.4	3012.4	3031.1	3018.0
170°	3054.5	3047.0	3044.2	3062.8	3047.0
172.5°	3077.8	3070.3	3067.6	3086.3	3070.3
175°	3096.6	3089.1	3083.4	3102.2	3086.3
177.5°	3106.8	3099.3	3093.7	3109.7	3093.7
180°	3102.2	3102.2	3102.2	3102.2	3102.2

TEST NUMBER: P922738

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.11	6.78	7.25	7.91	9.49	2.07	2.74	3.21	3.87	5.45
	3H	7.77	8.37	8.92	9.50	11.10	3.24	3.83	4.39	4.97	6.57
	4H	8.37	8.93	9.53	10.07	11.67	3.68	4.24	4.84	5.38	6.98
	6H	8.78	9.30	9.94	10.44	12.05	3.98	4.50	5.15	5.65	7.26
	8H	8.90	9.39	10.07	10.55	12.15	4.07	4.56	5.24	5.72	7.32
	12H	8.95	9.42	10.13	10.57	12.20	4.10	4.57	5.28	5.72	7.35
4H	2H	6.11	6.67	7.27	7.81	9.41	2.64	3.21	3.81	4.35	5.95
	3H	7.91	8.39	9.09	9.55	11.16	3.97	4.44	5.14	5.61	7.22
	4H	8.60	9.03	9.77	10.18	11.81	4.51	4.94	5.68	6.09	7.72
	6H	9.10	9.47	10.28	10.64	12.26	4.91	5.28	6.09	6.46	8.08
	8H	9.27	9.61	10.44	10.78	12.42	5.03	5.38	6.21	6.54	8.18
	12H	9.35	9.67	10.55	10.84	12.48	5.09	5.40	6.28	6.58	8.22
8H	4H	8.55	8.90	9.73	10.06	11.70	4.77	5.12	5.95	6.28	7.92
	6H	9.10	9.39	10.30	10.60	12.23	5.28	5.56	6.47	6.77	8.40
	8H	9.32	9.57	10.52	10.75	12.41	5.46	5.71	6.66	6.90	8.55
	12H	9.45	9.66	10.65	10.85	12.53	5.57	5.79	6.77	6.97	8.66
12H	4H	8.49	8.81	9.69	9.99	11.63	4.77	5.08	5.96	6.26	7.90
	6H	9.08	9.33	10.28	10.51	12.17	5.32	5.57	6.53	6.76	8.41
	8H	9.29	9.51	10.49	10.69	12.38	5.52	5.74	6.73	6.92	8.61

END OF REPORT