

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917265

Luminaire Tested: DFN2DIP-SQ3F0-040D070US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917265
REPORT IS A COMBINATION OF REPORTS P901435 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-040D070US930-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8878.6 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 84.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917265

CATALOG NUMBER: DFN2DIP-SQ3F0-040D070US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917265

CATALOG NUMBER: DFN2DIP-SQ3F0-040D070US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37
2	86	79	73	68	78	72	67	62	58	54	51	46	43	41	34	32	31
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12
10	45	33	26	21	41	31	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1454	1454	1454
5°	1455	1433	1443
10°	1443	1412	1423
15°	1420	1388	1392
20°	1391	1355	1360
25°	1361	1315	1324
30°	1325	1279	1277
35°	1290	1235	1228
40°	1247	1191	1181
45°	1204	1147	1134
50°	1158	1101	1078
55°	1109	1047	1027
60°	1053	984	969
65°	993	918	900
70°	915	838	826
75°	809	742	756
80°	680	619	625
85°	479	410	409

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1320 cd/sqm

TEST NUMBER: P917265

CATALOG NUMBER: DFN2DIP-SQ3F0-040D070US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	1.3
10°-20°	336.0	3.8
20°-30°	493.8	5.6
30°-40°	573.6	6.5
40°-50°	572.9	6.5
50°-60°	499.5	5.6
60°-70°	369.3	4.2
70°-80°	208.9	2.4
80°-90°	58.5	0.7
90°-100°	63.5	0.7
100°-110°	236.8	2.7
110°-120°	627.9	7.1
120°-130°	1041.5	11.7
130°-140°	1106.3	12.5
140°-150°	1028.1	11.6
150°-160°	826.6	9.3
160°-170°	532.6	6.0
170°-180°	183.3	2.1
0°-30°	949.3	10.7
0°-40°	1522.9	17.2
0°-60°	2595.3	29.2
0°-90°	3232.0	36.4
90°-120°	928.2	10.5
90°-150°	4104.1	46.2
90°-180°	5647.0	63.6
0°-180°	8878.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1269	1264	1251	1260	1258	120
15°	1208	1201	1185	1190	1184	340
25°	1093	1084	1063	1065	1063	503
35°	943	931	912	904	898	589
45°	768	759	741	727	722	592
55°	581	574	559	544	538	519
65°	392	384	372	361	355	387
75°	205	203	196	189	192	219
85°	50	49	48	44	43	56
90°	1	17	28	35	38	8
95°	90	44	54	61	60	107
105°	424	466	85	100	106	453
115°	801	825	860	215	114	789
125°	1133	1151	1178	1188	1192	1010
135°	1402	1424	1437	1451	1448	1083
145°	1626	1625	1649	1658	1652	1017
155°	1791	1778	1795	1803	1792	825
165°	1887	1879	1883	1893	1883	533
175°	1930	1920	1923	1933	1919	184
180°	1926	1926	1926	1926	1926	

TEST NUMBER: P917265

CATALOG NUMBER: DFN2DIP-SQ3F0-040D070US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.9	1268.9	1268.9	1268.9	1268.9
2.5°	1276.3	1270.2	1256.8	1268.9	1266.6
5°	1268.9	1264.1	1250.7	1260.4	1258.1
7.5°	1260.4	1253.1	1239.7	1249.5	1247.1
10°	1247.1	1238.5	1223.9	1233.6	1230.0
12.5°	1228.7	1221.4	1206.8	1212.9	1210.4
15°	1207.9	1200.7	1184.8	1189.7	1183.6
17.5°	1182.3	1175.1	1159.2	1165.2	1159.2
20°	1154.2	1147.0	1129.9	1133.5	1128.8
22.5°	1126.3	1115.2	1099.3	1099.3	1096.9
25°	1093.2	1083.5	1062.8	1065.2	1062.8
27.5°	1056.6	1048.1	1032.3	1028.7	1022.6
30°	1020.1	1010.3	992.1	988.4	983.5
32.5°	981.0	973.8	954.2	946.9	941.9
35°	943.2	931.1	911.5	904.2	898.1
37.5°	900.5	889.5	869.9	861.4	855.3
40°	856.6	846.8	827.2	816.4	811.5
42.5°	813.9	804.0	784.6	772.3	765.1
45°	767.5	759.0	740.6	727.3	722.4
47.5°	722.4	713.8	694.3	680.9	673.6
50°	674.7	668.6	651.6	634.5	628.4
52.5°	628.4	619.9	604.1	590.6	582.0
55°	580.9	573.5	558.9	544.2	538.2
57.5°	533.2	527.2	511.2	496.6	491.7
60°	485.6	480.8	463.7	450.3	446.6
62.5°	439.3	430.7	418.6	406.3	401.5
65°	391.8	384.3	372.2	361.2	355.1
67.5°	342.9	336.7	325.9	317.3	312.4
70°	297.7	292.9	281.8	273.3	268.5
72.5°	251.4	246.5	240.4	231.9	228.2
75°	205.0	202.6	196.4	189.1	191.6
77.5°	163.5	158.6	156.1	152.5	148.9
80°	122.1	120.7	118.3	114.7	112.3
82.5°	83.0	83.0	81.9	76.9	76.9
85°	50.0	48.8	47.6	43.9	42.7
87.5°	22.0	19.6	17.1	13.5	12.1
90°	1.3	16.7	27.8	34.9	37.6
92.5°	34.9	29.3	33.4	36.3	37.6
95°	90.5	44.5	54.3	61.4	59.9
97.5°	163.0	48.8	71.0	75.3	76.6
100°	246.8	55.8	79.4	90.5	93.4
102.5°	338.6	336.0	82.3	97.5	101.7
105°	423.7	465.5	85.0	100.3	105.9
107.5°	522.6	557.4	87.9	103.1	108.8
110°	617.5	646.6	243.9	104.6	110.1

TEST NUMBER: P917265

CATALOG NUMBER: DFN2DIP-SQ3F0-040D070US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	706.7	731.6	708.0	107.2	111.5
115°	801.4	825.0	859.9	214.7	114.4
117.5°	883.6	911.4	935.2	735.8	370.7
120°	975.6	996.5	1021.7	1038.4	850.2
122.5°	1053.5	1075.9	1103.9	1112.1	1113.6
125°	1133.0	1151.2	1177.7	1187.5	1191.6
127.5°	1205.5	1225.0	1246.0	1260.0	1261.3
130°	1273.8	1296.2	1311.4	1326.8	1325.5
132.5°	1343.5	1361.7	1377.0	1389.5	1388.2
135°	1402.1	1424.4	1436.9	1450.9	1448.1
137.5°	1463.3	1480.1	1494.1	1508.1	1503.9
140°	1523.2	1534.5	1549.7	1562.3	1555.3
142.5°	1573.5	1583.3	1601.3	1612.4	1605.5
145°	1626.5	1625.1	1648.7	1658.5	1651.5
147.5°	1672.3	1668.3	1691.9	1698.8	1693.4
150°	1717.0	1707.3	1729.7	1737.9	1731.0
152.5°	1754.6	1743.5	1764.4	1772.8	1763.1
155°	1790.9	1778.4	1795.1	1803.4	1792.4
157.5°	1820.2	1809.1	1821.6	1831.4	1820.2
160°	1845.3	1836.9	1845.3	1853.6	1843.8
162.5°	1867.5	1859.2	1866.1	1875.9	1863.4
165°	1887.0	1878.8	1882.8	1892.6	1882.8
167.5°	1902.4	1893.9	1898.3	1908.0	1895.5
170°	1915.0	1906.6	1909.3	1919.1	1906.6
172.5°	1923.3	1915.0	1917.8	1927.5	1915.0
175°	1930.2	1920.4	1923.3	1933.0	1919.1
177.5°	1933.0	1923.3	1924.8	1934.5	1921.9
180°	1926.1	1926.1	1926.1	1926.1	1926.1



TEST NUMBER: P917265

CATALOG NUMBER: DFN2DIP-SQ3F0-040D070US930-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.13	7.88	8.20	8.95	10.40	6.69	7.44	7.75	8.51	9.96
	3H	8.78	9.45	9.85	10.53	12.00	8.29	8.96	9.36	10.04	11.51
	4H	9.36	10.00	10.45	11.08	12.55	8.86	9.50	9.95	10.58	12.06
	6H	9.75	10.34	10.84	11.42	12.91	9.25	9.84	10.34	10.92	12.41
	8H	9.85	10.41	10.95	11.51	12.99	9.35	9.91	10.45	11.00	12.49
	12H	9.89	10.42	11.00	11.51	13.02	9.38	9.91	10.49	11.01	12.51
4H	2H	7.58	8.21	8.67	9.29	10.77	7.22	7.86	8.31	8.94	10.41
	3H	9.43	9.96	10.53	11.06	12.55	9.02	9.55	10.12	10.66	12.15
	4H	10.13	10.62	11.24	11.72	13.23	9.71	10.20	10.81	11.29	12.80
	6H	10.64	11.06	11.75	12.17	13.68	10.20	10.62	11.32	11.74	13.25
	8H	10.78	11.17	11.89	12.28	13.80	10.34	10.74	11.46	11.85	13.37
	12H	10.85	11.20	11.98	12.32	13.85	10.40	10.75	11.53	11.88	13.40
8H	4H	10.32	10.71	11.43	11.82	13.34	9.94	10.33	11.05	11.44	12.96
	6H	10.94	11.26	12.07	12.41	13.93	10.55	10.88	11.69	12.03	13.54
	8H	11.15	11.44	12.29	12.57	14.10	10.76	11.04	11.90	12.18	13.71
	12H	11.28	11.52	12.42	12.65	14.23	10.86	11.11	12.01	12.24	13.82
12H	4H	10.29	10.65	11.42	11.77	13.30	9.93	10.28	11.06	11.40	12.93
	6H	10.96	11.25	12.10	12.38	13.92	10.59	10.87	11.73	12.01	13.54
	8H	11.20	11.44	12.34	12.57	14.15	10.82	11.06	11.96	12.19	13.77