

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917270

Luminaire Tested: DFN2DIP-SQ3F0-040D080US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917270
REPORT IS A COMBINATION OF REPORTS P899934 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-040D080US930-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8544.3 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 92.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917270
CATALOG NUMBER: DFN2DIP-SQ3F0-040D080US930-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P917270

CATALOG NUMBER: DFN2DIP-SQ3F0-040D080US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	40	40	40	33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	36	35	34	28
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29	32	31	29	24
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25	29	27	25	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22	26	24	22	18
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19	23	21	19	16
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17	21	19	17	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15	19	17	15	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	18	16	14	11
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13	17	14	13	10
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1544	1544	1544
5°	1546	1519	1529
10°	1530	1488	1479
15°	1508	1438	1401
20°	1479	1369	1307
25°	1449	1292	1215
30°	1410	1213	1099
35°	1371	1129	997
40°	1332	1042	881
45°	1286	945	775
50°	1239	847	672
55°	1190	743	573
60°	1132	634	471
65°	1067	524	423
70°	986	421	382
75°	886	369	347
80°	740	306	299
85°	502	200	222

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2076 cd/sqm



TEST NUMBER: P917270

CATALOG NUMBER: DFN2DIP-SQ3F0-040D080US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.5
10°-20°	346.8	4.1
20°-30°	486.9	5.7
30°-40°	530.7	6.2
40°-50°	487.8	5.7
50°-60°	383.1	4.5
60°-70°	249.3	2.9
70°-80°	128.4	1.5
80°-90°	38.6	0.5
90°-100°	127.6	1.5
100°-110°	405.6	4.7
110°-120°	694.1	8.1
120°-130°	912.8	10.7
130°-140°	1024.6	12.0
140°-150°	1004.7	11.8
150°-160°	842.8	9.9
160°-170°	558.9	6.5
170°-180°	195.4	2.3
0°-30°	960.0	11.2
0°-40°	1490.7	17.4
0°-60°	2361.5	27.6
0°-90°	2777.9	32.5
90°-120°	1227.3	14.4
90°-150°	4169.4	48.8
90°-180°	5766.0	67.5
0°-180°	8544.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1348	1348	1348	1348	1348	
5°	1348	1342	1326	1337	1333	128
15°	1282	1268	1227	1204	1192	361
25°	1164	1125	1044	994	976	535
35°	1003	940	833	756	729	628
45°	820	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	60
90°	2	22	61	57	59	8
95°	91	108	111	111	108	101
105°	374	379	383	386	386	395
115°	696	706	703	702	696	689
125°	1013	1029	1024	1018	1016	905
135°	1310	1330	1333	1332	1326	1013
145°	1591	1603	1613	1615	1608	994
155°	1819	1824	1830	1838	1833	837
165°	1979	1977	1977	1989	1981	558
175°	2059	2054	2050	2063	2052	196
180°	2063	2063	2063	2063	2063	



TEST NUMBER: P917270

CATALOG NUMBER: DFN2DIP-SQ3F0-040D080US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.9	1347.9	1347.9	1347.9	1347.9
2.5°	1354.0	1347.9	1334.4	1346.7	1344.2
5°	1347.9	1341.7	1325.8	1336.8	1333.3
7.5°	1336.8	1329.6	1312.5	1317.3	1311.2
10°	1322.3	1313.7	1289.3	1285.6	1278.4
12.5°	1304.0	1293.0	1260.0	1252.7	1239.3
15°	1282.0	1268.5	1227.1	1204.0	1191.8
17.5°	1256.4	1236.8	1185.5	1158.8	1139.2
20°	1227.1	1202.6	1141.7	1111.3	1084.3
22.5°	1195.4	1167.3	1096.5	1055.1	1036.9
25°	1163.7	1124.6	1044.1	994.2	975.7
27.5°	1125.9	1084.3	995.3	938.0	909.9
30°	1085.7	1039.2	941.6	879.5	846.5
32.5°	1046.6	990.4	890.5	817.3	786.7
35°	1002.7	940.4	833.2	756.3	729.4
37.5°	960.0	892.8	779.4	695.2	664.8
40°	914.8	841.7	723.3	636.7	605.0
42.5°	868.5	790.4	667.2	576.9	546.5
45°	819.7	737.9	609.9	523.3	494.0
47.5°	773.4	686.8	555.1	468.4	441.6
50°	722.1	635.5	501.3	417.1	391.6
52.5°	672.1	580.6	450.1	369.6	346.4
55°	623.3	528.2	396.4	323.3	300.1
57.5°	573.3	475.7	348.9	280.5	261.1
60°	522.0	424.4	298.8	236.7	217.2
62.5°	472.1	374.5	256.1	197.6	187.9
65°	420.9	322.0	212.2	170.8	167.1
67.5°	372.1	273.2	170.8	150.0	146.3
70°	320.8	225.7	141.5	129.3	124.3
72.5°	272.1	181.7	118.3	108.6	106.2
75°	224.4	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.5
80°	132.9	70.8	58.5	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.2	23.2	23.2
87.5°	19.6	9.7	9.7	8.6	8.6
90°	1.9	22.4	61.0	57.2	59.1
92.5°	38.6	52.3	54.1	55.9	55.9
95°	90.8	108.2	111.3	111.3	108.2
97.5°	151.2	167.3	174.1	174.1	174.1
100°	220.8	235.1	240.0	240.0	238.1
102.5°	294.2	304.8	311.5	313.4	311.5
105°	374.4	379.4	383.1	386.2	386.2
107.5°	454.0	461.5	461.5	462.7	454.0
110°	531.1	541.0	541.0	541.0	536.1



TEST NUMBER: P917270

CATALOG NUMBER: DFN2DIP-SQ3F0-040D080US930-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	614.4	625.0	623.1	618.2	614.4
115°	696.5	706.5	703.4	701.5	696.5
117.5°	778.0	791.7	782.9	778.0	773.0
120°	860.1	873.8	860.1	860.1	854.4
122.5°	934.7	952.1	943.4	938.4	934.7
125°	1013.0	1028.6	1023.6	1018.0	1016.2
127.5°	1089.6	1108.8	1102.0	1094.5	1089.6
130°	1161.1	1183.4	1180.3	1176.6	1169.8
132.5°	1241.3	1258.7	1260.0	1251.2	1246.3
135°	1310.3	1329.6	1333.3	1331.5	1326.5
137.5°	1387.4	1403.0	1406.1	1404.8	1397.3
140°	1455.2	1470.7	1479.4	1479.4	1472.6
142.5°	1524.9	1540.4	1545.4	1547.3	1540.4
145°	1590.8	1603.2	1613.1	1615.0	1608.2
147.5°	1649.8	1665.4	1672.8	1676.0	1669.2
150°	1710.8	1721.3	1728.2	1733.8	1728.2
152.5°	1764.9	1775.5	1784.2	1791.0	1784.2
155°	1819.0	1824.0	1829.6	1838.3	1832.7
157.5°	1865.6	1869.4	1872.5	1884.9	1876.2
160°	1907.3	1911.1	1912.9	1923.5	1916.0
162.5°	1945.9	1945.9	1947.7	1959.6	1950.8
165°	1978.8	1976.9	1976.9	1989.4	1980.7
167.5°	2008.7	2003.1	2003.1	2015.5	2006.8
170°	2031.1	2026.1	2024.2	2036.7	2026.1
172.5°	2046.6	2041.7	2039.8	2052.2	2041.7
175°	2059.0	2054.1	2050.3	2062.8	2052.2
177.5°	2065.9	2060.9	2057.2	2067.8	2057.2
180°	2062.8	2062.8	2062.8	2062.8	2062.8



TEST NUMBER: P917270
 CATALOG NUMBER: DFN2DIP-SQ3F0-040D080US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.72	7.43	7.82	8.52	10.02	2.68	3.39	3.78	4.48	5.98
	3H	8.39	9.02	9.49	10.12	11.64	3.85	4.48	4.96	5.59	7.11
	4H	8.98	9.58	10.10	10.69	12.21	4.29	4.89	5.41	5.99	7.52
	6H	9.40	9.95	10.52	11.05	12.59	4.60	5.15	5.73	6.26	7.80
	8H	9.52	10.04	10.65	11.16	12.69	4.69	5.21	5.82	6.33	7.86
	12H	9.57	10.07	10.71	11.18	12.74	4.72	5.22	5.86	6.33	7.89
4H	2H	6.72	7.32	7.85	8.42	9.95	3.26	3.86	4.38	4.96	6.49
	3H	8.53	9.03	9.67	10.16	11.70	4.59	5.09	5.72	6.22	7.75
	4H	9.22	9.68	10.35	10.79	12.35	5.13	5.59	6.26	6.70	8.26
	6H	9.72	10.11	10.86	11.25	12.80	5.53	5.93	6.67	7.07	8.62
	8H	9.89	10.26	11.03	11.39	12.96	5.66	6.02	6.80	7.15	8.72
	12H	9.98	10.31	11.14	11.45	13.03	5.71	6.04	6.87	7.19	8.76
8H	4H	9.18	9.54	10.32	10.67	12.24	5.40	5.76	6.54	6.89	8.46
	6H	9.73	10.03	10.89	11.21	12.77	5.90	6.20	7.06	7.38	8.94
	8H	9.94	10.21	11.11	11.36	12.94	6.09	6.35	7.25	7.50	9.09
	12H	10.07	10.31	11.24	11.46	13.07	6.19	6.43	7.36	7.58	9.19
12H	4H	9.12	9.45	10.28	10.60	12.17	5.39	5.73	6.55	6.87	8.44
	6H	9.71	9.97	10.87	11.12	12.71	5.95	6.21	7.12	7.37	8.95
	8H	9.92	10.15	11.09	11.30	12.92	6.15	6.38	7.32	7.53	9.15