

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922775

Luminaire Tested: DFN2DIP-SQ3F0-050D110US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922775
REPORT IS A COMBINATION OF REPORTS P901510 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D110US940-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13500.5 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 128.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922775

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922775

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	48	63	55	49	44	43	39	35	33	30	28	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	15
7	55	44	36	31	50	40	33	28	32	27	24	24	21	19	17	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2111	2111	2111
5°	2113	2077	2090
10°	2091	2034	2022
15°	2061	1966	1916
20°	2022	1872	1786
25°	1981	1767	1661
30°	1928	1659	1503
35°	1875	1543	1364
40°	1821	1424	1204
45°	1759	1292	1060
50°	1694	1158	919
55°	1626	1016	783
60°	1548	867	644
65°	1458	716	579
70°	1348	575	523
75°	1211	504	474
80°	1012	418	409
85°	687	273	304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2269 cd/sqm

TEST NUMBER: P922775

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US940-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	1.3
10°-20°	474.1	3.5
20°-30°	665.6	4.9
30°-40°	725.6	5.4
40°-50°	666.9	4.9
50°-60°	523.7	3.9
60°-70°	340.9	2.5
70°-80°	175.5	1.3
80°-90°	50.6	0.4
90°-100°	109.2	0.8
100°-110°	406.9	3.0
110°-120°	1079.2	8.0
120°-130°	1789.9	13.3
130°-140°	1901.3	14.1
140°-150°	1767.1	13.1
150°-160°	1420.7	10.5
160°-170°	915.4	6.8
170°-180°	315.1	2.3
0°-30°	1312.4	9.7
0°-40°	2038.0	15.1
0°-60°	3228.6	23.9
0°-90°	3795.6	28.1
90°-120°	1595.3	11.8
90°-150°	7053.7	52.2
90°-180°	9705.0	71.9
0°-180°	13500.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1843	1843	1843	1843	1843	
5°	1843	1834	1813	1828	1823	175
15°	1753	1734	1678	1646	1629	494
25°	1591	1538	1427	1359	1334	732
35°	1371	1286	1139	1034	997	858
45°	1121	1009	834	715	675	865
55°	852	722	542	442	410	761
65°	575	440	290	234	228	570
75°	307	190	133	122	120	324
85°	72	37	32	32	32	82
90°	2	29	48	60	65	13
95°	156	76	93	106	103	184
105°	728	800	146	172	182	778
115°	1377	1418	1478	369	196	1356
125°	1947	1979	2024	2041	2048	1737
135°	2410	2448	2470	2494	2489	1862
145°	2796	2793	2834	2850	2838	1748
155°	3078	3057	3085	3100	3080	1418
165°	3243	3229	3236	3253	3236	916
175°	3317	3301	3306	3322	3298	316
180°	3310	3310	3310	3310	3310	

TEST NUMBER: P922775

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1842.7	1842.7	1842.7	1842.7	1842.7
2.5°	1851.0	1842.7	1824.4	1841.1	1837.7
5°	1842.7	1834.4	1812.7	1827.6	1822.7
7.5°	1827.6	1817.8	1794.4	1801.0	1792.6
10°	1807.7	1796.0	1762.7	1757.7	1747.7
12.5°	1782.7	1767.7	1722.6	1712.7	1694.2
15°	1752.7	1734.3	1677.7	1646.0	1629.3
17.5°	1717.6	1691.0	1620.9	1584.2	1557.5
20°	1677.7	1644.2	1560.8	1519.3	1482.5
22.5°	1634.3	1595.9	1499.1	1442.5	1417.6
25°	1590.9	1537.5	1427.4	1359.1	1334.0
27.5°	1539.3	1482.5	1360.8	1282.4	1244.0
30°	1484.3	1420.8	1287.4	1202.4	1157.3
32.5°	1430.8	1354.1	1217.5	1117.3	1075.6
35°	1370.8	1285.8	1139.1	1033.9	997.2
37.5°	1312.4	1220.7	1065.7	950.5	908.9
40°	1250.7	1150.8	988.8	870.5	827.2
42.5°	1187.4	1080.7	912.2	788.7	747.2
45°	1120.7	1008.9	833.8	715.3	675.3
47.5°	1057.3	939.0	758.8	640.3	603.7
50°	987.3	868.9	685.5	570.2	535.4
52.5°	918.8	793.7	615.4	505.3	473.7
55°	852.1	722.0	541.9	441.9	410.3
57.5°	783.8	650.4	477.0	383.6	356.9
60°	713.7	580.3	408.5	323.6	296.9
62.5°	645.4	512.0	350.2	270.2	256.9
65°	575.3	440.2	290.2	233.5	228.5
67.5°	508.6	373.5	233.5	205.1	200.1
70°	438.6	308.5	193.4	176.7	170.0
72.5°	371.9	248.4	161.8	148.5	145.1
75°	306.8	190.0	133.4	121.7	120.1
77.5°	241.8	135.0	105.1	98.4	95.0
80°	181.7	96.8	80.0	73.4	73.4
82.5°	126.7	65.1	55.0	51.6	51.6
85°	71.7	36.6	31.7	31.7	31.7
87.5°	26.8	13.3	13.3	11.7	11.7
90°	2.3	28.7	47.8	60.0	64.6
92.5°	60.0	50.4	57.4	62.3	64.6
95°	155.6	76.5	93.3	105.5	103.0
97.5°	280.2	83.9	122.0	129.4	131.7
100°	424.1	95.9	136.5	155.6	160.4
102.5°	581.9	577.4	141.3	167.6	175.0
105°	728.2	800.1	146.2	172.4	182.1
107.5°	898.3	958.0	151.1	177.2	186.9
110°	1061.2	1111.3	419.3	179.8	189.1

TEST NUMBER: P922775

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1214.6	1257.5	1216.8	184.3	191.7
115°	1377.2	1417.9	1478.0	368.9	196.5
117.5°	1518.7	1566.5	1607.4	1264.6	637.1
120°	1676.8	1712.6	1755.9	1784.6	1461.2
122.5°	1810.8	1849.1	1897.2	1911.5	1914.1
125°	1947.3	1978.6	2024.1	2040.9	2048.0
127.5°	2071.9	2105.4	2141.5	2165.4	2167.7
130°	2189.3	2227.8	2253.9	2280.4	2278.1
132.5°	2309.1	2340.4	2366.6	2388.2	2385.9
135°	2409.8	2448.2	2469.5	2493.8	2488.9
137.5°	2515.1	2543.8	2567.9	2591.8	2584.7
140°	2618.1	2637.3	2663.5	2685.1	2673.2
142.5°	2704.5	2721.2	2752.3	2771.3	2759.4
145°	2795.5	2792.9	2833.6	2850.4	2838.5
147.5°	2874.3	2867.2	2907.9	2919.8	2910.5
150°	2951.1	2934.4	2972.7	2987.0	2975.0
152.5°	3015.7	2996.6	3032.4	3047.0	3030.2
155°	3078.0	3056.6	3085.3	3099.6	3080.5
157.5°	3128.3	3109.2	3130.9	3147.6	3128.3
160°	3171.5	3157.0	3171.5	3185.7	3169.0
162.5°	3209.6	3195.4	3207.4	3224.2	3202.6
165°	3243.2	3229.0	3236.1	3252.9	3236.1
167.5°	3269.6	3255.2	3262.6	3279.4	3257.8
170°	3291.3	3276.8	3281.6	3298.4	3276.8
172.5°	3305.5	3291.3	3296.1	3312.9	3291.3
175°	3317.4	3300.7	3305.5	3322.3	3298.4
177.5°	3322.3	3305.5	3308.1	3324.8	3303.3
180°	3310.4	3310.4	3310.4	3310.4	3310.4

TEST NUMBER: P922775

CATALOG NUMBER: DFN2DIP-SQ3F0-050D110US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.21	7.89	8.34	9.01	10.56	3.17	3.85	4.30	4.97	6.52
	3H	8.87	9.48	10.01	10.61	12.18	4.34	4.95	5.48	6.08	7.65
	4H	9.47	10.05	10.62	11.17	12.75	4.78	5.36	5.93	6.48	8.06
	6H	9.88	10.41	11.04	11.54	13.13	5.09	5.62	6.24	6.75	8.34
	8H	10.00	10.50	11.16	11.65	13.23	5.17	5.68	6.33	6.82	8.40
	12H	10.06	10.53	11.22	11.67	13.27	5.21	5.68	6.37	6.82	8.43
4H	2H	7.21	7.79	8.36	8.91	10.49	3.75	4.32	4.90	5.45	7.03
	3H	9.02	9.50	10.18	10.65	12.24	5.08	5.56	6.23	6.71	8.30
	4H	9.70	10.14	10.86	11.28	12.89	5.61	6.05	6.77	7.19	8.80
	6H	10.20	10.58	11.37	11.75	13.34	6.02	6.39	7.18	7.56	9.16
	8H	10.37	10.73	11.54	11.88	13.50	6.14	6.49	7.30	7.65	9.26
	12H	10.46	10.78	11.64	11.94	13.56	6.19	6.51	7.37	7.68	9.30
8H	4H	9.66	10.01	10.82	11.16	12.78	5.88	6.23	7.04	7.39	9.00
	6H	10.21	10.50	11.40	11.70	13.31	6.38	6.67	7.57	7.87	9.48
	8H	10.42	10.68	11.62	11.85	13.48	6.57	6.82	7.76	8.00	9.63
	12H	10.55	10.77	11.75	11.95	13.61	6.67	6.90	7.87	8.07	9.73
12H	4H	9.60	9.92	10.78	11.09	12.71	5.88	6.19	7.06	7.36	8.98
	6H	10.19	10.44	11.38	11.62	13.25	6.43	6.68	7.62	7.86	9.49
	8H	10.40	10.62	11.59	11.79	13.46	6.63	6.85	7.82	8.02	9.69

END OF REPORT