

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922826

Luminaire Tested: DFN2DIP-SQ3F0-070D060US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922826
REPORT IS A COMBINATION OF REPORTS P899904 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-070D060US940-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10040.6 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 110.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922826
CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US940-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P922826

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51	53	52	51	46
2	91	83	77	72	84	78	72	68	67	63	59	56	54	51	47	45	43	47	45	43	39
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	34	31	29	34	31	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	31	28	26	31	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2956	2956	2956
5°	2959	2907	2927
10°	2928	2848	2831
15°	2885	2752	2682
20°	2830	2620	2501
25°	2774	2473	2326
30°	2698	2323	2104
35°	2624	2161	1909
40°	2549	1994	1686
45°	2462	1808	1484
50°	2372	1621	1286
55°	2277	1422	1096
60°	2168	1214	901
65°	2041	1002	810
70°	1888	805	732
75°	1695	705	664
80°	1417	586	572
85°	960	381	424

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2462 cd/sqm



TEST NUMBER: P922826

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.8	2.4
10°-20°	663.7	6.6
20°-30°	931.9	9.3
30°-40°	1015.8	10.1
40°-50°	933.6	9.3
50°-60°	733.2	7.3
60°-70°	477.3	4.8
70°-80°	245.7	2.4
80°-90°	67.5	0.7
90°-100°	104.7	1.0
100°-110°	332.7	3.3
110°-120°	569.3	5.7
120°-130°	748.8	7.5
130°-140°	840.5	8.4
140°-150°	824.2	8.2
150°-160°	691.4	6.9
160°-170°	458.5	4.6
170°-180°	160.3	1.6
0°-30°	1837.4	18.3
0°-40°	2853.2	28.4
0°-60°	4520.0	45.0
0°-90°	5310.5	52.9
90°-120°	1006.7	10.0
90°-150°	3420.1	34.1
90°-180°	4730.0	47.1
0°-180°	10040.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2580	2580	2580	2580	2580	
5°	2580	2568	2538	2559	2552	245
15°	2454	2428	2349	2304	2281	691
25°	2227	2152	1998	1903	1868	1024
35°	1919	1800	1595	1448	1396	1201
45°	1569	1412	1167	1002	946	1212
55°	1193	1011	759	619	574	1066
65°	806	616	406	327	320	799
75°	430	266	187	170	168	454
85°	100	51	44	44	44	115
90°	2	18	50	47	48	10
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P922826

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2579.8	2579.8	2579.8	2579.8	2579.8
2.5°	2591.4	2579.8	2554.0	2577.6	2572.9
5°	2579.8	2568.1	2537.7	2558.8	2551.8
7.5°	2558.8	2544.9	2512.2	2521.3	2509.7
10°	2530.8	2514.4	2467.8	2460.7	2446.8
12.5°	2495.8	2474.8	2411.6	2397.7	2371.9
15°	2453.7	2427.9	2348.7	2304.4	2281.1
17.5°	2404.7	2367.3	2269.2	2217.9	2180.5
20°	2348.7	2301.9	2185.2	2127.0	2075.5
22.5°	2288.0	2234.3	2098.7	2019.5	1984.6
25°	2227.3	2152.5	1998.4	1902.8	1867.7
27.5°	2155.0	2075.5	1905.1	1795.4	1741.6
30°	2078.0	1989.0	1802.2	1683.4	1620.2
32.5°	2003.1	1895.7	1704.4	1564.2	1505.7
35°	1919.1	1800.0	1594.7	1447.6	1396.1
37.5°	1837.5	1708.9	1491.9	1330.6	1272.5
40°	1751.0	1611.1	1384.4	1218.7	1158.0
42.5°	1662.3	1513.0	1277.1	1104.2	1046.1
45°	1569.0	1412.4	1167.4	1001.5	945.5
47.5°	1480.2	1314.6	1062.4	896.4	845.2
50°	1382.2	1216.5	959.6	798.3	749.6
52.5°	1286.3	1111.2	861.5	707.4	663.1
55°	1192.9	1010.8	758.7	618.8	574.4
57.5°	1097.3	910.5	667.8	537.0	499.6
60°	999.3	812.4	571.9	453.1	415.6
62.5°	903.6	716.8	490.2	378.3	359.6
65°	805.5	616.3	406.3	327.0	319.8
67.5°	712.1	522.9	327.0	287.0	280.2
70°	614.0	431.9	270.7	247.4	238.0
72.5°	520.7	347.8	226.4	207.9	203.1
75°	429.5	266.0	186.7	170.4	168.2
77.5°	338.6	189.0	147.1	137.7	133.0
80°	254.4	135.5	112.0	102.8	102.8
82.5°	177.4	91.1	77.0	72.3	72.3
85°	100.3	51.3	44.3	44.3	44.3
87.5°	37.4	18.5	18.5	16.3	16.3
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7



TEST NUMBER: P922826

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1



TEST NUMBER: P922826
 CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.14	12.00	12.08	12.95	14.18	7.10	7.96	8.04	8.91	10.14
	3H	12.82	13.58	13.77	14.54	15.80	8.29	9.05	9.24	10.01	11.27
	4H	13.42	14.15	14.39	15.11	16.38	8.73	9.46	9.70	10.42	11.69
	6H	13.84	14.51	14.82	15.48	16.76	9.05	9.72	10.03	10.69	11.96
	8H	13.97	14.60	14.95	15.59	16.86	9.14	9.77	10.12	10.76	12.03
	12H	14.03	14.63	15.02	15.61	16.91	9.18	9.78	10.17	10.76	12.06
4H	2H	11.16	11.88	12.13	12.85	14.11	7.70	8.42	8.67	9.39	10.65
	3H	12.99	13.59	13.97	14.58	15.86	9.05	9.65	10.02	10.64	11.92
	4H	13.68	14.23	14.67	15.21	16.52	9.59	10.14	10.58	11.12	12.43
	6H	14.19	14.66	15.19	15.67	16.97	10.00	10.47	11.00	11.48	12.79
	8H	14.36	14.80	15.36	15.81	17.12	10.13	10.57	11.13	11.57	12.89
	12H	14.46	14.85	15.48	15.87	17.19	10.19	10.59	11.21	11.61	12.93
8H	4H	13.65	14.09	14.65	15.09	16.40	9.87	10.31	10.87	11.31	12.63
	6H	14.21	14.57	15.23	15.62	16.93	10.38	10.74	11.40	11.79	13.10
	8H	14.42	14.74	15.46	15.77	17.11	10.56	10.88	11.60	11.92	13.25
	12H	14.56	14.84	15.59	15.87	17.24	10.68	10.96	11.72	11.99	13.36
12H	4H	13.60	14.00	14.62	15.02	16.34	9.87	10.27	10.89	11.29	12.61
	6H	14.18	14.50	15.22	15.54	16.87	10.43	10.75	11.46	11.78	13.11
	8H	14.40	14.68	15.44	15.71	17.08	10.63	10.91	11.67	11.94	13.32