

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922848

Luminaire Tested: DFN2DIP-SQ3F0-070D120US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922848
REPORT IS A COMBINATION OF REPORTS P900011 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-070D120US940-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15649.5 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 159.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922848

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922848

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US940-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39
2	87	80	74	68	79	73	67	63	59	56	53	47	45	43	36	35	33
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19
7	56	44	37	31	51	41	34	29	34	29	25	27	24	21	21	19	16
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2783	2783	2783
5°	2786	2742	2762
10°	2761	2703	2723
15°	2719	2657	2664
20°	2662	2594	2603
25°	2606	2518	2533
30°	2536	2447	2444
35°	2469	2364	2351
40°	2387	2280	2261
45°	2305	2196	2170
50°	2216	2107	2064
55°	2122	2005	1966
60°	2016	1884	1854
65°	1900	1758	1722
70°	1752	1604	1580
75°	1548	1420	1448
80°	1301	1185	1196
85°	916	785	783

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3403 cd/sqm

TEST NUMBER: P922848

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.6	1.5
10°-20°	643.2	4.1
20°-30°	945.2	6.0
30°-40°	1097.8	7.0
40°-50°	1096.5	7.0
50°-60°	956.1	6.1
60°-70°	706.8	4.5
70°-80°	399.9	2.6
80°-90°	115.2	0.7
90°-100°	209.4	1.3
100°-110°	665.4	4.3
110°-120°	1138.7	7.3
120°-130°	1497.5	9.6
130°-140°	1680.9	10.7
140°-150°	1648.3	10.5
150°-160°	1382.7	8.8
160°-170°	917.0	5.9
170°-180°	320.5	2.0
0°-30°	1817.0	11.6
0°-40°	2914.9	18.6
0°-60°	4967.4	31.7
0°-90°	6189.2	39.5
90°-120°	2013.4	12.9
90°-150°	6840.1	43.7
90°-180°	9460.0	60.4
0°-180°	15649.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2429	2429	2429	2429	2429	
5°	2429	2420	2394	2412	2408	231
15°	2312	2298	2268	2277	2266	651
25°	2093	2074	2034	2039	2034	963
35°	1805	1782	1745	1730	1719	1127
45°	1469	1453	1418	1392	1383	1134
55°	1112	1098	1070	1042	1030	994
65°	750	736	712	691	680	741
75°	392	388	376	362	367	419
85°	96	94	91	84	82	107
90°	3	37	100	94	97	15
95°	149	178	183	183	178	166
105°	614	622	628	634	634	648
115°	1143	1159	1154	1151	1143	1130
125°	1662	1688	1679	1670	1667	1485
135°	2150	2181	2188	2184	2176	1662
145°	2610	2630	2646	2650	2638	1631
155°	2984	2992	3002	3016	3007	1374
165°	3246	3243	3243	3264	3250	916
175°	3378	3370	3364	3384	3367	321
180°	3384	3384	3384	3384	3384	

TEST NUMBER: P922848

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2428.8	2428.8	2428.8	2428.8	2428.8
2.5°	2442.9	2431.2	2405.5	2428.8	2424.3
5°	2428.8	2419.7	2393.9	2412.4	2408.0
7.5°	2412.4	2398.5	2372.8	2391.7	2386.9
10°	2386.9	2370.5	2342.5	2361.2	2354.2
12.5°	2351.7	2337.9	2309.9	2321.5	2316.8
15°	2312.1	2298.2	2267.7	2277.2	2265.5
17.5°	2263.0	2249.2	2218.7	2230.3	2218.7
20°	2209.2	2195.4	2162.7	2169.6	2160.4
22.5°	2155.7	2134.7	2104.2	2104.2	2099.4
25°	2092.6	2073.9	2034.3	2038.8	2034.3
27.5°	2022.4	2006.1	1975.9	1968.9	1957.2
30°	1952.6	1933.7	1898.8	1891.9	1882.4
32.5°	1877.7	1863.9	1826.4	1812.3	1802.9
35°	1805.4	1782.1	1744.6	1730.5	1718.9
37.5°	1723.6	1702.5	1665.1	1648.8	1637.1
40°	1639.6	1620.8	1583.3	1562.5	1553.1
42.5°	1557.8	1539.0	1501.8	1478.3	1464.4
45°	1469.1	1452.8	1417.6	1392.0	1382.6
47.5°	1382.6	1366.3	1328.8	1303.1	1289.2
50°	1291.5	1279.8	1247.1	1214.4	1202.7
52.5°	1202.7	1186.4	1156.2	1130.4	1114.0
55°	1111.8	1097.7	1069.7	1041.7	1030.0
57.5°	1020.7	1009.0	978.5	950.5	941.1
60°	929.4	920.2	887.6	861.8	854.9
62.5°	840.7	824.4	801.1	777.8	768.4
65°	749.8	735.7	712.4	691.3	679.7
67.5°	656.4	644.5	623.7	607.3	597.9
70°	569.9	560.5	539.4	523.1	513.9
72.5°	481.2	471.8	460.1	443.8	436.8
75°	392.3	387.8	375.9	362.0	366.8
77.5°	313.0	303.5	298.8	291.9	285.0
80°	233.6	231.2	226.5	219.5	214.8
82.5°	158.8	158.8	156.6	147.2	147.2
85°	95.7	93.5	91.2	84.0	81.8
87.5°	42.1	37.5	32.7	25.8	23.3
90°	3.0	36.7	100.0	93.9	96.9
92.5°	63.2	85.7	88.7	91.8	91.8
95°	148.9	177.5	182.6	182.6	177.5
97.5°	247.9	274.5	285.7	285.7	285.7
100°	362.2	385.7	393.8	393.8	390.7
102.5°	482.6	499.9	511.1	514.2	511.1
105°	614.2	622.3	628.5	633.6	633.6
107.5°	744.8	757.1	757.1	759.0	744.8
110°	871.3	887.6	887.6	887.6	879.5

TEST NUMBER: P922848

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1008.0	1025.4	1022.3	1014.1	1008.0
115°	1142.6	1159.0	1153.9	1150.8	1142.6
117.5°	1276.3	1298.8	1284.5	1276.3	1268.2
120°	1411.0	1433.4	1411.0	1411.0	1401.9
122.5°	1533.5	1562.0	1547.7	1539.5	1533.5
125°	1662.0	1687.5	1679.4	1670.2	1667.1
127.5°	1787.5	1819.1	1807.9	1795.6	1787.5
130°	1904.8	1941.5	1936.4	1930.3	1919.0
132.5°	2036.4	2065.0	2067.0	2052.7	2044.6
135°	2149.6	2181.3	2187.5	2184.3	2176.2
137.5°	2276.2	2301.7	2306.8	2304.7	2292.5
140°	2387.4	2412.9	2427.1	2427.1	2415.9
142.5°	2501.7	2527.2	2535.3	2538.3	2527.2
145°	2609.8	2630.2	2646.5	2649.6	2638.4
147.5°	2706.7	2732.2	2744.5	2749.6	2738.4
150°	2806.7	2824.0	2835.3	2844.5	2835.3
152.5°	2895.5	2912.8	2927.1	2938.4	2927.1
155°	2984.2	2992.4	3001.6	3015.9	3006.7
157.5°	3060.8	3066.9	3071.9	3092.4	3078.1
160°	3129.1	3135.3	3138.3	3155.7	3143.4
162.5°	3192.3	3192.3	3195.4	3214.8	3200.5
165°	3246.4	3243.4	3243.4	3263.7	3249.5
167.5°	3295.4	3286.2	3286.2	3306.6	3292.4
170°	3332.1	3323.9	3320.9	3341.3	3323.9
172.5°	3357.6	3349.4	3346.4	3366.8	3349.4
175°	3378.1	3369.9	3363.8	3384.1	3366.8
177.5°	3389.3	3381.1	3374.9	3392.3	3374.9
180°	3384.1	3384.1	3384.1	3384.1	3384.1

TEST NUMBER: P922848

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.74	10.52	10.78	11.56	12.98	9.30	10.07	10.34	11.12	12.53
	3H	11.39	12.08	12.44	13.14	14.57	10.90	11.59	11.95	12.65	14.08
	4H	11.97	12.63	13.03	13.69	15.13	11.48	12.14	12.54	13.19	14.63
	6H	12.36	12.97	13.44	14.03	15.48	11.86	12.47	12.94	13.53	14.98
	8H	12.46	13.04	13.54	14.12	15.56	11.96	12.54	13.04	13.62	15.06
	12H	12.51	13.06	13.59	14.13	15.60	12.00	12.55	13.08	13.62	15.09
4H	2H	10.19	10.85	11.26	11.90	13.34	9.83	10.49	10.90	11.55	12.99
	3H	12.04	12.59	13.12	13.68	15.13	11.63	12.18	12.71	13.27	14.72
	4H	12.75	13.25	13.83	14.33	15.80	12.32	12.83	13.41	13.90	15.38
	6H	13.25	13.69	14.34	14.79	16.25	12.82	13.25	13.91	14.35	15.82
	8H	13.40	13.80	14.49	14.89	16.38	12.96	13.37	14.05	14.46	15.94
	12H	13.46	13.83	14.57	14.94	16.42	13.02	13.38	14.13	14.49	15.97
8H	4H	12.93	13.34	14.02	14.43	15.91	12.56	12.96	13.65	14.05	15.53
	6H	13.55	13.89	14.67	15.02	16.50	13.17	13.50	14.28	14.64	16.12
	8H	13.77	14.06	14.89	15.18	16.68	13.38	13.67	14.50	14.79	16.29
	12H	13.89	14.15	15.02	15.26	16.80	13.48	13.74	14.61	14.85	16.39
12H	4H	12.91	13.28	14.02	14.38	15.87	12.54	12.91	13.65	14.02	15.50
	6H	13.58	13.87	14.70	14.99	16.49	13.21	13.50	14.33	14.62	16.12
	8H	13.82	14.07	14.94	15.18	16.72	13.43	13.69	14.56	14.80	16.34