

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922856

Luminaire Tested: DFN2DIP-SQ3F0-080D050US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922856
REPORT IS A COMBINATION OF REPORTS P899887 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-080D050US940-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11008.2 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 113.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922856

CATALOG NUMBER: DFN2DIP-SQ3F0-080D050US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922856

CATALOG NUMBER: DFN2DIP-SQ3F0-080D050US940-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	61	60	58
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49
3	84	74	67	61	79	70	63	58	62	57	52	55	50	47	48	45	42
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	38	35	32
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28
7	60	48	40	34	56	45	38	32	40	34	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3180	3180	3180
5°	3183	3134	3156
10°	3156	3090	3113
15°	3107	3037	3045
20°	3043	2964	2975
25°	2978	2877	2895
30°	2898	2797	2794
35°	2821	2702	2686
40°	2728	2606	2584
45°	2635	2509	2480
50°	2533	2408	2359
55°	2425	2291	2247
60°	2304	2152	2119
65°	2171	2008	1968
70°	2002	1833	1806
75°	1769	1622	1654
80°	1487	1354	1367
85°	1047	897	895

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2635 cd/sqm

TEST NUMBER: P922856

CATALOG NUMBER: DFN2DIP-SQ3F0-080D050US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	2.4
10°-20°	735.1	6.7
20°-30°	1080.3	9.8
30°-40°	1254.7	11.4
40°-50°	1253.1	11.4
50°-60°	1092.7	9.9
60°-70°	807.7	7.3
70°-80°	457.0	4.2
80°-90°	124.6	1.1
90°-100°	87.3	0.8
100°-110°	277.2	2.5
110°-120°	474.5	4.3
120°-130°	624.0	5.7
130°-140°	700.4	6.4
140°-150°	686.8	6.2
150°-160°	576.1	5.2
160°-170°	382.1	3.5
170°-180°	133.5	1.2
0°-30°	2076.6	18.9
0°-40°	3331.3	30.3
0°-60°	5677.0	51.6
0°-90°	7066.4	64.2
90°-120°	838.9	7.6
90°-150°	2850.1	25.9
90°-180°	3942.0	35.8
0°-180°	11008.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2776	2776	2776	2776	2776	
5°	2776	2765	2736	2757	2752	263
15°	2642	2626	2592	2602	2589	744
25°	2392	2370	2325	2330	2325	1100
35°	2063	2037	1994	1978	1964	1288
45°	1679	1660	1620	1591	1580	1296
55°	1271	1254	1222	1190	1177	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	122
90°	1	15	42	39	40	11
95°	62	74	76	76	74	69
105°	256	259	262	264	264	270
115°	476	483	481	480	476	471
125°	692	703	700	696	695	619
135°	896	909	911	910	907	692
145°	1087	1096	1103	1104	1099	679
155°	1243	1247	1251	1257	1253	572
165°	1353	1351	1351	1360	1354	382
175°	1408	1404	1402	1410	1403	134
180°	1410	1410	1410	1410	1410	

TEST NUMBER: P922856

CATALOG NUMBER: DFN2DIP-SQ3F0-080D050US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2775.7	2775.7	2775.7	2775.7	2775.7
2.5°	2791.9	2778.6	2749.1	2775.7	2770.6
5°	2775.7	2765.3	2735.9	2757.1	2752.0
7.5°	2757.1	2741.2	2711.8	2733.3	2727.9
10°	2727.9	2709.2	2677.2	2698.4	2690.6
12.5°	2687.7	2671.8	2639.8	2653.1	2647.8
15°	2642.4	2626.5	2591.7	2602.5	2589.2
17.5°	2586.3	2570.4	2535.6	2549.0	2535.6
20°	2524.9	2509.0	2471.6	2479.6	2469.1
22.5°	2463.7	2439.6	2404.8	2404.8	2399.4
25°	2391.5	2370.3	2325.0	2330.0	2325.0
27.5°	2311.3	2292.7	2258.1	2250.1	2236.9
30°	2231.5	2209.9	2170.1	2162.1	2151.3
32.5°	2146.0	2130.1	2087.3	2071.2	2060.5
35°	2063.2	2036.7	1993.9	1977.7	1964.4
37.5°	1969.8	1945.7	1903.0	1884.3	1871.0
40°	1873.8	1852.3	1809.5	1785.7	1774.9
42.5°	1780.4	1758.8	1716.4	1689.4	1673.7
45°	1679.0	1660.3	1620.1	1590.9	1580.2
47.5°	1580.2	1561.5	1518.7	1489.2	1473.4
50°	1476.0	1462.7	1425.2	1387.9	1374.6
52.5°	1374.6	1355.8	1321.3	1291.9	1273.2
55°	1270.6	1254.5	1222.5	1190.5	1177.1
57.5°	1166.4	1153.2	1118.3	1086.3	1075.5
60°	1062.2	1051.8	1014.3	984.9	977.0
62.5°	960.8	942.2	915.5	888.9	878.2
65°	856.9	840.8	814.1	790.1	776.8
67.5°	750.1	736.6	712.7	694.1	683.3
70°	651.3	640.5	616.5	597.8	587.3
72.5°	549.9	539.2	525.8	507.2	499.3
75°	448.3	443.2	429.6	413.8	419.1
77.5°	357.7	346.9	341.5	333.6	325.7
80°	267.1	264.2	258.9	250.9	245.5
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.3	106.7	104.2	96.0	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	1.2	15.3	41.6	39.1	40.4
92.5°	26.4	35.7	37.0	38.3	38.3
95°	62.1	74.0	76.1	76.1	74.0
97.5°	103.3	114.3	119.0	119.0	119.0
100°	150.9	160.7	164.1	164.1	162.8
102.5°	201.1	208.3	212.9	214.3	212.9
105°	255.9	259.3	261.9	263.9	263.9
107.5°	310.3	315.4	315.4	316.3	310.3
110°	363.0	369.9	369.9	369.9	366.4



TEST NUMBER: P922856

CATALOG NUMBER: DFN2DIP-SQ3F0-080D050US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	420.0	427.2	426.0	422.6	420.0
115°	476.1	483.0	480.8	479.6	476.1
117.5°	531.8	541.2	535.2	531.8	528.4
120°	587.9	597.3	587.9	587.9	584.1
122.5°	638.9	650.9	644.9	641.5	638.9
125°	692.5	703.1	699.7	695.9	694.6
127.5°	744.8	758.0	753.3	748.1	744.8
130°	793.7	809.0	806.8	804.3	799.6
132.5°	848.6	860.4	861.3	855.3	851.9
135°	895.7	908.8	911.4	910.2	906.8
137.5°	948.4	959.0	961.2	960.3	955.2
140°	994.7	1005.4	1011.3	1011.3	1006.7
142.5°	1042.3	1053.0	1056.4	1057.7	1053.0
145°	1087.4	1095.9	1102.7	1104.0	1099.3
147.5°	1127.8	1138.4	1143.5	1145.7	1140.9
150°	1169.5	1176.7	1181.3	1185.2	1181.3
152.5°	1206.5	1213.7	1219.6	1224.3	1219.6
155°	1243.4	1246.8	1250.6	1256.6	1252.8
157.5°	1275.3	1277.8	1280.0	1288.5	1282.5
160°	1303.8	1306.4	1307.6	1314.8	1309.7
162.5°	1330.2	1330.2	1331.4	1339.5	1333.6
165°	1352.7	1351.4	1351.4	1359.9	1354.0
167.5°	1373.1	1369.2	1369.2	1377.8	1371.8
170°	1388.4	1385.0	1383.8	1392.2	1385.0
172.5°	1399.0	1395.6	1394.4	1402.8	1395.6
175°	1407.6	1404.1	1401.6	1410.1	1402.8
177.5°	1412.2	1408.8	1406.2	1413.5	1406.2
180°	1410.1	1410.1	1410.1	1410.1	1410.1

TEST NUMBER: P922856

CATALOG NUMBER: DFN2DIP-SQ3F0-080D050US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.47	13.48	13.30	14.33	15.38	12.03	13.03	12.85	13.88	14.93
	3H	14.14	15.04	14.98	15.90	16.98	13.65	14.55	14.49	15.41	16.49
	4H	14.73	15.58	15.58	16.45	17.54	14.24	15.09	15.09	15.95	17.04
	6H	15.13	15.92	16.00	16.79	17.90	14.63	15.42	15.50	16.29	17.40
	8H	15.24	15.99	16.12	16.88	17.98	14.74	15.49	15.61	16.38	17.48
	12H	15.29	16.01	16.17	16.89	18.02	14.78	15.50	15.66	16.38	17.51
4H	2H	12.95	13.80	13.81	14.66	15.76	12.59	13.44	13.45	14.31	15.40
	3H	14.82	15.53	15.69	16.43	17.54	14.41	15.12	15.28	16.02	17.13
	4H	15.54	16.19	16.42	17.08	18.21	15.11	15.76	16.00	16.66	17.79
	6H	16.06	16.62	16.95	17.53	18.67	15.62	16.18	16.52	17.10	18.24
	8H	16.21	16.73	17.11	17.64	18.79	15.77	16.29	16.67	17.21	18.35
	12H	16.28	16.76	17.20	17.69	18.84	15.84	16.31	16.76	17.24	18.39
8H	4H	15.74	16.26	16.64	17.18	18.33	15.36	15.89	16.26	16.80	17.95
	6H	16.37	16.81	17.30	17.76	18.91	15.99	16.42	16.92	17.38	18.52
	8H	16.59	16.98	17.53	17.92	19.09	16.20	16.58	17.14	17.53	18.69
	12H	16.73	17.06	17.67	18.00	19.22	16.31	16.65	17.26	17.59	18.81
12H	4H	15.73	16.20	16.65	17.14	18.29	15.36	15.84	16.28	16.77	17.92
	6H	16.40	16.79	17.34	17.73	18.90	16.03	16.41	16.97	17.36	18.52
	8H	16.65	16.99	17.59	17.92	19.14	16.27	16.60	17.21	17.54	18.76