

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922877

Luminaire Tested: DFN2DIP-SQ3F0-080D100US940-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P922877  
REPORT IS A COMBINATION OF REPORTS P901497 AND P898289  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-080D100US940-FLLONL  
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15890.3 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 153.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9952  
Total Harmonic Distortion (THDi): 0.069  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P922877  
CATALOG NUMBER: DFN2DIP-SQ3F0-080D100US940-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P922877

CATALOG NUMBER: DFN2DIP-SQ3F0-080D100US940-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				44
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	37				37
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	31				31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27				27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	31	29	27	23				23
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23	20				20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17				17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	12				12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11				11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3180	3180	3180
5°	3183	3134	3156
10°	3156	3090	3113
15°	3107	3037	3045
20°	3043	2964	2975
25°	2978	2877	2895
30°	2898	2797	2794
35°	2821	2702	2686
40°	2728	2606	2584
45°	2635	2509	2480
50°	2533	2408	2359
55°	2425	2291	2247
60°	2304	2152	2119
65°	2171	2008	1968
70°	2002	1833	1806
75°	1769	1622	1654
80°	1487	1354	1367
85°	1047	897	895

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2635 cd/sqm



TEST NUMBER: P922877

CATALOG NUMBER: DFN2DIP-SQ3F0-080D100US940-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	261.3	1.6
10°-20°	735.1	4.6
20°-30°	1080.3	6.8
30°-40°	1254.7	7.9
40°-50°	1253.1	7.9
50°-60°	1092.7	6.9
60°-70°	807.7	5.1
70°-80°	457.0	2.9
80°-90°	125.9	0.8
90°-100°	99.2	0.6
100°-110°	369.9	2.3
110°-120°	981.1	6.2
120°-130°	1627.2	10.2
130°-140°	1728.5	10.9
140°-150°	1606.5	10.1
150°-160°	1291.5	8.1
160°-170°	832.2	5.2
170°-180°	286.4	1.8
0°-30°	2076.6	13.1
0°-40°	3331.3	21.0
0°-60°	5677.0	35.7
0°-90°	7067.7	44.5
90°-120°	1450.3	9.1
90°-150°	6412.5	40.4
90°-180°	8823.0	55.5
0°-180°	15890.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2776	2776	2776	2776	2776	
5°	2776	2765	2736	2757	2752	263
15°	2642	2626	2592	2602	2589	744
25°	2392	2370	2325	2330	2325	1100
35°	2063	2037	1994	1978	1964	1288
45°	1679	1660	1620	1591	1580	1296
55°	1271	1254	1222	1190	1177	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	122
90°	2	26	43	55	59	15
95°	141	70	85	96	94	168
105°	662	727	133	157	166	707
115°	1252	1289	1344	335	179	1233
125°	1770	1799	1840	1855	1862	1579
135°	2191	2226	2245	2267	2263	1692
145°	2541	2539	2576	2591	2580	1589
155°	2798	2779	2805	2818	2800	1289
165°	2948	2935	2942	2957	2942	833
175°	3016	3001	3005	3020	2999	287
180°	3009	3009	3009	3009	3009	



TEST NUMBER: P922877

CATALOG NUMBER: DFN2DIP-SQ3F0-080D100US940-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2775.7	2775.7	2775.7	2775.7	2775.7
2.5°	2791.9	2778.6	2749.1	2775.7	2770.6
5°	2775.7	2765.3	2735.9	2757.1	2752.0
7.5°	2757.1	2741.2	2711.8	2733.3	2727.9
10°	2727.9	2709.2	2677.2	2698.4	2690.6
12.5°	2687.7	2671.8	2639.8	2653.1	2647.8
15°	2642.4	2626.5	2591.7	2602.5	2589.2
17.5°	2586.3	2570.4	2535.6	2549.0	2535.6
20°	2524.9	2509.0	2471.6	2479.6	2469.1
22.5°	2463.7	2439.6	2404.8	2404.8	2399.4
25°	2391.5	2370.3	2325.0	2330.0	2325.0
27.5°	2311.3	2292.7	2258.1	2250.1	2236.9
30°	2231.5	2209.9	2170.1	2162.1	2151.3
32.5°	2146.0	2130.1	2087.3	2071.2	2060.5
35°	2063.2	2036.7	1993.9	1977.7	1964.4
37.5°	1969.8	1945.7	1903.0	1884.3	1871.0
40°	1873.8	1852.3	1809.5	1785.7	1774.9
42.5°	1780.4	1758.8	1716.4	1689.4	1673.7
45°	1679.0	1660.3	1620.1	1590.9	1580.2
47.5°	1580.2	1561.5	1518.7	1489.2	1473.4
50°	1476.0	1462.7	1425.2	1387.9	1374.6
52.5°	1374.6	1355.8	1321.3	1291.9	1273.2
55°	1270.6	1254.5	1222.5	1190.5	1177.1
57.5°	1166.4	1153.2	1118.3	1086.3	1075.5
60°	1062.2	1051.8	1014.3	984.9	977.0
62.5°	960.8	942.2	915.5	888.9	878.2
65°	856.9	840.8	814.1	790.1	776.8
67.5°	750.1	736.6	712.7	694.1	683.3
70°	651.3	640.5	616.5	597.8	587.3
72.5°	549.9	539.2	525.8	507.2	499.3
75°	448.3	443.2	429.6	413.8	419.1
77.5°	357.7	346.9	341.5	333.6	325.7
80°	267.1	264.2	258.9	250.9	245.5
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.3	106.7	104.2	96.0	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	2.1	26.1	43.4	54.6	58.7
92.5°	54.6	45.7	52.3	56.6	58.7
95°	141.4	69.6	84.8	95.9	93.6
97.5°	254.7	76.2	110.9	117.6	119.8
100°	385.6	87.1	124.1	141.4	145.9
102.5°	529.1	524.9	128.5	152.3	159.0
105°	662.0	727.4	133.0	156.7	165.5
107.5°	816.6	870.9	137.3	161.1	169.9
110°	964.7	1010.3	381.1	163.5	171.9



TEST NUMBER: P922877

CATALOG NUMBER: DFN2DIP-SQ3F0-080D100US940-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1104.1	1143.2	1106.3	167.6	174.3
115°	1252.1	1289.1	1343.6	335.4	178.7
117.5°	1380.5	1424.1	1461.2	1149.7	579.3
120°	1524.4	1556.9	1596.3	1622.4	1328.4
122.5°	1646.2	1681.1	1724.7	1737.7	1740.0
125°	1770.3	1798.8	1840.1	1855.4	1861.8
127.5°	1883.6	1914.1	1946.9	1968.6	1970.7
130°	1990.3	2025.3	2049.1	2073.0	2071.0
132.5°	2099.2	2127.6	2151.4	2171.0	2169.0
135°	2190.8	2225.6	2245.1	2267.0	2262.6
137.5°	2286.4	2312.6	2334.5	2356.3	2349.7
140°	2380.0	2397.6	2421.4	2441.1	2430.2
142.5°	2458.6	2473.9	2502.1	2519.3	2508.6
145°	2541.4	2539.1	2576.1	2591.3	2580.4
147.5°	2613.0	2606.6	2643.5	2654.4	2645.9
150°	2682.8	2667.6	2702.5	2715.4	2704.6
152.5°	2741.5	2724.2	2756.8	2769.9	2754.7
155°	2798.2	2778.7	2804.9	2817.8	2800.5
157.5°	2843.9	2826.6	2846.3	2861.5	2843.9
160°	2883.3	2870.1	2883.3	2896.2	2880.9
162.5°	2917.9	2904.9	2915.8	2931.1	2911.4
165°	2948.4	2935.4	2941.9	2957.2	2941.9
167.5°	2972.4	2959.2	2966.0	2981.3	2961.5
170°	2992.0	2978.9	2983.3	2998.6	2978.9
172.5°	3005.0	2992.0	2996.5	3011.8	2992.0
175°	3015.9	3000.6	3005.0	3020.3	2998.6
177.5°	3020.3	3005.0	3007.4	3022.6	3002.9
180°	3009.4	3009.4	3009.4	3009.4	3009.4



TEST NUMBER: P922877  
 CATALOG NUMBER: DFN2DIP-SQ3F0-080D100US940-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.73	11.54	11.73	12.55	13.90	10.28	11.09	11.28	12.11	13.46
	3H	12.38	13.11	13.39	14.13	15.50	11.89	12.62	12.90	13.64	15.01
	4H	12.96	13.65	13.99	14.68	16.05	12.47	13.16	13.49	14.18	15.56
	6H	13.35	13.99	14.39	15.02	16.41	12.85	13.49	13.89	14.52	15.91
	8H	13.46	14.06	14.50	15.11	16.49	12.95	13.56	14.00	14.61	15.99
	12H	13.50	14.08	14.55	15.12	16.53	12.99	13.57	14.04	14.61	16.02
4H	2H	11.18	11.87	12.21	12.89	14.27	10.82	11.51	11.85	12.54	13.91
	3H	13.03	13.61	14.07	14.66	16.05	12.62	13.20	13.67	14.26	15.64
	4H	13.74	14.27	14.79	15.31	16.73	13.32	13.85	14.36	14.89	16.30
	6H	14.25	14.70	15.31	15.77	17.18	13.82	14.27	14.87	15.34	16.75
	8H	14.40	14.82	15.45	15.88	17.30	13.96	14.38	15.02	15.44	16.87
	12H	14.46	14.85	15.54	15.92	17.35	14.01	14.40	15.09	15.47	16.90
8H	4H	13.93	14.35	14.99	15.42	16.84	13.55	13.98	14.61	15.04	16.46
	6H	14.55	14.90	15.63	16.01	17.43	14.17	14.52	15.25	15.62	17.04
	8H	14.77	15.08	15.86	16.16	17.60	14.38	14.68	15.47	15.77	17.21
	12H	14.90	15.17	15.99	16.25	17.73	14.48	14.76	15.58	15.84	17.32
12H	4H	13.91	14.30	14.99	15.37	16.80	13.54	13.93	14.62	15.00	16.43
	6H	14.58	14.89	15.67	15.98	17.41	14.21	14.52	15.30	15.60	17.04
	8H	14.82	15.09	15.91	16.17	17.65	14.44	14.71	15.53	15.79	17.27