

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917371

Luminaire Tested: DFN2DIP-SQ3F0-070D060US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917371
REPORT IS A COMBINATION OF REPORTS P901424 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-070D060US930-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9693.9 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 110.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917371

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917371

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	50
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	50	49	48	48	48	43
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	41	41	41	37
3	82	73	66	60	76	68	62	57	58	53	50	49	45	43	40	38	36	36	36	32
4	76	65	57	52	70	60	54	49	52	47	43	44	40	37	36	34	31	31	31	28
5	70	58	50	45	64	54	47	42	47	41	37	40	35	32	33	30	28	28	28	24
6	64	52	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	25	25	22
7	59	47	40	34	55	44	37	32	38	33	29	33	29	25	28	24	22	22	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	20	20	18
9	52	40	32	27	48	37	30	26	32	27	23	28	24	21	24	20	18	18	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2703	2703	2703
5°	2705	2658	2676
10°	2677	2604	2588
15°	2638	2516	2453
20°	2588	2396	2287
25°	2536	2261	2126
30°	2467	2124	1924
35°	2400	1976	1746
40°	2331	1823	1541
45°	2251	1653	1357
50°	2168	1482	1176
55°	2082	1300	1002
60°	1982	1110	824
65°	1866	916	741
70°	1726	736	669
75°	1550	645	607
80°	1295	536	523
85°	878	349	388

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2251 cd/sqm

TEST NUMBER: P917371

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	2.3
10°-20°	606.9	6.3
20°-30°	852.0	8.8
30°-40°	928.8	9.6
40°-50°	853.6	8.8
50°-60°	670.4	6.9
60°-70°	436.4	4.5
70°-80°	224.6	2.3
80°-90°	60.2	0.6
90°-100°	54.4	0.6
100°-110°	202.9	2.1
110°-120°	538.2	5.6
120°-130°	892.7	9.2
130°-140°	948.2	9.8
140°-150°	881.3	9.1
150°-160°	708.5	7.3
160°-170°	456.5	4.7
170°-180°	157.1	1.6
0°-30°	1679.9	17.3
0°-40°	2608.7	26.9
0°-60°	4132.7	42.6
0°-90°	4853.9	50.1
90°-120°	795.6	8.2
90°-150°	3517.8	36.3
90°-180°	4840.0	49.9
0°-180°	9693.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2359	2359	2359	2359	2359	
5°	2359	2348	2320	2340	2333	224
15°	2244	2220	2147	2107	2086	632
25°	2036	1968	1827	1740	1708	937
35°	1755	1646	1458	1324	1276	1098
45°	1434	1291	1067	916	864	1108
55°	1091	924	694	566	525	975
65°	736	564	371	299	292	730
75°	393	243	171	156	154	415
85°	92	47	40	40	40	105
90°	1	14	24	30	32	9
95°	78	38	47	53	51	92
105°	363	399	73	86	91	388
115°	687	707	737	184	98	676
125°	971	987	1009	1018	1021	866
135°	1202	1221	1232	1244	1241	928
145°	1394	1393	1413	1422	1416	872
155°	1535	1524	1539	1546	1536	707
165°	1618	1610	1614	1622	1614	457
175°	1654	1646	1648	1657	1645	157
180°	1651	1651	1651	1651	1651	

TEST NUMBER: P917371

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2358.7	2358.7	2358.7	2358.7	2358.7
2.5°	2369.3	2358.7	2335.2	2356.7	2352.4
5°	2358.7	2348.1	2320.3	2339.5	2333.1
7.5°	2339.5	2326.8	2296.9	2305.3	2294.7
10°	2313.9	2299.0	2256.3	2249.8	2237.1
12.5°	2281.9	2262.7	2205.0	2192.3	2168.7
15°	2243.5	2219.9	2147.4	2106.9	2085.6
17.5°	2198.6	2164.5	2074.8	2027.8	1993.6
20°	2147.4	2104.6	1998.0	1944.7	1897.6
22.5°	2092.0	2042.8	1918.9	1846.4	1814.5
25°	2036.5	1968.0	1827.2	1739.8	1707.6
27.5°	1970.3	1897.6	1741.8	1641.5	1592.4
30°	1899.9	1818.6	1647.8	1539.1	1481.4
32.5°	1831.5	1733.2	1558.4	1430.2	1376.7
35°	1754.7	1645.8	1458.1	1323.6	1276.4
37.5°	1680.0	1562.4	1364.1	1216.6	1163.4
40°	1600.9	1473.0	1265.8	1114.3	1058.7
42.5°	1519.9	1383.3	1167.7	1009.6	956.4
45°	1434.5	1291.4	1067.4	915.7	864.5
47.5°	1353.4	1201.9	971.3	819.6	772.7
50°	1263.7	1112.2	877.3	729.9	685.3
52.5°	1176.1	1015.9	787.7	646.8	606.3
55°	1090.7	924.2	693.7	565.7	525.2
57.5°	1003.3	832.5	610.6	491.0	456.8
60°	913.6	742.8	522.9	414.3	380.0
62.5°	826.1	655.4	448.2	345.8	328.8
65°	736.5	563.5	371.4	299.0	292.4
67.5°	651.1	478.1	299.0	262.4	256.2
70°	561.4	394.9	247.5	226.2	217.6
72.5°	476.1	318.0	207.0	190.0	185.7
75°	392.7	243.2	170.7	155.8	153.8
77.5°	309.6	172.8	134.5	125.9	121.6
80°	232.6	123.8	102.4	94.0	94.0
82.5°	162.2	83.3	70.4	66.1	66.1
85°	91.7	46.9	40.5	40.5	40.5
87.5°	34.2	17.0	17.0	14.9	14.9
90°	1.1	14.3	23.8	29.9	32.2
92.5°	29.9	25.1	28.6	31.1	32.2
95°	77.6	38.2	46.6	52.7	51.4
97.5°	139.7	41.8	60.8	64.6	65.7
100°	211.5	47.8	68.1	77.6	80.0
102.5°	290.2	288.0	70.5	83.6	87.2
105°	363.1	399.0	72.9	85.9	90.8
107.5°	448.0	477.8	75.3	88.4	93.2
110°	529.3	554.2	209.1	89.7	94.3

TEST NUMBER: P917371

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	605.7	627.1	606.8	91.9	95.6
115°	686.9	707.2	737.1	184.0	98.0
117.5°	757.3	781.2	801.6	630.7	317.7
120°	836.3	854.1	875.7	890.0	728.7
122.5°	903.0	922.2	946.2	953.2	954.6
125°	971.2	986.8	1009.4	1017.8	1021.3
127.5°	1033.3	1050.0	1068.0	1079.9	1081.1
130°	1091.8	1111.0	1124.1	1137.3	1136.1
132.5°	1151.6	1167.2	1180.2	1191.0	1189.8
135°	1201.8	1221.0	1231.6	1243.7	1241.2
137.5°	1254.3	1268.6	1280.7	1292.6	1289.1
140°	1305.6	1315.3	1328.4	1339.1	1333.2
142.5°	1348.7	1357.1	1372.6	1382.1	1376.1
145°	1394.2	1392.9	1413.2	1421.6	1415.6
147.5°	1433.5	1429.9	1450.2	1456.1	1451.5
150°	1471.8	1463.4	1482.5	1489.6	1483.7
152.5°	1504.0	1494.4	1512.3	1519.6	1511.2
155°	1535.0	1524.4	1538.7	1545.8	1536.3
157.5°	1560.2	1550.6	1561.4	1569.8	1560.2
160°	1581.7	1574.4	1581.7	1588.8	1580.5
162.5°	1600.7	1593.6	1599.5	1607.9	1597.2
165°	1617.5	1610.4	1613.9	1622.3	1613.9
167.5°	1630.6	1623.4	1627.1	1635.5	1624.6
170°	1641.4	1634.2	1636.6	1644.9	1634.2
172.5°	1648.5	1641.4	1643.8	1652.2	1641.4
175°	1654.5	1646.1	1648.5	1656.8	1644.9
177.5°	1656.8	1648.5	1649.8	1658.2	1647.4
180°	1650.9	1650.9	1650.9	1650.9	1650.9

TEST NUMBER: P917371

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.57	11.40	11.54	12.38	13.65	6.53	7.37	7.50	8.34	9.61
	3H	12.25	12.99	13.22	13.97	15.27	7.72	8.46	8.69	9.44	10.74
	4H	12.85	13.55	13.84	14.54	15.85	8.16	8.87	9.15	9.85	11.16
	6H	13.27	13.92	14.27	14.91	16.22	8.48	9.12	9.48	10.12	11.43
	8H	13.40	14.01	14.40	15.02	16.33	8.57	9.18	9.57	10.19	11.50
	12H	13.46	14.04	14.46	15.04	16.38	8.61	9.19	9.62	10.19	11.53
4H	2H	10.59	11.29	11.58	12.28	13.58	7.13	7.83	8.12	8.82	10.12
	3H	12.41	13.00	13.42	14.01	15.33	8.47	9.05	9.47	10.07	11.39
	4H	13.10	13.64	14.11	14.64	15.99	9.01	9.55	10.02	10.55	11.90
	6H	13.61	14.07	14.64	15.10	16.44	9.43	9.88	10.45	10.92	12.25
	8H	13.79	14.21	14.81	15.24	16.59	9.55	9.98	10.57	11.00	12.36
	12H	13.88	14.26	14.92	15.30	16.66	9.61	10.00	10.65	11.04	12.39
8H	4H	13.07	13.50	14.09	14.52	15.87	9.29	9.72	10.31	10.74	12.10
	6H	13.63	13.98	14.68	15.05	16.40	9.80	10.15	10.85	11.22	12.57
	8H	13.84	14.15	14.90	15.21	16.57	9.99	10.30	11.04	11.35	12.72
	12H	13.98	14.25	15.04	15.30	16.71	10.10	10.37	11.16	11.42	12.83
12H	4H	13.02	13.41	14.06	14.45	15.80	9.29	9.68	10.34	10.72	12.08
	6H	13.60	13.92	14.66	14.97	16.34	9.85	10.16	10.90	11.21	12.58
	8H	13.82	14.09	14.88	15.14	16.55	10.05	10.33	11.11	11.37	12.79