

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922958

Luminaire Tested: DFN2DIP-SQ3F0-100D120US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922958
REPORT IS A COMBINATION OF REPORTS P900018 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D120US940-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17049.4 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 192.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922958

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922958

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	33
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4223	4223	4223
5°	4227	4153	4181
10°	4182	4069	4044
15°	4122	3931	3832
20°	4043	3744	3573
25°	3962	3533	3323
30°	3855	3318	3006
35°	3749	3087	2727
40°	3642	2848	2408
45°	3517	2583	2120
50°	3388	2316	1837
55°	3253	2031	1566
60°	3096	1734	1288
65°	2916	1432	1157
70°	2697	1150	1046
75°	2422	1008	948
80°	2023	837	818
85°	1372	545	606

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3517 cd/sqm

TEST NUMBER: P922958

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.4	2.0
10°-20°	948.2	5.6
20°-30°	1331.2	7.8
30°-40°	1451.1	8.5
40°-50°	1333.8	7.8
50°-60°	1047.4	6.1
60°-70°	681.8	4.0
70°-80°	351.0	2.1
80°-90°	99.2	0.6
90°-100°	209.4	1.2
100°-110°	665.4	3.9
110°-120°	1138.7	6.7
120°-130°	1497.5	8.8
130°-140°	1680.9	9.9
140°-150°	1648.3	9.7
150°-160°	1382.7	8.1
160°-170°	917.0	5.4
170°-180°	320.5	1.9
0°-30°	2624.8	15.4
0°-40°	4076.0	23.9
0°-60°	6457.2	37.9
0°-90°	7589.1	44.5
90°-120°	2013.4	11.8
90°-150°	6840.1	40.1
90°-180°	9460.0	55.5
0°-180°	17049.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3685	3669	3625	3655	3645	349
15°	3505	3468	3355	3292	3259	988
25°	3182	3075	2855	2718	2668	1463
35°	2742	2572	2278	2068	1994	1716
45°	2241	2018	1668	1431	1351	1731
55°	1704	1444	1084	884	821	1523
65°	1151	880	580	467	457	1141
75°	614	380	267	243	240	649
85°	143	73	63	63	63	164
90°	3	37	100	94	97	17
95°	149	178	183	183	178	166
105°	614	622	628	634	634	648
115°	1143	1159	1154	1151	1143	1130
125°	1662	1688	1679	1670	1667	1485
135°	2150	2181	2188	2184	2176	1662
145°	2610	2630	2646	2650	2638	1631
155°	2984	2992	3002	3016	3007	1374
165°	3246	3243	3243	3264	3250	916
175°	3378	3370	3364	3384	3367	321
180°	3384	3384	3384	3384	3384	

TEST NUMBER: P922958

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3685.4	3685.4	3685.4	3685.4	3685.4
2.5°	3702.0	3685.4	3648.6	3682.2	3675.5
5°	3685.4	3668.8	3625.2	3655.4	3645.4
7.5°	3655.4	3635.5	3588.8	3601.9	3585.3
10°	3615.4	3592.0	3525.5	3515.2	3495.4
12.5°	3565.5	3535.4	3445.1	3425.3	3388.5
15°	3505.3	3468.5	3355.2	3291.9	3258.7
17.5°	3435.2	3381.8	3241.7	3168.4	3115.0
20°	3355.2	3288.4	3121.7	3038.6	2964.9
22.5°	3268.6	3191.8	2998.2	2885.0	2835.1
25°	3181.9	3075.1	2854.9	2718.3	2668.1
27.5°	3078.5	2964.9	2721.5	2564.7	2488.0
30°	2968.5	2841.4	2574.6	2404.9	2314.6
32.5°	2861.7	2708.0	2434.9	2234.6	2151.1
35°	2741.7	2571.5	2278.1	2068.0	1994.3
37.5°	2624.9	2441.2	2131.3	1900.9	1817.8
40°	2501.4	2301.5	1977.7	1741.0	1654.3
42.5°	2374.7	2161.3	1824.5	1577.5	1494.3
45°	2241.3	2017.7	1667.8	1430.7	1350.7
47.5°	2114.7	1877.9	1517.7	1280.6	1207.4
50°	1974.5	1737.8	1370.8	1140.5	1070.8
52.5°	1837.5	1587.4	1230.7	1010.6	947.3
55°	1704.1	1444.1	1083.9	884.0	820.6
57.5°	1567.6	1300.7	954.0	767.1	713.7
60°	1427.4	1160.7	817.1	647.2	593.8
62.5°	1290.8	1024.0	700.3	540.4	513.8
65°	1150.8	880.4	580.3	467.1	456.8
67.5°	1017.4	747.0	467.1	410.1	400.2
70°	877.2	617.2	386.7	353.5	340.1
72.5°	743.8	496.8	323.4	296.9	290.2
75°	613.6	380.0	266.8	243.4	240.2
77.5°	483.8	270.0	210.2	196.7	190.0
80°	363.4	193.6	160.0	146.9	146.9
82.5°	253.3	130.2	110.0	103.3	103.3
85°	143.3	73.2	63.3	63.3	63.3
87.5°	53.4	26.6	26.6	23.4	23.4
90°	3.0	36.7	100.0	93.9	96.9
92.5°	63.2	85.7	88.7	91.8	91.8
95°	148.9	177.5	182.6	182.6	177.5
97.5°	247.9	274.5	285.7	285.7	285.7
100°	362.2	385.7	393.8	393.8	390.7
102.5°	482.6	499.9	511.1	514.2	511.1
105°	614.2	622.3	628.5	633.6	633.6
107.5°	744.8	757.1	757.1	759.0	744.8
110°	871.3	887.6	887.6	887.6	879.5

TEST NUMBER: P922958

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1008.0	1025.4	1022.3	1014.1	1008.0
115°	1142.6	1159.0	1153.9	1150.8	1142.6
117.5°	1276.3	1298.8	1284.5	1276.3	1268.2
120°	1411.0	1433.4	1411.0	1411.0	1401.9
122.5°	1533.5	1562.0	1547.7	1539.5	1533.5
125°	1662.0	1687.5	1679.4	1670.2	1667.1
127.5°	1787.5	1819.1	1807.9	1795.6	1787.5
130°	1904.8	1941.5	1936.4	1930.3	1919.0
132.5°	2036.4	2065.0	2067.0	2052.7	2044.6
135°	2149.6	2181.3	2187.5	2184.3	2176.2
137.5°	2276.2	2301.7	2306.8	2304.7	2292.5
140°	2387.4	2412.9	2427.1	2427.1	2415.9
142.5°	2501.7	2527.2	2535.3	2538.3	2527.2
145°	2609.8	2630.2	2646.5	2649.6	2638.4
147.5°	2706.7	2732.2	2744.5	2749.6	2738.4
150°	2806.7	2824.0	2835.3	2844.5	2835.3
152.5°	2895.5	2912.8	2927.1	2938.4	2927.1
155°	2984.2	2992.4	3001.6	3015.9	3006.7
157.5°	3060.8	3066.9	3071.9	3092.4	3078.1
160°	3129.1	3135.3	3138.3	3155.7	3143.4
162.5°	3192.3	3192.3	3195.4	3214.8	3200.5
165°	3246.4	3243.4	3243.4	3263.7	3249.5
167.5°	3295.4	3286.2	3286.2	3306.6	3292.4
170°	3332.1	3323.9	3320.9	3341.3	3323.9
172.5°	3357.6	3349.4	3346.4	3366.8	3349.4
175°	3378.1	3369.9	3363.8	3384.1	3366.8
177.5°	3389.3	3381.1	3374.9	3392.3	3374.9
180°	3384.1	3384.1	3384.1	3384.1	3384.1

TEST NUMBER: P922958

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.58	12.37	12.59	13.38	14.73	7.54	8.33	8.55	9.34	10.69
	3H	13.25	13.95	14.27	14.98	16.35	8.72	9.42	9.74	10.45	11.82
	4H	13.85	14.52	14.89	15.55	16.93	9.16	9.83	10.20	10.86	12.23
	6H	14.27	14.88	15.31	15.91	17.30	9.48	10.09	10.52	11.12	12.51
	8H	14.39	14.98	15.44	16.02	17.41	9.56	10.15	10.61	11.19	12.58
	12H	14.45	15.01	15.50	16.05	17.46	9.60	10.16	10.65	11.20	12.61
4H	2H	11.59	12.26	12.63	13.28	14.66	8.13	8.80	9.17	9.82	11.20
	3H	13.41	13.97	14.46	15.02	16.41	9.47	10.02	10.51	11.08	12.47
	4H	14.10	14.61	15.15	15.65	17.07	10.01	10.52	11.06	11.56	12.98
	6H	14.61	15.04	15.67	16.11	17.52	10.42	10.85	11.48	11.92	13.33
	8H	14.78	15.18	15.84	16.25	17.67	10.54	10.95	11.61	12.01	13.44
	12H	14.87	15.24	15.95	16.31	17.74	10.60	10.97	11.68	12.05	13.47
8H	4H	14.06	14.47	15.12	15.53	16.95	10.28	10.69	11.35	11.75	13.17
	6H	14.62	14.96	15.71	16.06	17.48	10.79	11.13	11.88	12.23	13.65
	8H	14.83	15.13	15.93	16.22	17.66	10.98	11.27	12.07	12.36	13.80
	12H	14.97	15.23	16.06	16.31	17.79	11.09	11.35	12.18	12.43	13.91
12H	4H	14.01	14.38	15.09	15.45	16.88	10.28	10.65	11.37	11.73	13.16
	6H	14.60	14.89	15.69	15.98	17.42	10.84	11.13	11.93	12.22	13.66
	8H	14.81	15.07	15.91	16.15	17.63	11.04	11.30	12.14	12.38	13.86