

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925465

Luminaire Tested: DFN2DIP-SQ3F0-040D110US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925465
REPORT IS A COMBINATION OF REPORTS P901507 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-040D110US950-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14166.9 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 118.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925465

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925465

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35
1	93	88	85	81	82	79	76	73	62	59	58	45	44	43	31	30	29
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	47	43	40	35	33	30	24	22	21
4	70	60	52	46	62	54	47	42	42	38	34	31	28	26	21	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14
7	55	43	35	30	49	39	32	27	30	26	22	23	20	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1701	1701	1701
5°	1703	1676	1688
10°	1688	1653	1665
15°	1662	1624	1629
20°	1628	1585	1592
25°	1593	1539	1549
30°	1550	1496	1494
35°	1509	1445	1437
40°	1459	1394	1382
45°	1409	1342	1326
50°	1355	1288	1261
55°	1297	1226	1202
60°	1232	1151	1134
65°	1162	1074	1053
70°	1071	981	966
75°	946	868	885
80°	795	724	732
85°	560	479	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2427 cd/sqm

TEST NUMBER: P925465

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US950-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.8	1.0
10°-20°	393.2	2.8
20°-30°	577.9	4.1
30°-40°	671.2	4.7
40°-50°	670.3	4.7
50°-60°	584.5	4.1
60°-70°	432.1	3.0
70°-80°	244.5	1.7
80°-90°	70.7	0.5
90°-100°	116.8	0.8
100°-110°	435.4	3.1
110°-120°	1154.6	8.2
120°-130°	1915.0	13.5
130°-140°	2034.2	14.4
140°-150°	1890.5	13.3
150°-160°	1519.9	10.7
160°-170°	979.4	6.9
170°-180°	337.1	2.4
0°-30°	1110.8	7.8
0°-40°	1782.0	12.6
0°-60°	3036.8	21.4
0°-90°	3784.1	26.7
90°-120°	1706.7	12.0
90°-150°	7546.4	53.3
90°-180°	10383.0	73.3
0°-180°	14166.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1485	1485	1485	1485	1485	
5°	1485	1479	1463	1475	1472	141
15°	1413	1405	1386	1392	1385	398
25°	1279	1268	1244	1246	1244	589
35°	1104	1090	1067	1058	1051	689
45°	898	888	867	851	845	693
55°	680	671	654	637	630	608
65°	458	450	436	423	416	453
75°	240	237	230	221	224	256
85°	58	57	56	51	50	65
90°	2	31	51	64	69	13
95°	166	82	100	113	110	197
105°	779	856	156	184	195	832
115°	1474	1517	1581	395	210	1451
125°	2083	2117	2166	2183	2191	1858
135°	2578	2619	2642	2668	2663	1992
145°	2991	2988	3032	3050	3037	1871
155°	3293	3270	3301	3316	3296	1517
165°	3470	3454	3462	3480	3462	980
175°	3549	3531	3536	3554	3529	338
180°	3542	3542	3542	3542	3542	

TEST NUMBER: P925465

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US950-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1484.8	1484.8	1484.8	1484.8	1484.8
2.5°	1493.5	1486.3	1470.6	1484.8	1482.1
5°	1484.8	1479.2	1463.4	1474.8	1472.1
7.5°	1474.8	1466.3	1450.6	1462.1	1459.2
10°	1459.2	1449.2	1432.1	1443.5	1439.2
12.5°	1437.7	1429.2	1412.1	1419.3	1416.3
15°	1413.4	1405.0	1386.4	1392.1	1385.0
17.5°	1383.5	1375.0	1356.4	1363.5	1356.4
20°	1350.6	1342.1	1322.1	1326.3	1320.8
22.5°	1317.9	1305.0	1286.4	1286.4	1283.5
25°	1279.2	1267.9	1243.6	1246.4	1243.6
27.5°	1236.4	1226.4	1208.0	1203.7	1196.6
30°	1193.6	1182.2	1160.8	1156.5	1150.8
32.5°	1147.9	1139.5	1116.6	1108.0	1102.2
35°	1103.7	1089.5	1066.6	1058.0	1050.8
37.5°	1053.7	1040.8	1017.9	1008.0	1000.8
40°	1002.4	990.8	967.9	955.2	949.5
42.5°	952.4	940.8	918.1	903.7	895.2
45°	898.1	888.2	866.6	851.1	845.2
47.5°	845.2	835.2	812.4	796.7	788.2
50°	789.5	782.4	762.4	742.4	735.2
52.5°	735.2	725.3	706.8	691.1	681.1
55°	679.7	671.0	654.0	636.8	629.7
57.5°	623.9	616.9	598.2	581.1	575.4
60°	568.2	562.6	542.6	526.9	522.6
62.5°	514.0	504.0	489.8	475.5	469.7
65°	458.4	449.7	435.5	422.6	415.6
67.5°	401.3	394.0	381.3	371.3	365.6
70°	348.4	342.7	329.8	319.8	314.2
72.5°	294.2	288.4	281.3	271.3	267.0
75°	239.8	237.1	229.8	221.3	224.2
77.5°	191.3	185.6	182.7	178.4	174.2
80°	142.8	141.3	138.4	134.2	131.4
82.5°	97.1	97.1	95.8	90.0	90.0
85°	58.5	57.1	55.7	51.3	50.0
87.5°	25.8	22.9	20.0	15.7	14.2
90°	2.5	30.7	51.1	64.2	69.1
92.5°	64.2	53.9	61.4	66.7	69.1
95°	166.5	81.9	99.8	112.9	110.2
97.5°	299.7	89.8	130.5	138.4	140.9
100°	453.7	102.6	146.1	166.5	171.6
102.5°	622.6	617.7	151.2	179.3	187.2
105°	779.0	856.0	156.5	184.4	194.8
107.5°	961.1	1024.9	161.6	189.6	200.0
110°	1135.4	1189.0	448.6	192.3	202.3

TEST NUMBER: P925465

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1299.4	1345.3	1301.8	197.2	205.1
115°	1473.5	1517.0	1581.3	394.7	210.3
117.5°	1624.8	1675.9	1719.7	1353.0	681.6
120°	1793.9	1832.3	1878.5	1909.2	1563.2
122.5°	1937.3	1978.3	2029.7	2045.0	2047.8
125°	2083.3	2116.8	2165.5	2183.4	2191.1
127.5°	2216.6	2252.5	2291.1	2316.7	2319.2
130°	2342.3	2383.4	2411.3	2439.7	2437.3
132.5°	2470.4	2503.9	2531.9	2555.0	2552.6
135°	2578.2	2619.2	2642.0	2668.0	2662.7
137.5°	2690.8	2721.5	2747.3	2772.9	2765.3
140°	2800.9	2821.6	2849.6	2872.7	2859.9
142.5°	2893.4	2911.3	2944.5	2964.9	2952.2
145°	2990.8	2988.0	3031.5	3049.6	3036.8
147.5°	3075.1	3067.5	3111.0	3123.8	3113.8
150°	3157.3	3139.3	3180.3	3195.6	3182.8
152.5°	3226.3	3205.9	3244.3	3259.8	3241.9
155°	3293.0	3270.1	3300.8	3316.1	3295.7
157.5°	3346.8	3326.4	3349.6	3367.5	3346.8
160°	3393.1	3377.5	3393.1	3408.3	3390.3
162.5°	3433.8	3418.7	3431.4	3449.4	3426.3
165°	3469.8	3454.5	3462.2	3480.1	3462.2
167.5°	3498.0	3482.6	3490.5	3508.4	3485.3
170°	3521.2	3505.7	3510.8	3528.8	3505.7
172.5°	3536.4	3521.2	3526.4	3544.3	3521.2
175°	3549.2	3531.2	3536.4	3554.4	3528.8
177.5°	3554.4	3536.4	3539.1	3557.1	3534.0
180°	3541.6	3541.6	3541.6	3541.6	3541.6

TEST NUMBER: P925465

CATALOG NUMBER: DFN2DIP-SQ3F0-040D110US950-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.40	7.08	7.53	8.21	9.78	5.96	6.64	7.09	7.77	9.33
	3H	8.04	8.66	9.18	9.79	11.37	7.55	8.17	8.69	9.30	10.88
	4H	8.62	9.20	9.77	10.34	11.92	8.12	8.71	9.28	9.84	11.43
	6H	9.01	9.54	10.16	10.68	12.28	8.51	9.04	9.66	10.18	11.78
	8H	9.10	9.61	10.27	10.76	12.36	8.60	9.11	9.76	10.26	11.86
	12H	9.14	9.63	10.31	10.77	12.39	8.63	9.12	9.80	10.26	11.88
4H	2H	6.84	7.42	7.99	8.55	10.14	6.48	7.06	7.64	8.20	9.79
	3H	8.68	9.17	9.84	10.33	11.93	8.27	8.76	9.44	9.92	11.52
	4H	9.38	9.83	10.55	10.98	12.60	8.96	9.41	10.12	10.55	12.17
	6H	9.88	10.27	11.05	11.44	13.05	9.45	9.83	10.62	11.00	12.62
	8H	10.03	10.38	11.20	11.55	13.17	9.59	9.95	10.76	11.11	12.74
	12H	10.09	10.41	11.28	11.59	13.22	9.64	9.96	10.83	11.14	12.77
8H	4H	9.56	9.92	10.73	11.08	12.71	9.18	9.54	10.35	10.70	12.33
	6H	10.18	10.47	11.37	11.68	13.30	9.79	10.09	10.98	11.29	12.92
	8H	10.39	10.65	11.59	11.83	13.48	10.00	10.26	11.20	11.44	13.09
	12H	10.51	10.74	11.71	11.92	13.60	10.10	10.33	11.30	11.51	13.19
12H	4H	9.54	9.86	10.72	11.03	12.67	9.17	9.49	10.35	10.67	12.30
	6H	10.20	10.46	11.40	11.64	13.29	9.83	10.09	11.03	11.27	12.92
	8H	10.43	10.66	11.63	11.84	13.52	10.05	10.28	11.25	11.46	13.14

END OF REPORT