

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925491

Luminaire Tested: DFN2DIP-SQ3F0-050D080US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925491
REPORT IS A COMBINATION OF REPORTS P901456 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D080US950-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11610.2 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 102.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925491
CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US950-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P925491
 CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				35
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36	30				30
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31	26				26
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27	22				22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19				19
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21	17				17
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18	15				15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16	14				14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12				12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11				11
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2259	2259	2259
5°	2261	2222	2237
10°	2237	2176	2163
15°	2205	2103	2050
20°	2163	2003	1911
25°	2120	1890	1777
30°	2062	1775	1608
35°	2006	1651	1459
40°	1948	1523	1288
45°	1881	1382	1134
50°	1812	1239	983
55°	1740	1086	838
60°	1656	927	689
65°	1560	766	619
70°	1443	615	559
75°	1296	539	507
80°	1082	448	437
85°	734	292	325

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1881 cd/sqm



TEST NUMBER: P925491

CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	1.6
10°-20°	507.2	4.4
20°-30°	712.1	6.1
30°-40°	776.3	6.7
40°-50°	713.5	6.1
50°-60°	560.3	4.8
60°-70°	364.7	3.1
70°-80°	187.7	1.6
80°-90°	52.5	0.5
90°-100°	84.9	0.7
100°-110°	316.6	2.7
110°-120°	839.7	7.2
120°-130°	1392.7	12.0
130°-140°	1479.4	12.7
140°-150°	1374.9	11.8
150°-160°	1105.4	9.5
160°-170°	712.3	6.1
170°-180°	245.2	2.1
0°-30°	1404.1	12.1
0°-40°	2180.4	18.8
0°-60°	3454.1	29.8
0°-90°	4059.1	35.0
90°-120°	1241.3	10.7
90°-150°	5488.3	47.3
90°-180°	7551.0	65.0
0°-180°	11610.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1971	1963	1939	1955	1950	187
15°	1875	1855	1795	1761	1743	528
25°	1702	1645	1527	1454	1427	783
35°	1467	1376	1219	1106	1067	918
45°	1199	1079	892	765	722	926
55°	912	772	580	473	439	815
65°	616	471	310	250	244	610
75°	328	203	143	130	128	347
85°	77	39	34	34	34	88
90°	2	22	37	47	50	11
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	



TEST NUMBER: P925491

CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US950-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1971.4	1971.4	1971.4	1971.4	1971.4
2.5°	1980.3	1971.4	1951.8	1969.7	1966.1
5°	1971.4	1962.6	1939.3	1955.3	1950.1
7.5°	1955.3	1944.7	1919.7	1926.8	1917.8
10°	1933.9	1921.5	1885.9	1880.4	1869.7
12.5°	1907.2	1891.2	1842.9	1832.3	1812.6
15°	1875.1	1855.4	1794.9	1761.0	1743.1
17.5°	1837.6	1809.1	1734.1	1694.9	1666.3
20°	1794.9	1759.1	1669.9	1625.4	1586.0
22.5°	1748.5	1707.4	1603.9	1543.3	1516.6
25°	1702.0	1644.9	1527.2	1454.1	1427.2
27.5°	1646.8	1586.0	1455.8	1371.9	1330.9
30°	1587.9	1520.0	1377.3	1286.4	1238.1
32.5°	1530.8	1448.6	1302.5	1195.4	1150.7
35°	1466.6	1375.6	1218.6	1106.2	1066.9
37.5°	1404.1	1305.9	1140.1	1016.9	972.4
40°	1338.1	1231.1	1057.9	931.3	884.9
42.5°	1270.3	1156.2	975.9	843.8	799.4
45°	1199.0	1079.4	892.1	765.3	722.5
47.5°	1131.2	1004.6	811.9	685.1	645.9
50°	1056.3	929.6	733.3	610.1	572.8
52.5°	983.0	849.2	658.4	540.6	506.8
55°	911.6	772.5	579.7	472.8	438.9
57.5°	838.6	695.8	510.3	410.4	381.8
60°	763.6	620.9	437.0	346.2	317.6
62.5°	690.5	547.8	374.6	289.1	274.8
65°	615.5	471.0	310.4	249.9	244.4
67.5°	544.2	399.6	249.9	219.4	214.1
70°	469.3	330.1	206.9	189.1	181.9
72.5°	397.9	265.8	173.1	158.8	155.2
75°	328.3	203.3	142.7	130.2	128.5
77.5°	258.7	144.4	112.5	105.2	101.6
80°	194.4	103.5	85.6	78.5	78.5
82.5°	135.6	69.6	58.9	55.2	55.2
85°	76.7	39.2	33.9	33.9	33.9
87.5°	28.6	14.2	14.2	12.5	12.5
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2



TEST NUMBER: P925491

CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7



TEST NUMBER: P925491
 CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.35	9.07	9.43	10.15	11.62	4.31	5.03	5.40	6.11	7.59
	3H	10.02	10.66	11.11	11.75	13.24	5.49	6.13	6.58	7.22	8.71
	4H	10.62	11.23	11.72	12.32	13.81	5.93	6.54	7.03	7.63	9.12
	6H	11.03	11.59	12.14	12.68	14.19	6.24	6.80	7.35	7.89	9.40
	8H	11.15	11.69	12.26	12.79	14.29	6.32	6.86	7.43	7.96	9.46
	12H	11.21	11.71	12.33	12.81	14.34	6.36	6.86	7.48	7.97	9.49
4H	2H	8.35	8.97	9.46	10.05	11.55	4.89	5.50	6.00	6.59	8.09
	3H	10.17	10.68	11.28	11.79	13.30	6.23	6.73	7.34	7.85	9.36
	4H	10.85	11.32	11.97	12.42	13.95	6.76	7.23	7.88	8.33	9.86
	6H	11.36	11.76	12.48	12.88	14.41	7.17	7.57	8.30	8.70	10.22
	8H	11.53	11.90	12.65	13.02	14.56	7.29	7.66	8.42	8.78	10.32
	12H	11.62	11.95	12.76	13.08	14.63	7.35	7.69	8.49	8.82	10.36
8H	4H	10.81	11.18	11.94	12.30	13.84	7.03	7.41	8.16	8.52	10.06
	6H	11.37	11.68	12.51	12.84	14.37	7.54	7.85	8.68	9.01	10.54
	8H	11.58	11.85	12.73	12.99	14.55	7.72	7.99	8.88	9.13	10.69
	12H	11.71	11.95	12.87	13.09	14.68	7.83	8.07	8.99	9.21	10.80
12H	4H	10.76	11.10	11.90	12.23	13.77	7.03	7.37	8.17	8.50	10.04
	6H	11.34	11.61	12.49	12.75	14.31	7.59	7.85	8.74	9.00	10.55
	8H	11.55	11.79	12.71	12.93	14.52	7.79	8.02	8.94	9.16	10.75