

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917531

Luminaire Tested: DFN2DIP-SQ3F0-110D100US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917531
REPORT IS A COMBINATION OF REPORTS P901504 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D100US930-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15694.5 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 189.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917531

CATALOG NUMBER: DFN2DIP-SQ3F0-110D100US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917531

CATALOG NUMBER: DFN2DIP-SQ3F0-110D100US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	83	81	73	71	69	61	59	58	49	48	47
2	90	82	77	72	82	76	71	67	65	61	58	54	51	49	44	42	40
3	82	73	66	60	75	68	61	56	57	53	49	48	45	42	39	37	35
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	36	42	36	32	35	31	28	29	26	24
7	59	47	39	34	55	44	37	32	38	33	29	32	28	25	27	24	21
8	55	43	35	30	51	40	33	29	35	29	26	30	25	22	25	22	19
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4247	4247	4247
5°	4251	4177	4205
10°	4206	4092	4067
15°	4146	3954	3854
20°	4066	3765	3593
25°	3985	3554	3342
30°	3877	3337	3023
35°	3771	3105	2743
40°	3663	2864	2422
45°	3537	2598	2132
50°	3407	2330	1848
55°	3271	2043	1575
60°	3114	1744	1295
65°	2932	1440	1164
70°	2712	1157	1051
75°	2435	1013	954
80°	2035	841	822
85°	1380	548	610

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3537 cd/sqm

TEST NUMBER: P917531

CATALOG NUMBER: DFN2DIP-SQ3F0-110D100US930-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.4	2.2
10°-20°	953.6	6.1
20°-30°	1338.9	8.5
30°-40°	1459.5	9.3
40°-50°	1341.4	8.5
50°-60°	1053.5	6.7
60°-70°	685.7	4.4
70°-80°	353.0	2.2
80°-90°	95.0	0.6
90°-100°	90.7	0.6
100°-110°	338.2	2.2
110°-120°	897.0	5.7
120°-130°	1487.8	9.5
130°-140°	1580.4	10.1
140°-150°	1468.8	9.4
150°-160°	1180.9	7.5
160°-170°	760.9	4.8
170°-180°	261.9	1.7
0°-30°	2639.9	16.8
0°-40°	4099.4	26.1
0°-60°	6494.2	41.4
0°-90°	7627.9	48.6
90°-120°	1326.0	8.4
90°-150°	5862.9	37.4
90°-180°	8067.0	51.4
0°-180°	15694.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3707	3707	3707	3707	3707	
5°	3707	3690	3646	3676	3666	351
15°	3525	3488	3374	3311	3277	993
25°	3200	3093	2871	2734	2683	1472
35°	2757	2586	2291	2080	2006	1726
45°	2254	2029	1677	1439	1358	1741
55°	1714	1452	1090	889	825	1532
65°	1157	885	584	470	459	1147
75°	617	382	268	245	242	653
85°	144	74	64	64	64	165
90°	2	24	40	50	54	15
95°	129	64	78	88	86	153
105°	605	665	122	143	151	647
115°	1145	1179	1228	307	163	1127
125°	1619	1645	1682	1696	1702	1444
135°	2003	2035	2053	2073	2069	1547
145°	2324	2322	2355	2369	2359	1453
155°	2558	2541	2564	2576	2560	1179
165°	2696	2684	2690	2704	2690	762
175°	2757	2744	2748	2762	2742	262
180°	2752	2752	2752	2752	2752	

TEST NUMBER: P917531

CATALOG NUMBER: DFN2DIP-SQ3F0-110D100US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3706.6	3706.6	3706.6	3706.6	3706.6
2.5°	3723.3	3706.6	3669.6	3703.4	3696.6
5°	3706.6	3689.9	3646.1	3676.3	3666.4
7.5°	3676.3	3656.4	3609.4	3622.6	3605.8
10°	3636.1	3612.6	3545.7	3535.4	3515.5
12.5°	3585.9	3555.7	3464.9	3445.0	3407.9
15°	3525.4	3488.4	3374.5	3310.8	3277.3
17.5°	3455.0	3401.3	3260.3	3186.6	3132.9
20°	3374.5	3307.3	3139.6	3056.0	2982.0
22.5°	3287.4	3210.1	3015.5	2901.6	2851.3
25°	3200.1	3092.7	2871.3	2733.9	2683.4
27.5°	3096.3	2982.0	2737.1	2579.4	2502.2
30°	2985.5	2857.8	2589.5	2418.6	2327.8
32.5°	2878.1	2723.6	2448.8	2247.5	2163.5
35°	2757.4	2586.2	2291.2	2079.8	2005.8
37.5°	2640.0	2455.3	2143.5	1911.8	1828.2
40°	2515.8	2314.7	1989.1	1750.9	1663.8
42.5°	2388.3	2173.7	1835.0	1586.6	1502.9
45°	2254.2	2029.3	1677.3	1438.8	1358.4
47.5°	2126.8	1888.7	1526.4	1287.9	1214.3
50°	1985.8	1747.8	1378.8	1147.0	1076.9
52.5°	1848.1	1596.5	1237.8	1016.4	952.7
55°	1713.9	1452.4	1090.1	889.0	825.3
57.5°	1576.6	1308.2	959.4	771.6	717.8
60°	1435.7	1167.3	821.7	650.9	597.2
62.5°	1298.3	1030.0	704.3	543.5	516.7
65°	1157.3	885.4	583.7	469.8	459.4
67.5°	1023.2	751.3	469.8	412.5	402.5
70°	882.2	620.7	389.0	355.6	342.0
72.5°	748.0	499.7	325.3	298.6	291.8
75°	617.1	382.2	268.3	244.8	241.7
77.5°	486.5	271.6	211.4	197.9	191.1
80°	365.5	194.7	160.9	147.7	147.7
82.5°	254.8	130.9	110.7	104.0	104.0
85°	144.1	73.7	63.7	63.7	63.7
87.5°	53.7	26.7	26.7	23.5	23.5
90°	1.9	23.9	39.7	49.9	53.6
92.5°	49.9	41.8	47.8	51.8	53.6
95°	129.3	63.6	77.5	87.7	85.6
97.5°	232.8	69.7	101.4	107.5	109.5
100°	352.5	79.7	113.5	129.3	133.4
102.5°	483.7	480.0	117.5	139.3	145.4
105°	605.3	665.0	121.6	143.2	151.3
107.5°	746.7	796.3	125.6	147.3	155.3
110°	882.1	923.7	348.5	149.4	157.2



TEST NUMBER: P917531

CATALOG NUMBER: DFN2DIP-SQ3F0-110D100US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1009.5	1045.2	1011.5	153.2	159.4
115°	1144.8	1178.6	1228.5	306.6	163.4
117.5°	1262.2	1302.0	1336.0	1051.2	529.6
120°	1393.8	1423.5	1459.5	1483.4	1214.5
122.5°	1505.1	1537.0	1576.9	1588.8	1590.9
125°	1618.6	1644.6	1682.4	1696.4	1702.3
127.5°	1722.2	1750.0	1780.0	1799.9	1801.8
130°	1819.7	1851.7	1873.5	1895.4	1893.5
132.5°	1919.3	1945.3	1967.1	1985.0	1983.1
135°	2003.0	2034.9	2052.7	2072.7	2068.7
137.5°	2090.5	2114.4	2134.5	2154.3	2148.4
140°	2176.0	2192.2	2213.9	2231.9	2221.9
142.5°	2247.9	2261.9	2287.6	2303.5	2293.6
145°	2323.6	2321.5	2355.3	2369.3	2359.3
147.5°	2389.1	2383.2	2417.0	2426.9	2419.2
150°	2452.9	2439.0	2470.9	2482.7	2472.8
152.5°	2506.6	2490.7	2520.6	2532.6	2518.6
155°	2558.4	2540.6	2564.5	2576.3	2560.5
157.5°	2600.2	2584.4	2602.4	2616.3	2600.2
160°	2636.2	2624.1	2636.2	2648.0	2634.1
162.5°	2667.8	2656.0	2665.9	2679.9	2661.9
165°	2695.7	2683.9	2689.8	2703.8	2689.8
167.5°	2717.7	2705.6	2711.8	2725.8	2707.8
170°	2735.7	2723.7	2727.7	2741.6	2723.7
172.5°	2747.5	2735.7	2739.7	2753.7	2735.7
175°	2757.4	2743.5	2747.5	2761.5	2741.6
177.5°	2761.5	2747.5	2749.7	2763.6	2745.6
180°	2751.6	2751.6	2751.6	2751.6	2751.6

TEST NUMBER: P917531

CATALOG NUMBER: DFN2DIP-SQ3F0-110D100US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.01	12.82	12.98	13.81	15.10	7.97	8.79	8.94	9.77	11.06
	3H	13.68	14.41	14.66	15.40	16.72	9.15	9.88	10.13	10.87	12.19
	4H	14.28	14.97	15.28	15.97	17.30	9.59	10.29	10.59	11.28	12.61
	6H	14.70	15.34	15.71	16.34	17.68	9.91	10.54	10.92	11.55	12.88
	8H	14.82	15.43	15.84	16.45	17.78	9.99	10.60	11.01	11.62	12.95
	12H	14.88	15.46	15.90	16.47	17.83	10.04	10.61	11.06	11.62	12.98
4H	2H	12.02	12.71	13.03	13.71	15.03	8.56	9.25	9.56	10.25	11.57
	3H	13.84	14.42	14.86	15.45	16.78	9.90	10.48	10.91	11.50	12.84
	4H	14.53	15.06	15.55	16.08	17.44	10.44	10.97	11.46	11.99	13.35
	6H	15.04	15.49	16.07	16.54	17.89	10.85	11.31	11.89	12.35	13.70
	8H	15.21	15.64	16.25	16.67	18.04	10.98	11.40	12.01	12.44	13.81
	12H	15.31	15.69	16.36	16.74	18.11	11.04	11.42	12.09	12.47	13.85
8H	4H	14.50	14.92	15.53	15.95	17.32	10.72	11.14	11.75	12.17	13.55
	6H	15.06	15.41	16.11	16.48	17.85	11.23	11.58	12.29	12.65	14.02
	8H	15.27	15.58	16.34	16.64	18.03	11.41	11.72	12.48	12.78	14.17
	12H	15.40	15.67	16.47	16.73	18.16	11.53	11.80	12.60	12.85	14.28
12H	4H	14.45	14.83	15.50	15.88	17.25	10.72	11.10	11.77	12.15	13.53
	6H	15.03	15.34	16.10	16.40	17.79	11.28	11.58	12.34	12.64	14.03
	8H	15.25	15.52	16.32	16.57	18.00	11.48	11.75	12.55	12.81	14.24

END OF REPORT