

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925548

Luminaire Tested: DFN2DIP-SQ3F0-070D050US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925548
REPORT IS A COMBINATION OF REPORTS P899885 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-070D050US950-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10832.7 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 102.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925548
CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US950-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P925548

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	61
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	56	56	56	51
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	47	47	47	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	40	40	40	37
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	35	35	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	30	30	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	33	30	27	27	27	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	24	24	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	21	21	21	19
9	52	39	32	27	48	37	30	25	33	27	23	30	25	21	26	22	19	19	19	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	17	17	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2977	2977	2977
5°	2980	2934	2955
10°	2954	2892	2914
15°	2909	2843	2850
20°	2848	2775	2785
25°	2788	2694	2710
30°	2713	2618	2615
35°	2641	2529	2515
40°	2554	2439	2419
45°	2466	2349	2321
50°	2371	2254	2208
55°	2270	2145	2103
60°	2157	2015	1984
65°	2033	1880	1842
70°	1875	1716	1690
75°	1656	1519	1549
80°	1391	1267	1280
85°	981	840	838

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2466 cd/sqm



TEST NUMBER: P925548

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.6	2.3
10°-20°	688.1	6.4
20°-30°	1011.3	9.3
30°-40°	1174.5	10.8
40°-50°	1173.1	10.8
50°-60°	1022.9	9.4
60°-70°	756.1	7.0
70°-80°	427.8	3.9
80°-90°	117.2	1.1
90°-100°	93.4	0.9
100°-110°	296.6	2.7
110°-120°	507.6	4.7
120°-130°	667.5	6.2
130°-140°	749.3	6.9
140°-150°	734.8	6.8
150°-160°	616.4	5.7
160°-170°	408.8	3.8
170°-180°	142.9	1.3
0°-30°	1943.9	17.9
0°-40°	3118.5	28.8
0°-60°	5314.4	49.1
0°-90°	6615.6	61.1
90°-120°	897.5	8.3
90°-150°	3049.2	28.1
90°-180°	4217.0	38.9
0°-180°	10832.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2598	2598	2598	2598	2598	
5°	2598	2589	2561	2581	2576	247
15°	2474	2459	2426	2436	2424	697
25°	2239	2219	2176	2181	2176	1030
35°	1932	1907	1866	1851	1839	1206
45°	1572	1554	1517	1489	1479	1213
55°	1189	1174	1144	1114	1102	1063
65°	802	787	762	740	727	793
75°	420	415	402	387	392	448
85°	102	100	98	90	88	114
90°	1	16	45	42	43	10
95°	66	79	81	81	79	74
105°	274	277	280	282	282	289
115°	509	517	514	513	509	504
125°	741	752	749	744	743	662
135°	958	972	975	974	970	741
145°	1163	1172	1180	1181	1176	727
155°	1330	1334	1338	1344	1340	612
165°	1447	1446	1446	1455	1449	408
175°	1506	1502	1500	1509	1501	143
180°	1509	1509	1509	1509	1509	



TEST NUMBER: P925548

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2598.4	2598.4	2598.4	2598.4	2598.4
2.5°	2613.6	2601.1	2573.5	2598.4	2593.6
5°	2598.4	2588.7	2561.1	2581.0	2576.2
7.5°	2581.0	2566.1	2538.5	2558.7	2553.7
10°	2553.7	2536.1	2506.2	2526.1	2518.7
12.5°	2516.0	2501.2	2471.2	2483.6	2478.6
15°	2473.6	2458.7	2426.1	2436.2	2423.7
17.5°	2421.1	2406.3	2373.6	2386.1	2373.6
20°	2363.5	2348.7	2313.7	2321.2	2311.4
22.5°	2306.3	2283.8	2251.2	2251.2	2246.1
25°	2238.8	2218.8	2176.5	2181.2	2176.5
27.5°	2163.7	2146.2	2113.9	2106.4	2093.9
30°	2089.0	2068.7	2031.4	2024.0	2013.9
32.5°	2008.8	1994.1	1954.0	1938.9	1928.8
35°	1931.5	1906.6	1866.5	1851.4	1838.9
37.5°	1844.0	1821.5	1781.4	1763.9	1751.4
40°	1754.1	1734.0	1693.9	1671.7	1661.6
42.5°	1666.6	1646.5	1606.7	1581.5	1566.7
45°	1571.7	1554.3	1516.6	1489.3	1479.2
47.5°	1479.2	1461.7	1421.7	1394.1	1379.3
50°	1381.7	1369.2	1334.2	1299.3	1286.8
52.5°	1286.8	1269.3	1237.0	1209.4	1191.8
55°	1189.4	1174.4	1144.4	1114.5	1102.0
57.5°	1091.9	1079.5	1046.8	1016.9	1006.9
60°	994.4	984.5	949.6	922.0	914.6
62.5°	899.4	882.0	857.1	832.2	822.1
65°	802.2	787.0	762.2	739.6	727.1
67.5°	702.2	689.6	667.2	649.8	639.7
70°	609.7	599.7	577.1	559.6	549.8
72.5°	514.8	504.8	492.3	474.8	467.4
75°	419.7	414.9	402.1	387.3	392.4
77.5°	334.9	324.7	319.7	312.2	304.9
80°	249.9	247.4	242.3	234.9	229.8
82.5°	169.9	169.9	167.5	157.5	157.5
85°	102.4	100.0	97.6	89.9	87.5
87.5°	45.0	40.1	35.0	27.6	24.9
90°	1.3	16.4	44.6	41.9	43.2
92.5°	28.2	38.2	39.6	40.9	40.9
95°	66.4	79.2	81.4	81.4	79.2
97.5°	110.5	122.3	127.4	127.4	127.4
100°	161.4	171.9	175.5	175.5	174.2
102.5°	215.1	222.9	227.8	229.2	227.8
105°	273.8	277.4	280.2	282.4	282.4
107.5°	332.0	337.4	337.4	338.4	332.0
110°	388.4	395.7	395.7	395.7	392.0



TEST NUMBER: P925548

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	449.3	457.1	455.7	452.1	449.3
115°	509.3	516.7	514.4	513.1	509.3
117.5°	569.0	579.0	572.6	569.0	565.3
120°	629.0	639.0	629.0	629.0	624.9
122.5°	683.5	696.3	689.9	686.3	683.5
125°	740.9	752.2	748.6	744.5	743.2
127.5°	796.8	810.9	805.9	800.4	796.8
130°	849.2	865.5	863.2	860.5	855.5
132.5°	907.8	920.5	921.5	915.1	911.5
135°	958.3	972.3	975.1	973.7	970.1
137.5°	1014.7	1026.0	1028.3	1027.4	1021.9
140°	1064.2	1075.6	1081.9	1081.9	1077.0
142.5°	1115.1	1126.6	1130.2	1131.5	1126.6
145°	1163.4	1172.5	1179.7	1181.1	1176.1
147.5°	1206.6	1218.0	1223.4	1225.7	1220.6
150°	1251.2	1258.9	1263.9	1268.0	1263.9
152.5°	1290.8	1298.5	1304.8	1309.8	1304.8
155°	1330.3	1333.9	1338.0	1344.4	1340.3
157.5°	1364.4	1367.1	1369.4	1378.5	1372.1
160°	1394.8	1397.6	1398.9	1406.7	1401.2
162.5°	1423.1	1423.1	1424.4	1433.1	1426.7
165°	1447.2	1445.8	1445.8	1454.9	1448.6
167.5°	1469.0	1464.9	1464.9	1474.0	1467.6
170°	1485.4	1481.8	1480.4	1489.5	1481.8
172.5°	1496.7	1493.1	1491.8	1500.8	1493.1
175°	1505.9	1502.2	1499.5	1508.6	1500.8
177.5°	1510.8	1507.2	1504.5	1512.2	1504.5
180°	1508.6	1508.6	1508.6	1508.6	1508.6



TEST NUMBER: P925548
 CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.99	12.96	12.85	13.84	14.94	11.55	12.52	12.40	13.39	14.50
	3H	13.65	14.53	14.52	15.41	16.54	13.16	14.04	14.03	14.92	16.05
	4H	14.24	15.07	15.13	15.96	17.10	13.75	14.57	14.63	15.47	16.61
	6H	14.65	15.41	15.54	16.31	17.46	14.15	14.91	15.04	15.81	16.96
	8H	14.75	15.48	15.66	16.39	17.55	14.25	14.97	15.15	15.89	17.04
	12H	14.80	15.49	15.71	16.40	17.58	14.29	14.98	15.20	15.89	17.07
4H	2H	12.46	13.28	13.35	14.18	15.32	12.11	12.93	13.00	13.82	14.96
	3H	14.33	15.02	15.23	15.94	17.10	13.92	14.61	14.82	15.54	16.69
	4H	15.05	15.67	15.96	16.59	17.78	14.62	15.25	15.53	16.17	17.35
	6H	15.56	16.10	16.49	17.05	18.23	15.13	15.67	16.06	16.62	17.80
	8H	15.71	16.22	16.64	17.16	18.35	15.28	15.78	16.20	16.72	17.92
	12H	15.79	16.25	16.74	17.20	18.40	15.34	15.80	16.29	16.75	17.95
8H	4H	15.25	15.75	16.18	16.69	17.89	14.87	15.38	15.80	16.32	17.51
	6H	15.88	16.30	16.83	17.28	18.47	15.49	15.91	16.45	16.89	18.09
	8H	16.10	16.47	17.06	17.44	18.65	15.70	16.07	16.67	17.04	18.26
	12H	16.23	16.56	17.20	17.52	18.78	15.82	16.14	16.79	17.11	18.37
12H	4H	15.24	15.69	16.19	16.65	17.85	14.87	15.33	15.82	16.28	17.48
	6H	15.91	16.28	16.87	17.25	18.46	15.53	15.90	16.50	16.88	18.09
	8H	16.15	16.48	17.12	17.44	18.70	15.77	16.10	16.74	17.06	18.32