

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925552

Luminaire Tested: DFN2DIP-SQ3F0-070D060US950-FLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P925552  
REPORT IS A COMBINATION OF REPORTS P899903 AND P896733  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-070D060US950-FLLFLL  
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11677.0 lumens  
Efficiency: N/A  
Efficacy: 105.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 110.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9963  
Total Harmonic Distortion (THDi): 0.065  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P925552

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US950-FLLFLL

### Luminous Intensity Polar Plot



TEST NUMBER: P925552

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US950-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |
| 0   | 109 | 109 | 109 | 109 | 101 | 101 | 101 | 101 | 87 | 87 | 87 | 74 | 74 | 74 | 62 | 62 | 62 |
| 1   | 99  | 95  | 91  | 87  | 92  | 88  | 85  | 82  | 76 | 74 | 72 | 65 | 63 | 62 | 55 | 54 | 53 |
| 2   | 90  | 83  | 77  | 71  | 84  | 77  | 72  | 67  | 67 | 63 | 59 | 57 | 54 | 52 | 48 | 46 | 44 |
| 3   | 82  | 73  | 65  | 60  | 76  | 68  | 62  | 56  | 59 | 54 | 50 | 51 | 47 | 44 | 43 | 40 | 38 |
| 4   | 75  | 65  | 57  | 50  | 70  | 60  | 53  | 48  | 53 | 47 | 43 | 45 | 41 | 37 | 38 | 35 | 33 |
| 5   | 69  | 58  | 49  | 43  | 64  | 54  | 47  | 41  | 47 | 41 | 37 | 41 | 36 | 32 | 35 | 31 | 28 |
| 6   | 64  | 52  | 43  | 38  | 59  | 48  | 41  | 36  | 42 | 36 | 32 | 37 | 32 | 28 | 31 | 28 | 25 |
| 7   | 59  | 47  | 39  | 33  | 55  | 44  | 37  | 31  | 38 | 33 | 28 | 33 | 29 | 25 | 29 | 25 | 22 |
| 8   | 55  | 42  | 35  | 29  | 51  | 40  | 33  | 28  | 35 | 29 | 25 | 31 | 26 | 23 | 26 | 23 | 20 |
| 9   | 51  | 39  | 31  | 26  | 48  | 37  | 30  | 25  | 32 | 27 | 23 | 28 | 24 | 20 | 24 | 21 | 18 |
| 10  | 48  | 36  | 28  | 23  | 45  | 34  | 27  | 22  | 30 | 24 | 20 | 26 | 22 | 18 | 23 | 19 | 16 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2977 | 2977 | 2977 |
| 5°  | 2980 | 2934 | 2955 |
| 10° | 2954 | 2892 | 2914 |
| 15° | 2909 | 2843 | 2850 |
| 20° | 2848 | 2775 | 2785 |
| 25° | 2788 | 2694 | 2710 |
| 30° | 2713 | 2618 | 2615 |
| 35° | 2641 | 2529 | 2515 |
| 40° | 2554 | 2439 | 2419 |
| 45° | 2466 | 2349 | 2321 |
| 50° | 2371 | 2254 | 2208 |
| 55° | 2270 | 2145 | 2103 |
| 60° | 2157 | 2015 | 1984 |
| 65° | 2033 | 1880 | 1842 |
| 70° | 1875 | 1716 | 1690 |
| 75° | 1656 | 1519 | 1549 |
| 80° | 1391 | 1267 | 1280 |
| 85° | 981  | 840  | 838  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 2466 cd/sqm

TEST NUMBER: P925552

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US950-FLLFLL

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 244.6   | 2.1       |
| 10°-20°   | 688.1   | 5.9       |
| 20°-30°   | 1011.3  | 8.7       |
| 30°-40°   | 1174.5  | 10.1      |
| 40°-50°   | 1173.1  | 10.0      |
| 50°-60°   | 1022.9  | 8.8       |
| 60°-70°   | 756.1   | 6.5       |
| 70°-80°   | 427.8   | 3.7       |
| 80°-90°   | 118.1   | 1.0       |
| 90°-100°  | 112.0   | 1.0       |
| 100°-110° | 355.9   | 3.0       |
| 110°-120° | 609.1   | 5.2       |
| 120°-130° | 801.1   | 6.9       |
| 130°-140° | 899.2   | 7.7       |
| 140°-150° | 881.7   | 7.6       |
| 150°-160° | 739.6   | 6.3       |
| 160°-170° | 490.5   | 4.2       |
| 170°-180° | 171.4   | 1.5       |
| 0°-30°    | 1943.9  | 16.6      |
| 0°-40°    | 3118.5  | 26.7      |
| 0°-60°    | 5314.4  | 45.5      |
| 0°-90°    | 6616.4  | 56.7      |
| 90°-120°  | 1077.0  | 9.2       |
| 90°-150°  | 3659.0  | 31.3      |
| 90°-180°  | 5061.0  | 43.3      |
| 0°-180°   | 11677.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|------|------|-------|------|-------|------|------|
| 0°   | 2598 | 2598  | 2598 | 2598  | 2598 |      |
| 5°   | 2598 | 2589  | 2561 | 2581  | 2576 | 247  |
| 15°  | 2474 | 2459  | 2426 | 2436  | 2424 | 697  |
| 25°  | 2239 | 2219  | 2176 | 2181  | 2176 | 1030 |
| 35°  | 1932 | 1907  | 1866 | 1851  | 1839 | 1206 |
| 45°  | 1572 | 1554  | 1517 | 1489  | 1479 | 1213 |
| 55°  | 1189 | 1174  | 1144 | 1114  | 1102 | 1063 |
| 65°  | 802  | 787   | 762  | 740   | 727  | 793  |
| 75°  | 420  | 415   | 402  | 387   | 392  | 448  |
| 85°  | 102  | 100   | 98   | 90    | 88   | 114  |
| 90°  | 2    | 20    | 54   | 50    | 52   | 11   |
| 95°  | 80   | 95    | 98   | 98    | 95   | 89   |
| 105° | 329  | 333   | 336  | 339   | 339  | 347  |
| 115° | 611  | 620   | 617  | 616   | 611  | 605  |
| 125° | 889  | 903   | 898  | 893   | 892  | 794  |
| 135° | 1150 | 1167  | 1170 | 1168  | 1164 | 889  |
| 145° | 1396 | 1407  | 1416 | 1417  | 1411 | 872  |
| 155° | 1596 | 1601  | 1606 | 1613  | 1608 | 735  |
| 165° | 1737 | 1735  | 1735 | 1746  | 1738 | 490  |
| 175° | 1807 | 1803  | 1799 | 1810  | 1801 | 172  |
| 180° | 1810 | 1810  | 1810 | 1810  | 1810 |      |

TEST NUMBER: P925552

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US950-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 0°     | 2598.4 | 2598.4 | 2598.4 | 2598.4 | 2598.4 |
| 2.5°   | 2613.6 | 2601.1 | 2573.5 | 2598.4 | 2593.6 |
| 5°     | 2598.4 | 2588.7 | 2561.1 | 2581.0 | 2576.2 |
| 7.5°   | 2581.0 | 2566.1 | 2538.5 | 2558.7 | 2553.7 |
| 10°    | 2553.7 | 2536.1 | 2506.2 | 2526.1 | 2518.7 |
| 12.5°  | 2516.0 | 2501.2 | 2471.2 | 2483.6 | 2478.6 |
| 15°    | 2473.6 | 2458.7 | 2426.1 | 2436.2 | 2423.7 |
| 17.5°  | 2421.1 | 2406.3 | 2373.6 | 2386.1 | 2373.6 |
| 20°    | 2363.5 | 2348.7 | 2313.7 | 2321.2 | 2311.4 |
| 22.5°  | 2306.3 | 2283.8 | 2251.2 | 2251.2 | 2246.1 |
| 25°    | 2238.8 | 2218.8 | 2176.5 | 2181.2 | 2176.5 |
| 27.5°  | 2163.7 | 2146.2 | 2113.9 | 2106.4 | 2093.9 |
| 30°    | 2089.0 | 2068.7 | 2031.4 | 2024.0 | 2013.9 |
| 32.5°  | 2008.8 | 1994.1 | 1954.0 | 1938.9 | 1928.8 |
| 35°    | 1931.5 | 1906.6 | 1866.5 | 1851.4 | 1838.9 |
| 37.5°  | 1844.0 | 1821.5 | 1781.4 | 1763.9 | 1751.4 |
| 40°    | 1754.1 | 1734.0 | 1693.9 | 1671.7 | 1661.6 |
| 42.5°  | 1666.6 | 1646.5 | 1606.7 | 1581.5 | 1566.7 |
| 45°    | 1571.7 | 1554.3 | 1516.6 | 1489.3 | 1479.2 |
| 47.5°  | 1479.2 | 1461.7 | 1421.7 | 1394.1 | 1379.3 |
| 50°    | 1381.7 | 1369.2 | 1334.2 | 1299.3 | 1286.8 |
| 52.5°  | 1286.8 | 1269.3 | 1237.0 | 1209.4 | 1191.8 |
| 55°    | 1189.4 | 1174.4 | 1144.4 | 1114.5 | 1102.0 |
| 57.5°  | 1091.9 | 1079.5 | 1046.8 | 1016.9 | 1006.9 |
| 60°    | 994.4  | 984.5  | 949.6  | 922.0  | 914.6  |
| 62.5°  | 899.4  | 882.0  | 857.1  | 832.2  | 822.1  |
| 65°    | 802.2  | 787.0  | 762.2  | 739.6  | 727.1  |
| 67.5°  | 702.2  | 689.6  | 667.2  | 649.8  | 639.7  |
| 70°    | 609.7  | 599.7  | 577.1  | 559.6  | 549.8  |
| 72.5°  | 514.8  | 504.8  | 492.3  | 474.8  | 467.4  |
| 75°    | 419.7  | 414.9  | 402.1  | 387.3  | 392.4  |
| 77.5°  | 334.9  | 324.7  | 319.7  | 312.2  | 304.9  |
| 80°    | 249.9  | 247.4  | 242.3  | 234.9  | 229.8  |
| 82.5°  | 169.9  | 169.9  | 167.5  | 157.5  | 157.5  |
| 85°    | 102.4  | 100.0  | 97.6   | 89.9   | 87.5   |
| 87.5°  | 45.0   | 40.1   | 35.0   | 27.6   | 24.9   |
| 90°    | 1.6    | 19.7   | 53.5   | 50.2   | 51.8   |
| 92.5°  | 33.9   | 45.9   | 47.5   | 49.1   | 49.1   |
| 95°    | 79.7   | 94.9   | 97.7   | 97.7   | 94.9   |
| 97.5°  | 132.6  | 146.8  | 152.8  | 152.8  | 152.8  |
| 100°   | 193.8  | 206.3  | 210.6  | 210.6  | 209.0  |
| 102.5° | 258.2  | 267.4  | 273.4  | 275.0  | 273.4  |
| 105°   | 328.6  | 332.9  | 336.2  | 339.0  | 339.0  |
| 107.5° | 398.4  | 405.0  | 405.0  | 406.0  | 398.4  |
| 110°   | 466.1  | 474.8  | 474.8  | 474.8  | 470.4  |

TEST NUMBER: P925552

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US950-FLLFL

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 112.5° | 539.2  | 548.5  | 546.8  | 542.4  | 539.2  |
| 115°   | 611.2  | 620.0  | 617.2  | 615.6  | 611.2  |
| 117.5° | 682.8  | 694.8  | 687.1  | 682.8  | 678.4  |
| 120°   | 754.8  | 766.8  | 754.8  | 754.8  | 749.8  |
| 122.5° | 820.2  | 835.5  | 827.9  | 823.6  | 820.2  |
| 125°   | 889.0  | 902.7  | 898.3  | 893.4  | 891.8  |
| 127.5° | 956.2  | 973.1  | 967.1  | 960.6  | 956.2  |
| 130°   | 1019.0 | 1038.6 | 1035.9 | 1032.6 | 1026.6 |
| 132.5° | 1089.4 | 1104.6 | 1105.7 | 1098.1 | 1093.7 |
| 135°   | 1150.0 | 1166.8 | 1170.1 | 1168.5 | 1164.1 |
| 137.5° | 1217.6 | 1231.2 | 1234.0 | 1232.9 | 1226.4 |
| 140°   | 1277.1 | 1290.8 | 1298.4 | 1298.4 | 1292.4 |
| 142.5° | 1338.2 | 1351.8 | 1356.2 | 1357.8 | 1351.8 |
| 145°   | 1396.1 | 1407.0 | 1415.7 | 1417.4 | 1411.3 |
| 147.5° | 1447.9 | 1461.5 | 1468.1 | 1470.8 | 1464.8 |
| 150°   | 1501.4 | 1510.7 | 1516.7 | 1521.5 | 1516.7 |
| 152.5° | 1548.8 | 1558.2 | 1565.8 | 1571.8 | 1565.8 |
| 155°   | 1596.3 | 1600.7 | 1605.6 | 1613.3 | 1608.3 |
| 157.5° | 1637.3 | 1640.6 | 1643.3 | 1654.2 | 1646.6 |
| 160°   | 1673.9 | 1677.1 | 1678.8 | 1688.0 | 1681.5 |
| 162.5° | 1707.7 | 1707.7 | 1709.3 | 1719.7 | 1712.0 |
| 165°   | 1736.6 | 1734.9 | 1734.9 | 1745.9 | 1738.3 |
| 167.5° | 1762.8 | 1757.9 | 1757.9 | 1768.8 | 1761.2 |
| 170°   | 1782.5 | 1778.1 | 1776.4 | 1787.3 | 1778.1 |
| 172.5° | 1796.1 | 1791.7 | 1790.1 | 1801.0 | 1791.7 |
| 175°   | 1807.0 | 1802.7 | 1799.3 | 1810.3 | 1801.0 |
| 177.5° | 1813.0 | 1808.7 | 1805.3 | 1814.6 | 1805.3 |
| 180°   | 1810.3 | 1810.3 | 1810.3 | 1810.3 | 1810.3 |

TEST NUMBER: P925552

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US950-FLLFLL

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 11.62            | 12.55 | 12.52 | 13.46 | 14.64 | 11.18          | 12.10 | 12.07 | 13.02 | 14.19 |
|                 | 3H   | 13.28            | 14.11 | 14.19 | 15.04 | 16.24 | 12.79          | 13.62 | 13.70 | 14.55 | 15.75 |
|                 | 4H   | 13.87            | 14.65 | 14.79 | 15.59 | 16.79 | 13.38          | 14.16 | 14.30 | 15.09 | 16.30 |
|                 | 6H   | 14.27            | 14.99 | 15.21 | 15.93 | 17.15 | 13.77          | 14.49 | 14.70 | 15.43 | 16.65 |
|                 | 8H   | 14.37            | 15.06 | 15.32 | 16.02 | 17.24 | 13.87          | 14.56 | 14.82 | 15.52 | 16.73 |
|                 | 12H  | 14.42            | 15.08 | 15.37 | 16.03 | 17.27 | 13.91          | 14.57 | 14.86 | 15.52 | 16.76 |
| 4H              | 2H   | 12.09            | 12.87 | 13.02 | 13.80 | 15.01 | 11.73          | 12.52 | 12.66 | 13.45 | 14.65 |
|                 | 3H   | 13.95            | 14.61 | 14.89 | 15.57 | 16.79 | 13.54          | 14.20 | 14.48 | 15.16 | 16.38 |
|                 | 4H   | 14.67            | 15.26 | 15.62 | 16.22 | 17.47 | 14.24          | 14.84 | 15.19 | 15.80 | 17.04 |
|                 | 6H   | 15.18            | 15.70 | 16.14 | 16.68 | 17.92 | 14.75          | 15.26 | 15.71 | 16.24 | 17.49 |
|                 | 8H   | 15.33            | 15.81 | 16.29 | 16.79 | 18.05 | 14.89          | 15.37 | 15.86 | 16.35 | 17.61 |
|                 | 12H  | 15.40            | 15.84 | 16.39 | 16.83 | 18.09 | 14.95          | 15.39 | 15.94 | 16.38 | 17.65 |
| 8H              | 4H   | 14.86            | 15.34 | 15.83 | 16.32 | 17.58 | 14.49          | 14.97 | 15.45 | 15.94 | 17.20 |
|                 | 6H   | 15.49            | 15.89 | 16.48 | 16.91 | 18.16 | 15.11          | 15.51 | 16.10 | 16.52 | 17.78 |
|                 | 8H   | 15.71            | 16.06 | 16.71 | 17.07 | 18.34 | 15.32          | 15.67 | 16.32 | 16.67 | 17.95 |
|                 | 12H  | 15.84            | 16.15 | 16.84 | 17.15 | 18.47 | 15.43          | 15.74 | 16.43 | 16.74 | 18.06 |
| 12H             | 4H   | 14.85            | 15.29 | 15.84 | 16.28 | 17.54 | 14.48          | 14.92 | 15.47 | 15.91 | 17.17 |
|                 | 6H   | 15.52            | 15.87 | 16.52 | 16.88 | 18.15 | 15.15          | 15.50 | 16.15 | 16.50 | 17.78 |
|                 | 8H   | 15.76            | 16.07 | 16.76 | 17.07 | 18.39 | 15.38          | 15.69 | 16.38 | 16.69 | 18.01 |