

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925588

Luminaire Tested: DFN2DIP-SQ3F0-080D060US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925588
REPORT IS A COMBINATION OF REPORTS P899905 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-080D060US950-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12621.4 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 121.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925588

CATALOG NUMBER: DFN2DIP-SQ3F0-080D060US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925588

CATALOG NUMBER: DFN2DIP-SQ3F0-080D060US950-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89		77	77	77		65
1	100	96	92	88	93	89	86	83	78	75	73		67	66	64		58
2	91	84	77	72	85	78	73	68	68	64	61		59	56	53		51
3	83	73	66	60	77	69	62	57	60	55	51		52	48	45		45
4	76	65	57	51	71	61	54	48	54	48	43		47	42	39		40
5	70	58	50	44	65	55	47	42	48	42	38		42	37	34		36
6	64	52	44	38	60	49	42	36	43	37	33		38	33	29		33
7	60	47	39	33	56	44	37	32	39	33	29		35	30	26		30
8	55	43	35	30	52	40	33	28	36	30	26		32	27	23		28
9	52	39	32	26	48	37	30	25	33	27	23		29	24	21		26
10	48	36	29	24	45	34	27	23	30	25	21		27	22	19		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3403	3403	3403
5°	3406	3353	3377
10°	3376	3306	3330
15°	3324	3249	3257
20°	3255	3171	3183
25°	3186	3078	3098
30°	3100	2992	2989
35°	3019	2890	2874
40°	2919	2788	2765
45°	2819	2685	2653
50°	2709	2576	2523
55°	2595	2451	2404
60°	2465	2303	2267
65°	2323	2149	2106
70°	2142	1961	1932
75°	1893	1736	1770
80°	1591	1448	1462
85°	1120	960	958

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2819 cd/sqm

TEST NUMBER: P925588

CATALOG NUMBER: DFN2DIP-SQ3F0-080D060US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.5	2.2
10°-20°	786.4	6.2
20°-30°	1155.7	9.2
30°-40°	1342.3	10.6
40°-50°	1340.6	10.6
50°-60°	1169.0	9.3
60°-70°	864.1	6.8
70°-80°	488.9	3.9
80°-90°	134.2	1.1
90°-100°	112.0	0.9
100°-110°	355.9	2.8
110°-120°	609.1	4.8
120°-130°	801.1	6.3
130°-140°	899.2	7.1
140°-150°	881.7	7.0
150°-160°	739.6	5.9
160°-170°	490.5	3.9
170°-180°	171.4	1.4
0°-30°	2221.6	17.6
0°-40°	3563.9	28.2
0°-60°	6073.6	48.1
0°-90°	7560.8	59.9
90°-120°	1077.0	8.5
90°-150°	3659.0	29.0
90°-180°	5061.0	40.1
0°-180°	12621.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2970	2970	2970	2970	2970	
5°	2970	2958	2927	2950	2944	282
15°	2827	2810	2773	2784	2770	796
25°	2558	2536	2487	2493	2487	1177
35°	2207	2179	2133	2116	2102	1378
45°	1796	1776	1733	1702	1691	1386
55°	1359	1342	1308	1274	1259	1215
65°	917	900	871	845	831	906
75°	480	474	460	443	448	512
85°	117	114	112	103	100	130
90°	2	20	54	50	52	12
95°	80	95	98	98	95	89
105°	329	333	336	339	339	347
115°	611	620	617	616	611	605
125°	889	903	898	893	892	794
135°	1150	1167	1170	1168	1164	889
145°	1396	1407	1416	1417	1411	872
155°	1596	1601	1606	1613	1608	735
165°	1737	1735	1735	1746	1738	490
175°	1807	1803	1799	1810	1801	172
180°	1810	1810	1810	1810	1810	

TEST NUMBER: P925588

CATALOG NUMBER: DFN2DIP-SQ3F0-080D060US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2969.6	2969.6	2969.6	2969.6	2969.6
2.5°	2986.9	2972.7	2941.2	2969.6	2964.2
5°	2969.6	2958.4	2927.0	2949.7	2944.2
7.5°	2949.7	2932.7	2901.2	2924.2	2918.5
10°	2918.5	2898.4	2864.2	2886.9	2878.5
12.5°	2875.5	2858.5	2824.2	2838.4	2832.7
15°	2827.0	2810.0	2772.7	2784.2	2770.0
17.5°	2767.0	2750.0	2712.7	2727.0	2712.7
20°	2701.3	2684.3	2644.3	2652.8	2641.5
22.5°	2635.8	2610.0	2572.7	2572.7	2567.0
25°	2558.5	2535.8	2487.4	2492.8	2487.4
27.5°	2472.8	2452.8	2415.8	2407.3	2393.1
30°	2387.4	2364.3	2321.7	2313.2	2301.6
32.5°	2295.9	2278.9	2233.1	2215.9	2204.4
35°	2207.4	2178.9	2133.1	2115.9	2101.7
37.5°	2107.4	2081.6	2035.9	2015.9	2001.7
40°	2004.7	1981.6	1936.0	1910.5	1898.9
42.5°	1904.8	1881.7	1836.3	1807.4	1790.6
45°	1796.3	1776.3	1733.2	1702.0	1690.6
47.5°	1690.6	1670.5	1624.8	1593.3	1576.3
50°	1579.1	1564.8	1524.8	1484.8	1470.6
52.5°	1470.6	1450.6	1413.6	1382.2	1362.1
55°	1359.4	1342.1	1307.9	1273.7	1259.4
57.5°	1247.9	1233.7	1196.4	1162.2	1150.6
60°	1136.4	1125.2	1085.2	1053.7	1045.2
62.5°	1027.9	1008.0	979.5	951.0	939.5
65°	916.8	899.5	871.0	845.2	831.0
67.5°	802.5	788.0	762.5	742.6	731.1
70°	696.8	685.3	659.6	639.6	628.3
72.5°	588.3	576.9	562.6	542.6	534.1
75°	479.6	474.1	459.6	442.7	448.4
77.5°	382.6	371.1	365.4	356.9	348.4
80°	285.7	282.7	276.9	268.5	262.6
82.5°	194.2	194.2	191.5	179.9	179.9
85°	117.0	114.2	111.5	102.7	100.0
87.5°	51.5	45.8	40.0	31.5	28.5
90°	1.6	19.7	53.5	50.2	51.8
92.5°	33.9	45.9	47.5	49.1	49.1
95°	79.7	94.9	97.7	97.7	94.9
97.5°	132.6	146.8	152.8	152.8	152.8
100°	193.8	206.3	210.6	210.6	209.0
102.5°	258.2	267.4	273.4	275.0	273.4
105°	328.6	332.9	336.2	339.0	339.0
107.5°	398.4	405.0	405.0	406.0	398.4
110°	466.1	474.8	474.8	474.8	470.4

TEST NUMBER: P925588

CATALOG NUMBER: DFN2DIP-SQ3F0-080D060US950-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	539.2	548.5	546.8	542.4	539.2
115°	611.2	620.0	617.2	615.6	611.2
117.5°	682.8	694.8	687.1	682.8	678.4
120°	754.8	766.8	754.8	754.8	749.8
122.5°	820.2	835.5	827.9	823.6	820.2
125°	889.0	902.7	898.3	893.4	891.8
127.5°	956.2	973.1	967.1	960.6	956.2
130°	1019.0	1038.6	1035.9	1032.6	1026.6
132.5°	1089.4	1104.6	1105.7	1098.1	1093.7
135°	1150.0	1166.8	1170.1	1168.5	1164.1
137.5°	1217.6	1231.2	1234.0	1232.9	1226.4
140°	1277.1	1290.8	1298.4	1298.4	1292.4
142.5°	1338.2	1351.8	1356.2	1357.8	1351.8
145°	1396.1	1407.0	1415.7	1417.4	1411.3
147.5°	1447.9	1461.5	1468.1	1470.8	1464.8
150°	1501.4	1510.7	1516.7	1521.5	1516.7
152.5°	1548.8	1558.2	1565.8	1571.8	1565.8
155°	1596.3	1600.7	1605.6	1613.3	1608.3
157.5°	1637.3	1640.6	1643.3	1654.2	1646.6
160°	1673.9	1677.1	1678.8	1688.0	1681.5
162.5°	1707.7	1707.7	1709.3	1719.7	1712.0
165°	1736.6	1734.9	1734.9	1745.9	1738.3
167.5°	1762.8	1757.9	1757.9	1768.8	1761.2
170°	1782.5	1778.1	1776.4	1787.3	1778.1
172.5°	1796.1	1791.7	1790.1	1801.0	1791.7
175°	1807.0	1802.7	1799.3	1810.3	1801.0
177.5°	1813.0	1808.7	1805.3	1814.6	1805.3
180°	1810.3	1810.3	1810.3	1810.3	1810.3

TEST NUMBER: P925588

CATALOG NUMBER: DFN2DIP-SQ3F0-080D060US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.36	13.32	13.23	14.20	15.33	11.91	12.87	12.78	13.76	14.88
	3H	14.02	14.88	14.90	15.78	16.93	13.53	14.39	14.41	15.29	16.44
	4H	14.61	15.42	15.51	16.33	17.49	14.12	14.93	15.01	15.83	16.99
	6H	15.01	15.76	15.92	16.67	17.84	14.51	15.26	15.42	16.17	17.34
	8H	15.12	15.83	16.03	16.76	17.93	14.62	15.33	15.53	16.26	17.43
	12H	15.17	15.85	16.09	16.77	17.97	14.66	15.34	15.58	16.26	17.46
4H	2H	12.83	13.64	13.73	14.54	15.70	12.47	13.29	13.37	14.19	15.35
	3H	14.70	15.37	15.61	16.31	17.48	14.29	14.97	15.20	15.90	17.08
	4H	15.41	16.03	16.33	16.96	18.16	14.99	15.61	15.91	16.54	17.74
	6H	15.93	16.46	16.86	17.42	18.62	15.49	16.03	16.43	16.98	18.18
	8H	16.08	16.58	17.01	17.52	18.74	15.64	16.14	16.58	17.09	18.30
	12H	16.15	16.60	17.11	17.57	18.79	15.70	16.15	16.66	17.12	18.34
8H	4H	15.61	16.11	16.55	17.06	18.27	15.23	15.73	16.17	16.68	17.90
	6H	16.24	16.65	17.20	17.64	18.86	15.86	16.27	16.82	17.26	18.47
	8H	16.46	16.82	17.43	17.80	19.03	16.07	16.43	17.04	17.41	18.64
	12H	16.59	16.91	17.57	17.89	19.16	16.18	16.50	17.16	17.48	18.75
12H	4H	15.60	16.05	16.56	17.02	18.24	15.23	15.68	16.19	16.65	17.87
	6H	16.27	16.64	17.24	17.62	18.84	15.90	16.26	16.87	17.24	18.47
	8H	16.51	16.83	17.49	17.81	19.08	16.13	16.45	17.11	17.43	18.70

END OF REPORT