

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925622

Luminaire Tested: DFN2DIP-SQ3F0-090D050US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925622
REPORT IS A COMBINATION OF REPORTS P899890 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-090D050US950-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11519.6 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 124.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925622

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925622

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	68	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	47	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	37	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4066	4066	4066
5°	4070	3999	4026
10°	4027	3918	3893
15°	3969	3786	3690
20°	3893	3605	3440
25°	3815	3402	3199
30°	3712	3195	2894
35°	3610	2972	2626
40°	3507	2742	2319
45°	3387	2487	2041
50°	3262	2230	1769
55°	3132	1956	1508
60°	2981	1670	1240
65°	2808	1379	1115
70°	2597	1107	1007
75°	2332	970	913
80°	1948	805	787
85°	1320	525	584

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3387 cd/sqm

TEST NUMBER: P925622

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.6	2.9
10°-20°	913.0	7.9
20°-30°	1281.8	11.1
30°-40°	1397.3	12.1
40°-50°	1284.2	11.1
50°-60°	1008.6	8.8
60°-70°	656.5	5.7
70°-80°	337.9	2.9
80°-90°	90.6	0.8
90°-100°	93.4	0.8
100°-110°	296.6	2.6
110°-120°	507.6	4.4
120°-130°	667.5	5.8
130°-140°	749.3	6.5
140°-150°	734.8	6.4
150°-160°	616.4	5.4
160°-170°	408.8	3.5
170°-180°	142.9	1.2
0°-30°	2527.4	21.9
0°-40°	3924.6	34.1
0°-60°	6217.4	54.0
0°-90°	7302.4	63.4
90°-120°	897.5	7.8
90°-150°	3049.2	26.5
90°-180°	4217.0	36.6
0°-180°	11519.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3549	3549	3549	3549	3549	
5°	3549	3533	3491	3520	3510	336
15°	3375	3340	3231	3170	3138	951
25°	3064	2961	2749	2617	2569	1409
35°	2640	2476	2194	1991	1920	1652
45°	2158	1943	1606	1378	1300	1667
55°	1641	1390	1044	851	790	1466
65°	1108	848	559	450	440	1099
75°	591	366	257	234	231	625
85°	138	70	61	61	61	158
90°	1	16	45	42	43	11
95°	66	79	81	81	79	74
105°	274	277	280	282	282	289
115°	509	517	514	513	509	504
125°	741	752	749	744	743	662
135°	958	972	975	974	970	741
145°	1163	1172	1180	1181	1176	727
155°	1330	1334	1338	1344	1340	612
165°	1447	1446	1446	1455	1449	408
175°	1506	1502	1500	1509	1501	143
180°	1509	1509	1509	1509	1509	

TEST NUMBER: P925622

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3548.6	3548.6	3548.6	3548.6	3548.6
2.5°	3564.6	3548.6	3513.1	3545.5	3539.1
5°	3548.6	3532.6	3490.7	3519.6	3510.1
7.5°	3519.6	3500.5	3455.6	3468.2	3452.1
10°	3481.1	3458.6	3394.6	3384.7	3365.6
12.5°	3433.1	3404.2	3317.2	3298.2	3262.7
15°	3375.2	3339.8	3230.7	3169.7	3137.7
17.5°	3307.7	3256.3	3121.3	3050.8	2999.4
20°	3230.7	3166.3	3005.8	2925.7	2854.8
22.5°	3147.2	3073.3	2886.9	2777.9	2729.9
25°	3063.8	2960.8	2749.0	2617.4	2569.0
27.5°	2964.3	2854.8	2620.4	2469.5	2395.6
30°	2858.3	2736.0	2479.1	2315.5	2228.6
32.5°	2755.3	2607.5	2344.5	2151.7	2071.2
35°	2639.9	2476.0	2193.5	1991.2	1920.3
37.5°	2527.4	2350.7	2052.1	1830.3	1750.3
40°	2408.6	2216.0	1904.3	1676.4	1592.9
42.5°	2286.5	2081.2	1756.7	1519.0	1438.8
45°	2158.1	1942.8	1605.8	1377.5	1300.5
47.5°	2036.1	1808.2	1461.3	1233.0	1162.5
50°	1901.2	1673.2	1320.0	1098.1	1031.0
52.5°	1769.4	1528.5	1185.1	973.1	912.1
55°	1640.9	1390.5	1043.6	851.2	790.1
57.5°	1509.4	1252.5	918.6	738.7	687.3
60°	1374.4	1117.5	786.8	623.2	571.7
62.5°	1243.0	986.1	674.3	520.3	494.7
65°	1108.0	847.7	558.8	449.7	439.9
67.5°	979.6	719.2	449.7	394.9	385.3
70°	844.7	594.2	372.4	340.4	327.4
72.5°	716.2	478.3	311.4	285.8	279.4
75°	590.8	366.0	256.9	234.4	231.3
77.5°	465.7	260.0	202.3	189.5	183.0
80°	349.9	186.4	154.0	141.4	141.4
82.5°	243.9	125.4	106.0	99.5	99.5
85°	137.9	70.5	61.0	61.0	61.0
87.5°	51.4	25.6	25.6	22.5	22.5
90°	1.3	16.4	44.6	41.9	43.2
92.5°	28.2	38.2	39.6	40.9	40.9
95°	66.4	79.2	81.4	81.4	79.2
97.5°	110.5	122.3	127.4	127.4	127.4
100°	161.4	171.9	175.5	175.5	174.2
102.5°	215.1	222.9	227.8	229.2	227.8
105°	273.8	277.4	280.2	282.4	282.4
107.5°	332.0	337.4	337.4	338.4	332.0
110°	388.4	395.7	395.7	395.7	392.0

TEST NUMBER: P925622

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	449.3	457.1	455.7	452.1	449.3
115°	509.3	516.7	514.4	513.1	509.3
117.5°	569.0	579.0	572.6	569.0	565.3
120°	629.0	639.0	629.0	629.0	624.9
122.5°	683.5	696.3	689.9	686.3	683.5
125°	740.9	752.2	748.6	744.5	743.2
127.5°	796.8	810.9	805.9	800.4	796.8
130°	849.2	865.5	863.2	860.5	855.5
132.5°	907.8	920.5	921.5	915.1	911.5
135°	958.3	972.3	975.1	973.7	970.1
137.5°	1014.7	1026.0	1028.3	1027.4	1021.9
140°	1064.2	1075.6	1081.9	1081.9	1077.0
142.5°	1115.1	1126.6	1130.2	1131.5	1126.6
145°	1163.4	1172.5	1179.7	1181.1	1176.1
147.5°	1206.6	1218.0	1223.4	1225.7	1220.6
150°	1251.2	1258.9	1263.9	1268.0	1263.9
152.5°	1290.8	1298.5	1304.8	1309.8	1304.8
155°	1330.3	1333.9	1338.0	1344.4	1340.3
157.5°	1364.4	1367.1	1369.4	1378.5	1372.1
160°	1394.8	1397.6	1398.9	1406.7	1401.2
162.5°	1423.1	1423.1	1424.4	1433.1	1426.7
165°	1447.2	1445.8	1445.8	1454.9	1448.6
167.5°	1469.0	1464.9	1464.9	1474.0	1467.6
170°	1485.4	1481.8	1480.4	1489.5	1481.8
172.5°	1496.7	1493.1	1491.8	1500.8	1493.1
175°	1505.9	1502.2	1499.5	1508.6	1500.8
177.5°	1510.8	1507.2	1504.5	1512.2	1504.5
180°	1508.6	1508.6	1508.6	1508.6	1508.6

TEST NUMBER: P925622

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.15	14.10	13.99	14.96	16.03	9.11	10.07	9.95	10.92	11.99
	3H	14.83	15.69	15.69	16.55	17.65	10.30	11.16	11.16	12.02	13.12
	4H	15.45	16.25	16.32	17.12	18.23	10.76	11.56	11.63	12.43	13.54
	6H	15.87	16.61	16.75	17.49	18.61	11.08	11.82	11.96	12.70	13.82
	8H	16.00	16.70	16.89	17.60	18.72	11.17	11.87	12.06	12.77	13.89
	12H	16.06	16.73	16.96	17.62	18.77	11.21	11.88	12.11	12.77	13.92
4H	2H	13.18	13.99	14.06	14.86	15.97	9.72	10.52	10.60	11.40	12.51
	3H	15.02	15.69	15.90	16.59	17.71	11.07	11.74	11.96	12.65	13.77
	4H	15.71	16.32	16.61	17.22	18.37	11.62	12.23	12.52	13.13	14.28
	6H	16.23	16.75	17.14	17.68	18.83	12.04	12.56	12.95	13.49	14.64
	8H	16.40	16.89	17.32	17.81	18.98	12.17	12.66	13.08	13.58	14.74
	12H	16.50	16.94	17.43	17.88	19.05	12.24	12.67	13.17	13.61	14.78
8H	4H	15.69	16.18	16.60	17.10	18.26	11.91	12.40	12.82	13.32	14.48
	6H	16.25	16.66	17.19	17.62	18.78	12.42	12.83	13.36	13.79	14.95
	8H	16.47	16.82	17.42	17.78	18.96	12.61	12.97	13.56	13.92	15.10
	12H	16.61	16.92	17.56	17.87	19.10	12.73	13.04	13.68	13.99	15.22
12H	4H	15.64	16.08	16.58	17.02	18.19	11.92	12.36	12.85	13.30	14.47
	6H	16.23	16.58	17.18	17.54	18.72	12.47	12.83	13.42	13.78	14.96
	8H	16.45	16.76	17.40	17.71	18.94	12.68	13.00	13.63	13.94	15.17