

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920064

Luminaire Tested: DFN2DIP-SQ3F0-060D070US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920064
REPORT IS A COMBINATION OF REPORTS P899919 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-060D070US935-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10448.2 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 105.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920064
CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P920064

CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				49
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41				41
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39	35				35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29				29
4	74	63	55	49	68	59	52	46	50	45	40	42	38	34	34	31	29	25				25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22				22
6	63	51	43	37	58	47	40	35	40	35	30	34	29	26	28	25	22	19				19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17				17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15				15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16	14				14
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14	12				12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2303	2303	2303
5°	2305	2270	2286
10°	2285	2237	2254
15°	2250	2199	2205
20°	2203	2146	2155
25°	2157	2084	2097
30°	2099	2025	2023
35°	2043	1956	1945
40°	1975	1887	1871
45°	1908	1817	1796
50°	1834	1744	1708
55°	1756	1659	1627
60°	1668	1559	1535
65°	1572	1455	1425
70°	1450	1327	1308
75°	1281	1175	1198
80°	1077	980	990
85°	757	649	648

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1917 cd/sqm



TEST NUMBER: P920064

CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.2	1.8
10°-20°	532.3	5.1
20°-30°	782.3	7.5
30°-40°	908.6	8.7
40°-50°	907.5	8.7
50°-60°	791.3	7.6
60°-70°	584.9	5.6
70°-80°	330.9	3.2
80°-90°	92.8	0.9
90°-100°	117.9	1.1
100°-110°	374.8	3.6
110°-120°	641.3	6.1
120°-130°	843.5	8.1
130°-140°	946.7	9.1
140°-150°	928.4	8.9
150°-160°	778.8	7.5
160°-170°	516.5	4.9
170°-180°	180.5	1.7
0°-30°	1503.8	14.4
0°-40°	2412.4	23.1
0°-60°	4111.1	39.3
0°-90°	5119.7	49.0
90°-120°	1134.1	10.9
90°-150°	3852.7	36.9
90°-180°	5328.0	51.0
0°-180°	10448.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2010	2010	2010	2010	2010	
5°	2010	2002	1981	1997	1993	191
15°	1914	1902	1877	1885	1875	539
25°	1732	1716	1684	1687	1684	797
35°	1494	1475	1444	1432	1422	933
45°	1216	1202	1173	1152	1144	938
55°	920	908	885	862	852	823
65°	620	609	590	572	562	614
75°	325	321	311	300	304	347
85°	79	77	75	70	68	88
90°	2	21	56	53	55	10
95°	84	100	103	103	100	93
105°	346	350	354	357	357	365
115°	644	653	650	648	644	637
125°	936	950	946	941	939	837
135°	1211	1229	1232	1230	1226	936
145°	1470	1481	1491	1492	1486	918
155°	1681	1685	1691	1699	1694	774
165°	1828	1827	1827	1838	1830	516
175°	1903	1898	1895	1906	1896	181
180°	1906	1906	1906	1906	1906	



TEST NUMBER: P920064

CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2010.1	2010.1	2010.1	2010.1	2010.1
2.5°	2021.8	2012.2	1990.8	2010.1	2006.4
5°	2010.1	2002.5	1981.2	1996.6	1992.9
7.5°	1996.6	1985.1	1963.8	1979.3	1975.5
10°	1975.5	1962.0	1938.7	1954.1	1948.4
12.5°	1946.4	1934.8	1911.7	1921.3	1917.4
15°	1913.5	1902.0	1876.8	1884.6	1875.0
17.5°	1872.9	1861.5	1836.3	1845.8	1836.3
20°	1828.4	1817.0	1789.8	1795.6	1788.0
22.5°	1784.2	1766.7	1741.5	1741.5	1737.6
25°	1731.8	1716.5	1683.6	1687.3	1683.6
27.5°	1673.8	1660.3	1635.2	1629.5	1619.9
30°	1616.0	1600.3	1571.5	1565.7	1557.9
32.5°	1554.0	1542.6	1511.6	1499.9	1492.1
35°	1494.2	1474.9	1443.9	1432.2	1422.5
37.5°	1426.5	1409.0	1378.1	1364.5	1354.9
40°	1356.9	1341.3	1310.4	1293.2	1285.4
42.5°	1289.3	1273.7	1242.9	1223.5	1211.9
45°	1215.9	1202.3	1173.2	1152.1	1144.3
47.5°	1144.3	1130.7	1099.8	1078.5	1066.9
50°	1068.8	1059.2	1032.2	1005.0	995.4
52.5°	995.4	981.9	956.8	935.6	922.0
55°	920.1	908.4	885.3	862.1	852.5
57.5°	844.7	835.1	809.9	786.7	778.9
60°	769.2	761.6	734.6	713.3	707.5
62.5°	695.8	682.3	663.0	643.7	635.9
65°	620.5	608.9	589.6	572.1	562.5
67.5°	543.2	533.4	516.2	502.7	494.8
70°	471.7	463.9	446.4	432.9	425.3
72.5°	398.2	390.5	380.8	367.3	361.5
75°	324.6	321.0	311.1	299.6	303.5
77.5°	259.0	251.2	247.3	241.6	235.8
80°	193.4	191.3	187.4	181.7	177.8
82.5°	131.5	131.5	129.6	121.8	121.8
85°	79.1	77.3	75.4	69.5	67.7
87.5°	34.9	31.0	27.0	21.4	19.3
90°	1.7	20.7	56.3	52.9	54.6
92.5°	35.6	48.3	50.0	51.7	51.7
95°	83.9	100.0	102.9	102.9	100.0
97.5°	139.7	154.5	160.9	160.9	160.9
100°	204.0	217.2	221.8	221.8	220.1
102.5°	271.8	281.5	287.9	289.6	287.9
105°	345.9	350.5	354.0	356.9	356.9
107.5°	419.5	426.4	426.4	427.6	419.5
110°	490.8	500.0	500.0	500.0	495.3



TEST NUMBER: P920064

CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	567.7	577.6	575.8	571.2	567.7
115°	643.6	652.8	650.0	648.2	643.6
117.5°	718.8	731.5	723.5	718.8	714.3
120°	794.7	807.4	794.7	794.7	789.5
122.5°	863.7	879.8	871.8	867.1	863.7
125°	936.1	950.5	945.9	940.7	939.0
127.5°	1006.8	1024.6	1018.3	1011.4	1006.8
130°	1072.9	1093.6	1090.7	1087.3	1080.9
132.5°	1147.0	1163.1	1164.2	1156.2	1151.6
135°	1210.8	1228.6	1232.1	1230.3	1225.7
137.5°	1282.0	1296.4	1299.2	1298.1	1291.2
140°	1344.7	1359.1	1367.1	1367.1	1360.8
142.5°	1409.0	1423.4	1428.0	1429.7	1423.4
145°	1470.0	1481.4	1490.6	1492.4	1486.1
147.5°	1524.6	1538.9	1545.8	1548.7	1542.4
150°	1580.9	1590.6	1597.0	1602.1	1597.0
152.5°	1630.8	1640.6	1648.6	1655.0	1648.6
155°	1680.8	1685.4	1690.7	1698.7	1693.5
157.5°	1724.0	1727.4	1730.3	1741.8	1733.7
160°	1762.5	1765.9	1767.6	1777.4	1770.5
162.5°	1798.1	1798.1	1799.8	1810.7	1802.7
165°	1828.5	1826.8	1826.8	1838.3	1830.2
167.5°	1856.1	1851.0	1851.0	1862.4	1854.4
170°	1876.8	1872.2	1870.5	1882.0	1872.2
172.5°	1891.2	1886.5	1884.8	1896.3	1886.5
175°	1902.6	1898.1	1894.6	1906.1	1896.3
177.5°	1909.0	1904.4	1900.9	1910.7	1900.9
180°	1906.1	1906.1	1906.1	1906.1	1906.1



TEST NUMBER: P920064
 CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.04	10.89	11.01	11.87	13.16	9.60	10.45	10.56	11.43	12.72
	3H	11.70	12.46	12.67	13.45	14.76	11.21	11.97	12.18	12.96	14.27
	4H	12.28	13.01	13.27	14.00	15.31	11.79	12.51	12.78	13.50	14.82
	6H	12.68	13.34	13.68	14.34	15.67	12.18	12.84	13.18	13.84	15.17
	8H	12.78	13.41	13.79	14.43	15.75	12.28	12.91	13.29	13.93	15.25
	12H	12.83	13.43	13.84	14.44	15.79	12.32	12.92	13.33	13.93	15.28
4H	2H	10.50	11.22	11.49	12.22	13.53	10.14	10.87	11.14	11.86	13.18
	3H	12.36	12.96	13.36	13.98	15.31	11.95	12.55	12.96	13.58	14.91
	4H	13.07	13.62	14.08	14.64	15.99	12.64	13.20	13.66	14.21	15.56
	6H	13.58	14.05	14.60	15.09	16.44	13.15	13.62	14.17	14.66	16.01
	8H	13.73	14.17	14.75	15.20	16.57	13.29	13.73	14.31	14.76	16.13
	12H	13.80	14.20	14.84	15.24	16.61	13.35	13.75	14.39	14.79	16.16
8H	4H	13.26	13.70	14.29	14.74	16.10	12.88	13.33	13.91	14.36	15.72
	6H	13.88	14.25	14.93	15.32	16.69	13.50	13.87	14.55	14.94	16.30
	8H	14.10	14.43	15.16	15.48	16.86	13.71	14.03	14.77	15.09	16.47
	12H	14.23	14.51	15.29	15.57	16.99	13.82	14.10	14.88	15.16	16.58
12H	4H	13.24	13.65	14.29	14.69	16.06	12.88	13.28	13.92	14.32	15.69
	6H	13.91	14.24	14.97	15.29	16.68	13.54	13.86	14.60	14.92	16.30
	8H	14.15	14.43	15.21	15.49	16.91	13.77	14.05	14.83	15.11	16.53