

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920066

Luminaire Tested: DFN2DIP-SQ3F0-060D070US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920066
REPORT IS A COMBINATION OF REPORTS P899920 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-060D070US935-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9725.0 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 105.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920066

CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P920066

CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45	45	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39	39	39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33	33	33
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29	29	29
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25	25	25
5	69	57	50	44	63	53	46	41	45	40	36	37	33	30	30	28	25	22	22	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	18	18	18
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16	16	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14	14	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2446	2446	2446
5°	2449	2406	2422
10°	2423	2357	2343
15°	2388	2278	2220
20°	2342	2169	2070
25°	2296	2047	1925
30°	2233	1922	1741
35°	2172	1788	1580
40°	2110	1650	1395
45°	2038	1497	1228
50°	1963	1342	1064
55°	1884	1177	907
60°	1794	1005	746
65°	1689	829	671
70°	1562	666	606
75°	1403	583	549
80°	1172	484	474
85°	795	316	351

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2038 cd/sqm

TEST NUMBER: P920066

CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.1	2.1
10°-20°	549.3	5.6
20°-30°	771.2	7.9
30°-40°	840.7	8.6
40°-50°	772.7	7.9
50°-60°	606.8	6.2
60°-70°	395.0	4.1
70°-80°	203.3	2.1
80°-90°	57.3	0.6
90°-100°	117.9	1.2
100°-110°	374.8	3.9
110°-120°	641.3	6.6
120°-130°	843.5	8.7
130°-140°	946.7	9.7
140°-150°	928.4	9.5
150°-160°	778.8	8.0
160°-170°	516.5	5.3
170°-180°	180.5	1.9
0°-30°	1520.7	15.6
0°-40°	2361.4	24.3
0°-60°	3740.9	38.5
0°-90°	4396.5	45.2
90°-120°	1134.1	11.7
90°-150°	3852.7	39.6
90°-180°	5328.0	54.8
0°-180°	9725.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2135	2135	2135	2135	2135	
5°	2135	2126	2100	2118	2112	202
15°	2031	2009	1944	1907	1888	572
25°	1843	1782	1654	1575	1546	848
35°	1588	1490	1320	1198	1155	994
45°	1298	1169	966	829	782	1003
55°	987	837	628	512	475	882
65°	667	510	336	271	265	661
75°	356	220	154	141	139	376
85°	83	42	37	37	37	95
90°	2	21	56	53	55	10
95°	84	100	103	103	100	93
105°	346	350	354	357	357	365
115°	644	653	650	648	644	637
125°	936	950	946	941	939	837
135°	1211	1229	1232	1230	1226	936
145°	1470	1481	1491	1492	1486	918
155°	1681	1685	1691	1699	1694	774
165°	1828	1827	1827	1838	1830	516
175°	1903	1898	1895	1906	1896	181
180°	1906	1906	1906	1906	1906	

TEST NUMBER: P920066

CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2135.1	2135.1	2135.1	2135.1	2135.1
2.5°	2144.7	2135.1	2113.7	2133.2	2129.3
5°	2135.1	2125.5	2100.2	2117.7	2111.9
7.5°	2117.7	2106.2	2079.1	2086.7	2077.1
10°	2094.5	2080.9	2042.5	2036.5	2025.0
12.5°	2065.6	2048.1	1995.9	1984.4	1963.1
15°	2030.7	2009.4	1943.8	1907.1	1887.8
17.5°	1990.2	1959.2	1878.0	1835.6	1804.7
20°	1943.8	1905.0	1808.5	1760.3	1717.7
22.5°	1893.6	1849.1	1737.0	1671.4	1642.4
25°	1843.4	1781.5	1654.0	1574.9	1545.7
27.5°	1783.6	1717.7	1576.7	1485.8	1441.4
30°	1719.8	1646.1	1491.6	1393.2	1340.9
32.5°	1657.9	1568.9	1410.7	1294.6	1246.2
35°	1588.4	1489.8	1319.8	1198.0	1155.4
37.5°	1520.7	1414.3	1234.8	1101.3	1053.1
40°	1449.1	1333.3	1145.7	1008.6	958.4
42.5°	1375.8	1252.1	1057.0	913.9	865.7
45°	1298.5	1168.9	966.2	828.8	782.5
47.5°	1225.1	1088.0	879.3	741.9	699.5
50°	1143.9	1006.8	794.2	660.7	620.3
52.5°	1064.5	919.6	713.0	585.5	548.8
55°	987.3	836.6	627.9	512.1	475.4
57.5°	908.2	753.5	552.7	444.4	413.5
60°	827.0	672.4	473.4	375.0	344.0
62.5°	747.9	593.3	405.7	313.1	297.6
65°	666.7	510.1	336.2	270.6	264.7
67.5°	589.4	432.7	270.6	237.6	231.9
70°	508.2	357.5	224.0	204.8	197.0
72.5°	430.9	287.8	187.4	172.0	168.1
75°	355.5	220.2	154.5	141.0	139.2
77.5°	280.3	156.4	121.7	114.0	110.1
80°	210.5	112.1	92.6	85.1	85.1
82.5°	146.8	75.4	63.7	59.8	59.8
85°	83.0	42.4	36.7	36.7	36.7
87.5°	31.0	15.4	15.4	13.5	13.5
90°	1.7	20.7	56.3	52.9	54.6
92.5°	35.6	48.3	50.0	51.7	51.7
95°	83.9	100.0	102.9	102.9	100.0
97.5°	139.7	154.5	160.9	160.9	160.9
100°	204.0	217.2	221.8	221.8	220.1
102.5°	271.8	281.5	287.9	289.6	287.9
105°	345.9	350.5	354.0	356.9	356.9
107.5°	419.5	426.4	426.4	427.6	419.5
110°	490.8	500.0	500.0	500.0	495.3

TEST NUMBER: P920066

CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	567.7	577.6	575.8	571.2	567.7
115°	643.6	652.8	650.0	648.2	643.6
117.5°	718.8	731.5	723.5	718.8	714.3
120°	794.7	807.4	794.7	794.7	789.5
122.5°	863.7	879.8	871.8	867.1	863.7
125°	936.1	950.5	945.9	940.7	939.0
127.5°	1006.8	1024.6	1018.3	1011.4	1006.8
130°	1072.9	1093.6	1090.7	1087.3	1080.9
132.5°	1147.0	1163.1	1164.2	1156.2	1151.6
135°	1210.8	1228.6	1232.1	1230.3	1225.7
137.5°	1282.0	1296.4	1299.2	1298.1	1291.2
140°	1344.7	1359.1	1367.1	1367.1	1360.8
142.5°	1409.0	1423.4	1428.0	1429.7	1423.4
145°	1470.0	1481.4	1490.6	1492.4	1486.1
147.5°	1524.6	1538.9	1545.8	1548.7	1542.4
150°	1580.9	1590.6	1597.0	1602.1	1597.0
152.5°	1630.8	1640.6	1648.6	1655.0	1648.6
155°	1680.8	1685.4	1690.7	1698.7	1693.5
157.5°	1724.0	1727.4	1730.3	1741.8	1733.7
160°	1762.5	1765.9	1767.6	1777.4	1770.5
162.5°	1798.1	1798.1	1799.8	1810.7	1802.7
165°	1828.5	1826.8	1826.8	1838.3	1830.2
167.5°	1856.1	1851.0	1851.0	1862.4	1854.4
170°	1876.8	1872.2	1870.5	1882.0	1872.2
172.5°	1891.2	1886.5	1884.8	1896.3	1886.5
175°	1902.6	1898.1	1894.6	1906.1	1896.3
177.5°	1909.0	1904.4	1900.9	1910.7	1900.9
180°	1906.1	1906.1	1906.1	1906.1	1906.1

TEST NUMBER: P920066

CATALOG NUMBER: DFN2DIP-SQ3F0-060D070US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.75	10.55	10.76	11.56	12.90	5.71	6.51	6.72	7.52	8.86
	3H	11.42	12.13	12.44	13.15	14.51	6.89	7.60	7.91	8.62	9.98
	4H	12.03	12.70	13.06	13.72	15.09	7.34	8.01	8.37	9.03	10.40
	6H	12.44	13.06	13.48	14.09	15.47	7.65	8.27	8.69	9.30	10.68
	8H	12.57	13.15	13.61	14.20	15.57	7.74	8.32	8.78	9.37	10.74
	12H	12.63	13.18	13.67	14.22	15.62	7.78	8.33	8.82	9.37	10.77
4H	2H	9.77	10.44	10.80	11.46	12.83	6.30	6.97	7.34	8.00	9.36
	3H	11.59	12.14	12.63	13.19	14.58	7.64	8.20	8.68	9.25	10.63
	4H	12.27	12.78	13.32	13.83	15.23	8.18	8.69	9.23	9.74	11.14
	6H	12.78	13.22	13.84	14.28	15.69	8.59	9.03	9.65	10.10	11.50
	8H	12.95	13.36	14.01	14.42	15.84	8.72	9.13	9.78	10.18	11.60
	12H	13.04	13.41	14.12	14.49	15.91	8.78	9.15	9.85	10.22	11.64
8H	4H	12.24	12.65	13.29	13.70	15.12	8.46	8.87	9.52	9.92	11.34
	6H	12.80	13.13	13.88	14.23	15.65	8.97	9.30	10.05	10.40	11.82
	8H	13.01	13.31	14.10	14.39	15.82	9.15	9.45	10.24	10.53	11.96
	12H	13.14	13.40	14.23	14.48	15.95	9.26	9.52	10.36	10.60	12.08
12H	4H	12.19	12.56	13.26	13.63	15.05	8.46	8.83	9.54	9.90	11.32
	6H	12.77	13.07	13.86	14.15	15.58	9.01	9.31	10.10	10.39	11.83
	8H	12.99	13.25	14.08	14.32	15.80	9.22	9.48	10.31	10.56	12.03

END OF REPORT